

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026995

Luminaire Tested: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026995
REPORT IS A COMBINATION OF REPORTS P1002489 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8286.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	80	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7881	7881	7881	7881
5°	7887	8940	7894	6782
10°	7839	10191	7825	5822
15°	7782	11049	7733	5261
20°	7683	12107	7613	4803
25°	7596	13873	7458	4531
30°	7470	14636	7341	4286
35°	7272	11732	7120	4088
40°	6963	8109	6860	3879
45°	6573	6037	6498	3706
50°	6125	4970	6023	3567
55°	5642	4239	5598	3447
60°	5168	3628	5079	3353
65°	4658	3133	4583	3218
70°	4118	2601	4063	2980
75°	3546	2012	3498	2586
80°	2802	1361	2698	1901
85°	1790	682	1732	970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 12038 cd/sqm

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.4	1.4
10°-20°	352.6	4.3
20°-30°	572.8	6.9
30°-40°	700.0	8.4
40°-50°	635.0	7.7
50°-60°	505.8	6.1
60°-70°	352.3	4.3
70°-80°	187.7	2.3
80°-90°	48.9	0.6
90°-100°	53.2	0.6
100°-110°	353.6	4.3
110°-120°	636.8	7.7
120°-130°	817.3	9.9
130°-140°	879.0	10.6
140°-150°	825.0	10.0
150°-160°	667.3	8.1
160°-170°	431.6	5.2
170°-180°	148.8	1.8
0°-30°	1043.8	12.6
0°-40°	1743.8	21.0
0°-60°	2884.6	34.8
0°-90°	3473.3	41.9
90°-120°	1043.5	12.6
90°-150°	3564.9	43.0
90°-180°	4813.0	58.1
0°-180°	8286.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1230	1230	1230	1230	1230	
5°	1229	1419	1230	1076	1229	117
15°	1181	1772	1174	844	1181	333
25°	1087	2180	1067	712	1087	501
35°	946	1750	926	610	946	591
45°	744	825	735	506	744	573
55°	523	508	519	414	523	468
65°	324	312	318	321	324	321
75°	157	154	154	197	157	167
85°	31	34	30	49	31	37
90°	1	28	1	28	1	6
95°	66	24	66	24	66	81
105°	342	345	342	345	342	362
115°	641	636	641	636	641	636
125°	912	912	912	912	912	814
135°	1137	1132	1137	1132	1137	877
145°	1318	1315	1318	1315	1318	824
155°	1452	1441	1452	1441	1452	669
165°	1532	1524	1532	1524	1532	433
175°	1567	1560	1567	1560	1567	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1232.1	1239.4	1247.8	1254.1	1264.5	1267.6	1272.9	1276.0	1279.1	1282.3	1284.3
5°	1229.0	1246.7	1262.4	1273.9	1293.7	1301.0	1310.4	1321.9	1335.5	1347.0	1354.3
7.5°	1220.6	1248.8	1269.7	1292.7	1319.8	1337.6	1347.0	1371.0	1392.9	1409.6	1431.6
10°	1210.2	1243.6	1276.0	1310.4	1349.1	1368.9	1387.7	1421.1	1451.4	1478.6	1500.5
12.5°	1198.7	1239.4	1278.1	1323.0	1375.2	1399.2	1411.7	1469.2	1506.7	1521.4	1564.2
15°	1181.0	1229.0	1284.3	1339.7	1383.5	1411.7	1446.2	1492.1	1529.7	1562.1	1596.5
17.5°	1164.3	1216.5	1272.9	1334.5	1398.2	1434.7	1460.8	1501.5	1542.3	1584.0	1616.4
20°	1137.1	1205.0	1262.4	1328.2	1403.4	1429.5	1456.6	1504.7	1548.5	1593.4	1634.1
22.5°	1115.2	1179.9	1258.2	1320.9	1384.6	1410.7	1444.1	1494.2	1546.4	1597.6	1657.1
25°	1087.0	1159.0	1226.9	1293.7	1359.5	1387.7	1418.0	1482.7	1537.0	1602.8	1668.6
27.5°	1056.7	1130.8	1198.7	1259.3	1320.9	1359.5	1391.9	1459.8	1531.8	1603.9	1689.5
30°	1024.3	1094.3	1159.0	1218.6	1286.4	1326.1	1358.5	1437.8	1518.2	1610.1	1712.5
32.5°	989.9	1055.7	1111.0	1171.6	1243.6	1280.2	1324.0	1410.7	1505.7	1615.3	1743.8
35°	946.0	1008.7	1057.8	1119.4	1191.4	1238.4	1284.3	1381.4	1492.1	1614.3	1761.5
37.5°	902.2	951.2	998.2	1064.0	1147.6	1190.4	1238.4	1344.9	1471.2	1611.2	1768.8
40°	850.0	898.0	938.7	1005.5	1093.3	1142.3	1192.5	1304.2	1447.2	1599.7	1742.7
42.5°	797.8	838.5	883.4	953.3	1037.9	1090.1	1143.4	1267.6	1415.9	1566.3	1670.7
45°	743.5	774.8	823.9	887.6	977.4	1027.5	1088.0	1222.7	1372.1	1505.7	1557.9
47.5°	687.1	718.4	764.3	825.9	914.7	974.2	1031.6	1166.3	1316.7	1420.1	1420.1
50°	632.8	657.8	702.7	764.3	854.1	908.4	966.9	1110.0	1231.1	1307.3	1239.4
52.5°	574.3	602.5	640.1	704.8	793.6	842.7	906.3	1028.5	1143.4	1174.7	1070.3
55°	523.1	546.1	581.6	643.2	725.7	776.9	831.2	948.1	1045.2	1043.1	931.4
57.5°	469.9	488.7	526.3	582.7	658.9	704.8	759.1	860.4	939.8	911.6	806.1
60°	420.8	434.4	470.9	516.9	590.0	632.8	685.0	767.5	828.0	788.4	681.8
62.5°	369.6	385.3	414.5	459.4	524.2	558.6	597.3	680.8	719.4	683.9	575.3
65°	323.7	336.2	362.3	399.9	458.4	489.7	523.1	592.0	628.6	577.4	487.6
67.5°	277.8	292.4	311.2	344.6	390.5	419.8	449.0	508.5	525.2	479.3	404.1
70°	234.9	247.5	265.2	289.2	327.9	354.0	375.9	425.0	436.5	393.7	334.1
72.5°	193.2	201.5	216.1	236.0	271.5	286.1	309.1	342.5	357.1	318.5	275.7
75°	156.6	162.9	172.3	186.9	210.9	226.6	245.4	276.7	275.7	248.5	218.2
77.5°	121.1	122.2	132.6	146.2	160.8	174.4	183.8	205.7	207.8	191.1	166.0
80°	86.7	89.8	94.0	104.4	116.9	122.2	133.7	147.2	149.3	136.8	120.1
82.5°	55.3	57.4	60.6	66.8	75.2	81.4	87.7	92.9	98.2	90.8	77.3
85°	31.3	32.4	35.5	37.6	41.8	44.9	50.1	55.3	54.3	49.1	44.9
87.5°	15.7	15.7	15.7	17.8	19.8	19.8	21.9	23.0	24.0	21.9	19.8
90°	1.2	3.3	5.3	7.4	9.5	10.5	11.4	13.2	15.0	16.8	18.6
92.5°	22.1	19.8	17.4	15.1	12.8	11.6	12.4	13.9	15.5	17.0	18.6
95°	66.2	65.4	64.6	63.9	63.1	62.7	57.8	48.0	38.2	28.4	18.6
97.5°	124.3	125.8	127.4	128.9	130.4	131.2	118.9	94.4	69.9	45.4	20.9
100°	194.0	194.8	195.5	196.3	197.0	197.4	197.9	199.0	200.0	201.1	202.1
102.5°	264.8	265.8	266.8	267.9	268.9	269.4	269.7	270.2	270.7	271.3	271.8
105°	341.5	342.5	343.5	344.6	345.6	346.1	346.1	346.1	346.1	346.1	346.1
107.5°	420.4	420.4	420.4	420.4	420.4	420.4	420.7	421.2	421.7	422.3	422.8
110°	497.1	497.1	497.1	497.1	497.1	497.1	497.4	497.9	498.4	498.9	499.4

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	569.1	569.9	570.7	571.4	572.2	572.6	572.7	573.0	573.2	573.5	573.7
115°	641.1	642.4	643.7	645.0	646.3	646.9	647.0	647.3	647.6	647.8	648.1
117.5°	716.6	716.6	716.6	716.6	716.6	716.6	717.1	718.1	719.2	720.2	721.2
120°	786.3	786.0	785.8	785.5	785.2	785.1	785.5	786.3	787.0	787.8	788.6
122.5°	847.8	849.1	850.4	851.7	853.0	853.6	853.7	854.0	854.3	854.5	854.8
125°	911.7	913.5	915.3	917.1	918.9	919.8	919.8	919.8	919.8	919.8	919.8
127.5°	973.3	974.6	975.9	977.2	978.5	979.1	979.0	978.7	978.4	978.2	977.9
130°	1029.0	1030.3	1031.6	1032.9	1034.2	1034.8	1034.9	1035.2	1035.5	1035.7	1036.0
132.5°	1084.8	1086.3	1087.9	1089.4	1090.9	1091.7	1091.3	1090.5	1089.8	1089.0	1088.2
135°	1137.0	1138.6	1140.1	1141.7	1143.2	1144.0	1143.7	1143.2	1142.7	1142.2	1141.7
137.5°	1185.8	1187.4	1188.9	1190.5	1192.0	1192.8	1192.5	1192.0	1191.5	1190.9	1190.4
140°	1233.4	1233.9	1234.4	1234.9	1235.4	1235.7	1235.6	1235.3	1235.1	1234.8	1234.6
142.5°	1276.4	1276.6	1276.9	1277.1	1277.4	1277.5	1277.8	1278.3	1278.8	1279.4	1279.9
145°	1318.2	1318.7	1319.2	1319.7	1320.2	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5
147.5°	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1355.5	1355.8	1356.0	1356.3	1356.5
150°	1390.2	1389.7	1389.2	1388.7	1388.2	1387.9	1388.2	1388.7	1389.2	1389.7	1390.2
152.5°	1423.9	1422.6	1421.3	1420.0	1418.7	1418.1	1418.4	1418.9	1419.4	1419.9	1420.4
155°	1451.8	1450.2	1448.7	1447.1	1445.6	1444.8	1445.1	1445.6	1446.1	1446.6	1447.1
157.5°	1473.8	1473.0	1472.2	1471.5	1470.7	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3
160°	1497.0	1495.5	1493.9	1492.4	1490.9	1490.1	1490.2	1490.5	1490.7	1491.0	1491.2
162.5°	1515.6	1514.1	1512.5	1511.0	1509.5	1508.7	1508.8	1509.1	1509.3	1509.6	1509.8
165°	1531.9	1530.3	1528.8	1527.2	1525.7	1524.9	1525.0	1525.3	1525.6	1525.8	1526.1
167.5°	1544.7	1543.1	1541.6	1540.0	1538.5	1537.7	1537.8	1538.1	1538.4	1538.6	1538.9
170°	1555.1	1553.3	1551.5	1549.7	1547.9	1547.0	1547.1	1547.4	1547.7	1547.9	1548.2
172.5°	1562.1	1560.3	1558.5	1556.7	1554.9	1554.0	1554.3	1554.8	1555.3	1555.8	1556.3
175°	1566.7	1565.2	1563.6	1562.1	1560.6	1559.8	1559.9	1560.2	1560.4	1560.7	1560.9
177.5°	1570.2	1568.6	1567.1	1565.5	1564.0	1563.2	1563.3	1563.6	1563.9	1564.1	1564.4
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1286.4	1293.7	1300.0	1305.2	1309.4	1315.7	1311.5	1312.5	1314.6	1318.8	1318.8
5°	1370.0	1381.4	1387.7	1408.6	1413.8	1412.8	1409.6	1426.3	1425.3	1419.0	1418.0
7.5°	1451.4	1471.2	1489.0	1505.7	1510.9	1524.5	1527.6	1534.9	1532.9	1543.3	1538.1
10°	1525.5	1556.9	1573.6	1598.6	1604.9	1611.2	1619.5	1623.7	1633.1	1632.1	1632.1
12.5°	1583.0	1620.6	1642.5	1648.8	1672.8	1680.1	1687.4	1701.0	1697.8	1698.9	1705.1
15°	1627.9	1664.4	1683.2	1712.5	1729.2	1737.5	1750.0	1764.7	1762.6	1772.0	1769.9
17.5°	1661.3	1695.7	1730.2	1774.1	1775.1	1797.0	1826.3	1832.5	1846.1	1836.7	1836.7
20°	1688.4	1734.4	1783.5	1839.8	1846.1	1859.7	1895.2	1919.2	1934.9	1929.6	1932.8
22.5°	1717.7	1783.5	1840.9	1897.3	1927.6	1951.6	1986.0	2023.6	2037.2	2045.5	2043.5
25°	1755.3	1824.2	1908.8	1987.1	2018.4	2064.3	2110.3	2146.8	2157.3	2180.2	2159.4
27.5°	1793.9	1891.0	1996.5	2088.4	2128.0	2165.6	2221.0	2248.1	2261.7	2272.1	2264.8
30°	1826.3	1959.9	2074.8	2159.4	2187.6	2209.5	2240.8	2247.1	2241.9	2250.2	2260.6
32.5°	1876.4	2006.9	2104.0	2144.7	2141.6	2140.6	2116.5	2083.1	2075.8	2056.0	2083.1
35°	1903.5	2008.0	2045.5	1991.2	1969.3	1929.6	1853.4	1803.3	1759.4	1750.0	1752.1
37.5°	1887.9	1928.6	1883.7	1740.6	1705.1	1644.6	1543.3	1472.3	1439.9	1414.9	1447.2
40°	1803.3	1758.4	1635.2	1460.8	1409.6	1352.2	1257.2	1218.6	1172.6	1163.2	1206.0
42.5°	1663.4	1526.6	1352.2	1217.5	1164.3	1131.9	1052.5	1016.0	983.6	969.0	993.0
45°	1473.3	1307.3	1131.9	1021.2	976.3	937.7	890.7	852.0	831.2	824.9	844.7
47.5°	1277.0	1101.6	961.7	879.2	832.2	803.0	759.1	737.2	720.5	722.6	725.7
50°	1089.1	929.3	821.8	739.3	716.3	693.3	664.1	645.3	636.9	640.1	638.0
52.5°	927.2	797.8	706.9	643.2	632.8	610.8	586.8	571.2	568.0	569.1	572.2
55°	785.2	683.9	611.9	565.9	554.5	538.8	524.2	513.7	505.4	508.5	507.5
57.5°	677.7	588.9	533.6	496.0	487.6	478.2	464.7	459.4	456.3	450.0	455.3
60°	582.7	510.6	462.6	439.6	432.3	426.0	411.4	405.1	403.1	399.9	408.3
62.5°	492.9	441.7	405.1	384.3	376.9	370.7	363.4	358.2	359.2	355.0	359.2
65°	421.8	380.1	354.0	335.2	325.8	321.6	320.6	312.2	311.2	312.2	313.3
67.5°	356.1	320.6	300.7	289.2	281.9	277.8	274.6	269.4	273.6	270.4	272.5
70°	296.5	272.5	251.6	240.2	237.0	238.1	232.9	230.8	231.8	229.7	231.8
72.5°	239.1	219.3	210.9	202.6	198.4	197.3	194.2	191.1	194.2	193.2	193.2
75°	191.1	176.5	167.1	161.8	161.8	159.8	154.5	154.5	154.5	153.5	154.5
77.5°	147.2	134.7	130.5	125.3	125.3	122.2	121.1	121.1	119.0	122.2	120.1
80°	109.6	100.2	94.0	90.8	90.8	89.8	87.7	86.7	87.7	86.7	86.7
82.5°	71.0	66.8	63.7	60.6	59.5	60.6	59.5	57.4	58.5	57.4	59.5
85°	40.7	36.5	36.5	34.5	35.5	33.4	34.5	32.4	31.3	34.5	32.4
87.5°	17.8	16.7	16.7	14.6	14.6	14.6	13.6	14.6	13.6	12.5	13.6
90°	19.9	21.2	22.5	23.8	24.4	24.8	25.6	26.3	27.1	27.9	27.1
92.5°	19.9	21.2	22.5	23.8	24.4	24.5	24.8	25.1	25.3	25.6	25.3
95°	19.9	21.2	22.5	23.8	24.4	24.4	24.4	24.4	24.4	24.4	24.4
97.5°	21.4	21.9	22.4	22.9	23.2	23.3	23.6	23.9	24.1	24.4	24.1
100°	163.6	125.2	86.7	48.2	29.0	28.5	27.5	26.4	25.4	24.4	25.4
102.5°	272.3	272.8	273.3	273.8	274.1	263.3	241.6	219.9	198.2	176.5	198.2
105°	346.1	346.1	346.1	346.1	346.1	346.0	345.7	345.4	345.2	344.9	345.2
107.5°	423.0	423.3	423.5	423.8	423.9	423.4	422.4	421.3	420.3	419.3	420.3
110°	498.6	497.8	497.1	496.3	495.9	496.0	496.3	496.6	496.8	497.1	496.8

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	572.7	571.7	570.6	569.6	569.1	568.8	568.3	567.8	567.3	566.8	567.3
115°	647.1	646.0	645.0	643.9	643.4	642.6	641.1	639.5	638.0	636.4	638.0
117.5°	719.7	718.1	716.6	715.1	714.3	714.0	713.5	713.0	712.4	711.9	712.4
120°	788.1	787.6	787.1	786.6	786.3	785.7	784.4	783.1	781.8	780.5	781.8
122.5°	854.3	853.8	853.3	852.8	852.5	851.7	850.2	848.6	847.1	845.5	847.1
125°	918.8	917.8	916.7	915.7	915.2	914.8	914.0	913.3	912.5	911.7	912.5
127.5°	977.4	976.9	976.4	975.9	975.6	974.6	972.5	970.4	968.4	966.3	968.4
130°	1035.2	1034.4	1033.7	1032.9	1032.5	1031.9	1030.6	1029.3	1028.0	1026.7	1028.0
132.5°	1088.2	1088.2	1088.2	1088.2	1088.2	1087.6	1086.3	1085.0	1083.7	1082.4	1083.7
135°	1141.2	1140.6	1140.1	1139.6	1139.3	1138.5	1137.0	1135.5	1133.9	1132.4	1133.9
137.5°	1190.4	1190.4	1190.4	1190.4	1190.4	1189.8	1188.5	1187.2	1185.9	1184.6	1185.9
140°	1235.1	1235.6	1236.1	1236.6	1236.9	1236.1	1234.6	1233.0	1231.5	1229.9	1231.5
142.5°	1279.9	1279.9	1279.9	1279.9	1279.9	1279.1	1277.6	1276.0	1274.5	1272.9	1274.5
145°	1320.8	1321.0	1321.3	1321.6	1321.7	1320.9	1319.4	1317.8	1316.3	1314.7	1316.3
147.5°	1356.8	1357.0	1357.3	1357.6	1357.7	1356.8	1355.0	1353.2	1351.4	1349.6	1351.4
150°	1390.7	1391.2	1391.7	1392.2	1392.5	1391.5	1389.4	1387.3	1385.3	1383.2	1385.3
152.5°	1420.9	1421.4	1421.9	1422.4	1422.7	1421.8	1420.0	1418.2	1416.4	1414.6	1416.4
155°	1447.9	1448.7	1449.4	1450.2	1450.6	1449.6	1447.5	1445.4	1443.4	1441.3	1443.4
157.5°	1471.1	1471.9	1472.6	1473.4	1473.8	1472.8	1470.7	1468.6	1466.6	1464.5	1466.6
160°	1492.2	1493.3	1494.3	1495.4	1495.9	1494.9	1492.8	1490.7	1488.7	1486.6	1488.7
162.5°	1511.4	1512.9	1514.5	1516.0	1516.8	1515.6	1513.3	1511.0	1508.6	1506.3	1508.6
165°	1527.7	1529.2	1530.8	1532.3	1533.1	1532.1	1530.0	1527.9	1525.9	1523.8	1525.9
167.5°	1540.7	1542.5	1544.3	1546.1	1547.0	1545.8	1543.5	1541.2	1538.8	1536.5	1538.8
170°	1550.2	1552.3	1554.3	1556.4	1557.4	1556.2	1553.9	1551.6	1549.3	1547.0	1549.3
172.5°	1558.1	1559.9	1561.7	1563.5	1564.4	1563.2	1560.9	1558.6	1556.3	1554.0	1556.3
175°	1563.0	1565.0	1567.1	1569.2	1570.2	1569.0	1566.7	1564.4	1562.1	1559.8	1562.1
177.5°	1566.2	1568.0	1569.8	1571.6	1572.5	1571.5	1569.4	1567.3	1565.3	1563.2	1565.3
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1316.7	1309.4	1311.5	1309.4	1304.2	1301.0	1292.7	1282.3	1278.1	1272.9	1269.7
5°	1422.2	1416.9	1415.9	1407.6	1405.5	1392.9	1372.1	1361.6	1349.1	1336.5	1324.0
7.5°	1537.0	1530.8	1509.9	1506.7	1508.8	1493.2	1466.0	1445.1	1419.0	1401.3	1377.3
10°	1632.1	1619.5	1601.8	1602.8	1595.5	1574.6	1547.5	1525.5	1488.0	1465.0	1430.5
12.5°	1689.5	1679.0	1677.0	1666.5	1660.2	1633.1	1600.7	1572.5	1544.3	1513.0	1486.9
15°	1759.4	1745.9	1736.5	1721.8	1717.7	1689.5	1654.0	1621.6	1589.2	1560.0	1504.7
17.5°	1836.7	1822.1	1786.6	1783.5	1758.4	1731.2	1696.8	1648.8	1614.3	1572.5	1531.8
20°	1924.4	1903.5	1857.6	1846.1	1826.3	1781.4	1734.4	1681.1	1625.8	1583.0	1534.9
22.5°	2022.6	1986.0	1952.6	1916.1	1901.4	1846.1	1781.4	1716.6	1649.8	1591.3	1533.9
25°	2150.0	2101.9	2054.9	2018.4	1993.3	1921.3	1834.6	1749.0	1671.7	1595.5	1520.3
27.5°	2250.2	2208.4	2157.3	2109.2	2076.9	1991.2	1892.1	1781.4	1685.3	1592.4	1512.0
30°	2257.5	2245.0	2213.7	2187.6	2152.1	2060.2	1950.5	1825.2	1706.2	1593.4	1495.3
32.5°	2120.7	2145.8	2159.4	2163.5	2156.2	2103.0	2002.7	1864.9	1725.0	1584.0	1480.6
35°	1826.3	1893.1	1975.6	2006.9	2037.2	2065.4	2013.2	1893.1	1731.2	1581.9	1457.7
37.5°	1503.6	1564.2	1701.0	1763.6	1799.1	1910.8	1953.7	1888.9	1743.8	1584.0	1435.7
40°	1213.3	1309.4	1407.6	1492.1	1547.5	1672.8	1805.4	1820.0	1726.0	1564.2	1407.6
42.5°	1021.2	1077.6	1151.7	1230.0	1279.1	1427.4	1607.0	1712.5	1670.7	1531.8	1373.1
45°	869.8	911.6	981.5	1007.6	1070.3	1212.3	1402.3	1554.8	1575.7	1480.6	1333.4
47.5°	746.6	782.1	827.0	859.4	909.5	1016.0	1176.8	1344.9	1445.1	1410.7	1278.1
50°	657.8	687.1	724.7	743.5	775.8	871.9	993.0	1160.1	1294.8	1306.3	1206.0
52.5°	583.7	600.4	629.6	650.5	676.6	735.1	844.7	982.6	1134.0	1196.6	1117.3
55°	519.0	532.5	558.6	572.2	585.8	635.9	721.5	846.8	988.8	1071.3	1026.4
57.5°	460.5	472.0	493.9	506.4	513.7	561.8	627.6	725.7	853.1	953.3	928.3
60°	412.5	422.9	435.4	444.8	453.2	492.9	538.8	618.2	732.0	829.1	822.8
62.5°	361.3	370.7	384.3	393.7	401.0	426.0	464.7	525.2	622.3	712.1	729.9
65°	316.4	323.7	333.1	337.3	346.7	365.5	396.8	451.1	530.4	610.8	623.4
67.5°	275.7	277.8	284.0	293.4	295.5	312.2	340.4	381.1	442.7	508.5	528.4
70°	231.8	234.9	240.2	247.5	251.6	262.1	286.1	313.3	366.5	423.9	438.6
72.5°	193.2	197.3	199.4	203.6	205.7	222.4	232.9	260.0	296.5	344.6	360.2
75°	156.6	160.8	161.8	163.9	166.0	173.3	188.0	204.7	234.9	266.3	287.1
77.5°	124.3	123.2	125.3	128.4	127.4	133.7	143.1	157.7	177.5	203.6	217.2
80°	87.7	87.7	90.8	94.0	92.9	99.2	102.3	112.8	129.5	146.2	151.4
82.5°	58.5	58.5	61.6	61.6	63.7	64.7	68.9	74.1	87.7	96.1	99.2
85°	33.4	33.4	34.5	34.5	34.5	36.5	39.7	41.8	45.9	51.2	53.3
87.5°	13.6	14.6	14.6	14.6	14.6	16.7	16.7	18.8	19.8	21.9	21.9
90°	26.3	25.6	24.8	24.4	23.8	22.5	21.2	19.9	18.6	16.8	15.0
92.5°	25.1	24.8	24.5	24.4	23.8	22.5	21.2	19.9	18.6	17.0	15.5
95°	24.4	24.4	24.4	24.4	23.8	22.5	21.2	19.9	18.6	28.4	38.2
97.5°	23.9	23.6	23.3	23.2	22.9	22.4	21.9	21.4	20.9	45.4	69.9
100°	26.4	27.5	28.5	29.0	48.2	86.7	125.2	163.6	202.1	201.1	200.0
102.5°	219.9	241.6	263.3	274.1	273.8	273.3	272.8	272.3	271.8	271.3	270.7
105°	345.4	345.7	346.0	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1
107.5°	421.3	422.4	423.4	423.9	423.8	423.5	423.3	423.0	422.8	422.3	421.7
110°	496.6	496.3	496.0	495.9	496.3	497.1	497.8	498.6	499.4	498.9	498.4

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	567.8	568.3	568.8	569.1	569.6	570.6	571.7	572.7	573.7	573.5	573.2
115°	639.5	641.1	642.6	643.4	643.9	645.0	646.0	647.1	648.1	647.8	647.6
117.5°	713.0	713.5	714.0	714.3	715.1	716.6	718.1	719.7	721.2	720.2	719.2
120°	783.1	784.4	785.7	786.3	786.6	787.1	787.6	788.1	788.6	787.8	787.0
122.5°	848.6	850.2	851.7	852.5	852.8	853.3	853.8	854.3	854.8	854.5	854.3
125°	913.3	914.0	914.8	915.2	915.7	916.7	917.8	918.8	919.8	919.8	919.8
127.5°	970.4	972.5	974.6	975.6	975.9	976.4	976.9	977.4	977.9	978.2	978.4
130°	1029.3	1030.6	1031.9	1032.5	1032.9	1033.7	1034.4	1035.2	1036.0	1035.7	1035.5
132.5°	1085.0	1086.3	1087.6	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1089.0	1089.8
135°	1135.5	1137.0	1138.5	1139.3	1139.6	1140.1	1140.6	1141.2	1141.7	1142.2	1142.7
137.5°	1187.2	1188.5	1189.8	1190.4	1190.4	1190.4	1190.4	1190.4	1190.4	1190.9	1191.5
140°	1233.0	1234.6	1236.1	1236.9	1236.6	1236.1	1235.6	1235.1	1234.6	1234.8	1235.1
142.5°	1276.0	1277.6	1279.1	1279.9	1279.9	1279.9	1279.9	1279.9	1279.9	1279.4	1278.8
145°	1317.8	1319.4	1320.9	1321.7	1321.6	1321.3	1321.0	1320.8	1320.5	1320.5	1320.5
147.5°	1353.2	1355.0	1356.8	1357.7	1357.6	1357.3	1357.0	1356.8	1356.5	1356.3	1356.0
150°	1387.3	1389.4	1391.5	1392.5	1392.2	1391.7	1391.2	1390.7	1390.2	1389.7	1389.2
152.5°	1418.2	1420.0	1421.8	1422.7	1422.4	1421.9	1421.4	1420.9	1420.4	1419.9	1419.4
155°	1445.4	1447.5	1449.6	1450.6	1450.2	1449.4	1448.7	1447.9	1447.1	1446.6	1446.1
157.5°	1468.6	1470.7	1472.8	1473.8	1473.4	1472.6	1471.9	1471.1	1470.3	1470.3	1470.3
160°	1490.7	1492.8	1494.9	1495.9	1495.4	1494.3	1493.3	1492.2	1491.2	1491.0	1490.7
162.5°	1511.0	1513.3	1515.6	1516.8	1516.0	1514.5	1512.9	1511.4	1509.8	1509.6	1509.3
165°	1527.9	1530.0	1532.1	1533.1	1532.3	1530.8	1529.2	1527.7	1526.1	1525.8	1525.6
167.5°	1541.2	1543.5	1545.8	1547.0	1546.1	1544.3	1542.5	1540.7	1538.9	1538.6	1538.4
170°	1551.6	1553.9	1556.2	1557.4	1556.4	1554.3	1552.3	1550.2	1548.2	1547.9	1547.7
172.5°	1558.6	1560.9	1563.2	1564.4	1563.5	1561.7	1559.9	1558.1	1556.3	1555.8	1555.3
175°	1564.4	1566.7	1569.0	1570.2	1569.2	1567.1	1565.0	1563.0	1560.9	1560.7	1560.4
177.5°	1567.3	1569.4	1571.5	1572.5	1571.6	1569.8	1568.0	1566.2	1564.4	1564.1	1563.9
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1265.5	1260.3	1254.1	1254.1	1246.7	1243.6	1237.4	1235.3	1230.0	1221.7	1215.4
5°	1310.4	1296.9	1288.5	1281.2	1265.5	1254.1	1242.6	1230.0	1217.5	1202.9	1186.2
7.5°	1354.3	1329.2	1317.8	1305.2	1282.3	1258.2	1235.3	1218.6	1201.8	1178.9	1158.0
10°	1400.2	1368.9	1348.0	1331.3	1295.8	1265.5	1232.1	1208.1	1182.0	1152.8	1125.6
12.5°	1438.9	1398.2	1380.4	1349.1	1308.4	1271.8	1230.0	1193.5	1159.0	1124.6	1091.2
15°	1471.2	1432.6	1388.8	1376.2	1319.8	1267.6	1220.6	1173.7	1130.8	1096.4	1057.8
17.5°	1481.7	1432.6	1410.7	1380.4	1313.6	1259.3	1199.8	1148.6	1107.9	1056.7	1026.4
20°	1484.8	1437.8	1407.6	1379.4	1319.8	1247.8	1189.3	1126.7	1077.6	1026.4	978.4
22.5°	1476.5	1421.1	1391.9	1364.7	1297.9	1236.3	1168.4	1099.5	1042.1	995.1	947.1
25°	1460.8	1396.1	1367.9	1338.6	1274.9	1207.1	1132.9	1067.2	1013.9	957.5	910.5
27.5°	1439.9	1365.8	1333.4	1303.1	1240.5	1176.8	1106.8	1039.0	979.4	919.9	876.1
30°	1413.8	1328.2	1299.0	1259.3	1198.7	1138.2	1074.5	1006.6	939.8	883.4	835.3
32.5°	1380.4	1290.6	1252.0	1214.4	1148.6	1093.3	1032.7	969.0	904.3	848.9	798.8
35°	1350.1	1247.8	1205.0	1167.4	1094.3	1035.8	985.7	926.2	868.8	811.3	766.4
37.5°	1309.4	1205.0	1153.8	1115.2	1041.0	981.5	934.5	888.6	828.0	772.7	730.9
40°	1266.6	1151.7	1103.7	1065.1	987.8	923.1	878.2	837.4	788.4	737.2	693.3
42.5°	1228.0	1100.6	1049.4	1002.4	924.1	866.7	820.7	789.4	744.5	698.6	658.9
45°	1178.9	1046.3	990.9	941.8	866.7	804.0	760.2	735.1	701.7	656.8	622.3
47.5°	1128.8	987.8	930.4	882.3	800.9	745.5	702.7	678.7	655.7	620.2	585.8
50°	1063.0	926.2	874.0	818.6	738.2	681.8	646.3	622.3	604.6	579.5	550.3
52.5°	990.9	862.5	806.1	758.1	678.7	627.6	586.8	573.3	555.5	536.7	511.6
55°	914.7	793.6	739.3	692.3	619.2	567.0	533.6	519.0	505.4	490.8	474.1
57.5°	838.5	721.5	670.4	628.6	560.7	510.6	483.5	463.6	454.2	445.9	432.3
60°	743.5	644.3	604.6	567.0	500.2	454.2	428.1	413.5	405.1	401.0	394.7
62.5°	659.9	578.5	534.6	498.1	444.8	404.1	379.0	367.6	360.2	358.2	350.8
65°	571.2	501.2	466.7	435.4	389.5	352.9	332.0	318.5	313.3	312.2	312.2
67.5°	487.6	431.2	396.8	374.9	335.2	302.8	283.0	277.8	274.6	270.4	269.4
70°	409.3	364.4	334.1	315.3	279.8	255.8	240.2	231.8	231.8	228.7	226.6
72.5°	340.4	295.5	275.7	260.0	230.8	209.9	198.4	196.3	189.0	188.0	188.0
75°	266.3	232.9	219.3	205.7	183.8	169.2	159.8	154.5	150.4	150.4	151.4
77.5°	200.5	177.5	165.0	154.5	138.9	129.5	122.2	120.1	115.9	115.9	115.9
80°	142.0	129.5	120.1	111.7	100.2	91.9	87.7	83.5	83.5	82.5	83.5
82.5°	91.9	81.4	76.2	75.2	64.7	61.6	56.4	57.4	54.3	53.3	55.3
85°	53.3	48.0	41.8	39.7	35.5	31.3	29.2	30.3	29.2	28.2	29.2
87.5°	20.9	17.8	16.7	16.7	13.6	12.5	11.5	12.5	10.4	10.4	11.5
90°	13.2	11.4	10.5	9.5	7.4	5.3	3.3	1.2	3.3	5.3	7.4
92.5°	13.9	12.4	11.6	12.8	15.1	17.4	19.8	22.1	19.8	17.4	15.1
95°	48.0	57.8	62.7	63.1	63.9	64.6	65.4	66.2	65.4	64.6	63.9
97.5°	94.4	118.9	131.2	130.4	128.9	127.4	125.8	124.3	125.8	127.4	128.9
100°	199.0	197.9	197.4	197.0	196.3	195.5	194.8	194.0	194.8	195.5	196.3
102.5°	270.2	269.7	269.4	268.9	267.9	266.8	265.8	264.8	265.8	266.8	267.9
105°	346.1	346.1	346.1	345.6	344.6	343.5	342.5	341.5	342.5	343.5	344.6
107.5°	421.2	420.7	420.4	420.4	420.4	420.4	420.4	420.4	420.4	420.4	420.4
110°	497.9	497.4	497.1	497.1	497.1	497.1	497.1	497.1	497.1	497.1	497.1

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	573.0	572.7	572.6	572.2	571.4	570.7	569.9	569.1	569.9	570.7	571.4
115°	647.3	647.0	646.9	646.3	645.0	643.7	642.4	641.1	642.4	643.7	645.0
117.5°	718.1	717.1	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6	716.6
120°	786.3	785.5	785.1	785.2	785.5	785.8	786.0	786.3	786.0	785.8	785.5
122.5°	854.0	853.7	853.6	853.0	851.7	850.4	849.1	847.8	849.1	850.4	851.7
125°	919.8	919.8	919.8	918.9	917.1	915.3	913.5	911.7	913.5	915.3	917.1
127.5°	978.7	979.0	979.1	978.5	977.2	975.9	974.6	973.3	974.6	975.9	977.2
130°	1035.2	1034.9	1034.8	1034.2	1032.9	1031.6	1030.3	1029.0	1030.3	1031.6	1032.9
132.5°	1090.5	1091.3	1091.7	1090.9	1089.4	1087.9	1086.3	1084.8	1086.3	1087.9	1089.4
135°	1143.2	1143.7	1144.0	1143.2	1141.7	1140.1	1138.6	1137.0	1138.6	1140.1	1141.7
137.5°	1192.0	1192.5	1192.8	1192.0	1190.5	1188.9	1187.4	1185.8	1187.4	1188.9	1190.5
140°	1235.3	1235.6	1235.7	1235.4	1234.9	1234.4	1233.9	1233.4	1233.9	1234.4	1234.9
142.5°	1278.3	1277.8	1277.5	1277.4	1277.1	1276.9	1276.6	1276.4	1276.6	1276.9	1277.1
145°	1320.5	1320.5	1320.5	1320.2	1319.7	1319.2	1318.7	1318.2	1318.7	1319.2	1319.7
147.5°	1355.8	1355.5	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4	1355.4
150°	1388.7	1388.2	1387.9	1388.2	1388.7	1389.2	1389.7	1390.2	1389.7	1389.2	1388.7
152.5°	1418.9	1418.4	1418.1	1418.7	1420.0	1421.3	1422.6	1423.9	1422.6	1421.3	1420.0
155°	1445.6	1445.1	1444.8	1445.6	1447.1	1448.7	1450.2	1451.8	1450.2	1448.7	1447.1
157.5°	1470.3	1470.3	1470.3	1470.7	1471.5	1472.2	1473.0	1473.8	1473.0	1472.2	1471.5
160°	1490.5	1490.2	1490.1	1490.9	1492.4	1493.9	1495.5	1497.0	1495.5	1493.9	1492.4
162.5°	1509.1	1508.8	1508.7	1509.5	1511.0	1512.5	1514.1	1515.6	1514.1	1512.5	1511.0
165°	1525.3	1525.0	1524.9	1525.7	1527.2	1528.8	1530.3	1531.9	1530.3	1528.8	1527.2
167.5°	1538.1	1537.8	1537.7	1538.5	1540.0	1541.6	1543.1	1544.7	1543.1	1541.6	1540.0
170°	1547.4	1547.1	1547.0	1547.9	1549.7	1551.5	1553.3	1555.1	1553.3	1551.5	1549.7
172.5°	1554.8	1554.3	1554.0	1554.9	1556.7	1558.5	1560.3	1562.1	1560.3	1558.5	1556.7
175°	1560.2	1559.9	1559.8	1560.6	1562.1	1563.6	1565.2	1566.7	1565.2	1563.6	1562.1
177.5°	1563.6	1563.3	1563.2	1564.0	1565.5	1567.1	1568.6	1570.2	1568.6	1567.1	1565.5
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1213.3	1211.2	1206.0	1202.9	1192.5	1179.9	1175.7	1165.3	1169.5	1162.2	1162.2
5°	1181.0	1171.6	1165.3	1155.9	1136.1	1122.5	1107.9	1100.6	1096.4	1091.2	1087.0
7.5°	1139.2	1131.9	1125.6	1107.9	1085.9	1067.2	1049.4	1042.1	1028.5	1019.1	1014.9
10°	1102.7	1092.2	1077.6	1056.7	1033.7	1009.7	994.1	978.4	968.0	962.7	951.2
12.5°	1065.1	1052.5	1036.9	1006.6	981.5	966.9	938.7	924.1	918.9	914.7	901.1
15°	1026.4	1012.9	994.1	965.9	943.9	909.5	892.8	881.3	868.8	867.7	857.3
17.5°	992.0	975.3	959.6	925.1	898.0	867.7	858.3	845.8	834.3	821.8	816.5
20°	948.1	932.5	921.0	883.4	853.1	834.3	818.6	808.2	800.9	788.4	786.3
22.5°	908.4	891.7	876.1	847.9	821.8	797.8	779.0	767.5	764.3	759.1	749.7
25°	869.8	853.1	834.3	808.2	781.0	764.3	747.6	740.3	734.1	725.7	718.4
27.5°	837.4	821.8	804.0	771.6	748.7	736.1	718.4	710.0	701.7	697.5	694.4
30°	798.8	781.0	767.5	742.4	717.4	700.6	688.1	680.8	673.5	669.3	667.2
32.5°	761.2	744.5	735.1	708.0	688.1	668.3	658.9	653.7	649.5	645.3	641.1
35°	730.9	714.2	699.6	674.5	654.7	641.1	633.8	625.5	622.3	618.2	618.2
37.5°	693.3	680.8	666.2	642.2	624.4	614.0	607.7	597.3	596.2	594.1	591.0
40°	661.0	648.4	634.9	614.0	598.3	585.8	577.4	572.2	569.1	567.0	564.9
42.5°	626.5	612.9	606.7	582.7	569.1	556.5	552.4	547.1	546.1	541.9	536.7
45°	593.1	581.6	569.1	551.3	539.8	529.4	523.1	519.0	513.7	512.7	509.6
47.5°	563.9	550.3	538.8	522.1	509.6	501.2	496.0	490.8	486.6	483.5	480.3
50°	526.3	515.8	506.4	488.7	478.2	469.9	462.6	458.4	454.2	454.2	454.2
52.5°	489.7	480.3	472.0	459.4	446.9	439.6	431.2	428.1	426.0	422.9	426.0
55°	454.2	444.8	436.5	427.1	412.5	406.2	397.8	394.7	395.7	395.7	398.9
57.5°	416.6	409.3	404.1	392.6	379.0	372.8	367.6	364.4	364.4	368.6	369.6
60°	380.1	372.8	363.4	352.9	344.6	337.3	334.1	335.2	335.2	337.3	342.5
62.5°	339.4	335.2	330.0	315.3	310.1	304.9	300.7	303.9	302.8	308.0	315.3
65°	301.8	297.6	290.3	283.0	276.7	271.5	270.4	271.5	273.6	278.8	287.1
67.5°	260.0	260.0	253.7	247.5	242.2	237.0	238.1	239.1	241.2	247.5	260.0
70°	225.5	221.4	215.1	210.9	206.7	204.7	202.6	206.7	213.0	217.2	226.6
72.5°	188.0	184.8	179.6	175.4	174.4	172.3	171.2	173.3	179.6	186.9	197.3
75°	148.3	149.3	146.2	143.1	143.1	139.9	142.0	142.0	148.3	155.6	163.9
77.5°	114.9	113.8	112.8	110.7	109.6	109.6	109.6	111.7	118.0	122.2	130.5
80°	81.4	82.5	79.4	80.4	79.4	80.4	80.4	84.6	87.7	92.9	99.2
82.5°	54.3	54.3	52.2	53.3	53.3	53.3	54.3	56.4	60.6	64.7	68.9
85°	30.3	31.3	29.2	31.3	31.3	31.3	32.4	33.4	36.5	37.6	41.8
87.5°	11.5	13.6	13.6	11.5	12.5	13.6	14.6	13.6	15.7	17.8	18.8
90°	9.5	10.5	11.4	13.2	15.0	16.8	18.6	19.9	21.2	22.5	23.8
92.5°	12.8	11.6	12.4	13.9	15.5	17.0	18.6	19.9	21.2	22.5	23.8
95°	63.1	62.7	57.8	48.0	38.2	28.4	18.6	19.9	21.2	22.5	23.8
97.5°	130.4	131.2	118.9	94.4	69.9	45.4	20.9	21.4	21.9	22.4	22.9
100°	197.0	197.4	197.9	199.0	200.0	201.1	202.1	163.6	125.2	86.7	48.2
102.5°	268.9	269.4	269.7	270.2	270.7	271.3	271.8	272.3	272.8	273.3	273.8
105°	345.6	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1
107.5°	420.4	420.4	420.7	421.2	421.7	422.3	422.8	423.0	423.3	423.5	423.8
110°	497.1	497.1	497.4	497.9	498.4	498.9	499.4	498.6	497.8	497.1	496.3

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	572.2	572.6	572.7	573.0	573.2	573.5	573.7	572.7	571.7	570.6	569.6
115°	646.3	646.9	647.0	647.3	647.6	647.8	648.1	647.1	646.0	645.0	643.9
117.5°	716.6	716.6	717.1	718.1	719.2	720.2	721.2	719.7	718.1	716.6	715.1
120°	785.2	785.1	785.5	786.3	787.0	787.8	788.6	788.1	787.6	787.1	786.6
122.5°	853.0	853.6	853.7	854.0	854.3	854.5	854.8	854.3	853.8	853.3	852.8
125°	918.9	919.8	919.8	919.8	919.8	919.8	919.8	918.8	917.8	916.7	915.7
127.5°	978.5	979.1	979.0	978.7	978.4	978.2	977.9	977.4	976.9	976.4	975.9
130°	1034.2	1034.8	1034.9	1035.2	1035.5	1035.7	1036.0	1035.2	1034.4	1033.7	1032.9
132.5°	1090.9	1091.7	1091.3	1090.5	1089.8	1089.0	1088.2	1088.2	1088.2	1088.2	1088.2
135°	1143.2	1144.0	1143.7	1143.2	1142.7	1142.2	1141.7	1141.2	1140.6	1140.1	1139.6
137.5°	1192.0	1192.8	1192.5	1192.0	1191.5	1190.9	1190.4	1190.4	1190.4	1190.4	1190.4
140°	1235.4	1235.7	1235.6	1235.3	1235.1	1234.8	1234.6	1235.1	1235.6	1236.1	1236.6
142.5°	1277.4	1277.5	1277.8	1278.3	1278.8	1279.4	1279.9	1279.9	1279.9	1279.9	1279.9
145°	1320.2	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.8	1321.0	1321.3	1321.6
147.5°	1355.4	1355.4	1355.5	1355.8	1356.0	1356.3	1356.5	1356.8	1357.0	1357.3	1357.6
150°	1388.2	1387.9	1388.2	1388.7	1389.2	1389.7	1390.2	1390.7	1391.2	1391.7	1392.2
152.5°	1418.7	1418.1	1418.4	1418.9	1419.4	1419.9	1420.4	1420.9	1421.4	1421.9	1422.4
155°	1445.6	1444.8	1445.1	1445.6	1446.1	1446.6	1447.1	1447.9	1448.7	1449.4	1450.2
157.5°	1470.7	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1471.1	1471.9	1472.6	1473.4
160°	1490.9	1490.1	1490.2	1490.5	1490.7	1491.0	1491.2	1492.2	1493.3	1494.3	1495.4
162.5°	1509.5	1508.7	1508.8	1509.1	1509.3	1509.6	1509.8	1511.4	1512.9	1514.5	1516.0
165°	1525.7	1524.9	1525.0	1525.3	1525.6	1525.8	1526.1	1527.7	1529.2	1530.8	1532.3
167.5°	1538.5	1537.7	1537.8	1538.1	1538.4	1538.6	1538.9	1540.7	1542.5	1544.3	1546.1
170°	1547.9	1547.0	1547.1	1547.4	1547.7	1547.9	1548.2	1550.2	1552.3	1554.3	1556.4
172.5°	1554.9	1554.0	1554.3	1554.8	1555.3	1555.8	1556.3	1558.1	1559.9	1561.7	1563.5
175°	1560.6	1559.8	1559.9	1560.2	1560.4	1560.7	1560.9	1563.0	1565.0	1567.1	1569.2
177.5°	1564.0	1563.2	1563.3	1563.6	1563.9	1564.1	1564.4	1566.2	1568.0	1569.8	1571.6
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1166.3	1159.0	1158.0	1160.1	1155.9	1162.2	1160.1	1162.2	1156.9	1162.2	1159.0
5°	1085.9	1083.9	1079.7	1074.5	1075.5	1076.5	1081.8	1076.5	1080.7	1081.8	1087.0
7.5°	1010.8	1006.6	1009.7	1007.6	998.2	996.1	998.2	1001.4	1007.6	1011.8	1014.9
10°	950.2	948.1	943.9	940.8	935.6	932.5	936.6	932.5	940.8	948.1	948.1
12.5°	904.3	895.9	890.7	889.6	878.2	880.2	884.4	887.6	896.9	901.1	901.1
15°	856.2	850.0	847.9	843.7	839.5	843.7	841.6	844.7	848.9	853.1	855.2
17.5°	814.5	813.4	814.5	804.0	807.1	801.9	803.0	808.2	805.1	808.2	814.5
20°	776.9	779.0	775.8	771.6	771.6	765.4	772.7	770.6	771.6	777.9	787.3
22.5°	748.7	747.6	744.5	741.4	737.2	738.2	739.3	737.2	745.5	750.8	751.8
25°	718.4	716.3	715.3	712.1	708.0	712.1	711.1	712.1	714.2	722.6	716.3
27.5°	690.2	686.0	688.1	685.0	683.9	685.0	685.0	686.0	688.1	689.2	690.2
30°	666.2	662.0	661.0	658.9	657.8	658.9	661.0	658.9	667.2	666.2	666.2
32.5°	640.1	636.9	634.9	634.9	633.8	632.8	633.8	634.9	641.1	636.9	641.1
35°	615.0	612.9	612.9	610.8	609.8	609.8	609.8	614.0	611.9	615.0	615.0
37.5°	591.0	591.0	590.0	587.9	586.8	587.9	586.8	588.9	587.9	588.9	590.0
40°	565.9	563.9	562.8	562.8	559.7	556.5	559.7	559.7	560.7	563.9	564.9
42.5°	535.7	536.7	536.7	532.5	532.5	532.5	533.6	534.6	534.6	536.7	536.7
45°	509.6	507.5	507.5	507.5	505.4	506.4	508.5	508.5	508.5	508.5	506.4
47.5°	480.3	480.3	481.4	481.4	484.5	483.5	483.5	482.4	480.3	480.3	481.4
50°	453.2	456.3	457.4	457.4	458.4	459.4	459.4	457.4	456.3	453.2	453.2
52.5°	427.1	429.2	431.2	434.4	436.5	435.4	435.4	433.3	429.2	428.1	427.1
55°	398.9	402.0	406.2	409.3	412.5	413.5	413.5	409.3	405.1	399.9	399.9
57.5°	372.8	375.9	383.2	386.3	390.5	390.5	388.4	385.3	379.0	374.9	371.7
60°	346.7	351.9	357.1	363.4	368.6	369.6	366.5	362.3	355.0	349.8	345.6
62.5°	318.5	323.7	334.1	340.4	344.6	344.6	344.6	339.4	330.0	322.7	316.4
65°	291.3	296.5	305.9	314.3	317.4	320.6	317.4	312.2	304.9	296.5	290.3
67.5°	263.1	269.4	278.8	285.1	289.2	292.4	290.3	286.1	276.7	265.2	261.0
70°	231.8	234.9	248.5	254.8	261.0	263.1	261.0	254.8	245.4	232.9	228.7
72.5°	202.6	205.7	218.2	223.5	228.7	230.8	227.6	223.5	215.1	203.6	198.4
75°	169.2	174.4	180.6	189.0	195.3	197.3	194.2	191.1	180.6	173.3	169.2
77.5°	133.7	138.9	147.2	154.5	160.8	159.8	155.6	156.6	145.1	136.8	133.7
80°	101.3	105.5	111.7	118.0	121.1	121.1	120.1	115.9	111.7	105.5	100.2
82.5°	70.0	75.2	80.4	84.6	84.6	85.6	83.5	82.5	78.3	73.1	72.0
85°	41.8	42.8	47.0	47.0	51.2	49.1	48.0	51.2	47.0	43.9	42.8
87.5°	18.8	17.8	18.8	18.8	17.8	19.8	19.8	18.8	19.8	18.8	18.8
90°	24.4	24.8	25.6	26.3	27.1	27.9	27.1	26.3	25.6	24.8	24.4
92.5°	24.4	24.5	24.8	25.1	25.3	25.6	25.3	25.1	24.8	24.5	24.4
95°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4
97.5°	23.2	23.3	23.6	23.9	24.1	24.4	24.1	23.9	23.6	23.3	23.2
100°	29.0	28.5	27.5	26.4	25.4	24.4	25.4	26.4	27.5	28.5	29.0
102.5°	274.1	263.3	241.6	219.9	198.2	176.5	198.2	219.9	241.6	263.3	274.1
105°	346.1	346.0	345.7	345.4	345.2	344.9	345.2	345.4	345.7	346.0	346.1
107.5°	423.9	423.4	422.4	421.3	420.3	419.3	420.3	421.3	422.4	423.4	423.9
110°	495.9	496.0	496.3	496.6	496.8	497.1	496.8	496.6	496.3	496.0	495.9

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	569.1	568.8	568.3	567.8	567.3	566.8	567.3	567.8	568.3	568.8	569.1
115°	643.4	642.6	641.1	639.5	638.0	636.4	638.0	639.5	641.1	642.6	643.4
117.5°	714.3	714.0	713.5	713.0	712.4	711.9	712.4	713.0	713.5	714.0	714.3
120°	786.3	785.7	784.4	783.1	781.8	780.5	781.8	783.1	784.4	785.7	786.3
122.5°	852.5	851.7	850.2	848.6	847.1	845.5	847.1	848.6	850.2	851.7	852.5
125°	915.2	914.8	914.0	913.3	912.5	911.7	912.5	913.3	914.0	914.8	915.2
127.5°	975.6	974.6	972.5	970.4	968.4	966.3	968.4	970.4	972.5	974.6	975.6
130°	1032.5	1031.9	1030.6	1029.3	1028.0	1026.7	1028.0	1029.3	1030.6	1031.9	1032.5
132.5°	1088.2	1087.6	1086.3	1085.0	1083.7	1082.4	1083.7	1085.0	1086.3	1087.6	1088.2
135°	1139.3	1138.5	1137.0	1135.5	1133.9	1132.4	1133.9	1135.5	1137.0	1138.5	1139.3
137.5°	1190.4	1189.8	1188.5	1187.2	1185.9	1184.6	1185.9	1187.2	1188.5	1189.8	1190.4
140°	1236.9	1236.1	1234.6	1233.0	1231.5	1229.9	1231.5	1233.0	1234.6	1236.1	1236.9
142.5°	1279.9	1279.1	1277.6	1276.0	1274.5	1272.9	1274.5	1276.0	1277.6	1279.1	1279.9
145°	1321.7	1320.9	1319.4	1317.8	1316.3	1314.7	1316.3	1317.8	1319.4	1320.9	1321.7
147.5°	1357.7	1356.8	1355.0	1353.2	1351.4	1349.6	1351.4	1353.2	1355.0	1356.8	1357.7
150°	1392.5	1391.5	1389.4	1387.3	1385.3	1383.2	1385.3	1387.3	1389.4	1391.5	1392.5
152.5°	1422.7	1421.8	1420.0	1418.2	1416.4	1414.6	1416.4	1418.2	1420.0	1421.8	1422.7
155°	1450.6	1449.6	1447.5	1445.4	1443.4	1441.3	1443.4	1445.4	1447.5	1449.6	1450.6
157.5°	1473.8	1472.8	1470.7	1468.6	1466.6	1464.5	1466.6	1468.6	1470.7	1472.8	1473.8
160°	1495.9	1494.9	1492.8	1490.7	1488.7	1486.6	1488.7	1490.7	1492.8	1494.9	1495.9
162.5°	1516.8	1515.6	1513.3	1511.0	1508.6	1506.3	1508.6	1511.0	1513.3	1515.6	1516.8
165°	1533.1	1532.1	1530.0	1527.9	1525.9	1523.8	1525.9	1527.9	1530.0	1532.1	1533.1
167.5°	1547.0	1545.8	1543.5	1541.2	1538.8	1536.5	1538.8	1541.2	1543.5	1545.8	1547.0
170°	1557.4	1556.2	1553.9	1551.6	1549.3	1547.0	1549.3	1551.6	1553.9	1556.2	1557.4
172.5°	1564.4	1563.2	1560.9	1558.6	1556.3	1554.0	1556.3	1558.6	1560.9	1563.2	1564.4
175°	1570.2	1569.0	1566.7	1564.4	1562.1	1559.8	1562.1	1564.4	1566.7	1569.0	1570.2
177.5°	1572.5	1571.5	1569.4	1567.3	1565.3	1563.2	1565.3	1567.3	1569.4	1571.5	1572.5
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1168.4	1162.2	1169.5	1160.1	1162.2	1173.7	1172.6	1183.1	1189.3	1188.3	1193.5
5°	1091.2	1091.2	1094.3	1093.3	1103.7	1113.1	1125.6	1136.1	1147.6	1153.8	1161.1
7.5°	1014.9	1025.4	1027.5	1032.7	1045.2	1060.9	1073.4	1089.1	1105.8	1117.3	1125.6
10°	952.3	960.6	969.0	973.2	986.7	1007.6	1025.4	1050.4	1071.3	1083.9	1095.3
12.5°	896.9	906.3	910.5	929.3	938.7	952.3	977.4	1004.5	1027.5	1041.0	1050.4
15°	857.3	862.5	871.9	883.4	892.8	909.5	930.4	960.6	982.6	994.1	1026.4
17.5°	823.9	830.1	835.3	840.6	855.2	872.9	892.8	918.9	947.1	966.9	983.6
20°	789.4	792.5	798.8	807.1	817.6	834.3	852.0	879.2	904.3	919.9	941.8
22.5°	748.7	758.1	764.3	770.6	782.1	800.9	817.6	837.4	868.8	886.5	909.5
25°	724.7	728.8	733.0	740.3	748.7	765.4	784.2	805.1	830.1	848.9	868.8
27.5°	693.3	699.6	704.8	714.2	719.4	733.0	750.8	771.6	801.9	817.6	834.3
30°	667.2	673.5	677.7	681.8	689.2	703.8	720.5	737.2	765.4	785.2	801.9
32.5°	641.1	647.4	652.6	655.7	663.1	672.5	686.0	706.9	730.9	744.5	766.4
35°	618.2	618.2	624.4	628.6	634.9	643.2	655.7	671.4	696.5	714.2	734.1
37.5°	592.0	593.1	598.3	601.4	607.7	616.1	628.6	643.2	664.1	677.7	697.5
40°	564.9	568.0	570.1	575.3	582.7	585.8	598.3	615.0	635.9	648.4	665.1
42.5°	537.8	539.8	545.1	549.2	555.5	560.7	569.1	584.7	600.4	619.2	632.8
45°	507.5	512.7	515.8	523.1	526.3	531.5	539.8	552.4	571.2	582.7	598.3
47.5°	481.4	483.5	485.5	494.9	501.2	504.3	512.7	520.0	539.8	550.3	564.9
50°	453.2	453.2	456.3	460.5	467.8	474.1	481.4	489.7	505.4	515.8	530.4
52.5°	427.1	423.9	426.0	428.1	435.4	441.7	449.0	460.5	475.1	481.4	493.9
55°	398.9	393.7	396.8	399.9	402.0	410.4	418.7	426.0	437.5	446.9	458.4
57.5°	368.6	367.6	365.5	366.5	371.7	376.9	383.2	392.6	406.2	413.5	419.8
60°	341.4	335.2	333.1	335.2	338.3	341.4	349.8	358.2	369.6	376.9	384.3
62.5°	313.3	307.0	302.8	299.7	302.8	310.1	315.3	321.6	331.0	339.4	345.6
65°	286.1	276.7	272.5	270.4	269.4	274.6	278.8	287.1	295.5	298.6	305.9
67.5°	255.8	247.5	242.2	239.1	239.1	239.1	243.3	251.6	260.0	261.0	268.4
70°	225.5	216.1	210.9	206.7	204.7	206.7	212.0	213.0	220.3	222.4	226.6
72.5°	193.2	184.8	178.6	173.3	174.4	176.5	176.5	178.6	182.7	188.0	188.0
75°	162.9	151.4	148.3	144.1	142.0	142.0	142.0	146.2	149.3	153.5	152.5
77.5°	128.4	122.2	115.9	113.8	110.7	109.6	111.7	111.7	113.8	116.9	118.0
80°	99.2	91.9	87.7	85.6	81.4	80.4	81.4	81.4	84.6	83.5	84.6
82.5°	68.9	63.7	60.6	57.4	55.3	56.4	55.3	55.3	56.4	55.3	55.3
85°	39.7	38.6	36.5	35.5	34.5	32.4	34.5	33.4	32.4	31.3	33.4
87.5°	18.8	17.8	17.8	15.7	15.7	14.6	15.7	15.7	14.6	14.6	14.6
90°	23.8	22.5	21.2	19.9	18.6	16.8	15.0	13.2	11.4	10.5	9.5
92.5°	23.8	22.5	21.2	19.9	18.6	17.0	15.5	13.9	12.4	11.6	12.8
95°	23.8	22.5	21.2	19.9	18.6	28.4	38.2	48.0	57.8	62.7	63.1
97.5°	22.9	22.4	21.9	21.4	20.9	45.4	69.9	94.4	118.9	131.2	130.4
100°	48.2	86.7	125.2	163.6	202.1	201.1	200.0	199.0	197.9	197.4	197.0
102.5°	273.8	273.3	272.8	272.3	271.8	271.3	270.7	270.2	269.7	269.4	268.9
105°	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1	346.1	345.6
107.5°	423.8	423.5	423.3	423.0	422.8	422.3	421.7	421.2	420.7	420.4	420.4
110°	496.3	497.1	497.8	498.6	499.4	498.9	498.4	497.9	497.4	497.1	497.1

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	569.6	570.6	571.7	572.7	573.7	573.5	573.2	573.0	572.7	572.6	572.2
115°	643.9	645.0	646.0	647.1	648.1	647.8	647.6	647.3	647.0	646.9	646.3
117.5°	715.1	716.6	718.1	719.7	721.2	720.2	719.2	718.1	717.1	716.6	716.6
120°	786.6	787.1	787.6	788.1	788.6	787.8	787.0	786.3	785.5	785.1	785.2
122.5°	852.8	853.3	853.8	854.3	854.8	854.5	854.3	854.0	853.7	853.6	853.0
125°	915.7	916.7	917.8	918.8	919.8	919.8	919.8	919.8	919.8	919.8	918.9
127.5°	975.9	976.4	976.9	977.4	977.9	978.2	978.4	978.7	979.0	979.1	978.5
130°	1032.9	1033.7	1034.4	1035.2	1036.0	1035.7	1035.5	1035.2	1034.9	1034.8	1034.2
132.5°	1088.2	1088.2	1088.2	1088.2	1088.2	1089.0	1089.8	1090.5	1091.3	1091.7	1090.9
135°	1139.6	1140.1	1140.6	1141.2	1141.7	1142.2	1142.7	1143.2	1143.7	1144.0	1143.2
137.5°	1190.4	1190.4	1190.4	1190.4	1190.4	1190.9	1191.5	1192.0	1192.5	1192.8	1192.0
140°	1236.6	1236.1	1235.6	1235.1	1234.6	1234.8	1235.1	1235.3	1235.6	1235.7	1235.4
142.5°	1279.9	1279.9	1279.9	1279.9	1279.9	1279.4	1278.8	1278.3	1277.8	1277.5	1277.4
145°	1321.6	1321.3	1321.0	1320.8	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.2
147.5°	1357.6	1357.3	1357.0	1356.8	1356.5	1356.3	1356.0	1355.8	1355.5	1355.4	1355.4
150°	1392.2	1391.7	1391.2	1390.7	1390.2	1389.7	1389.2	1388.7	1388.2	1387.9	1388.2
152.5°	1422.4	1421.9	1421.4	1420.9	1420.4	1419.9	1419.4	1418.9	1418.4	1418.1	1418.7
155°	1450.2	1449.4	1448.7	1447.9	1447.1	1446.6	1446.1	1445.6	1445.1	1444.8	1445.6
157.5°	1473.4	1472.6	1471.9	1471.1	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.7
160°	1495.4	1494.3	1493.3	1492.2	1491.2	1491.0	1490.7	1490.5	1490.2	1490.1	1490.9
162.5°	1516.0	1514.5	1512.9	1511.4	1509.8	1509.6	1509.3	1509.1	1508.8	1508.7	1509.5
165°	1532.3	1530.8	1529.2	1527.7	1526.1	1525.8	1525.6	1525.3	1525.0	1524.9	1525.7
167.5°	1546.1	1544.3	1542.5	1540.7	1538.9	1538.6	1538.4	1538.1	1537.8	1537.7	1538.5
170°	1556.4	1554.3	1552.3	1550.2	1548.2	1547.9	1547.7	1547.4	1547.1	1547.0	1547.9
172.5°	1563.5	1561.7	1559.9	1558.1	1556.3	1555.8	1555.3	1554.8	1554.3	1554.0	1554.9
175°	1569.2	1567.1	1565.0	1563.0	1560.9	1560.7	1560.4	1560.2	1559.9	1559.8	1560.6
177.5°	1571.6	1569.8	1568.0	1566.2	1564.4	1564.1	1563.9	1563.6	1563.3	1563.2	1564.0
180°	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7	1566.7

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1230.0	1230.0	1230.0	1230.0
2.5°	1200.8	1211.2	1218.6	1232.1
5°	1173.7	1192.5	1210.2	1229.0
7.5°	1146.5	1168.4	1196.6	1220.6
10°	1116.2	1144.4	1177.8	1210.2
12.5°	1085.9	1119.4	1155.9	1198.7
15°	1049.4	1092.2	1135.0	1181.0
17.5°	1017.0	1060.9	1106.8	1164.3
20°	980.5	1028.5	1078.6	1137.1
22.5°	948.1	1001.4	1053.6	1115.2
25°	911.6	963.8	1021.2	1087.0
27.5°	881.3	929.3	985.7	1056.7
30°	844.7	896.9	953.3	1024.3
32.5°	810.3	860.4	919.9	989.9
35°	774.8	825.9	879.2	946.0
37.5°	741.4	785.2	838.5	902.2
40°	703.8	751.8	799.8	850.0
42.5°	669.3	713.2	758.1	797.8
45°	630.7	668.3	711.1	743.5
47.5°	595.2	628.6	662.0	687.1
50°	559.7	585.8	610.8	632.8
52.5°	517.9	547.1	560.7	574.3
55°	480.3	497.0	509.6	523.1
57.5°	443.8	451.1	457.4	469.9
60°	395.7	404.1	411.4	420.8
62.5°	354.0	358.2	360.2	369.6
65°	314.3	313.3	318.5	323.7
67.5°	271.5	270.4	275.7	277.8
70°	229.7	228.7	229.7	234.9
72.5°	190.0	190.0	191.1	193.2
75°	153.5	153.5	154.5	156.6
77.5°	115.9	118.0	116.9	121.1
80°	84.6	82.5	84.6	86.7
82.5°	55.3	57.4	57.4	55.3
85°	31.3	31.3	31.3	31.3
87.5°	13.6	13.6	14.6	15.7
90°	7.4	5.3	3.3	1.2
92.5°	15.1	17.4	19.8	22.1
95°	63.9	64.6	65.4	66.2
97.5°	128.9	127.4	125.8	124.3
100°	196.3	195.5	194.8	194.0
102.5°	267.9	266.8	265.8	264.8
105°	344.6	343.5	342.5	341.5
107.5°	420.4	420.4	420.4	420.4
110°	497.1	497.1	497.1	497.1

TEST NUMBER: P1026995

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	571.4	570.7	569.9	569.1
115°	645.0	643.7	642.4	641.1
117.5°	716.6	716.6	716.6	716.6
120°	785.5	785.8	786.0	786.3
122.5°	851.7	850.4	849.1	847.8
125°	917.1	915.3	913.5	911.7
127.5°	977.2	975.9	974.6	973.3
130°	1032.9	1031.6	1030.3	1029.0
132.5°	1089.4	1087.9	1086.3	1084.8
135°	1141.7	1140.1	1138.6	1137.0
137.5°	1190.5	1188.9	1187.4	1185.8
140°	1234.9	1234.4	1233.9	1233.4
142.5°	1277.1	1276.9	1276.6	1276.4
145°	1319.7	1319.2	1318.7	1318.2
147.5°	1355.4	1355.4	1355.4	1355.4
150°	1388.7	1389.2	1389.7	1390.2
152.5°	1420.0	1421.3	1422.6	1423.9
155°	1447.1	1448.7	1450.2	1451.8
157.5°	1471.5	1472.2	1473.0	1473.8
160°	1492.4	1493.9	1495.5	1497.0
162.5°	1511.0	1512.5	1514.1	1515.6
165°	1527.2	1528.8	1530.3	1531.9
167.5°	1540.0	1541.6	1543.1	1544.7
170°	1549.7	1551.5	1553.3	1555.1
172.5°	1556.7	1558.5	1560.3	1562.1
175°	1562.1	1563.6	1565.2	1566.7
177.5°	1565.5	1567.1	1568.6	1570.2
180°	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)