

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027291

Luminaire Tested: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027291
REPORT IS A COMBINATION OF REPORTS P1005852 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5660.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027291

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027291

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	57	55	54
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	45	42	39
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30
6	65	53	45	39	60	49	42	37	44	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	24
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8895	8895	8895
5°	8896	8673	8687
10°	8809	8454	8380
15°	8684	8149	7976
20°	8530	7781	7553
25°	8353	7421	7099
30°	8137	7026	6622
35°	7915	6625	6115
40°	7705	6213	5621
45°	7452	5768	5103
50°	7196	5296	4576
55°	6898	4830	4030
60°	6594	4298	3463
65°	6230	3704	2852
70°	5807	3016	2245
75°	5224	2268	1636
80°	4405	1469	1104
85°	3299	790	622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7452 cd/sqm

TEST NUMBER: P1027291

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	2.3
10°-20°	365.1	6.5
20°-30°	529.4	9.4
30°-40°	603.2	10.7
40°-50°	587.9	10.4
50°-60°	494.8	8.7
60°-70°	346.7	6.1
70°-80°	177.7	3.1
80°-90°	45.5	0.8
90°-100°	26.3	0.5
100°-110°	174.8	3.1
110°-120°	314.7	5.6
120°-130°	404.0	7.1
130°-140°	434.5	7.7
140°-150°	407.8	7.2
150°-160°	329.9	5.8
160°-170°	213.3	3.8
170°-180°	73.6	1.3
0°-30°	1025.3	18.1
0°-40°	1628.5	28.8
0°-60°	2711.2	47.9
0°-90°	3281.1	58.0
90°-120°	515.8	9.1
90°-150°	1762.1	31.1
90°-180°	2379.0	42.0
0°-180°	5660.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1370	1381	1379	131
15°	1318	1312	1290	1289	1279	372
25°	1195	1180	1141	1127	1116	550
35°	1030	1004	957	927	912	645
45°	843	813	755	713	697	650
55°	640	606	547	500	483	572
65°	433	397	342	300	284	429
75°	231	199	155	132	125	244
85°	58	39	34	32	32	63
90°	1	5	9	12	14	5
95°	33	31	9	12	12	40
105°	169	171	171	171	170	179
115°	317	320	320	318	315	314
125°	451	455	455	452	451	403
135°	562	566	564	563	560	433
145°	652	653	653	653	650	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1027291

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1391.4	1388.3	1377.8	1388.3	1387.2
5°	1386.2	1382.0	1370.4	1380.9	1378.8
7.5°	1375.7	1371.5	1357.9	1366.3	1364.2
10°	1360.0	1356.8	1342.1	1345.3	1342.1
12.5°	1342.1	1337.9	1317.0	1319.1	1313.8
15°	1318.0	1311.7	1289.7	1288.7	1279.2
17.5°	1292.9	1283.4	1257.2	1252.0	1244.6
20°	1262.4	1252.0	1218.4	1213.2	1203.7
22.5°	1228.9	1218.4	1182.8	1171.2	1163.9
25°	1195.3	1179.6	1140.8	1127.2	1115.7
27.5°	1157.6	1138.7	1097.8	1080.0	1068.5
30°	1115.7	1095.7	1051.7	1027.6	1018.1
32.5°	1074.8	1050.6	1005.6	978.3	965.7
35°	1029.7	1004.5	957.3	926.9	912.2
37.5°	986.7	956.3	908.0	872.4	857.7
40°	940.5	909.1	858.8	818.9	806.3
42.5°	892.3	859.8	807.4	769.6	749.7
45°	843.0	812.6	755.0	713.0	697.3
47.5°	791.7	760.2	702.5	659.5	641.7
50°	743.4	708.8	649.1	605.0	589.3
52.5°	691.0	655.3	599.8	551.5	535.8
55°	639.6	606.1	547.3	500.2	483.4
57.5°	587.2	551.5	494.9	448.8	434.1
60°	536.9	500.2	443.5	397.4	381.7
62.5°	483.4	448.8	391.1	349.2	333.4
65°	433.0	397.4	341.8	299.9	284.2
67.5°	382.7	347.1	293.6	253.7	241.2
70°	331.3	295.7	243.3	210.8	198.2
72.5°	281.0	246.4	198.2	168.8	161.5
75°	230.7	199.2	155.2	132.1	124.8
77.5°	179.3	154.1	117.4	99.6	93.3
80°	136.3	111.1	81.8	72.3	70.3
82.5°	94.4	72.3	54.5	51.4	50.3
85°	57.7	38.8	33.6	32.5	31.5
87.5°	24.1	16.8	15.7	15.7	14.7
90°	0.6	5.2	9.2	12.1	13.8
92.5°	10.9	5.7	9.2	12.1	12.6
95°	32.7	31.0	9.2	12.1	12.1
97.5°	61.4	64.9	10.3	11.5	12.1
100°	95.9	97.6	99.9	14.4	12.1
102.5°	130.9	133.2	134.3	135.5	87.3
105°	168.8	171.1	171.1	171.1	170.5
107.5°	207.8	207.8	209.0	209.5	207.2
110°	245.7	245.7	246.8	245.1	245.7

TEST NUMBER: P1027291

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.3	283.0	283.6	281.3	280.1
115°	316.9	319.8	320.3	318.0	314.6
117.5°	354.2	354.2	356.5	353.1	351.9
120°	388.6	388.1	389.8	388.6	385.8
122.5°	419.1	421.9	422.5	421.4	417.9
125°	450.6	454.7	454.7	452.4	450.6
127.5°	481.1	483.9	483.4	482.2	477.6
130°	508.6	511.5	512.1	510.3	507.5
132.5°	536.2	539.6	537.9	537.9	535.0
135°	562.0	565.5	564.3	563.2	559.7
137.5°	586.1	589.6	588.4	588.4	585.6
140°	609.7	610.8	610.2	611.4	607.9
142.5°	630.9	631.5	632.6	632.6	629.2
145°	651.6	652.7	652.7	653.3	649.8
147.5°	669.9	669.9	670.5	671.1	667.1
150°	687.2	686.0	687.2	688.3	683.7
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)