

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027300

Luminaire Tested: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027300
REPORT IS A COMBINATION OF REPORTS P1005891 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6433.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027300

CATALOG NUMBER: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027300

CATALOG NUMBER: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	50	48	48	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	41	41	37
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	56	51	69	60	53	48	51	46	42	43	39	36	36	33	31	31	31	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	27	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21	21	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8857	8857	8857
5°	8858	8636	8650
10°	8772	8418	8344
15°	8647	8114	7943
20°	8494	7747	7521
25°	8317	7389	7069
30°	8102	6996	6594
35°	7882	6596	6089
40°	7672	6186	5597
45°	7420	5743	5081
50°	7165	5273	4556
55°	6869	4810	4012
60°	6566	4280	3448
65°	6205	3689	2839
70°	5783	3002	2234
75°	5201	2257	1628
80°	4385	1461	1099
85°	3282	785	618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7420 cd/sqm

TEST NUMBER: P1027300

CATALOG NUMBER: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	2.0
10°-20°	363.6	5.7
20°-30°	527.2	8.2
30°-40°	600.6	9.3
40°-50°	585.4	9.1
50°-60°	492.7	7.7
60°-70°	345.2	5.4
70°-80°	177.0	2.8
80°-90°	45.7	0.7
90°-100°	35.0	0.5
100°-110°	232.6	3.6
110°-120°	418.8	6.5
120°-130°	537.6	8.4
130°-140°	578.2	9.0
140°-150°	542.6	8.4
150°-160°	438.9	6.8
160°-170°	283.9	4.4
170°-180°	97.9	1.5
0°-30°	1020.9	15.9
0°-40°	1621.5	25.2
0°-60°	2699.6	42.0
0°-90°	3267.5	50.8
90°-120°	686.3	10.7
90°-150°	2344.8	36.4
90°-180°	3165.0	49.2
0°-180°	6433.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1380	1376	1365	1375	1373	131
15°	1312	1306	1284	1283	1274	370
25°	1190	1175	1136	1122	1111	548
35°	1025	1000	953	923	908	642
45°	839	809	752	710	694	647
55°	637	604	545	498	481	570
65°	431	396	340	299	283	427
75°	230	198	154	132	124	243
85°	57	39	33	32	31	63
90°	1	7	12	16	18	5
95°	44	41	12	16	16	53
105°	225	228	228	228	227	238
115°	422	426	426	423	419	418
125°	600	605	605	602	600	536
135°	748	752	751	749	745	577
145°	867	869	869	869	865	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1027300

CATALOG NUMBER: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1382.3	1382.3	1382.3	1382.3	1382.3
2.5°	1385.5	1382.3	1371.9	1382.3	1381.3
5°	1380.3	1376.1	1364.6	1375.0	1373.0
7.5°	1369.8	1365.6	1352.1	1360.4	1358.3
10°	1354.2	1351.0	1336.4	1339.5	1336.4
12.5°	1336.4	1332.2	1311.4	1313.4	1308.2
15°	1312.4	1306.1	1284.2	1283.2	1273.8
17.5°	1287.3	1277.9	1251.8	1246.6	1239.3
20°	1257.1	1246.6	1213.2	1208.0	1198.6
22.5°	1223.7	1213.2	1177.7	1166.2	1158.9
25°	1190.2	1174.6	1135.9	1122.4	1110.9
27.5°	1152.7	1133.9	1093.1	1075.4	1063.9
30°	1110.9	1091.1	1047.2	1023.2	1013.8
32.5°	1070.2	1046.2	1001.3	974.1	961.6
35°	1025.3	1000.2	953.2	923.0	908.3
37.5°	982.5	952.2	904.2	868.7	854.0
40°	936.5	905.2	855.1	815.4	802.9
42.5°	888.5	856.1	803.9	766.3	746.5
45°	839.4	809.2	751.7	710.0	694.3
47.5°	788.3	757.0	699.5	656.7	639.0
50°	740.2	705.8	646.3	602.4	586.8
52.5°	688.0	652.5	597.2	549.2	533.5
55°	636.9	603.5	545.0	498.0	481.3
57.5°	584.7	549.2	492.8	446.9	432.2
60°	534.6	498.0	441.6	395.7	380.0
62.5°	481.3	446.9	389.4	347.7	332.0
65°	431.2	395.7	340.4	298.6	282.9
67.5°	381.1	345.6	292.3	252.7	240.1
70°	329.9	294.4	242.2	209.9	197.3
72.5°	279.8	245.4	197.3	168.1	160.8
75°	229.7	198.4	154.5	131.6	124.2
77.5°	178.5	153.5	116.9	99.2	92.9
80°	135.7	110.7	81.4	72.0	70.0
82.5°	94.0	72.0	54.3	51.2	50.1
85°	57.4	38.6	33.4	32.4	31.3
87.5°	24.0	16.7	15.7	15.7	14.6
90°	0.8	6.9	12.2	16.0	18.3
92.5°	14.5	7.6	12.2	16.0	16.8
95°	43.5	41.3	12.2	16.0	16.0
97.5°	81.7	86.3	13.8	15.3	16.0
100°	127.6	129.9	132.9	19.1	16.0
102.5°	174.2	177.2	178.8	180.3	116.1
105°	224.6	227.6	227.6	227.6	226.9
107.5°	276.5	276.5	278.1	278.8	275.8
110°	326.9	326.9	328.5	326.2	326.9



TEST NUMBER: P1027300

CATALOG NUMBER: S125RDIP-B850D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.3	376.6	377.4	374.3	372.8
115°	421.7	425.5	426.3	423.2	418.6
117.5°	471.3	471.3	474.4	469.8	468.3
120°	517.2	516.4	518.7	517.2	513.3
122.5°	557.6	561.5	562.2	560.7	556.1
125°	599.7	605.0	605.0	602.0	599.7
127.5°	640.1	644.0	643.2	641.7	635.6
130°	676.8	680.6	681.4	679.1	675.3
132.5°	713.5	718.1	715.8	715.8	712.0
135°	747.9	752.4	750.9	749.4	744.8
137.5°	779.9	784.5	783.0	783.0	779.2
140°	811.3	812.8	812.0	813.6	809.0
142.5°	839.5	840.3	841.8	841.8	837.2
145°	867.0	868.6	868.6	869.3	864.7
147.5°	891.5	891.5	892.2	893.0	887.6
150°	914.4	912.9	914.4	915.9	909.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)