

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027006

Luminaire Tested: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027006
REPORT IS A COMBINATION OF REPORTS P1002500 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8286.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027006

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027006

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	49	41	36	56	45	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1027006

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.5
10°-20°	353.3	4.3
20°-30°	521.6	6.3
30°-40°	608.6	7.3
40°-50°	611.2	7.4
50°-60°	536.5	6.5
60°-70°	399.6	4.8
70°-80°	228.2	2.8
80°-90°	68.2	0.8
90°-100°	53.4	0.6
100°-110°	355.1	4.3
110°-120°	639.5	7.7
120°-130°	820.9	9.9
130°-140°	882.9	10.7
140°-150°	828.6	10.0
150°-160°	670.3	8.1
160°-170°	433.5	5.2
170°-180°	149.5	1.8
0°-30°	1000.0	12.1
0°-40°	1608.5	19.4
0°-60°	2756.3	33.3
0°-90°	3452.4	41.7
90°-120°	1048.1	12.6
90°-150°	3580.4	43.2
90°-180°	4834.0	58.3
0°-180°	8286.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	10	19	24	28	7
95°	66	63	19	24	24	81
105°	343	348	348	348	346	363
115°	644	650	651	646	639	638
125°	916	924	924	919	916	818
135°	1142	1149	1147	1144	1137	880
145°	1324	1326	1326	1327	1320	828
155°	1458	1451	1453	1457	1448	672
165°	1539	1532	1533	1540	1530	435
175°	1574	1567	1568	1577	1567	150
180°	1574	1574	1574	1574	1574	

TEST NUMBER: P1027006

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	1.2	10.5	18.7	24.5	28.0
92.5°	22.2	11.7	18.7	24.5	25.7
95°	66.5	63.0	18.7	24.5	24.5
97.5°	124.8	131.8	21.0	23.3	24.5
100°	194.8	198.3	203.0	29.2	24.5
102.5°	266.0	270.6	273.0	275.3	177.3
105°	342.9	347.6	347.6	347.6	346.4
107.5°	422.3	422.3	424.6	425.8	421.1
110°	499.2	499.2	501.6	498.1	499.2

TEST NUMBER: P1027006

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.6	575.1	576.2	571.6	569.2
115°	643.9	649.7	650.9	646.2	639.2
117.5°	719.7	719.7	724.4	717.4	715.0
120°	789.7	788.5	792.0	789.7	783.9
122.5°	851.5	857.4	858.5	856.2	849.2
125°	915.7	923.8	923.8	919.2	915.7
127.5°	977.5	983.3	982.2	979.8	970.5
130°	1033.5	1039.3	1040.5	1037.0	1031.2
132.5°	1089.5	1096.5	1093.0	1093.0	1087.1
135°	1142.0	1149.0	1146.6	1144.3	1137.3
137.5°	1191.0	1198.0	1195.6	1195.6	1189.8
140°	1238.8	1241.1	1240.0	1242.3	1235.3
142.5°	1281.9	1283.1	1285.4	1285.4	1278.5
145°	1323.9	1326.3	1326.3	1327.4	1320.4
147.5°	1361.3	1361.3	1362.4	1363.6	1355.4
150°	1396.3	1393.9	1396.3	1398.6	1389.3
152.5°	1430.1	1424.3	1426.6	1428.9	1420.8
155°	1458.1	1451.1	1453.4	1456.9	1447.6
157.5°	1480.2	1476.8	1476.8	1480.2	1470.9
160°	1503.6	1496.6	1497.7	1502.4	1493.1
162.5°	1522.2	1515.2	1516.4	1523.4	1512.9
165°	1538.6	1531.6	1532.7	1539.7	1530.4
167.5°	1551.4	1544.4	1545.6	1553.7	1543.2
170°	1561.9	1553.7	1554.9	1564.2	1553.7
172.5°	1568.9	1560.7	1563.1	1571.2	1560.7
175°	1573.6	1566.6	1567.7	1577.1	1566.6
177.5°	1577.1	1570.1	1571.2	1579.4	1570.1
180°	1573.6	1573.6	1573.6	1573.6	1573.6

(END OF REPORT)