

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027016

Luminaire Tested: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027016
REPORT IS A COMBINATION OF REPORTS P1002555 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4794.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027016

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027016

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	100	95	91	87	94	90	86	82	79	76	73	69	67	65	60	59	57	53		
2	91	83	76	70	85	78	72	67	69	64	60	60	57	54	52	50	47	43		
3	83	72	65	58	77	68	61	55	60	55	50	53	49	45	46	43	40	36		
4	76	64	56	49	71	60	53	47	53	47	42	47	42	38	41	37	34	31		
5	69	57	48	42	65	54	46	40	48	41	37	42	37	33	37	33	30	27		
6	64	51	43	36	60	48	41	35	43	37	32	38	33	29	33	29	26	23		
7	59	46	38	32	55	44	36	31	39	33	28	35	29	26	31	26	23	21		
8	55	42	34	28	51	40	32	27	36	29	25	32	27	23	28	24	21	18		
9	51	38	31	25	48	36	29	24	33	27	22	29	24	20	26	22	19	16		
10	48	35	28	23	45	33	27	22	30	24	20	27	22	19	24	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6852	6852	6852
5°	6864	6708	6725
10°	6812	6571	6553
15°	6729	6412	6341
20°	6617	6220	6131
25°	6484	6016	5877
30°	6324	5793	5646
35°	6173	5587	5434
40°	6021	5370	5219
45°	5849	5183	5026
50°	5684	4978	4852
55°	5484	4784	4650
60°	5267	4563	4442
65°	5039	4329	4209
70°	4778	4017	3966
75°	4368	3707	3669
80°	3829	3332	3341
85°	3299	3033	3169

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5849 cd/sqm

TEST NUMBER: P1027016

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	2.1
10°-20°	287.3	6.0
20°-30°	427.2	8.9
30°-40°	505.9	10.6
40°-50°	523.1	10.9
50°-60°	481.9	10.1
60°-70°	389.5	8.1
70°-80°	260.6	5.4
80°-90°	135.4	2.8
90°-100°	92.2	1.9
100°-110°	164.7	3.4
110°-120°	233.3	4.9
120°-130°	272.6	5.7
130°-140°	279.7	5.8
140°-150°	255.6	5.3
150°-160°	205.3	4.3
160°-170°	132.7	2.8
170°-180°	45.8	1.0
0°-30°	815.7	17.0
0°-40°	1321.6	27.6
0°-60°	2326.6	48.5
0°-90°	3112.1	64.9
90°-120°	490.2	10.2
90°-150°	1298.1	27.1
90°-180°	1682.0	35.1
0°-180°	4794.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1070	1067	1060	1068	1067	101
15°	1021	1022	1015	1021	1017	288
25°	928	931	925	929	924	427
35°	803	810	807	810	810	503
45°	662	673	678	686	687	511
55°	508	525	542	554	558	455
65°	350	374	400	415	419	348
75°	193	220	254	275	280	204
85°	58	92	129	152	160	60
90°	17	54	92	118	126	13
95°	34	60	82	107	114	36
105°	114	133	164	185	192	121
115°	204	213	240	258	262	202
125°	285	286	307	322	326	254
135°	352	353	360	372	376	271
145°	406	406	406	412	414	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1027016

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1069.5	1069.5	1069.5	1069.5	1069.5
2.5°	1072.6	1070.5	1063.2	1070.5	1069.5
5°	1069.5	1067.4	1060.0	1068.4	1067.4
7.5°	1062.1	1061.1	1053.7	1061.1	1060.0
10°	1051.6	1051.6	1043.2	1050.6	1049.5
12.5°	1037.0	1038.0	1031.7	1037.0	1033.8
15°	1021.2	1022.3	1014.9	1021.2	1017.0
17.5°	1001.3	1003.4	996.1	1001.3	998.2
20°	979.3	981.4	974.0	977.2	977.2
22.5°	954.1	958.3	949.9	954.1	951.0
25°	927.9	931.1	924.8	929.0	923.7
27.5°	899.6	903.8	896.5	899.6	897.5
30°	867.1	873.4	867.1	869.2	868.1
32.5°	837.7	843.0	838.8	840.9	839.8
35°	803.1	810.5	807.3	810.5	810.5
37.5°	769.6	775.9	774.8	779.0	778.0
40°	735.0	743.4	742.3	746.5	748.6
42.5°	697.2	708.8	711.9	717.2	717.2
45°	661.6	673.1	678.4	685.7	686.8
47.5°	624.9	635.4	643.8	654.3	656.4
50°	587.2	598.7	610.2	621.8	624.9
52.5°	547.3	562.0	576.7	589.3	591.3
55°	508.5	525.3	542.1	553.6	557.8
57.5°	468.7	488.6	507.5	520.1	523.2
60°	428.8	449.8	470.8	486.5	489.6
62.5°	390.0	411.0	434.1	451.9	456.1
65°	350.2	374.3	399.5	415.2	419.4
67.5°	313.5	336.6	361.7	380.6	385.8
70°	272.6	296.7	324.0	343.9	350.2
72.5°	232.8	257.9	288.3	310.4	314.5
75°	192.9	220.2	253.7	274.7	279.9
77.5°	154.1	185.6	217.0	240.1	244.3
80°	118.5	149.9	185.6	208.6	212.8
82.5°	86.0	119.5	156.2	178.2	186.6
85°	57.7	92.3	129.0	152.0	160.4
87.5°	36.7	70.2	105.9	130.0	137.4
90°	17.2	53.5	91.7	117.6	126.0
92.5°	21.5	48.7	87.5	112.3	120.1
95°	34.0	60.2	82.2	107.1	114.4
97.5°	50.8	78.1	78.7	101.5	109.2
100°	71.2	94.3	129.3	98.0	102.9
102.5°	91.9	113.3	146.5	168.2	144.5
105°	114.4	132.7	164.2	185.1	192.1
107.5°	137.7	152.4	183.5	204.8	209.7
110°	160.2	172.8	202.9	221.7	229.4



TEST NUMBER: P1027016

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.3	192.9	221.6	239.0	245.6
115°	203.5	212.6	240.2	257.7	261.9
117.5°	225.6	230.9	258.5	274.2	280.9
120°	247.0	249.9	275.1	292.1	296.7
122.5°	265.0	267.8	291.2	307.3	311.5
125°	284.6	286.0	307.0	322.4	326.5
127.5°	302.5	303.2	320.7	335.7	339.1
130°	319.6	320.4	335.4	349.1	352.5
132.5°	335.7	337.9	347.3	362.0	364.4
135°	351.8	352.9	359.6	372.4	375.6
137.5°	366.8	367.9	371.4	384.0	386.4
140°	380.4	381.1	381.8	394.0	396.1
142.5°	393.6	392.9	393.7	403.1	405.1
145°	406.5	406.2	406.2	411.7	413.8
147.5°	416.9	416.9	417.2	419.7	419.3
150°	427.6	426.9	427.6	428.3	426.5
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)