

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027019

Luminaire Tested: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027019
REPORT IS A COMBINATION OF REPORTS P1002558 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4867.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027019

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027019

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	63	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53	53	53	49
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45	45	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	39	39	36
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	34	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	30	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	26	26	24
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24	24	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	21	21	19
10	50	37	30	25	47	35	29	24	32	26	22	30	25	21	27	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8382	8382	8382
5°	8383	8187	8203
10°	8313	7999	7975
15°	8204	7775	7706
20°	8056	7515	7397
25°	7898	7231	7066
30°	7707	6935	6718
35°	7503	6625	6328
40°	7292	6297	5981
45°	7063	5978	5613
50°	6812	5616	5184
55°	6564	5216	4788
60°	6268	4794	4329
65°	5912	4307	3854
70°	5551	3746	3306
75°	4945	3084	2673
80°	4214	2304	1965
85°	3253	1364	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7063 cd/sqm

TEST NUMBER: P1027019

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	2.5
10°-20°	348.7	7.2
20°-30°	514.8	10.6
30°-40°	600.6	12.3
40°-50°	603.2	12.4
50°-60°	529.5	10.9
60°-70°	394.4	8.1
70°-80°	225.2	4.6
80°-90°	65.7	1.4
90°-100°	16.1	0.3
100°-110°	107.4	2.2
110°-120°	193.3	4.0
120°-130°	248.2	5.1
130°-140°	266.9	5.5
140°-150°	250.5	5.1
150°-160°	202.6	4.2
160°-170°	131.0	2.7
170°-180°	45.2	0.9
0°-30°	986.9	20.3
0°-40°	1587.5	32.6
0°-60°	2720.3	55.9
0°-90°	3405.7	70.0
90°-120°	316.8	6.5
90°-150°	1082.4	22.2
90°-180°	1461.0	30.0
0°-180°	4867.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1306	1304	1294	1303	1302	124
15°	1245	1242	1231	1236	1236	351
25°	1130	1125	1112	1114	1110	520
35°	976	972	957	952	944	611
45°	799	795	782	770	767	616
55°	609	606	591	582	574	543
65°	411	409	397	388	384	408
75°	218	216	211	208	204	232
85°	57	58	58	57	55	62
90°	0	3	6	7	8	5
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	196	197	195	193	193
125°	277	279	279	278	277	247
135°	345	347	347	346	344	266
145°	400	401	401	401	399	250
155°	441	439	439	440	438	203
165°	465	463	463	466	463	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1027019

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1308.2	1308.2	1308.2	1308.2	1308.2
2.5°	1312.4	1309.3	1298.9	1309.3	1308.2
5°	1306.2	1304.1	1293.7	1303.1	1302.0
7.5°	1296.8	1294.8	1283.4	1292.7	1291.7
10°	1283.4	1281.3	1269.9	1278.2	1277.2
12.5°	1266.8	1262.7	1252.3	1258.6	1258.6
15°	1245.1	1242.0	1230.6	1235.8	1235.8
17.5°	1222.3	1217.2	1205.8	1212.0	1206.8
20°	1192.3	1190.2	1176.8	1184.0	1178.9
22.5°	1162.3	1158.2	1145.7	1149.9	1146.8
25°	1130.2	1125.0	1111.6	1113.7	1110.5
27.5°	1093.0	1089.8	1076.4	1077.4	1074.3
30°	1056.7	1053.6	1038.1	1036.0	1032.9
32.5°	1017.4	1012.2	998.8	994.6	988.4
35°	976.0	971.9	957.4	952.2	943.9
37.5°	933.6	928.4	914.9	907.7	902.5
40°	890.1	884.9	870.4	861.1	858.0
42.5°	843.5	839.4	824.9	816.6	811.4
45°	799.0	794.9	782.5	770.0	766.9
47.5°	750.4	751.4	735.9	723.5	716.2
50°	703.8	700.7	688.3	674.8	667.6
52.5°	656.2	654.1	640.7	629.3	621.0
55°	608.6	605.5	591.0	581.7	574.4
57.5°	557.9	556.8	544.4	532.0	528.9
60°	510.3	506.1	494.7	484.4	477.1
62.5°	460.6	457.5	448.2	436.8	431.6
65°	410.9	408.8	397.4	388.1	384.0
67.5°	362.2	358.1	349.8	341.5	339.5
70°	316.7	311.5	302.2	296.0	291.9
72.5°	267.0	263.9	258.7	251.5	247.4
75°	218.4	216.3	211.1	208.0	203.9
77.5°	172.8	171.8	168.7	166.6	163.5
80°	130.4	130.4	128.3	127.3	125.2
82.5°	93.1	91.1	91.1	89.0	89.0
85°	56.9	58.0	58.0	56.9	54.9
87.5°	27.9	27.9	26.9	26.9	24.8
90°	0.4	3.2	5.6	7.4	8.5
92.5°	6.7	3.5	5.6	7.4	7.8
95°	20.1	19.0	5.6	7.4	7.4
97.5°	37.7	39.8	6.3	7.1	7.4
100°	58.9	59.9	61.4	8.8	7.4
102.5°	80.4	81.8	82.5	83.2	53.6
105°	103.7	105.1	105.1	105.1	104.7
107.5°	127.7	127.7	128.4	128.7	127.3
110°	150.9	150.9	151.6	150.6	150.9

TEST NUMBER: P1027019

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.8	173.9	174.2	172.8	172.1
115°	194.7	196.4	196.8	195.4	193.2
117.5°	217.6	217.6	219.0	216.9	216.2
120°	238.7	238.4	239.4	238.7	237.0
122.5°	257.4	259.2	259.5	258.8	256.7
125°	276.8	279.3	279.3	277.9	276.8
127.5°	295.5	297.3	296.9	296.2	293.4
130°	312.4	314.2	314.6	313.5	311.7
132.5°	329.4	331.5	330.4	330.4	328.7
135°	345.2	347.4	346.6	345.9	343.8
137.5°	360.0	362.2	361.5	361.5	359.7
140°	374.5	375.2	374.9	375.6	373.4
142.5°	387.6	387.9	388.6	388.6	386.5
145°	400.2	401.0	401.0	401.3	399.2
147.5°	411.5	411.5	411.9	412.2	409.8
150°	422.1	421.4	422.1	422.8	420.0
152.5°	432.3	430.6	431.3	432.0	429.5
155°	440.8	438.7	439.4	440.5	437.6
157.5°	447.5	446.4	446.4	447.5	444.7
160°	454.6	452.4	452.8	454.2	451.4
162.5°	460.2	458.1	458.4	460.6	457.4
165°	465.1	463.0	463.4	465.5	462.7
167.5°	469.0	466.9	467.3	469.7	466.5
170°	472.2	469.7	470.1	472.9	469.7
172.5°	474.3	471.8	472.5	475.0	471.8
175°	475.7	473.6	474.0	476.8	473.6
177.5°	476.8	474.7	475.0	477.5	474.7
180°	475.7	475.7	475.7	475.7	475.7

(END OF REPORT)