

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027021

Luminaire Tested: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027021
REPORT IS A COMBINATION OF REPORTS P1002560 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4931.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027021

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027021

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	35	29	24	32	26	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1027021

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.5
10°-20°	353.3	7.2
20°-30°	521.6	10.6
30°-40°	608.6	12.3
40°-50°	611.2	12.4
50°-60°	536.5	10.9
60°-70°	399.6	8.1
70°-80°	228.2	4.6
80°-90°	66.6	1.4
90°-100°	16.4	0.3
100°-110°	108.8	2.2
110°-120°	195.8	4.0
120°-130°	251.4	5.1
130°-140°	270.4	5.5
140°-150°	253.8	5.1
150°-160°	205.3	4.2
160°-170°	132.7	2.7
170°-180°	45.8	0.9
0°-30°	1000.0	20.3
0°-40°	1608.5	32.6
0°-60°	2756.3	55.9
0°-90°	3450.7	70.0
90°-120°	321.0	6.5
90°-150°	1096.5	22.2
90°-180°	1480.0	30.0
0°-180°	4931.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	0	3	6	8	9	5
95°	20	19	6	8	8	25
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	282	280	251
135°	350	352	351	350	348	270
145°	406	406	406	406	404	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1027021

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	0.4	3.2	5.7	7.5	8.6
92.5°	6.8	3.6	5.7	7.5	7.9
95°	20.4	19.3	5.7	7.5	7.5
97.5°	38.2	40.4	6.4	7.1	7.5
100°	59.7	60.7	62.2	8.9	7.5
102.5°	81.4	82.9	83.6	84.3	54.3
105°	105.0	106.5	106.5	106.5	106.1
107.5°	129.3	129.3	130.0	130.4	129.0
110°	152.9	152.9	153.6	152.5	152.9

TEST NUMBER: P1027021

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	176.1	176.5	175.0	174.3
115°	197.2	199.0	199.3	197.9	195.8
117.5°	220.4	220.4	221.8	219.7	219.0
120°	241.8	241.5	242.6	241.8	240.1
122.5°	260.8	262.6	262.9	262.2	260.1
125°	280.4	282.9	282.9	281.5	280.4
127.5°	299.4	301.1	300.8	300.1	297.2
130°	316.5	318.3	318.6	317.6	315.8
132.5°	333.6	335.8	334.7	334.7	332.9
135°	349.7	351.9	351.2	350.4	348.3
137.5°	364.7	366.9	366.2	366.2	364.4
140°	379.4	380.1	379.7	380.4	378.3
142.5°	392.6	392.9	393.7	393.7	391.5
145°	405.5	406.2	406.2	406.5	404.4
147.5°	416.9	416.9	417.2	417.6	415.1
150°	427.6	426.9	427.6	428.3	425.5
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)