

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027338

Luminaire Tested: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027338
REPORT IS A COMBINATION OF REPORTS P1001268 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7916.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027338

CATALOG NUMBER: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027338

CATALOG NUMBER: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	81	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10807	10807	10807
5°	10807	10556	10576
10°	10717	10314	10281
15°	10577	10024	9935
20°	10387	9689	9537
25°	10183	9322	9111
30°	9936	8941	8662
35°	9673	8542	8159
40°	9401	8119	7711
45°	9107	7707	7237
50°	8783	7240	6683
55°	8462	6724	6174
60°	8081	6181	5582
65°	7623	5553	4969
70°	7157	4830	4262
75°	6376	3977	3446
80°	5432	2971	2535
85°	4197	1756	1397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9107 cd/sqm

TEST NUMBER: P1027338

CATALOG NUMBER: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.0
10°-20°	449.6	5.7
20°-30°	663.7	8.4
30°-40°	774.4	9.8
40°-50°	777.7	9.8
50°-60°	682.7	8.6
60°-70°	508.5	6.4
70°-80°	290.4	3.7
80°-90°	85.8	1.1
90°-100°	84.0	1.1
100°-110°	249.4	3.2
110°-120°	423.0	5.3
120°-130°	556.9	7.0
130°-140°	624.1	7.9
140°-150°	611.7	7.7
150°-160°	513.8	6.5
160°-170°	341.6	4.3
170°-180°	119.5	1.5
0°-30°	1272.4	16.1
0°-40°	2046.8	25.9
0°-60°	3507.2	44.3
0°-90°	4391.9	55.5
90°-120°	756.4	9.6
90°-150°	2549.1	32.2
90°-180°	3524.0	44.5
0°-180°	7916.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1687	1687	1687	1687	1687	
5°	1684	1681	1668	1680	1679	160
15°	1605	1601	1587	1593	1593	453
25°	1457	1450	1433	1436	1432	670
35°	1258	1253	1234	1228	1217	787
45°	1030	1025	1009	993	989	794
55°	785	781	762	750	741	700
65°	530	527	512	500	495	525
75°	282	279	272	268	263	300
85°	73	75	75	73	71	80
90°	1	9	16	21	24	9
95°	64	66	76	82	84	67
105°	224	229	235	241	244	239
115°	424	427	429	428	427	419
125°	618	624	625	623	622	554
135°	804	810	811	811	807	620
145°	974	978	981	981	978	609
155°	1114	1114	1115	1119	1114	513
165°	1212	1210	1211	1214	1209	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1027338

CATALOG NUMBER: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1686.7	1686.7	1686.7	1686.7	1686.7
2.5°	1692.0	1688.0	1674.7	1688.0	1686.7
5°	1684.0	1681.3	1668.0	1680.0	1678.7
7.5°	1672.0	1669.3	1654.6	1666.7	1665.3
10°	1654.6	1652.0	1637.3	1648.0	1646.6
12.5°	1633.3	1628.0	1614.6	1622.6	1622.6
15°	1605.3	1601.3	1586.6	1593.3	1593.3
17.5°	1575.9	1569.2	1554.6	1562.6	1555.9
20°	1537.2	1534.6	1517.2	1526.5	1519.9
22.5°	1498.5	1493.2	1477.2	1482.5	1478.5
25°	1457.2	1450.5	1433.1	1435.8	1431.8
27.5°	1409.1	1405.1	1387.8	1389.1	1385.1
30°	1362.4	1358.4	1338.4	1335.7	1331.7
32.5°	1311.7	1305.0	1287.7	1282.4	1274.3
35°	1258.3	1253.0	1234.3	1227.6	1217.0
37.5°	1203.6	1197.0	1179.6	1170.3	1163.6
40°	1147.6	1140.9	1122.2	1110.2	1106.2
42.5°	1087.5	1082.2	1063.5	1052.8	1046.2
45°	1030.2	1024.8	1008.8	992.8	988.8
47.5°	967.4	968.8	948.8	932.7	923.4
50°	907.4	903.4	887.4	870.0	860.7
52.5°	846.0	843.3	826.0	811.3	800.6
55°	784.6	780.6	761.9	749.9	740.6
57.5°	719.2	717.9	701.9	685.9	681.9
60°	657.9	652.5	637.8	624.5	615.2
62.5°	593.8	589.8	577.8	563.1	556.4
65°	529.8	527.1	512.4	500.4	495.1
67.5°	467.0	461.7	451.0	440.4	437.7
70°	408.3	401.7	389.6	381.6	376.3
72.5°	344.3	340.3	333.6	324.3	318.9
75°	281.6	278.9	272.2	268.2	262.9
77.5°	222.8	221.5	217.5	214.8	210.8
80°	168.1	168.1	165.5	164.1	161.5
82.5°	120.1	117.4	117.4	114.8	114.8
85°	73.4	74.7	74.7	73.4	70.7
87.5°	36.0	36.0	34.7	34.7	32.0
90°	1.0	8.8	15.7	20.6	23.6
92.5°	29.5	34.4	43.2	50.1	52.1
95°	63.9	65.8	75.7	82.5	84.5
97.5°	98.3	99.2	113.0	118.9	119.9
100°	137.6	137.6	150.3	159.2	161.2
102.5°	179.8	184.7	189.6	199.5	202.4
105°	224.0	229.0	234.8	240.7	243.7
107.5°	272.2	277.1	282.0	285.0	285.0
110°	322.3	327.2	330.2	333.1	332.1

TEST NUMBER: P1027338

CATALOG NUMBER: S125DIP-B1090D1090UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.4	375.4	379.3	380.3	378.3
115°	423.5	427.4	429.4	428.4	427.4
117.5°	474.6	475.6	477.6	478.5	474.6
120°	521.8	526.7	527.7	527.7	523.7
122.5°	572.9	573.9	576.8	575.8	572.9
125°	618.1	624.0	625.0	623.0	622.0
127.5°	668.2	671.1	672.1	671.1	669.2
130°	712.4	717.3	719.3	718.3	716.3
132.5°	756.6	765.5	764.5	763.5	760.6
135°	803.8	809.7	810.7	810.7	806.7
137.5°	848.0	853.9	855.9	856.9	851.9
140°	890.3	895.2	898.1	900.1	895.2
142.5°	932.5	936.4	940.4	941.4	936.4
145°	973.8	977.7	980.7	980.7	977.7
147.5°	1012.1	1015.1	1017.0	1020.0	1012.1
150°	1050.4	1049.4	1053.4	1053.4	1051.4
152.5°	1081.9	1083.8	1084.8	1087.8	1083.8
155°	1114.3	1114.3	1115.3	1119.2	1114.3
157.5°	1143.8	1141.8	1142.8	1146.7	1139.9
160°	1169.3	1166.4	1167.4	1171.3	1166.4
162.5°	1191.9	1190.0	1190.0	1194.9	1189.0
165°	1211.6	1209.6	1210.6	1214.5	1208.6
167.5°	1229.3	1225.3	1225.3	1231.2	1225.3
170°	1243.0	1239.1	1239.1	1245.0	1238.1
172.5°	1252.9	1248.9	1248.9	1254.8	1248.9
175°	1259.7	1255.8	1255.8	1261.7	1254.8
177.5°	1264.6	1260.7	1259.7	1265.6	1258.7
180°	1262.7	1262.7	1262.7	1262.7	1262.7

(END OF REPORT)