

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027357

Luminaire Tested: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027357
REPORT IS A COMBINATION OF REPORTS P1001287 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8676.8 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027357

CATALOG NUMBER: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027357

CATALOG NUMBER: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57
1	98	93	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40
3	81	72	64	58	75	66	60	55	57	52	48	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	52	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	23	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10775	10775	10775
5°	10775	10525	10545
10°	10686	10284	10251
15°	10546	9995	9905
20°	10356	9660	9508
25°	10152	9295	9084
30°	9907	8915	8636
35°	9644	8517	8135
40°	9373	8095	7688
45°	9080	7684	7215
50°	8757	7218	6663
55°	8437	6705	6155
60°	8056	6164	5564
65°	7600	5537	4954
70°	7136	4816	4249
75°	6356	3965	3436
80°	5416	2962	2528
85°	4185	1752	1393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9080 cd/sqm

TEST NUMBER: P1027357

CATALOG NUMBER: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	1.8
10°-20°	448.2	5.2
20°-30°	661.7	7.6
30°-40°	772.1	8.9
40°-50°	775.4	8.9
50°-60°	680.7	7.8
60°-70°	507.0	5.8
70°-80°	289.6	3.3
80°-90°	85.9	1.0
90°-100°	430.0	5.0
100°-110°	893.1	10.3
110°-120°	834.2	9.6
120°-130°	675.0	7.8
130°-140°	542.4	6.3
140°-150°	409.4	4.7
150°-160°	288.2	3.3
160°-170°	169.9	2.0
170°-180°	55.2	0.6
0°-30°	1268.7	14.6
0°-40°	2040.7	23.5
0°-60°	3496.8	40.3
0°-90°	4379.3	50.5
90°-120°	2157.3	24.9
90°-150°	3784.1	43.6
90°-180°	4298.0	49.5
0°-180°	8676.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1679	1676	1663	1675	1674	159
15°	1600	1596	1582	1588	1588	451
25°	1453	1446	1429	1432	1428	668
35°	1255	1249	1231	1224	1213	785
45°	1027	1022	1006	990	986	791
55°	782	778	760	748	738	698
65°	528	526	511	499	494	524
75°	281	278	271	267	262	299
85°	73	74	74	73	70	80
90°	1	10	18	24	26	8
95°	38	112	1020	463	270	40
105°	130	182	835	1643	1525	137
115°	232	280	670	1444	1699	229
125°	322	378	642	1149	1339	286
135°	378	454	638	963	1112	293
145°	440	504	640	797	877	276
155°	502	540	624	705	736	231
165°	548	563	599	635	645	154
175°	570	570	574	581	579	54
180°	571	571	571	571	571	

TEST NUMBER: P1027357

CATALOG NUMBER: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1681.7	1681.7	1681.7	1681.7	1681.7
2.5°	1687.0	1683.0	1669.7	1683.0	1681.7
5°	1679.0	1676.4	1663.1	1675.0	1673.7
7.5°	1667.0	1664.4	1649.7	1661.7	1660.4
10°	1649.7	1647.1	1632.5	1643.1	1641.8
12.5°	1628.5	1623.1	1609.8	1617.8	1617.8
15°	1600.5	1596.5	1581.9	1588.5	1588.5
17.5°	1571.3	1564.6	1550.0	1557.9	1551.3
20°	1532.7	1530.0	1512.7	1522.0	1515.4
22.5°	1494.1	1488.8	1472.8	1478.1	1474.1
25°	1452.8	1446.2	1428.9	1431.6	1427.6
27.5°	1404.9	1401.0	1383.7	1385.0	1381.0
30°	1358.4	1354.4	1334.4	1331.8	1327.8
32.5°	1307.8	1301.2	1283.9	1278.6	1270.6
35°	1254.6	1249.3	1230.7	1224.0	1213.4
37.5°	1200.1	1193.4	1176.1	1166.8	1160.1
40°	1144.2	1137.5	1118.9	1106.9	1102.9
42.5°	1084.3	1079.0	1060.4	1049.7	1043.1
45°	1027.1	1021.8	1005.8	989.8	985.9
47.5°	964.6	965.9	945.9	930.0	920.7
50°	904.7	900.7	884.7	867.4	858.1
52.5°	843.5	840.8	823.5	808.9	798.3
55°	782.3	778.3	759.7	747.7	738.4
57.5°	717.1	715.8	699.8	683.8	679.9
60°	655.9	650.6	636.0	622.6	613.3
62.5°	592.0	588.1	576.1	561.4	554.8
65°	528.2	525.5	510.9	498.9	493.6
67.5°	465.7	460.3	449.7	439.0	436.4
70°	407.1	400.5	388.5	380.5	375.2
72.5°	343.3	339.3	332.6	323.3	318.0
75°	280.7	278.1	271.4	267.4	262.1
77.5°	222.2	220.9	216.9	214.2	210.2
80°	167.6	167.6	165.0	163.6	161.0
82.5°	119.7	117.1	117.1	114.4	114.4
85°	73.2	74.5	74.5	73.2	70.5
87.5°	35.9	35.9	34.6	34.6	31.9
90°	1.2	10.4	18.4	24.2	26.5
92.5°	17.3	94.4	459.3	122.6	85.2
95°	38.0	112.2	1020.0	462.8	270.5
97.5°	58.7	121.4	1101.7	835.8	592.9
100°	80.6	139.3	1039.5	1181.2	897.9
102.5°	104.8	159.4	930.2	1473.5	1238.7
105°	130.1	181.9	834.6	1643.4	1525.3
107.5°	154.3	205.5	763.2	1691.1	1698.0
110°	180.7	230.2	716.0	1645.6	1776.3

TEST NUMBER: P1027357

CATALOG NUMBER: S125DIP-B1090D1270UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	207.2	255.0	688.4	1550.6	1767.1
115°	232.5	280.3	670.0	1444.2	1699.2
117.5°	255.6	306.2	659.6	1347.5	1596.7
120°	278.6	331.0	652.7	1266.4	1497.7
122.5°	302.8	355.2	647.0	1201.3	1410.2
125°	322.3	377.6	642.4	1148.9	1338.8
127.5°	338.5	399.4	640.1	1104.0	1273.2
130°	353.4	420.2	637.8	1058.5	1221.4
132.5°	364.9	438.6	637.8	1009.6	1169.6
135°	377.6	454.2	637.8	963.0	1112.1
137.5°	393.7	468.6	638.9	914.0	1052.2
140°	407.5	480.6	640.1	869.2	988.9
142.5°	423.6	492.1	641.2	830.6	930.2
145°	439.8	503.6	640.1	797.2	877.2
147.5°	457.0	514.0	637.8	768.4	830.0
150°	472.0	523.2	634.3	744.8	792.0
152.5°	488.1	532.4	629.7	724.7	762.1
155°	501.9	540.0	623.9	705.1	735.6
157.5°	514.6	547.4	618.2	686.7	711.4
160°	527.2	553.2	612.4	668.2	687.3
162.5°	537.6	558.9	605.5	651.6	665.4
165°	548.0	563.0	598.6	634.9	644.7
167.5°	554.9	565.2	591.7	619.3	625.1
170°	561.8	568.1	586.0	604.4	607.8
172.5°	566.4	569.2	579.1	592.3	591.7
175°	569.8	569.8	574.4	581.4	579.1
177.5°	572.1	569.8	571.0	574.4	571.0
180°	571.0	571.0	571.0	571.0	571.0

(END OF REPORT)