

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027070

Luminaire Tested: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027070
REPORT IS A COMBINATION OF REPORTS P1004971 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9013.0 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027070

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027070

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45			40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38			34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28			25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1027070

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	1.9
10°-20°	467.3	5.2
20°-30°	677.6	7.5
30°-40°	772.0	8.6
40°-50°	752.5	8.3
50°-60°	633.3	7.0
60°-70°	443.8	4.9
70°-80°	227.5	2.5
80°-90°	59.1	0.7
90°-100°	53.2	0.6
100°-110°	353.6	3.9
110°-120°	636.8	7.1
120°-130°	817.3	9.1
130°-140°	879.0	9.8
140°-150°	825.0	9.2
150°-160°	667.3	7.4
160°-170°	431.6	4.8
170°-180°	148.8	1.7
0°-30°	1312.2	14.6
0°-40°	2084.2	23.1
0°-60°	3470.0	38.5
0°-90°	4200.3	46.6
90°-120°	1043.5	11.6
90°-150°	3564.9	39.6
90°-180°	4813.0	53.4
0°-180°	9013.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	1	10	19	24	28	8
95°	66	63	19	24	24	81
105°	342	346	346	346	345	362
115°	641	647	648	643	636	636
125°	912	920	920	915	912	814
135°	1137	1144	1142	1139	1132	877
145°	1318	1320	1320	1322	1315	824
155°	1452	1445	1447	1451	1441	669
165°	1532	1525	1526	1533	1524	433
175°	1567	1560	1561	1570	1560	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1027070

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	1.2	10.5	18.6	24.4	27.9
92.5°	22.1	11.6	18.6	24.4	25.6
95°	66.2	62.7	18.6	24.4	24.4
97.5°	124.3	131.2	20.9	23.2	24.4
100°	194.0	197.4	202.1	29.0	24.4
102.5°	264.8	269.4	271.8	274.1	176.5
105°	341.5	346.1	346.1	346.1	344.9
107.5°	420.4	420.4	422.8	423.9	419.3
110°	497.1	497.1	499.4	495.9	497.1

TEST NUMBER: P1027070

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	569.1	572.6	573.7	569.1	566.8
115°	641.1	646.9	648.1	643.4	636.4
117.5°	716.6	716.6	721.2	714.3	711.9
120°	786.3	785.1	788.6	786.3	780.5
122.5°	847.8	853.6	854.8	852.5	845.5
125°	911.7	919.8	919.8	915.2	911.7
127.5°	973.3	979.1	977.9	975.6	966.3
130°	1029.0	1034.8	1036.0	1032.5	1026.7
132.5°	1084.8	1091.7	1088.2	1088.2	1082.4
135°	1137.0	1144.0	1141.7	1139.3	1132.4
137.5°	1185.8	1192.8	1190.4	1190.4	1184.6
140°	1233.4	1235.7	1234.6	1236.9	1229.9
142.5°	1276.4	1277.5	1279.9	1279.9	1272.9
145°	1318.2	1320.5	1320.5	1321.7	1314.7
147.5°	1355.4	1355.4	1356.5	1357.7	1349.6
150°	1390.2	1387.9	1390.2	1392.5	1383.2
152.5°	1423.9	1418.1	1420.4	1422.7	1414.6
155°	1451.8	1444.8	1447.1	1450.6	1441.3
157.5°	1473.8	1470.3	1470.3	1473.8	1464.5
160°	1497.0	1490.1	1491.2	1495.9	1486.6
162.5°	1515.6	1508.7	1509.8	1516.8	1506.3
165°	1531.9	1524.9	1526.1	1533.1	1523.8
167.5°	1544.7	1537.7	1538.9	1547.0	1536.5
170°	1555.1	1547.0	1548.2	1557.4	1547.0
172.5°	1562.1	1554.0	1556.3	1564.4	1554.0
175°	1566.7	1559.8	1560.9	1570.2	1559.8
177.5°	1570.2	1563.2	1564.4	1572.5	1563.2
180°	1566.7	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)