

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027072

Luminaire Tested: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027072
REPORT IS A COMBINATION OF REPORTS P1004973 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8962.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027072

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027072

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45			40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38			34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28			25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11319	11319	11319
5°	11321	11037	11055
10°	11210	10759	10664
15°	11052	10369	10150
20°	10855	9901	9611
25°	10629	9444	9034
30°	10354	8941	8427
35°	10072	8431	7783
40°	9805	7906	7153
45°	9484	7339	6494
50°	9157	6739	5823
55°	8778	6147	5127
60°	8391	5470	4407
65°	7930	4714	3629
70°	7392	3838	2856
75°	6648	2886	2082
80°	5607	1869	1403
85°	4197	1004	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9484 cd/sqm

TEST NUMBER: P1027072

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	1.9
10°-20°	464.7	5.2
20°-30°	673.8	7.5
30°-40°	767.6	8.6
40°-50°	748.2	8.3
50°-60°	629.6	7.0
60°-70°	441.2	4.9
70°-80°	226.2	2.5
80°-90°	58.7	0.7
90°-100°	52.9	0.6
100°-110°	351.6	3.9
110°-120°	633.2	7.1
120°-130°	812.7	9.1
130°-140°	874.1	9.8
140°-150°	820.4	9.2
150°-160°	663.6	7.4
160°-170°	429.2	4.8
170°-180°	148.0	1.7
0°-30°	1304.7	14.6
0°-40°	2072.3	23.1
0°-60°	3450.1	38.5
0°-90°	4176.3	46.6
90°-120°	1037.7	11.6
90°-150°	3544.9	39.6
90°-180°	4786.0	53.4
0°-180°	8962.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1764	1759	1744	1757	1755	167
15°	1677	1669	1641	1640	1628	473
25°	1521	1501	1452	1434	1420	700
35°	1310	1278	1218	1180	1161	821
45°	1073	1034	961	907	887	827
55°	814	771	696	636	615	728
65°	551	506	435	382	362	546
75°	294	254	198	168	159	310
85°	73	49	43	41	40	80
90°	1	10	18	24	28	8
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1027072

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1766.7	1766.7	1766.7	1766.7	1766.7
2.5°	1770.7	1766.7	1753.3	1766.7	1765.3
5°	1764.0	1758.7	1744.0	1757.3	1754.7
7.5°	1750.7	1745.3	1728.0	1738.6	1736.0
10°	1730.6	1726.6	1708.0	1712.0	1708.0
12.5°	1708.0	1702.6	1675.9	1678.6	1671.9
15°	1677.3	1669.3	1641.2	1639.9	1627.9
17.5°	1645.2	1633.2	1599.9	1593.2	1583.9
20°	1606.5	1593.2	1550.5	1543.8	1531.8
22.5°	1563.8	1550.5	1505.1	1490.5	1481.1
25°	1521.1	1501.1	1451.8	1434.4	1419.7
27.5°	1473.1	1449.1	1397.1	1374.4	1359.7
30°	1419.7	1394.4	1338.3	1307.7	1295.6
32.5°	1367.7	1337.0	1279.6	1244.9	1228.9
35°	1310.3	1278.3	1218.3	1179.6	1160.9
37.5°	1255.6	1216.9	1155.5	1110.2	1091.5
40°	1196.9	1156.9	1092.8	1042.1	1026.1
42.5°	1135.5	1094.2	1027.4	979.4	954.1
45°	1072.8	1034.1	960.7	907.4	887.3
47.5°	1007.4	967.4	894.0	839.3	816.6
50°	946.0	902.0	826.0	769.9	749.9
52.5°	879.3	834.0	763.2	701.9	681.8
55°	813.9	771.2	696.5	636.5	615.1
57.5°	747.2	701.9	629.8	571.1	552.4
60°	683.2	636.5	564.4	505.7	485.7
62.5°	615.1	571.1	497.7	444.3	424.3
65°	551.1	505.7	435.0	381.6	361.6
67.5°	487.0	441.7	373.6	322.9	306.9
70°	421.7	376.3	309.6	268.2	252.2
72.5°	357.6	313.6	252.2	214.8	205.5
75°	293.6	253.5	197.5	168.1	158.8
77.5°	228.2	196.1	149.4	126.8	118.8
80°	173.5	141.4	104.1	92.1	89.4
82.5°	120.1	92.1	69.4	65.4	64.0
85°	73.4	49.4	42.7	41.4	40.0
87.5°	30.7	21.3	20.0	20.0	18.7
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1027072

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)