

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027079

Luminaire Tested: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027079
REPORT IS A COMBINATION OF REPORTS P1005010 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5624.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027079

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1027079

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	99	95	92	98	94	91	88	85	83	80	77	75	73	70	68	67
2	95	87	81	76	90	83	77	73	75	71	67	68	65	62	62	59	57
3	86	77	69	63	82	73	67	61	67	61	57	61	56	53	55	52	49
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	49	45	42
5	73	61	53	47	69	58	51	45	54	47	42	49	44	40	45	40	37
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	41	36	33
7	63	50	42	36	59	48	40	35	44	38	33	41	35	31	37	33	29
8	58	46	38	32	55	44	36	31	40	34	30	37	32	28	34	30	26
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24
10	51	39	31	26	48	37	30	25	34	28	24	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11287	11287	11287
5°	11288	11005	11023
10°	11178	10728	10633
15°	11019	10340	10121
20°	10824	9873	9584
25°	10599	9417	9008
30°	10325	8915	8403
35°	10044	8406	7760
40°	9777	7883	7133
45°	9456	7319	6475
50°	9130	6720	5806
55°	8753	6129	5113
60°	8367	5454	4394
65°	7907	4700	3619
70°	7369	3827	2848
75°	6627	2877	2075
80°	5591	1864	1399
85°	4185	1002	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9456 cd/sqm

TEST NUMBER: P1027079

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	2.9
10°-20°	463.3	8.2
20°-30°	671.8	11.9
30°-40°	765.4	13.6
40°-50°	746.0	13.3
50°-60°	627.8	11.2
60°-70°	440.0	7.8
70°-80°	225.6	4.0
80°-90°	57.0	1.0
90°-100°	16.1	0.3
100°-110°	107.4	1.9
110°-120°	193.3	3.4
120°-130°	248.2	4.4
130°-140°	266.9	4.7
140°-150°	250.5	4.5
150°-160°	202.6	3.6
160°-170°	131.0	2.3
170°-180°	45.2	0.8
0°-30°	1300.9	23.1
0°-40°	2066.3	36.7
0°-60°	3440.2	61.2
0°-90°	4162.7	74.0
90°-120°	316.8	5.6
90°-150°	1082.4	19.2
90°-180°	1461.0	26.0
0°-180°	5624.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1759	1754	1739	1752	1750	167
15°	1672	1664	1636	1635	1623	472
25°	1517	1497	1448	1430	1416	698
35°	1307	1275	1215	1176	1158	818
45°	1070	1031	958	905	885	825
55°	812	769	694	635	613	726
65°	550	504	434	380	361	544
75°	293	253	197	168	158	309
85°	73	49	43	41	40	80
90°	0	3	6	7	8	5
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	196	197	195	193	193
125°	277	279	279	278	277	247
135°	345	347	347	346	344	266
145°	400	401	401	401	399	250
155°	441	439	439	440	438	203
165°	465	463	463	466	463	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1027079

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.6	1761.6	1761.6	1761.6	1761.6
2.5°	1765.6	1761.6	1748.3	1761.6	1760.3
5°	1758.9	1753.6	1739.0	1752.3	1749.6
7.5°	1745.6	1740.3	1723.0	1733.6	1731.0
10°	1725.7	1721.7	1703.0	1707.0	1703.0
12.5°	1703.0	1697.7	1671.1	1673.8	1667.1
15°	1672.4	1664.5	1636.5	1635.2	1623.2
17.5°	1640.5	1628.5	1595.3	1588.6	1579.3
20°	1601.9	1588.6	1546.0	1539.4	1527.4
22.5°	1559.3	1546.0	1500.8	1486.2	1476.9
25°	1516.8	1496.8	1447.6	1430.3	1415.7
27.5°	1468.9	1444.9	1393.0	1370.4	1355.8
30°	1415.7	1390.4	1334.5	1303.9	1291.9
32.5°	1363.8	1333.2	1276.0	1241.4	1225.4
35°	1306.6	1274.6	1214.7	1176.2	1157.5
37.5°	1252.0	1213.4	1152.2	1107.0	1088.4
40°	1193.5	1153.5	1089.7	1039.1	1023.2
42.5°	1132.3	1091.0	1024.5	976.6	951.3
45°	1069.7	1031.1	958.0	904.7	884.8
47.5°	1004.5	964.6	891.4	836.9	814.3
50°	943.3	899.4	823.6	767.7	747.7
52.5°	876.8	831.6	761.0	699.8	679.9
55°	811.6	769.0	694.5	634.6	613.4
57.5°	745.1	699.8	628.0	569.5	550.8
60°	681.2	634.6	562.8	504.3	484.3
62.5°	613.4	569.5	496.3	443.1	423.1
65°	549.5	504.3	433.7	380.5	360.6
67.5°	485.6	440.4	372.5	322.0	306.0
70°	420.4	375.2	308.7	267.4	251.5
72.5°	356.6	312.7	251.5	214.2	204.9
75°	292.7	252.8	196.9	167.6	158.3
77.5°	227.5	195.6	149.0	126.4	118.4
80°	173.0	141.0	103.8	91.8	89.1
82.5°	119.7	91.8	69.2	65.2	63.9
85°	73.2	49.2	42.6	41.2	39.9
87.5°	30.6	21.3	20.0	20.0	18.6
90°	0.4	3.2	5.6	7.4	8.5
92.5°	6.7	3.5	5.6	7.4	7.8
95°	20.1	19.0	5.6	7.4	7.4
97.5°	37.7	39.8	6.3	7.1	7.4
100°	58.9	59.9	61.4	8.8	7.4
102.5°	80.4	81.8	82.5	83.2	53.6
105°	103.7	105.1	105.1	105.1	104.7
107.5°	127.7	127.7	128.4	128.7	127.3
110°	150.9	150.9	151.6	150.6	150.9



TEST NUMBER: P1027079

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.8	173.9	174.2	172.8	172.1
115°	194.7	196.4	196.8	195.4	193.2
117.5°	217.6	217.6	219.0	216.9	216.2
120°	238.7	238.4	239.4	238.7	237.0
122.5°	257.4	259.2	259.5	258.8	256.7
125°	276.8	279.3	279.3	277.9	276.8
127.5°	295.5	297.3	296.9	296.2	293.4
130°	312.4	314.2	314.6	313.5	311.7
132.5°	329.4	331.5	330.4	330.4	328.7
135°	345.2	347.4	346.6	345.9	343.8
137.5°	360.0	362.2	361.5	361.5	359.7
140°	374.5	375.2	374.9	375.6	373.4
142.5°	387.6	387.9	388.6	388.6	386.5
145°	400.2	401.0	401.0	401.3	399.2
147.5°	411.5	411.5	411.9	412.2	409.8
150°	422.1	421.4	422.1	422.8	420.0
152.5°	432.3	430.6	431.3	432.0	429.5
155°	440.8	438.7	439.4	440.5	437.6
157.5°	447.5	446.4	446.4	447.5	444.7
160°	454.6	452.4	452.8	454.2	451.4
162.5°	460.2	458.1	458.4	460.6	457.4
165°	465.1	463.0	463.4	465.5	462.7
167.5°	469.0	466.9	467.3	469.7	466.5
170°	472.2	469.7	470.1	472.9	469.7
172.5°	474.3	471.8	472.5	475.0	471.8
175°	475.7	473.6	474.0	476.8	473.6
177.5°	476.8	474.7	475.0	477.5	474.7
180°	475.7	475.7	475.7	475.7	475.7

(END OF REPORT)