

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027365

Luminaire Tested: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027365
REPORT IS A COMBINATION OF REPORTS P1001310 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8582.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027365

CATALOG NUMBER: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot





TEST NUMBER: P1027365

CATALOG NUMBER: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57
1	98	94	90	86	90	87	83	80	74	71	69		62	60	58		51
2	89	82	76	70	82	76	70	66	65	61	57		54	51	49		45
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		39
4	74	64	56	50	69	59	52	47	51	45	41		43	39	35		35
5	68	57	48	42	63	53	45	40	45	40	35		38	34	31		32
6	63	51	43	37	58	47	40	35	41	35	31		35	30	27		29
7	58	46	38	32	54	43	36	31	37	31	27		31	27	24		26
8	54	42	34	29	50	39	32	27	34	28	24		29	24	21		24
9	50	38	31	25	46	36	29	24	31	25	22		26	22	19		22
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1027365

CATALOG NUMBER: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	1.9
10°-20°	452.1	5.3
20°-30°	667.5	7.8
30°-40°	778.8	9.1
40°-50°	782.2	9.1
50°-60°	686.6	8.0
60°-70°	511.4	6.0
70°-80°	292.1	3.4
80°-90°	86.7	1.0
90°-100°	99.2	1.2
100°-110°	294.8	3.4
110°-120°	499.9	5.8
120°-130°	658.2	7.7
130°-140°	737.5	8.6
140°-150°	722.9	8.4
150°-160°	607.2	7.1
160°-170°	403.6	4.7
170°-180°	141.3	1.6
0°-30°	1279.7	14.9
0°-40°	2058.4	24.0
0°-60°	3527.2	41.1
0°-90°	4417.3	51.5
90°-120°	894.0	10.4
90°-150°	3012.5	35.1
90°-180°	4165.0	48.5
0°-180°	8582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	10	19	24	28	10
95°	76	78	89	98	100	79
105°	265	271	278	284	288	282
115°	500	505	508	506	505	495
125°	730	737	739	736	735	654
135°	950	957	958	958	953	732
145°	1151	1156	1159	1159	1156	719
155°	1317	1317	1318	1323	1317	607
165°	1432	1430	1431	1435	1428	404
175°	1489	1484	1484	1491	1483	141
180°	1492	1492	1492	1492	1492	

TEST NUMBER: P1027365

CATALOG NUMBER: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	1.2	10.5	18.6	24.4	27.9
92.5°	34.8	40.6	51.1	59.2	61.5
95°	75.5	77.8	89.4	97.5	99.9
97.5°	116.1	117.3	133.5	140.5	141.7
100°	162.6	162.6	177.7	188.1	190.4
102.5°	212.5	218.3	224.1	235.7	239.2
105°	264.8	270.6	277.5	284.5	288.0
107.5°	321.7	327.5	333.3	336.8	336.8
110°	380.9	386.7	390.2	393.7	392.5



TEST NUMBER: P1027365

CATALOG NUMBER: S125DIP-B1090D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.3	443.6	448.2	449.4	447.1
115°	500.5	505.1	507.5	506.3	505.1
117.5°	560.9	562.1	564.4	565.5	560.9
120°	616.6	622.4	623.6	623.6	619.0
122.5°	677.0	678.2	681.7	680.5	677.0
125°	730.4	737.4	738.6	736.2	735.1
127.5°	789.7	793.1	794.3	793.1	790.8
130°	841.9	847.7	850.0	848.9	846.6
132.5°	894.2	904.6	903.5	902.3	898.8
135°	949.9	956.9	958.0	958.0	953.4
137.5°	1002.2	1009.1	1011.5	1012.6	1006.8
140°	1052.1	1057.9	1061.4	1063.7	1057.9
142.5°	1102.0	1106.7	1111.3	1112.5	1106.7
145°	1150.8	1155.5	1158.9	1158.9	1155.5
147.5°	1196.1	1199.6	1201.9	1205.4	1196.1
150°	1241.4	1240.2	1244.9	1244.9	1242.6
152.5°	1278.6	1280.9	1282.0	1285.5	1280.9
155°	1316.9	1316.9	1318.0	1322.7	1316.9
157.5°	1351.7	1349.4	1350.5	1355.2	1347.1
160°	1381.9	1378.4	1379.6	1384.2	1378.4
162.5°	1408.6	1406.3	1406.3	1412.1	1405.1
165°	1431.8	1429.5	1430.7	1435.3	1428.4
167.5°	1452.7	1448.1	1448.1	1455.1	1448.1
170°	1469.0	1464.4	1464.4	1471.3	1463.2
172.5°	1480.6	1476.0	1476.0	1482.9	1476.0
175°	1488.7	1484.1	1484.1	1491.1	1482.9
177.5°	1494.5	1489.9	1488.7	1495.7	1487.6
180°	1492.2	1492.2	1492.2	1492.2	1492.2

(END OF REPORT)