

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027080

Luminaire Tested: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027080
REPORT IS A COMBINATION OF REPORTS P1005011 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5672.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027080

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027080

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	104	99	95	92	98	94	91	88	85	83	80	77	75	73	70	68	67	63		
2	95	87	81	76	90	83	77	73	75	71	67	68	65	62	62	59	57	53		
3	86	77	69	63	82	73	67	61	67	61	57	61	56	53	55	52	49	46		
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	49	45	42	39		
5	73	61	53	47	69	58	51	45	54	47	42	49	44	40	45	40	37	34		
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	41	36	33	30		
7	63	50	42	36	59	48	40	35	44	38	33	41	35	31	37	33	29	27		
8	58	46	38	32	55	44	36	31	40	34	30	37	32	28	34	30	26	24		
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22		
10	51	39	31	26	48	37	30	25	34	28	24	32	27	23	29	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1027080

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	2.9
10°-20°	467.3	8.2
20°-30°	677.6	11.9
30°-40°	772.0	13.6
40°-50°	752.5	13.3
50°-60°	633.3	11.2
60°-70°	443.8	7.8
70°-80°	227.5	4.0
80°-90°	57.5	1.0
90°-100°	16.3	0.3
100°-110°	108.2	1.9
110°-120°	194.9	3.4
120°-130°	250.2	4.4
130°-140°	269.1	4.7
140°-150°	252.6	4.5
150°-160°	204.3	3.6
160°-170°	132.1	2.3
170°-180°	45.6	0.8
0°-30°	1312.2	23.1
0°-40°	2084.2	36.7
0°-60°	3470.0	61.2
0°-90°	4198.7	74.0
90°-120°	319.5	5.6
90°-150°	1091.3	19.2
90°-180°	1473.0	26.0
0°-180°	5672.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	0	3	6	8	8	5
95°	20	19	6	8	8	25
105°	104	106	106	106	106	111
115°	196	198	198	197	195	195
125°	279	282	282	280	279	249
135°	348	350	350	349	347	268
145°	404	404	404	405	402	252
155°	444	442	443	444	441	205
165°	469	467	467	469	466	132
175°	480	478	478	481	478	46
180°	480	480	480	480	480	

TEST NUMBER: P1027080

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	0.4	3.2	5.7	7.5	8.5
92.5°	6.8	3.6	5.7	7.5	7.8
95°	20.3	19.2	5.7	7.5	7.5
97.5°	38.0	40.2	6.4	7.1	7.5
100°	59.4	60.4	61.9	8.9	7.5
102.5°	81.1	82.5	83.2	83.9	54.0
105°	104.5	105.9	105.9	105.9	105.6
107.5°	128.7	128.7	129.4	129.8	128.3
110°	152.2	152.2	152.9	151.8	152.2



TEST NUMBER: P1027080

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.2	175.3	175.6	174.2	173.5
115°	196.3	198.0	198.4	197.0	194.8
117.5°	219.4	219.4	220.8	218.7	217.9
120°	240.7	240.3	241.4	240.7	238.9
122.5°	259.5	261.3	261.7	261.0	258.8
125°	279.1	281.6	281.6	280.2	279.1
127.5°	297.9	299.7	299.4	298.7	295.8
130°	315.0	316.8	317.1	316.1	314.3
132.5°	332.1	334.2	333.1	333.1	331.4
135°	348.1	350.2	349.5	348.8	346.6
137.5°	363.0	365.1	364.4	364.4	362.6
140°	377.6	378.3	377.9	378.6	376.5
142.5°	390.7	391.1	391.8	391.8	389.7
145°	403.5	404.2	404.2	404.6	402.5
147.5°	414.9	414.9	415.3	415.6	413.1
150°	425.6	424.9	425.6	426.3	423.4
152.5°	435.9	434.1	434.8	435.5	433.0
155°	444.4	442.3	443.0	444.1	441.2
157.5°	451.2	450.1	450.1	451.2	448.3
160°	458.3	456.2	456.5	457.9	455.1
162.5°	464.0	461.8	462.2	464.3	461.1
165°	469.0	466.8	467.2	469.3	466.5
167.5°	472.9	470.7	471.1	473.6	470.4
170°	476.1	473.6	473.9	476.8	473.6
172.5°	478.2	475.7	476.4	478.9	475.7
175°	479.6	477.5	477.8	480.7	477.5
177.5°	480.7	478.6	478.9	481.4	478.6
180°	479.6	479.6	479.6	479.6	479.6

(END OF REPORT)