

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027082

Luminaire Tested: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027082
REPORT IS A COMBINATION OF REPORTS P1005013 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5640.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027082

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027082

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	104	99	95	92	98	94	91	88	85	83	80	77	75	73	70	68	67	63		
2	95	87	81	76	90	83	77	73	75	71	67	68	65	62	62	59	57	53		
3	86	77	69	63	82	73	67	61	67	61	57	61	56	53	55	52	49	45		
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	49	45	42	39		
5	73	61	53	47	69	58	51	45	54	47	42	49	44	40	45	40	37	34		
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	41	36	33	30		
7	63	50	42	36	59	48	40	35	44	38	33	41	35	31	37	33	29	27		
8	58	46	38	32	55	44	36	31	40	34	30	37	32	28	34	30	26	24		
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22		
10	51	39	31	26	48	37	30	25	34	28	24	32	27	23	29	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11319	11319	11319
5°	11321	11037	11055
10°	11210	10759	10664
15°	11052	10369	10150
20°	10855	9901	9611
25°	10629	9444	9034
30°	10354	8941	8427
35°	10072	8431	7783
40°	9805	7906	7153
45°	9484	7339	6494
50°	9157	6739	5823
55°	8778	6147	5127
60°	8391	5470	4407
65°	7930	4714	3629
70°	7392	3838	2856
75°	6648	2886	2082
80°	5607	1869	1403
85°	4197	1004	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9484 cd/sqm

TEST NUMBER: P1027082

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	2.9
10°-20°	464.7	8.2
20°-30°	673.8	11.9
30°-40°	767.6	13.6
40°-50°	748.2	13.3
50°-60°	629.6	11.2
60°-70°	441.2	7.8
70°-80°	226.2	4.0
80°-90°	57.1	1.0
90°-100°	16.2	0.3
100°-110°	107.7	1.9
110°-120°	193.9	3.4
120°-130°	248.8	4.4
130°-140°	267.6	4.7
140°-150°	251.2	4.5
150°-160°	203.2	3.6
160°-170°	131.4	2.3
170°-180°	45.3	0.8
0°-30°	1304.7	23.1
0°-40°	2072.3	36.7
0°-60°	3450.1	61.2
0°-90°	4174.7	74.0
90°-120°	317.7	5.6
90°-150°	1085.4	19.2
90°-180°	1465.0	26.0
0°-180°	5640.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1764	1759	1744	1757	1755	167
15°	1677	1669	1641	1640	1628	473
25°	1521	1501	1452	1434	1420	700
35°	1310	1278	1218	1180	1161	821
45°	1073	1034	961	907	887	827
55°	814	771	696	636	615	728
65°	551	506	435	382	362	546
75°	294	254	198	168	159	310
85°	73	49	43	41	40	80
90°	0	3	6	7	8	5
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	197	197	196	194	194
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1027082

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1766.7	1766.7	1766.7	1766.7	1766.7
2.5°	1770.7	1766.7	1753.3	1766.7	1765.3
5°	1764.0	1758.7	1744.0	1757.3	1754.7
7.5°	1750.7	1745.3	1728.0	1738.6	1736.0
10°	1730.6	1726.6	1708.0	1712.0	1708.0
12.5°	1708.0	1702.6	1675.9	1678.6	1671.9
15°	1677.3	1669.3	1641.2	1639.9	1627.9
17.5°	1645.2	1633.2	1599.9	1593.2	1583.9
20°	1606.5	1593.2	1550.5	1543.8	1531.8
22.5°	1563.8	1550.5	1505.1	1490.5	1481.1
25°	1521.1	1501.1	1451.8	1434.4	1419.7
27.5°	1473.1	1449.1	1397.1	1374.4	1359.7
30°	1419.7	1394.4	1338.3	1307.7	1295.6
32.5°	1367.7	1337.0	1279.6	1244.9	1228.9
35°	1310.3	1278.3	1218.3	1179.6	1160.9
37.5°	1255.6	1216.9	1155.5	1110.2	1091.5
40°	1196.9	1156.9	1092.8	1042.1	1026.1
42.5°	1135.5	1094.2	1027.4	979.4	954.1
45°	1072.8	1034.1	960.7	907.4	887.3
47.5°	1007.4	967.4	894.0	839.3	816.6
50°	946.0	902.0	826.0	769.9	749.9
52.5°	879.3	834.0	763.2	701.9	681.8
55°	813.9	771.2	696.5	636.5	615.1
57.5°	747.2	701.9	629.8	571.1	552.4
60°	683.2	636.5	564.4	505.7	485.7
62.5°	615.1	571.1	497.7	444.3	424.3
65°	551.1	505.7	435.0	381.6	361.6
67.5°	487.0	441.7	373.6	322.9	306.9
70°	421.7	376.3	309.6	268.2	252.2
72.5°	357.6	313.6	252.2	214.8	205.5
75°	293.6	253.5	197.5	168.1	158.8
77.5°	228.2	196.1	149.4	126.8	118.8
80°	173.5	141.4	104.1	92.1	89.4
82.5°	120.1	92.1	69.4	65.4	64.0
85°	73.4	49.4	42.7	41.4	40.0
87.5°	30.7	21.3	20.0	20.0	18.7
90°	0.4	3.2	5.7	7.4	8.5
92.5°	6.7	3.5	5.7	7.4	7.8
95°	20.2	19.1	5.7	7.4	7.4
97.5°	37.8	40.0	6.4	7.1	7.4
100°	59.1	60.1	61.5	8.8	7.4
102.5°	80.6	82.0	82.7	83.5	53.7
105°	104.0	105.4	105.4	105.4	105.0
107.5°	128.0	128.0	128.7	129.1	127.7
110°	151.3	151.3	152.1	151.0	151.3



TEST NUMBER: P1027082

CATALOG NUMBER: S125RDIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.3	174.3	174.7	173.3	172.6
115°	195.2	197.0	197.3	195.9	193.8
117.5°	218.2	218.2	219.6	217.5	216.8
120°	239.4	239.0	240.1	239.4	237.6
122.5°	258.1	259.9	260.3	259.5	257.4
125°	277.6	280.1	280.1	278.6	277.6
127.5°	296.3	298.1	297.7	297.0	294.2
130°	313.3	315.1	315.4	314.4	312.6
132.5°	330.3	332.4	331.3	331.3	329.6
135°	346.2	348.3	347.6	346.9	344.8
137.5°	361.0	363.2	362.4	362.4	360.7
140°	375.5	376.2	375.9	376.6	374.5
142.5°	388.6	389.0	389.7	389.7	387.6
145°	401.3	402.1	402.1	402.4	400.3
147.5°	412.7	412.7	413.0	413.4	410.9
150°	423.3	422.6	423.3	424.0	421.1
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)