

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027368

Luminaire Tested: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027368
REPORT IS A COMBINATION OF REPORTS P1001313 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8665.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	82	76	71	83	77	71	67	65	61	58	55	52	50	45	44	42	42	42	37
3	82	73	65	60	76	68	61	56	58	53	49	49	45	42	40	38	36	36	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	31	31	27
5	69	57	49	43	64	54	46	41	46	41	36	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	24	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	22	19	19	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	17	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10172	10172	10172	10172
5°	10180	11539	10188	8754
10°	10118	13153	10100	7514
15°	10044	14261	9981	6790
20°	9917	15627	9826	6199
25°	9804	17905	9625	5848
30°	9642	18890	9475	5531
35°	9386	15143	9189	5277
40°	8987	10466	8855	5007
45°	8483	7792	8387	4783
50°	7905	6414	7774	4604
55°	7282	5471	7224	4449
60°	6671	4683	6555	4329
65°	6012	4045	5915	4152
70°	5315	3358	5245	3846
75°	4578	2597	4517	3339
80°	3616	1757	3484	2454
85°	2310	879	2236	1250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15537 cd/sqm

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.8	1.8
10°-20°	455.1	5.3
20°-30°	739.3	8.5
30°-40°	903.5	10.4
40°-50°	819.6	9.5
50°-60°	652.8	7.5
60°-70°	454.6	5.2
70°-80°	242.2	2.8
80°-90°	62.4	0.7
90°-100°	99.7	1.2
100°-110°	296.1	3.4
110°-120°	502.1	5.8
120°-130°	661.0	7.6
130°-140°	740.7	8.5
140°-150°	726.0	8.4
150°-160°	609.8	7.0
160°-170°	405.4	4.7
170°-180°	141.9	1.6
0°-30°	1347.2	15.5
0°-40°	2250.7	26.0
0°-60°	3723.1	43.0
0°-90°	4482.3	51.7
90°-120°	897.8	10.4
90°-150°	3025.6	34.9
90°-180°	4183.0	48.3
0°-180°	8665.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1588	1588	1588	1588	1588	
5°	1586	1832	1588	1390	1586	151
15°	1524	2287	1515	1089	1524	430
25°	1403	2814	1377	919	1403	646
35°	1221	2259	1195	787	1221	762
45°	960	1065	949	654	960	739
55°	675	656	670	534	675	604
65°	418	403	411	414	418	415
75°	202	198	200	255	202	215
85°	40	44	39	63	40	48
90°	1	28	1	28	1	8
95°	76	100	76	100	76	79
105°	266	289	266	289	266	284
115°	503	507	503	507	503	497
125°	734	738	734	738	734	657
135°	954	958	954	958	954	735
145°	1156	1160	1156	1160	1156	723
155°	1323	1323	1323	1323	1323	609
165°	1438	1434	1438	1434	1438	406
175°	1495	1489	1495	1489	1495	142
180°	1499	1499	1499	1499	1499	

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1590.3	1599.7	1610.5	1618.6	1632.1	1636.1	1642.9	1646.9	1651.0	1655.0	1657.7
5°	1586.3	1609.2	1629.4	1644.2	1669.8	1679.3	1691.4	1706.2	1723.7	1738.6	1748.0
7.5°	1575.5	1611.9	1638.8	1668.5	1703.5	1726.4	1738.6	1769.5	1797.9	1819.4	1847.7
10°	1562.0	1605.1	1646.9	1691.4	1741.2	1766.9	1791.1	1834.2	1873.3	1908.4	1936.7
12.5°	1547.2	1599.7	1649.6	1707.6	1774.9	1805.9	1822.1	1896.2	1944.8	1963.6	2018.9
15°	1524.3	1586.3	1657.7	1729.1	1785.7	1822.1	1866.6	1925.9	1974.4	2016.2	2060.7
17.5°	1502.7	1570.1	1642.9	1722.4	1804.6	1851.8	1885.5	1938.0	1990.6	2044.5	2086.3
20°	1467.7	1555.3	1629.4	1714.3	1811.3	1845.0	1880.1	1942.1	1998.7	2056.6	2109.2
22.5°	1439.4	1522.9	1624.0	1704.9	1787.1	1820.8	1863.9	1928.6	1996.0	2062.0	2138.8
25°	1403.0	1496.0	1583.6	1669.8	1754.7	1791.1	1830.2	1913.8	1983.8	2068.7	2153.6
27.5°	1363.9	1459.6	1547.2	1625.3	1704.9	1754.7	1796.5	1884.1	1977.1	2070.1	2180.6
30°	1322.1	1412.4	1496.0	1572.8	1660.4	1711.6	1753.4	1855.8	1959.6	2078.2	2210.3
32.5°	1277.6	1362.5	1434.0	1512.1	1605.1	1652.3	1708.9	1820.8	1943.4	2084.9	2250.7
35°	1221.0	1301.9	1365.2	1444.8	1537.7	1598.4	1657.7	1783.0	1925.9	2083.6	2273.6
37.5°	1164.4	1227.8	1288.4	1373.3	1481.1	1536.4	1598.4	1735.9	1898.9	2079.5	2283.0
40°	1097.0	1159.0	1211.6	1297.8	1411.1	1474.4	1539.1	1683.3	1867.9	2064.7	2249.3
42.5°	1029.7	1082.2	1140.2	1230.5	1339.6	1407.0	1475.7	1636.1	1827.5	2021.6	2156.3
45°	959.6	1000.0	1063.3	1145.6	1261.5	1326.2	1404.3	1578.2	1770.9	1943.4	2010.8
47.5°	886.8	927.2	986.5	1066.0	1180.6	1257.4	1331.5	1505.4	1699.5	1832.9	1832.9
50°	816.7	849.1	907.0	986.5	1102.4	1172.5	1248.0	1432.6	1589.0	1687.3	1599.7
52.5°	741.2	777.6	826.1	909.7	1024.3	1087.6	1169.8	1327.5	1475.7	1516.2	1381.4
55°	675.2	704.9	750.7	830.2	936.7	1002.7	1072.8	1223.7	1349.1	1346.4	1202.2
57.5°	606.5	630.7	679.2	752.0	850.4	909.7	979.8	1110.5	1212.9	1176.6	1040.4
60°	543.1	560.6	607.8	667.1	761.5	816.7	884.1	990.6	1068.7	1017.5	880.1
62.5°	477.1	497.3	535.0	593.0	676.6	721.0	770.9	878.7	928.6	882.8	742.6
65°	417.8	434.0	467.7	516.2	591.6	632.1	675.2	764.2	811.3	745.3	629.4
67.5°	358.5	377.4	401.6	444.7	504.0	541.8	579.5	656.3	677.9	618.6	521.6
70°	303.2	319.4	342.3	373.3	423.2	456.9	485.2	548.5	563.3	508.1	431.3
72.5°	249.3	260.1	279.0	304.6	350.4	369.3	398.9	442.1	460.9	411.1	355.8
75°	202.2	210.2	222.4	241.2	272.2	292.5	316.7	357.1	355.8	320.8	281.7
77.5°	156.3	157.7	171.2	188.7	207.5	225.1	237.2	265.5	268.2	246.6	214.3
80°	111.9	115.9	121.3	134.8	150.9	157.7	172.5	190.0	192.7	176.6	155.0
82.5°	71.4	74.1	78.2	86.3	97.0	105.1	113.2	119.9	126.7	117.3	99.7
85°	40.4	41.8	45.8	48.5	53.9	58.0	64.7	71.4	70.1	63.3	58.0
87.5°	20.2	20.2	20.2	22.9	25.6	25.6	28.3	29.6	31.0	28.3	25.6
90°	1.2	3.3	5.3	7.4	9.5	10.5	11.4	13.2	15.1	16.9	18.7
92.5°	35.0	36.3	37.6	38.9	40.2	40.8	42.0	44.3	46.6	49.0	51.3
95°	75.8	76.3	76.8	77.3	77.8	78.1	79.4	82.0	84.6	87.2	89.8
97.5°	116.6	116.9	117.1	117.4	117.7	117.8	119.6	123.2	126.9	130.5	134.1
100°	163.3	163.3	163.3	163.3	163.3	163.3	165.0	168.3	171.7	175.0	178.4
102.5°	213.4	214.7	216.0	217.3	218.6	219.3	219.9	221.2	222.5	223.8	225.1
105°	265.9	267.2	268.5	269.8	271.1	271.7	272.5	274.0	275.6	277.1	278.7
107.5°	323.1	324.4	325.7	327.0	328.3	328.9	329.5	330.8	332.1	333.4	334.7
110°	382.5	383.8	385.1	386.4	387.7	388.4	388.8	389.6	390.3	391.1	391.9

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	443.2	443.7	444.2	444.7	445.2	445.5	446.0	447.1	448.1	449.2	450.2
115°	502.7	503.7	504.7	505.8	506.8	507.3	507.6	508.1	508.6	509.2	509.7
117.5°	563.3	563.6	563.8	564.1	564.4	564.5	564.8	565.3	565.8	566.3	566.8
120°	619.3	620.6	621.9	623.2	624.5	625.1	625.2	625.5	625.8	626.0	626.3
122.5°	679.9	680.2	680.4	680.7	681.0	681.1	681.5	682.3	683.0	683.8	684.6
125°	733.6	735.2	736.7	738.3	739.8	740.6	740.7	741.0	741.3	741.5	741.8
127.5°	793.1	793.9	794.7	795.4	796.2	796.6	796.7	797.0	797.2	797.5	797.7
130°	845.6	846.9	848.2	849.5	850.8	851.4	851.7	852.2	852.7	853.2	853.7
132.5°	898.0	900.3	902.7	905.0	907.3	908.5	908.4	908.1	907.9	907.6	907.4
135°	954.0	955.6	957.1	958.7	960.2	961.0	961.1	961.4	961.7	961.9	962.2
137.5°	1006.5	1008.1	1009.6	1011.2	1012.7	1013.5	1013.8	1014.3	1014.8	1015.3	1015.8
140°	1056.6	1057.9	1059.2	1060.5	1061.8	1062.5	1062.9	1063.7	1064.4	1065.2	1066.0
142.5°	1106.8	1107.8	1108.9	1109.9	1111.0	1111.5	1112.0	1113.0	1114.1	1115.1	1116.1
145°	1155.8	1156.8	1157.8	1158.9	1159.9	1160.4	1160.8	1161.6	1162.3	1163.1	1163.9
147.5°	1201.3	1202.1	1202.9	1203.6	1204.4	1204.8	1205.1	1205.6	1206.1	1206.6	1207.1
150°	1246.8	1246.5	1246.3	1246.0	1245.7	1245.6	1246.1	1247.2	1248.2	1249.3	1250.3
152.5°	1284.1	1284.6	1285.1	1285.6	1286.1	1286.4	1286.5	1286.8	1287.1	1287.3	1287.6
155°	1322.6	1322.6	1322.6	1322.6	1322.6	1322.6	1322.7	1323.0	1323.2	1323.5	1323.7
157.5°	1357.6	1357.1	1356.5	1356.0	1355.5	1355.2	1355.3	1355.6	1355.9	1356.1	1356.4
160°	1387.9	1387.1	1386.3	1385.6	1384.8	1384.4	1384.5	1384.8	1385.0	1385.3	1385.5
162.5°	1414.7	1414.2	1413.7	1413.2	1412.7	1412.4	1412.4	1412.4	1412.4	1412.4	1412.4
165°	1438.0	1437.5	1437.0	1436.5	1436.0	1435.7	1435.8	1436.1	1436.4	1436.6	1436.9
167.5°	1459.0	1458.0	1457.0	1455.9	1454.9	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
170°	1475.3	1474.3	1473.3	1472.2	1471.2	1470.7	1470.7	1470.7	1470.7	1470.7	1470.7
172.5°	1487.0	1486.0	1484.9	1483.9	1482.8	1482.3	1482.3	1482.3	1482.3	1482.3	1482.3
175°	1495.2	1494.2	1493.1	1492.1	1491.0	1490.5	1490.5	1490.5	1490.5	1490.5	1490.5
177.5°	1501.0	1500.0	1498.9	1497.9	1496.8	1496.3	1496.2	1495.9	1495.7	1495.4	1495.2
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1660.4	1669.8	1677.9	1684.6	1690.0	1698.1	1692.7	1694.1	1696.8	1702.2	1702.2
5°	1768.2	1783.0	1791.1	1818.1	1824.8	1823.5	1819.4	1841.0	1839.6	1831.5	1830.2
7.5°	1873.3	1898.9	1921.8	1943.4	1950.1	1967.7	1971.7	1981.1	1978.4	1991.9	1985.2
10°	1969.0	2009.4	2031.0	2063.4	2071.4	2079.5	2090.3	2095.7	2107.8	2106.5	2106.5
12.5°	2043.1	2091.7	2120.0	2128.0	2159.0	2168.5	2177.9	2195.4	2191.4	2192.7	2200.8
15°	2101.1	2148.3	2172.5	2210.3	2231.8	2242.6	2258.8	2277.6	2274.9	2287.1	2284.4
17.5°	2144.2	2188.7	2233.2	2289.8	2291.1	2319.4	2357.2	2365.2	2382.8	2370.6	2370.6
20°	2179.3	2238.6	2301.9	2374.7	2382.8	2400.3	2446.1	2477.1	2497.3	2490.6	2494.6
22.5°	2217.0	2301.9	2376.0	2448.8	2487.9	2518.9	2563.4	2611.9	2629.4	2640.2	2637.5
25°	2265.5	2354.5	2463.6	2564.7	2605.1	2664.4	2723.7	2770.9	2784.4	2814.0	2787.1
27.5°	2315.4	2440.7	2576.8	2695.4	2746.6	2795.2	2866.6	2901.6	2919.2	2932.6	2923.2
30°	2357.2	2529.7	2677.9	2787.1	2823.5	2851.8	2892.2	2900.3	2893.5	2904.3	2917.8
32.5°	2421.8	2590.3	2715.6	2768.2	2764.2	2762.8	2731.8	2688.7	2679.3	2653.7	2688.7
35°	2456.9	2591.7	2640.2	2570.1	2541.8	2490.6	2392.2	2327.5	2270.9	2258.8	2261.5
37.5°	2436.7	2489.2	2431.3	2246.6	2200.8	2122.7	1991.9	1900.3	1858.5	1826.2	1867.9
40°	2327.5	2269.6	2110.5	1885.5	1819.4	1745.3	1622.6	1572.8	1513.5	1501.4	1556.6
42.5°	2146.9	1970.4	1745.3	1571.4	1502.7	1460.9	1358.5	1311.3	1269.5	1250.7	1281.7
45°	1901.6	1687.3	1460.9	1318.1	1260.1	1210.2	1149.6	1099.7	1072.8	1064.7	1090.3
47.5°	1648.3	1421.8	1241.2	1134.8	1074.1	1036.4	979.8	951.5	929.9	932.6	936.7
50°	1405.7	1199.5	1060.7	954.2	924.5	894.9	857.1	832.9	822.1	826.1	823.5
52.5°	1196.8	1029.7	912.4	830.2	816.7	788.4	757.4	737.2	733.2	734.5	738.5
55°	1013.5	882.8	789.8	730.5	715.6	695.4	676.6	663.1	652.3	656.3	655.0
57.5°	874.7	760.1	688.7	640.2	629.4	617.3	599.7	593.0	589.0	580.9	587.6
60°	752.0	659.0	597.0	567.4	558.0	549.9	531.0	522.9	520.2	516.2	527.0
62.5°	636.1	570.1	522.9	496.0	486.5	478.4	469.0	462.3	463.6	458.2	463.6
65°	544.5	490.6	456.9	432.6	420.5	415.1	413.7	403.0	401.6	403.0	404.3
67.5°	459.6	413.7	388.1	373.3	363.9	358.5	354.4	347.7	353.1	349.1	351.8
70°	382.8	351.8	324.8	310.0	305.9	307.3	300.5	297.8	299.2	296.5	299.2
72.5°	308.6	283.0	272.2	261.5	256.1	254.7	250.7	246.6	250.7	249.3	249.3
75°	246.6	227.8	215.6	208.9	208.9	206.2	199.5	199.5	199.5	198.1	199.5
77.5°	190.0	173.9	168.5	161.7	161.7	157.7	156.3	156.3	153.6	157.7	155.0
80°	141.5	129.4	121.3	117.3	117.3	115.9	113.2	111.9	113.2	111.9	111.9
82.5°	91.6	86.3	82.2	78.2	76.8	78.2	76.8	74.1	75.5	74.1	76.8
85°	52.6	47.2	47.2	44.5	45.8	43.1	44.5	41.8	40.4	44.5	41.8
87.5°	22.9	21.6	21.6	18.9	18.9	18.9	17.5	18.9	17.5	16.2	17.5
90°	20.0	21.3	22.6	23.9	24.5	24.9	25.7	26.4	27.2	28.0	27.2
92.5°	53.1	54.9	56.8	58.6	59.5	59.8	60.3	60.8	61.3	61.8	61.3
95°	91.6	93.4	95.3	97.1	98.0	98.3	98.8	99.3	99.8	100.3	99.8
97.5°	135.7	137.2	138.8	140.3	141.1	141.2	141.5	141.8	142.0	142.3	142.0
100°	180.7	183.1	185.4	187.7	188.9	189.2	189.7	190.2	190.8	191.3	190.8
102.5°	227.7	230.3	232.9	235.5	236.8	237.2	238.0	238.7	239.5	240.3	239.5
105°	280.3	281.8	283.4	284.9	285.7	286.1	286.9	287.6	288.4	289.2	288.4
107.5°	335.5	336.3	337.0	337.8	338.2	338.2	338.2	338.2	338.2	338.2	338.2
110°	392.7	393.5	394.2	395.0	395.4	395.3	395.0	394.7	394.5	394.2	394.5

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	450.5	450.7	451.0	451.3	451.4	451.1	450.6	450.1	449.5	449.0	449.5
115°	509.4	509.2	508.9	508.6	508.5	508.4	508.1	507.8	507.6	507.3	507.6
117.5°	567.1	567.3	567.6	567.9	568.0	567.5	566.4	565.4	564.3	563.3	564.3
120°	626.3	626.3	626.3	626.3	626.3	625.8	624.7	623.7	622.6	621.6	622.6
122.5°	684.3	684.1	683.8	683.5	683.4	683.0	682.2	681.5	680.7	679.9	680.7
125°	741.3	740.7	740.2	739.7	739.4	739.3	739.0	738.8	738.5	738.3	738.5
127.5°	797.5	797.2	797.0	796.7	796.6	796.3	795.8	795.3	794.7	794.2	794.7
130°	853.5	853.2	853.0	852.7	852.6	852.3	851.8	851.3	850.7	850.2	850.7
132.5°	907.1	906.9	906.6	906.3	906.2	905.8	905.0	904.3	903.5	902.7	903.5
135°	962.2	962.2	962.2	962.2	962.2	961.7	960.6	959.6	958.5	957.5	958.5
137.5°	1016.1	1016.3	1016.6	1016.9	1017.0	1016.4	1015.1	1013.8	1012.5	1011.2	1012.5
140°	1066.5	1067.0	1067.5	1068.0	1068.3	1067.7	1066.4	1065.1	1063.8	1062.5	1063.8
142.5°	1116.4	1116.6	1116.9	1117.2	1117.3	1116.7	1115.4	1114.1	1112.8	1111.5	1112.8
145°	1163.9	1163.9	1163.9	1163.9	1163.9	1163.5	1162.7	1162.0	1161.2	1160.4	1161.2
147.5°	1207.9	1208.7	1209.4	1210.2	1210.6	1209.6	1207.5	1205.4	1203.4	1201.3	1203.4
150°	1250.3	1250.3	1250.3	1250.3	1250.3	1250.0	1249.5	1249.0	1248.4	1247.9	1248.4
152.5°	1288.4	1289.2	1289.9	1290.7	1291.1	1290.6	1289.5	1288.5	1287.4	1286.4	1287.4
155°	1324.7	1325.8	1326.8	1327.9	1328.4	1327.8	1326.5	1325.2	1323.9	1322.6	1323.9
157.5°	1357.4	1358.4	1359.5	1360.5	1361.0	1360.1	1358.3	1356.5	1354.7	1352.9	1354.7
160°	1386.5	1387.6	1388.6	1389.7	1390.2	1389.6	1388.3	1387.0	1385.7	1384.4	1385.7
162.5°	1413.7	1415.0	1416.3	1417.6	1418.2	1417.4	1415.9	1414.3	1412.8	1411.2	1412.8
165°	1437.9	1438.9	1440.0	1441.0	1441.5	1440.7	1439.2	1437.6	1436.1	1434.5	1436.1
167.5°	1455.9	1457.5	1459.0	1460.5	1461.3	1460.5	1459.0	1457.5	1455.9	1454.4	1455.9
170°	1472.3	1473.8	1475.4	1476.9	1477.7	1476.8	1475.0	1473.1	1471.3	1469.5	1471.3
172.5°	1483.9	1485.4	1487.0	1488.5	1489.3	1488.5	1487.0	1485.4	1483.9	1482.3	1483.9
175°	1492.1	1493.6	1495.2	1496.7	1497.5	1496.6	1494.8	1492.9	1491.1	1489.3	1491.1
177.5°	1496.8	1498.3	1499.9	1501.4	1502.2	1501.3	1499.5	1497.6	1495.8	1494.0	1495.8
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1699.5	1690.0	1692.7	1690.0	1683.3	1679.3	1668.5	1655.0	1649.6	1642.9	1638.8
5°	1835.6	1828.8	1827.5	1816.7	1814.0	1797.9	1770.9	1757.4	1741.2	1725.1	1708.9
7.5°	1983.8	1975.7	1948.8	1944.8	1947.4	1927.2	1892.2	1865.2	1831.5	1808.6	1777.6
10°	2106.5	2090.3	2067.4	2068.7	2059.3	2032.4	1997.3	1969.0	1920.5	1890.8	1846.4
12.5°	2180.6	2167.1	2164.4	2151.0	2142.9	2107.8	2066.0	2029.7	1993.3	1952.8	1919.1
15°	2270.9	2253.4	2241.2	2222.4	2217.0	2180.6	2134.8	2093.0	2051.2	2013.5	1942.1
17.5°	2370.6	2351.8	2305.9	2301.9	2269.6	2234.5	2190.0	2128.0	2083.6	2029.7	1977.1
20°	2483.8	2456.9	2397.6	2382.8	2357.2	2299.2	2238.6	2169.8	2098.4	2043.1	1981.1
22.5°	2610.5	2563.4	2520.2	2473.1	2454.2	2382.8	2299.2	2215.6	2129.4	2053.9	1979.8
25°	2774.9	2712.9	2652.3	2605.1	2572.8	2479.8	2367.9	2257.4	2157.7	2059.3	1962.3
27.5°	2904.3	2850.4	2784.4	2722.4	2680.6	2570.1	2442.1	2299.2	2175.2	2055.3	1951.5
30°	2913.8	2897.6	2857.2	2823.5	2777.6	2659.0	2517.5	2355.8	2202.2	2056.6	1929.9
32.5°	2737.2	2769.6	2787.1	2792.5	2783.0	2714.3	2584.9	2407.0	2226.4	2044.5	1911.1
35°	2357.2	2443.4	2549.9	2590.3	2629.4	2665.8	2598.4	2443.4	2234.5	2041.8	1881.4
37.5°	1940.7	2018.9	2195.4	2276.3	2322.1	2466.3	2521.6	2438.0	2250.7	2044.5	1853.1
40°	1566.0	1690.0	1816.7	1925.9	1997.3	2159.0	2330.2	2349.1	2227.8	2018.9	1816.7
42.5°	1318.1	1390.8	1486.5	1587.6	1651.0	1842.3	2074.1	2210.3	2156.3	1977.1	1772.2
45°	1122.6	1176.6	1266.9	1300.5	1381.4	1564.7	1810.0	2006.7	2033.7	1911.1	1721.0
47.5°	963.6	1009.4	1067.4	1109.2	1173.9	1311.3	1518.9	1735.9	1865.2	1820.8	1649.6
50°	849.1	886.8	935.3	959.6	1001.4	1125.3	1281.7	1497.3	1671.2	1686.0	1556.6
52.5°	753.4	774.9	812.7	839.6	873.3	948.8	1090.3	1268.2	1463.6	1544.5	1442.1
55°	669.8	687.3	721.0	738.5	756.1	820.8	931.3	1093.0	1276.3	1382.8	1324.8
57.5°	594.3	609.2	637.5	653.6	663.1	725.1	810.0	936.7	1101.1	1230.5	1198.1
60°	532.3	545.8	562.0	574.1	584.9	636.1	695.4	797.8	944.7	1070.1	1062.0
62.5°	466.3	478.4	496.0	508.1	517.5	549.9	599.7	677.9	803.2	919.1	942.1
65°	408.4	417.8	429.9	435.3	447.4	471.7	512.1	582.2	684.6	788.4	804.6
67.5°	355.8	358.5	366.6	378.7	381.4	403.0	439.4	491.9	571.4	656.3	681.9
70°	299.2	303.2	310.0	319.4	324.8	338.3	369.3	404.3	473.0	547.2	566.0
72.5°	249.3	254.7	257.4	262.8	265.5	287.1	300.5	335.6	382.8	444.7	465.0
75°	202.2	207.5	208.9	211.6	214.3	223.7	242.6	264.2	303.2	343.7	370.6
77.5°	160.4	159.0	161.7	165.8	164.4	172.5	184.6	203.5	229.1	262.8	280.3
80°	113.2	113.2	117.3	121.3	119.9	128.0	132.1	145.6	167.1	188.7	195.4
82.5°	75.5	75.5	79.5	79.5	82.2	83.6	88.9	95.7	113.2	124.0	128.0
85°	43.1	43.1	44.5	44.5	44.5	47.2	51.2	53.9	59.3	66.0	68.7
87.5°	17.5	18.9	18.9	18.9	18.9	21.6	21.6	24.3	25.6	28.3	28.3
90°	26.4	25.7	24.9	24.5	23.9	22.6	21.3	20.0	18.7	16.9	15.1
92.5°	60.8	60.3	59.8	59.5	58.6	56.8	54.9	53.1	51.3	49.0	46.6
95°	99.3	98.8	98.3	98.0	97.1	95.3	93.4	91.6	89.8	87.2	84.6
97.5°	141.8	141.5	141.2	141.1	140.3	138.8	137.2	135.7	134.1	130.5	126.9
100°	190.2	189.7	189.2	188.9	187.7	185.4	183.1	180.7	178.4	175.0	171.7
102.5°	238.7	238.0	237.2	236.8	235.5	232.9	230.3	227.7	225.1	223.8	222.5
105°	287.6	286.9	286.1	285.7	284.9	283.4	281.8	280.3	278.7	277.1	275.6
107.5°	338.2	338.2	338.2	338.2	337.8	337.0	336.3	335.5	334.7	333.4	332.1
110°	394.7	395.0	395.3	395.4	395.0	394.2	393.5	392.7	391.9	391.1	390.3

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	450.1	450.6	451.1	451.4	451.3	451.0	450.7	450.5	450.2	449.2	448.1
115°	507.8	508.1	508.4	508.5	508.6	508.9	509.2	509.4	509.7	509.2	508.6
117.5°	565.4	566.4	567.5	568.0	567.9	567.6	567.3	567.1	566.8	566.3	565.8
120°	623.7	624.7	625.8	626.3	626.3	626.3	626.3	626.3	626.3	626.0	625.8
122.5°	681.5	682.2	683.0	683.4	683.5	683.8	684.1	684.3	684.6	683.8	683.0
125°	738.8	739.0	739.3	739.4	739.7	740.2	740.7	741.3	741.8	741.5	741.3
127.5°	795.3	795.8	796.3	796.6	796.7	797.0	797.2	797.5	797.7	797.5	797.2
130°	851.3	851.8	852.3	852.6	852.7	853.0	853.2	853.5	853.7	853.2	852.7
132.5°	904.3	905.0	905.8	906.2	906.3	906.6	906.9	907.1	907.4	907.6	907.9
135°	959.6	960.6	961.7	962.2	962.2	962.2	962.2	962.2	962.2	961.9	961.7
137.5°	1013.8	1015.1	1016.4	1017.0	1016.9	1016.6	1016.3	1016.1	1015.8	1015.3	1014.8
140°	1065.1	1066.4	1067.7	1068.3	1068.0	1067.5	1067.0	1066.5	1066.0	1065.2	1064.4
142.5°	1114.1	1115.4	1116.7	1117.3	1117.2	1116.9	1116.6	1116.4	1116.1	1115.1	1114.1
145°	1162.0	1162.7	1163.5	1163.9	1163.9	1163.9	1163.9	1163.9	1163.9	1163.1	1162.3
147.5°	1205.4	1207.5	1209.6	1210.6	1210.2	1209.4	1208.7	1207.9	1207.1	1206.6	1206.1
150°	1249.0	1249.5	1250.0	1250.3	1250.3	1250.3	1250.3	1250.3	1250.3	1249.3	1248.2
152.5°	1288.5	1289.5	1290.6	1291.1	1290.7	1289.9	1289.2	1288.4	1287.6	1287.3	1287.1
155°	1325.2	1326.5	1327.8	1328.4	1327.9	1326.8	1325.8	1324.7	1323.7	1323.5	1323.2
157.5°	1356.5	1358.3	1360.1	1361.0	1360.5	1359.5	1358.4	1357.4	1356.4	1356.1	1355.9
160°	1387.0	1388.3	1389.6	1390.2	1389.7	1388.6	1387.6	1386.5	1385.5	1385.3	1385.0
162.5°	1414.3	1415.9	1417.4	1418.2	1417.6	1416.3	1415.0	1413.7	1412.4	1412.4	1412.4
165°	1437.6	1439.2	1440.7	1441.5	1441.0	1440.0	1438.9	1437.9	1436.9	1436.6	1436.4
167.5°	1457.5	1459.0	1460.5	1461.3	1460.5	1459.0	1457.5	1455.9	1454.4	1454.4	1454.4
170°	1473.1	1475.0	1476.8	1477.7	1476.9	1475.4	1473.8	1472.3	1470.7	1470.7	1470.7
172.5°	1485.4	1487.0	1488.5	1489.3	1488.5	1487.0	1485.4	1483.9	1482.3	1482.3	1482.3
175°	1492.9	1494.8	1496.6	1497.5	1496.7	1495.2	1493.6	1492.1	1490.5	1490.5	1490.5
177.5°	1497.6	1499.5	1501.3	1502.2	1501.4	1499.9	1498.3	1496.8	1495.2	1495.4	1495.7
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1633.4	1626.7	1618.6	1618.6	1609.2	1605.1	1597.0	1594.3	1587.6	1576.8	1568.7
5°	1691.4	1673.9	1663.1	1653.6	1633.4	1618.6	1603.8	1587.6	1571.4	1552.6	1531.0
7.5°	1748.0	1715.6	1700.8	1684.6	1655.0	1624.0	1594.3	1572.8	1551.2	1521.6	1494.6
10°	1807.3	1766.9	1739.9	1718.3	1672.5	1633.4	1590.3	1559.3	1525.6	1487.9	1452.8
12.5°	1857.2	1804.6	1781.7	1741.2	1688.7	1641.5	1587.6	1540.4	1496.0	1451.5	1408.4
15°	1898.9	1849.1	1792.5	1776.3	1703.5	1636.1	1575.5	1514.8	1459.6	1415.1	1365.2
17.5°	1912.4	1849.1	1820.8	1781.7	1695.4	1625.3	1548.5	1482.5	1429.9	1363.9	1324.8
20°	1916.5	1855.8	1816.7	1780.3	1703.5	1610.5	1535.0	1454.2	1390.8	1324.8	1262.8
22.5°	1905.7	1834.2	1796.5	1761.5	1675.2	1595.7	1508.1	1419.1	1345.0	1284.4	1222.4
25°	1885.5	1801.9	1765.5	1727.8	1645.6	1558.0	1462.3	1377.4	1308.6	1235.9	1175.2
27.5°	1858.5	1762.8	1721.0	1681.9	1601.1	1518.9	1428.6	1341.0	1264.2	1187.3	1130.7
30°	1824.8	1714.3	1676.6	1625.3	1547.2	1469.0	1386.8	1299.2	1212.9	1140.2	1078.2
32.5°	1781.7	1665.8	1615.9	1567.4	1482.5	1411.1	1332.9	1250.7	1167.1	1095.7	1031.0
35°	1742.6	1610.5	1555.3	1506.7	1412.4	1336.9	1272.2	1195.4	1121.3	1047.2	989.2
37.5°	1690.0	1555.3	1489.2	1439.4	1343.7	1266.9	1206.2	1146.9	1068.7	997.3	943.4
40°	1634.8	1486.5	1424.5	1374.7	1274.9	1191.4	1133.4	1080.9	1017.5	951.5	894.9
42.5°	1584.9	1420.5	1354.5	1293.8	1192.7	1118.6	1059.3	1018.9	960.9	901.6	850.4
45°	1521.6	1350.4	1279.0	1215.6	1118.6	1037.7	981.1	948.8	905.7	847.7	803.2
47.5°	1456.9	1274.9	1200.8	1138.8	1033.7	962.3	907.0	876.0	846.4	800.5	756.1
50°	1372.0	1195.4	1128.0	1056.6	952.8	880.1	834.2	803.2	780.3	748.0	710.2
52.5°	1279.0	1113.2	1040.4	978.4	876.0	810.0	757.4	739.9	717.0	692.7	660.4
55°	1180.6	1024.3	954.2	893.5	799.2	731.8	688.7	669.8	652.3	633.4	611.9
57.5°	1082.2	931.3	865.2	811.3	723.7	659.0	624.0	598.4	586.3	575.5	558.0
60°	959.6	831.5	780.3	731.8	645.6	586.3	552.6	533.7	522.9	517.5	509.4
62.5°	851.8	746.6	690.0	642.9	574.1	521.6	489.2	474.4	465.0	462.3	452.8
65°	737.2	646.9	602.4	562.0	502.7	455.5	428.6	411.1	404.3	403.0	403.0
67.5°	629.4	556.6	512.1	483.8	432.6	390.8	365.2	358.5	354.4	349.1	347.7
70°	528.3	470.4	431.3	407.0	361.2	330.2	310.0	299.2	299.2	295.1	292.5
72.5°	439.4	381.4	355.8	335.6	297.8	270.9	256.1	253.4	243.9	242.6	242.6
75°	343.7	300.5	283.0	265.5	237.2	218.3	206.2	199.5	194.1	194.1	195.4
77.5°	258.8	229.1	212.9	199.5	179.2	167.1	157.7	155.0	149.6	149.6	149.6
80°	183.3	167.1	155.0	144.2	129.4	118.6	113.2	107.8	107.8	106.5	107.8
82.5°	118.6	105.1	98.4	97.0	83.6	79.5	72.8	74.1	70.1	68.7	71.4
85°	68.7	62.0	53.9	51.2	45.8	40.4	37.7	39.1	37.7	36.4	37.7
87.5°	27.0	22.9	21.6	21.6	17.5	16.2	14.8	16.2	13.5	13.5	14.8
90°	13.2	11.4	10.5	9.5	7.4	5.3	3.3	1.2	3.3	5.3	7.4
92.5°	44.3	42.0	40.8	40.2	38.9	37.6	36.3	35.0	36.3	37.6	38.9
95°	82.0	79.4	78.1	77.8	77.3	76.8	76.3	75.8	76.3	76.8	77.3
97.5°	123.2	119.6	117.8	117.7	117.4	117.1	116.9	116.6	116.9	117.1	117.4
100°	168.3	165.0	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3	163.3
102.5°	221.2	219.9	219.3	218.6	217.3	216.0	214.7	213.4	214.7	216.0	217.3
105°	274.0	272.5	271.7	271.1	269.8	268.5	267.2	265.9	267.2	268.5	269.8
107.5°	330.8	329.5	328.9	328.3	327.0	325.7	324.4	323.1	324.4	325.7	327.0
110°	389.6	388.8	388.4	387.7	386.4	385.1	383.8	382.5	383.8	385.1	386.4

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	447.1	446.0	445.5	445.2	444.7	444.2	443.7	443.2	443.7	444.2	444.7
115°	508.1	507.6	507.3	506.8	505.8	504.7	503.7	502.7	503.7	504.7	505.8
117.5°	565.3	564.8	564.5	564.4	564.1	563.8	563.6	563.3	563.6	563.8	564.1
120°	625.5	625.2	625.1	624.5	623.2	621.9	620.6	619.3	620.6	621.9	623.2
122.5°	682.3	681.5	681.1	681.0	680.7	680.4	680.2	679.9	680.2	680.4	680.7
125°	741.0	740.7	740.6	739.8	738.3	736.7	735.2	733.6	735.2	736.7	738.3
127.5°	797.0	796.7	796.6	796.2	795.4	794.7	793.9	793.1	793.9	794.7	795.4
130°	852.2	851.7	851.4	850.8	849.5	848.2	846.9	845.6	846.9	848.2	849.5
132.5°	908.1	908.4	908.5	907.3	905.0	902.7	900.3	898.0	900.3	902.7	905.0
135°	961.4	961.1	961.0	960.2	958.7	957.1	955.6	954.0	955.6	957.1	958.7
137.5°	1014.3	1013.8	1013.5	1012.7	1011.2	1009.6	1008.1	1006.5	1008.1	1009.6	1011.2
140°	1063.7	1062.9	1062.5	1061.8	1060.5	1059.2	1057.9	1056.6	1057.9	1059.2	1060.5
142.5°	1113.0	1112.0	1111.5	1111.0	1109.9	1108.9	1107.8	1106.8	1107.8	1108.9	1109.9
145°	1161.6	1160.8	1160.4	1159.9	1158.9	1157.8	1156.8	1155.8	1156.8	1157.8	1158.9
147.5°	1205.6	1205.1	1204.8	1204.4	1203.6	1202.9	1202.1	1201.3	1202.1	1202.9	1203.6
150°	1247.2	1246.1	1245.6	1245.7	1246.0	1246.3	1246.5	1246.8	1246.5	1246.3	1246.0
152.5°	1286.8	1286.5	1286.4	1286.1	1285.6	1285.1	1284.6	1284.1	1284.6	1285.1	1285.6
155°	1323.0	1322.7	1322.6	1322.6	1322.6	1322.6	1322.6	1322.6	1322.6	1322.6	1322.6
157.5°	1355.6	1355.3	1355.2	1355.5	1356.0	1356.5	1357.1	1357.6	1357.1	1356.5	1356.0
160°	1384.8	1384.5	1384.4	1384.8	1385.6	1386.3	1387.1	1387.9	1387.1	1386.3	1385.6
162.5°	1412.4	1412.4	1412.4	1412.7	1413.2	1413.7	1414.2	1414.7	1414.2	1413.7	1413.2
165°	1436.1	1435.8	1435.7	1436.0	1436.5	1437.0	1437.5	1438.0	1437.5	1437.0	1436.5
167.5°	1454.4	1454.4	1454.4	1454.9	1455.9	1457.0	1458.0	1459.0	1458.0	1457.0	1455.9
170°	1470.7	1470.7	1470.7	1471.2	1472.2	1473.3	1474.3	1475.3	1474.3	1473.3	1472.2
172.5°	1482.3	1482.3	1482.3	1482.8	1483.9	1484.9	1486.0	1487.0	1486.0	1484.9	1483.9
175°	1490.5	1490.5	1490.5	1491.0	1492.1	1493.1	1494.2	1495.2	1494.2	1493.1	1492.1
177.5°	1495.9	1496.2	1496.3	1496.8	1497.9	1498.9	1500.0	1501.0	1500.0	1498.9	1497.9
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1566.0	1563.3	1556.6	1552.6	1539.1	1522.9	1517.5	1504.0	1509.4	1500.0	1500.0
5°	1524.3	1512.1	1504.0	1491.9	1466.3	1448.8	1429.9	1420.5	1415.1	1408.4	1403.0
7.5°	1470.4	1460.9	1452.8	1429.9	1401.6	1377.4	1354.5	1345.0	1327.5	1315.4	1310.0
10°	1423.2	1409.7	1390.8	1363.9	1334.2	1303.2	1283.0	1262.8	1249.3	1242.6	1227.8
12.5°	1374.7	1358.5	1338.3	1299.2	1266.9	1248.0	1211.6	1192.7	1186.0	1180.6	1163.1
15°	1324.8	1307.3	1283.0	1246.6	1218.3	1173.9	1152.3	1137.5	1121.3	1120.0	1106.5
17.5°	1280.3	1258.8	1238.5	1194.1	1159.0	1120.0	1107.8	1091.6	1076.8	1060.7	1053.9
20°	1223.7	1203.5	1188.7	1140.2	1101.1	1076.8	1056.6	1043.1	1033.7	1017.5	1014.8
22.5°	1172.5	1150.9	1130.7	1094.3	1060.7	1029.7	1005.4	990.6	986.5	979.8	967.7
25°	1122.6	1101.1	1076.8	1043.1	1008.1	986.5	965.0	955.5	947.4	936.7	927.2
27.5°	1080.9	1060.7	1037.7	996.0	966.3	950.1	927.2	916.4	905.7	900.3	896.2
30°	1031.0	1008.1	990.6	958.2	925.9	904.3	888.1	878.7	869.3	863.9	861.2
32.5°	982.5	960.9	948.8	913.8	888.1	862.5	850.4	843.7	838.3	832.9	827.5
35°	943.4	921.8	903.0	870.6	845.0	827.5	818.1	807.3	803.2	797.8	797.8
37.5°	894.9	878.7	859.8	828.8	805.9	792.5	784.4	770.9	769.5	766.8	762.8
40°	853.1	836.9	819.4	792.5	772.2	756.1	745.3	738.5	734.5	731.8	729.1
42.5°	808.6	791.1	783.0	752.0	734.5	718.3	712.9	706.2	704.9	699.5	692.7
45°	765.5	750.7	734.5	711.6	696.8	683.3	675.2	669.8	663.1	661.7	657.7
47.5°	727.8	710.2	695.4	673.9	657.7	646.9	640.2	633.4	628.0	624.0	619.9
50°	679.2	665.8	653.6	630.7	617.3	606.5	597.0	591.6	586.3	586.3	586.3
52.5°	632.1	619.9	609.2	593.0	576.8	567.4	556.6	552.6	549.9	545.8	549.9
55°	586.3	574.1	563.3	551.2	532.3	524.3	513.5	509.4	510.8	510.8	514.8
57.5°	537.7	528.3	521.6	506.7	489.2	481.1	474.4	470.4	470.4	475.7	477.1
60°	490.6	481.1	469.0	455.5	444.7	435.3	431.3	432.6	432.6	435.3	442.1
62.5°	438.0	432.6	425.9	407.0	400.3	393.5	388.1	392.2	390.8	397.6	407.0
65°	389.5	384.1	374.7	365.2	357.1	350.4	349.1	350.4	353.1	359.8	370.6
67.5°	335.6	335.6	327.5	319.4	312.7	305.9	307.3	308.6	311.3	319.4	335.6
70°	291.1	285.7	277.6	272.2	266.8	264.2	261.5	266.8	274.9	280.3	292.5
72.5°	242.6	238.5	231.8	226.4	225.1	222.4	221.0	223.7	231.8	241.2	254.7
75°	191.4	192.7	188.7	184.6	184.6	180.6	183.3	183.3	191.4	200.8	211.6
77.5°	148.2	146.9	145.6	142.9	141.5	141.5	141.5	144.2	152.3	157.7	168.5
80°	105.1	106.5	102.4	103.8	102.4	103.8	103.8	109.2	113.2	119.9	128.0
82.5°	70.1	70.1	67.4	68.7	68.7	68.7	70.1	72.8	78.2	83.6	88.9
85°	39.1	40.4	37.7	40.4	40.4	40.4	41.8	43.1	47.2	48.5	53.9
87.5°	14.8	17.5	17.5	14.8	16.2	17.5	18.9	17.5	20.2	22.9	24.3
90°	9.5	10.5	11.4	13.2	15.1	16.9	18.7	20.0	21.3	22.6	23.9
92.5°	40.2	40.8	42.0	44.3	46.6	49.0	51.3	53.1	54.9	56.8	58.6
95°	77.8	78.1	79.4	82.0	84.6	87.2	89.8	91.6	93.4	95.3	97.1
97.5°	117.7	117.8	119.6	123.2	126.9	130.5	134.1	135.7	137.2	138.8	140.3
100°	163.3	163.3	165.0	168.3	171.7	175.0	178.4	180.7	183.1	185.4	187.7
102.5°	218.6	219.3	219.9	221.2	222.5	223.8	225.1	227.7	230.3	232.9	235.5
105°	271.1	271.7	272.5	274.0	275.6	277.1	278.7	280.3	281.8	283.4	284.9
107.5°	328.3	328.9	329.5	330.8	332.1	333.4	334.7	335.5	336.3	337.0	337.8
110°	387.7	388.4	388.8	389.6	390.3	391.1	391.9	392.7	393.5	394.2	395.0

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	445.2	445.5	446.0	447.1	448.1	449.2	450.2	450.5	450.7	451.0	451.3
115°	506.8	507.3	507.6	508.1	508.6	509.2	509.7	509.4	509.2	508.9	508.6
117.5°	564.4	564.5	564.8	565.3	565.8	566.3	566.8	567.1	567.3	567.6	567.9
120°	624.5	625.1	625.2	625.5	625.8	626.0	626.3	626.3	626.3	626.3	626.3
122.5°	681.0	681.1	681.5	682.3	683.0	683.8	684.6	684.3	684.1	683.8	683.5
125°	739.8	740.6	740.7	741.0	741.3	741.5	741.8	741.3	740.7	740.2	739.7
127.5°	796.2	796.6	796.7	797.0	797.2	797.5	797.7	797.5	797.2	797.0	796.7
130°	850.8	851.4	851.7	852.2	852.7	853.2	853.7	853.5	853.2	853.0	852.7
132.5°	907.3	908.5	908.4	908.1	907.9	907.6	907.4	907.1	906.9	906.6	906.3
135°	960.2	961.0	961.1	961.4	961.7	961.9	962.2	962.2	962.2	962.2	962.2
137.5°	1012.7	1013.5	1013.8	1014.3	1014.8	1015.3	1015.8	1016.1	1016.3	1016.6	1016.9
140°	1061.8	1062.5	1062.9	1063.7	1064.4	1065.2	1066.0	1066.5	1067.0	1067.5	1068.0
142.5°	1111.0	1111.5	1112.0	1113.0	1114.1	1115.1	1116.1	1116.4	1116.6	1116.9	1117.2
145°	1159.9	1160.4	1160.8	1161.6	1162.3	1163.1	1163.9	1163.9	1163.9	1163.9	1163.9
147.5°	1204.4	1204.8	1205.1	1205.6	1206.1	1206.6	1207.1	1207.9	1208.7	1209.4	1210.2
150°	1245.7	1245.6	1246.1	1247.2	1248.2	1249.3	1250.3	1250.3	1250.3	1250.3	1250.3
152.5°	1286.1	1286.4	1286.5	1286.8	1287.1	1287.3	1287.6	1288.4	1289.2	1289.9	1290.7
155°	1322.6	1322.6	1322.7	1323.0	1323.2	1323.5	1323.7	1324.7	1325.8	1326.8	1327.9
157.5°	1355.5	1355.2	1355.3	1355.6	1355.9	1356.1	1356.4	1357.4	1358.4	1359.5	1360.5
160°	1384.8	1384.4	1384.5	1384.8	1385.0	1385.3	1385.5	1386.5	1387.6	1388.6	1389.7
162.5°	1412.7	1412.4	1412.4	1412.4	1412.4	1412.4	1412.4	1413.7	1415.0	1416.3	1417.6
165°	1436.0	1435.7	1435.8	1436.1	1436.4	1436.6	1436.9	1437.9	1438.9	1440.0	1441.0
167.5°	1454.9	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1455.9	1457.5	1459.0	1460.5
170°	1471.2	1470.7	1470.7	1470.7	1470.7	1470.7	1470.7	1472.3	1473.8	1475.4	1476.9
172.5°	1482.8	1482.3	1482.3	1482.3	1482.3	1482.3	1482.3	1483.9	1485.4	1487.0	1488.5
175°	1491.0	1490.5	1490.5	1490.5	1490.5	1490.5	1490.5	1492.1	1493.6	1495.2	1496.7
177.5°	1496.8	1496.3	1496.2	1495.9	1495.7	1495.4	1495.2	1496.8	1498.3	1499.9	1501.4
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1505.4	1496.0	1494.6	1497.3	1491.9	1500.0	1497.3	1500.0	1493.3	1500.0	1496.0
5°	1401.6	1398.9	1393.5	1386.8	1388.1	1389.5	1396.2	1389.5	1394.9	1396.2	1403.0
7.5°	1304.6	1299.2	1303.2	1300.5	1288.4	1285.7	1288.4	1292.5	1300.5	1305.9	1310.0
10°	1226.4	1223.7	1218.3	1214.3	1207.6	1203.5	1208.9	1203.5	1214.3	1223.7	1223.7
12.5°	1167.1	1156.3	1149.6	1148.3	1133.4	1136.1	1141.5	1145.6	1157.7	1163.1	1163.1
15°	1105.1	1097.0	1094.3	1089.0	1083.6	1089.0	1086.3	1090.3	1095.7	1101.1	1103.8
17.5°	1051.2	1049.9	1051.2	1037.7	1041.8	1035.0	1036.4	1043.1	1039.1	1043.1	1051.2
20°	1002.7	1005.4	1001.4	996.0	996.0	987.9	997.3	994.6	996.0	1004.0	1016.2
22.5°	966.3	965.0	960.9	956.9	951.5	952.8	954.2	951.5	962.3	969.0	970.4
25°	927.2	924.5	923.2	919.1	913.8	919.1	917.8	919.1	921.8	932.6	924.5
27.5°	890.8	885.4	888.1	884.1	882.8	884.1	884.1	885.4	888.1	889.5	890.8
30°	859.8	854.5	853.1	850.4	849.1	850.4	853.1	850.4	861.2	859.8	859.8
32.5°	826.1	822.1	819.4	819.4	818.1	816.7	818.1	819.4	827.5	822.1	827.5
35°	793.8	791.1	791.1	788.4	787.1	787.1	787.1	792.5	789.8	793.8	793.8
37.5°	762.8	762.8	761.5	758.8	757.4	758.8	757.4	760.1	758.8	760.1	761.5
40°	730.5	727.8	726.4	726.4	722.4	718.3	722.4	722.4	723.7	727.8	729.1
42.5°	691.4	692.7	692.7	687.3	687.3	687.3	688.7	690.0	690.0	692.7	692.7
45°	657.7	655.0	655.0	655.0	652.3	653.6	656.3	656.3	656.3	656.3	653.6
47.5°	619.9	619.9	621.3	621.3	625.3	624.0	624.0	622.6	619.9	619.9	621.3
50°	584.9	589.0	590.3	590.3	591.6	593.0	593.0	590.3	589.0	584.9	584.9
52.5°	551.2	553.9	556.6	560.6	563.3	562.0	562.0	559.3	553.9	552.6	551.2
55°	514.8	518.9	524.3	528.3	532.3	533.7	533.7	528.3	522.9	516.2	516.2
57.5°	481.1	485.2	494.6	498.7	504.0	504.0	501.3	497.3	489.2	483.8	479.8
60°	447.4	454.2	460.9	469.0	475.7	477.1	473.0	467.7	458.2	451.5	446.1
62.5°	411.1	417.8	431.3	439.4	444.7	444.7	444.7	438.0	425.9	416.4	408.4
65°	376.0	382.8	394.9	405.7	409.7	413.7	409.7	403.0	393.5	382.8	374.7
67.5°	339.6	347.7	359.8	367.9	373.3	377.4	374.7	369.3	357.1	342.3	336.9
70°	299.2	303.2	320.8	328.8	336.9	339.6	336.9	328.8	316.7	300.5	295.1
72.5°	261.5	265.5	281.7	288.4	295.1	297.8	293.8	288.4	277.6	262.8	256.1
75°	218.3	225.1	233.2	243.9	252.0	254.7	250.7	246.6	233.2	223.7	218.3
77.5°	172.5	179.2	190.0	199.5	207.5	206.2	200.8	202.2	187.3	176.6	172.5
80°	130.7	136.1	144.2	152.3	156.3	156.3	155.0	149.6	144.2	136.1	129.4
82.5°	90.3	97.0	103.8	109.2	109.2	110.5	107.8	106.5	101.1	94.3	93.0
85°	53.9	55.3	60.6	60.6	66.0	63.3	62.0	66.0	60.6	56.6	55.3
87.5°	24.3	22.9	24.3	24.3	22.9	25.6	25.6	24.3	25.6	24.3	24.3
90°	24.5	24.9	25.7	26.4	27.2	28.0	27.2	26.4	25.7	24.9	24.5
92.5°	59.5	59.8	60.3	60.8	61.3	61.8	61.3	60.8	60.3	59.8	59.5
95°	98.0	98.3	98.8	99.3	99.8	100.3	99.8	99.3	98.8	98.3	98.0
97.5°	141.1	141.2	141.5	141.8	142.0	142.3	142.0	141.8	141.5	141.2	141.1
100°	188.9	189.2	189.7	190.2	190.8	191.3	190.8	190.2	189.7	189.2	188.9
102.5°	236.8	237.2	238.0	238.7	239.5	240.3	239.5	238.7	238.0	237.2	236.8
105°	285.7	286.1	286.9	287.6	288.4	289.2	288.4	287.6	286.9	286.1	285.7
107.5°	338.2	338.2	338.2	338.2	338.2	338.2	338.2	338.2	338.2	338.2	338.2
110°	395.4	395.3	395.0	394.7	394.5	394.2	394.5	394.7	395.0	395.3	395.4

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	451.4	451.1	450.6	450.1	449.5	449.0	449.5	450.1	450.6	451.1	451.4
115°	508.5	508.4	508.1	507.8	507.6	507.3	507.6	507.8	508.1	508.4	508.5
117.5°	568.0	567.5	566.4	565.4	564.3	563.3	564.3	565.4	566.4	567.5	568.0
120°	626.3	625.8	624.7	623.7	622.6	621.6	622.6	623.7	624.7	625.8	626.3
122.5°	683.4	683.0	682.2	681.5	680.7	679.9	680.7	681.5	682.2	683.0	683.4
125°	739.4	739.3	739.0	738.8	738.5	738.3	738.5	738.8	739.0	739.3	739.4
127.5°	796.6	796.3	795.8	795.3	794.7	794.2	794.7	795.3	795.8	796.3	796.6
130°	852.6	852.3	851.8	851.3	850.7	850.2	850.7	851.3	851.8	852.3	852.6
132.5°	906.2	905.8	905.0	904.3	903.5	902.7	903.5	904.3	905.0	905.8	906.2
135°	962.2	961.7	960.6	959.6	958.5	957.5	958.5	959.6	960.6	961.7	962.2
137.5°	1017.0	1016.4	1015.1	1013.8	1012.5	1011.2	1012.5	1013.8	1015.1	1016.4	1017.0
140°	1068.3	1067.7	1066.4	1065.1	1063.8	1062.5	1063.8	1065.1	1066.4	1067.7	1068.3
142.5°	1117.3	1116.7	1115.4	1114.1	1112.8	1111.5	1112.8	1114.1	1115.4	1116.7	1117.3
145°	1163.9	1163.5	1162.7	1162.0	1161.2	1160.4	1161.2	1162.0	1162.7	1163.5	1163.9
147.5°	1210.6	1209.6	1207.5	1205.4	1203.4	1201.3	1203.4	1205.4	1207.5	1209.6	1210.6
150°	1250.3	1250.0	1249.5	1249.0	1248.4	1247.9	1248.4	1249.0	1249.5	1250.0	1250.3
152.5°	1291.1	1290.6	1289.5	1288.5	1287.4	1286.4	1287.4	1288.5	1289.5	1290.6	1291.1
155°	1328.4	1327.8	1326.5	1325.2	1323.9	1322.6	1323.9	1325.2	1326.5	1327.8	1328.4
157.5°	1361.0	1360.1	1358.3	1356.5	1354.7	1352.9	1354.7	1356.5	1358.3	1360.1	1361.0
160°	1390.2	1389.6	1388.3	1387.0	1385.7	1384.4	1385.7	1387.0	1388.3	1389.6	1390.2
162.5°	1418.2	1417.4	1415.9	1414.3	1412.8	1411.2	1412.8	1414.3	1415.9	1417.4	1418.2
165°	1441.5	1440.7	1439.2	1437.6	1436.1	1434.5	1436.1	1437.6	1439.2	1440.7	1441.5
167.5°	1461.3	1460.5	1459.0	1457.5	1455.9	1454.4	1455.9	1457.5	1459.0	1460.5	1461.3
170°	1477.7	1476.8	1475.0	1473.1	1471.3	1469.5	1471.3	1473.1	1475.0	1476.8	1477.7
172.5°	1489.3	1488.5	1487.0	1485.4	1483.9	1482.3	1483.9	1485.4	1487.0	1488.5	1489.3
175°	1497.5	1496.6	1494.8	1492.9	1491.1	1489.3	1491.1	1492.9	1494.8	1496.6	1497.5
177.5°	1502.2	1501.3	1499.5	1497.6	1495.8	1494.0	1495.8	1497.6	1499.5	1501.3	1502.2
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6	1587.6
2.5°	1508.1	1500.0	1509.4	1497.3	1500.0	1514.8	1513.5	1527.0	1535.0	1533.7	1540.4
5°	1408.4	1408.4	1412.4	1411.1	1424.5	1436.7	1452.8	1466.3	1481.1	1489.2	1498.7
7.5°	1310.0	1323.5	1326.2	1332.9	1349.1	1369.3	1385.5	1405.7	1427.2	1442.1	1452.8
10°	1229.1	1239.9	1250.7	1256.1	1273.6	1300.5	1323.5	1355.8	1382.8	1398.9	1413.8
12.5°	1157.7	1169.8	1175.2	1199.5	1211.6	1229.1	1261.5	1296.5	1326.2	1343.7	1355.8
15°	1106.5	1113.2	1125.3	1140.2	1152.3	1173.9	1200.8	1239.9	1268.2	1283.0	1324.8
17.5°	1063.3	1071.4	1078.2	1084.9	1103.8	1126.7	1152.3	1186.0	1222.4	1248.0	1269.5
20°	1018.9	1022.9	1031.0	1041.8	1055.3	1076.8	1099.7	1134.8	1167.1	1187.3	1215.6
22.5°	966.3	978.4	986.5	994.6	1009.4	1033.7	1055.3	1080.9	1121.3	1144.2	1173.9
25°	935.3	940.7	946.1	955.5	966.3	987.9	1012.1	1039.1	1071.4	1095.7	1121.3
27.5°	894.9	903.0	909.7	921.8	928.6	946.1	969.0	996.0	1035.0	1055.3	1076.8
30°	861.2	869.3	874.7	880.1	889.5	908.4	929.9	951.5	987.9	1013.5	1035.0
32.5°	827.5	835.6	842.3	846.4	855.8	867.9	885.4	912.4	943.4	960.9	989.2
35°	797.8	797.8	805.9	811.3	819.4	830.2	846.4	866.6	898.9	921.8	947.4
37.5°	764.2	765.5	772.2	776.3	784.4	795.2	811.3	830.2	857.1	874.7	900.3
40°	729.1	733.2	735.9	742.6	752.0	756.1	772.2	793.8	820.8	836.9	858.5
42.5°	694.1	696.8	703.5	708.9	717.0	723.7	734.5	754.7	774.9	799.2	816.7
45°	655.0	661.7	665.8	675.2	679.2	686.0	696.8	712.9	737.2	752.0	772.2
47.5°	621.3	624.0	626.7	638.8	646.9	650.9	661.7	671.2	696.8	710.2	729.1
50°	584.9	584.9	589.0	594.3	603.8	611.9	621.3	632.1	652.3	665.8	684.6
52.5°	551.2	547.2	549.9	552.6	562.0	570.1	579.5	594.3	613.2	621.3	637.5
55°	514.8	508.1	512.1	516.2	518.9	529.7	540.4	549.9	564.7	576.8	591.6
57.5°	475.7	474.4	471.7	473.0	479.8	486.5	494.6	506.7	524.3	533.7	541.8
60°	440.7	432.6	429.9	432.6	436.7	440.7	451.5	462.3	477.1	486.5	496.0
62.5°	404.3	396.2	390.8	386.8	390.8	400.3	407.0	415.1	427.2	438.0	446.1
65°	369.3	357.1	351.8	349.1	347.7	354.4	359.8	370.6	381.4	385.4	394.9
67.5°	330.2	319.4	312.7	308.6	308.6	308.6	314.0	324.8	335.6	336.9	346.4
70°	291.1	279.0	272.2	266.8	264.2	266.8	273.6	274.9	284.4	287.1	292.5
72.5°	249.3	238.5	230.5	223.7	225.1	227.8	227.8	230.5	235.9	242.6	242.6
75°	210.2	195.4	191.4	186.0	183.3	183.3	183.3	188.7	192.7	198.1	196.8
77.5°	165.8	157.7	149.6	146.9	142.9	141.5	144.2	144.2	146.9	150.9	152.3
80°	128.0	118.6	113.2	110.5	105.1	103.8	105.1	105.1	109.2	107.8	109.2
82.5°	88.9	82.2	78.2	74.1	71.4	72.8	71.4	71.4	72.8	71.4	71.4
85°	51.2	49.9	47.2	45.8	44.5	41.8	44.5	43.1	41.8	40.4	43.1
87.5°	24.3	22.9	22.9	20.2	20.2	18.9	20.2	20.2	18.9	18.9	18.9
90°	23.9	22.6	21.3	20.0	18.7	16.9	15.1	13.2	11.4	10.5	9.5
92.5°	58.6	56.8	54.9	53.1	51.3	49.0	46.6	44.3	42.0	40.8	40.2
95°	97.1	95.3	93.4	91.6	89.8	87.2	84.6	82.0	79.4	78.1	77.8
97.5°	140.3	138.8	137.2	135.7	134.1	130.5	126.9	123.2	119.6	117.8	117.7
100°	187.7	185.4	183.1	180.7	178.4	175.0	171.7	168.3	165.0	163.3	163.3
102.5°	235.5	232.9	230.3	227.7	225.1	223.8	222.5	221.2	219.9	219.3	218.6
105°	284.9	283.4	281.8	280.3	278.7	277.1	275.6	274.0	272.5	271.7	271.1
107.5°	337.8	337.0	336.3	335.5	334.7	333.4	332.1	330.8	329.5	328.9	328.3
110°	395.0	394.2	393.5	392.7	391.9	391.1	390.3	389.6	388.8	388.4	387.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	451.3	451.0	450.7	450.5	450.2	449.2	448.1	447.1	446.0	445.5	445.2
115°	508.6	508.9	509.2	509.4	509.7	509.2	508.6	508.1	507.6	507.3	506.8
117.5°	567.9	567.6	567.3	567.1	566.8	566.3	565.8	565.3	564.8	564.5	564.4
120°	626.3	626.3	626.3	626.3	626.3	626.0	625.8	625.5	625.2	625.1	624.5
122.5°	683.5	683.8	684.1	684.3	684.6	683.8	683.0	682.3	681.5	681.1	681.0
125°	739.7	740.2	740.7	741.3	741.8	741.5	741.3	741.0	740.7	740.6	739.8
127.5°	796.7	797.0	797.2	797.5	797.7	797.5	797.2	797.0	796.7	796.6	796.2
130°	852.7	853.0	853.2	853.5	853.7	853.2	852.7	852.2	851.7	851.4	850.8
132.5°	906.3	906.6	906.9	907.1	907.4	907.6	907.9	908.1	908.4	908.5	907.3
135°	962.2	962.2	962.2	962.2	962.2	961.9	961.7	961.4	961.1	961.0	960.2
137.5°	1016.9	1016.6	1016.3	1016.1	1015.8	1015.3	1014.8	1014.3	1013.8	1013.5	1012.7
140°	1068.0	1067.5	1067.0	1066.5	1066.0	1065.2	1064.4	1063.7	1062.9	1062.5	1061.8
142.5°	1117.2	1116.9	1116.6	1116.4	1116.1	1115.1	1114.1	1113.0	1112.0	1111.5	1111.0
145°	1163.9	1163.9	1163.9	1163.9	1163.9	1163.1	1162.3	1161.6	1160.8	1160.4	1159.9
147.5°	1210.2	1209.4	1208.7	1207.9	1207.1	1206.6	1206.1	1205.6	1205.1	1204.8	1204.4
150°	1250.3	1250.3	1250.3	1250.3	1250.3	1249.3	1248.2	1247.2	1246.1	1245.6	1245.7
152.5°	1290.7	1289.9	1289.2	1288.4	1287.6	1287.3	1287.1	1286.8	1286.5	1286.4	1286.1
155°	1327.9	1326.8	1325.8	1324.7	1323.7	1323.5	1323.2	1323.0	1322.7	1322.6	1322.6
157.5°	1360.5	1359.5	1358.4	1357.4	1356.4	1356.1	1355.9	1355.6	1355.3	1355.2	1355.5
160°	1389.7	1388.6	1387.6	1386.5	1385.5	1385.3	1385.0	1384.8	1384.5	1384.4	1384.8
162.5°	1417.6	1416.3	1415.0	1413.7	1412.4	1412.4	1412.4	1412.4	1412.4	1412.4	1412.7
165°	1441.0	1440.0	1438.9	1437.9	1436.9	1436.6	1436.4	1436.1	1435.8	1435.7	1436.0
167.5°	1460.5	1459.0	1457.5	1455.9	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.9
170°	1476.9	1475.4	1473.8	1472.3	1470.7	1470.7	1470.7	1470.7	1470.7	1470.7	1471.2
172.5°	1488.5	1487.0	1485.4	1483.9	1482.3	1482.3	1482.3	1482.3	1482.3	1482.3	1482.8
175°	1496.7	1495.2	1493.6	1492.1	1490.5	1490.5	1490.5	1490.5	1490.5	1490.5	1491.0
177.5°	1501.4	1499.9	1498.3	1496.8	1495.2	1495.4	1495.7	1495.9	1496.2	1496.3	1496.8
180°	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7	1498.7

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1587.6	1587.6	1587.6	1587.6
2.5°	1549.9	1563.3	1572.8	1590.3
5°	1514.8	1539.1	1562.0	1586.3
7.5°	1479.8	1508.1	1544.5	1575.5
10°	1440.7	1477.1	1520.2	1562.0
12.5°	1401.6	1444.8	1491.9	1547.2
15°	1354.5	1409.7	1465.0	1524.3
17.5°	1312.7	1369.3	1428.6	1502.7
20°	1265.5	1327.5	1392.2	1467.7
22.5°	1223.7	1292.5	1359.8	1439.4
25°	1176.6	1243.9	1318.1	1403.0
27.5°	1137.5	1199.5	1272.2	1363.9
30°	1090.3	1157.7	1230.5	1322.1
32.5°	1045.8	1110.5	1187.3	1277.6
35°	1000.0	1066.0	1134.8	1221.0
37.5°	956.9	1013.5	1082.2	1164.4
40°	908.4	970.4	1032.3	1097.0
42.5°	863.9	920.5	978.4	1029.7
45°	814.0	862.5	917.8	959.6
47.5°	768.2	811.3	854.5	886.8
50°	722.4	756.1	788.4	816.7
52.5°	668.5	706.2	723.7	741.2
55°	619.9	641.5	657.7	675.2
57.5°	572.8	582.2	590.3	606.5
60°	510.8	521.6	531.0	543.1
62.5°	456.9	462.3	465.0	477.1
65°	405.7	404.3	411.1	417.8
67.5°	350.4	349.1	355.8	358.5
70°	296.5	295.1	296.5	303.2
72.5°	245.3	245.3	246.6	249.3
75°	198.1	198.1	199.5	202.2
77.5°	149.6	152.3	150.9	156.3
80°	109.2	106.5	109.2	111.9
82.5°	71.4	74.1	74.1	71.4
85°	40.4	40.4	40.4	40.4
87.5°	17.5	17.5	18.9	20.2
90°	7.4	5.3	3.3	1.2
92.5°	38.9	37.6	36.3	35.0
95°	77.3	76.8	76.3	75.8
97.5°	117.4	117.1	116.9	116.6
100°	163.3	163.3	163.3	163.3
102.5°	217.3	216.0	214.7	213.4
105°	269.8	268.5	267.2	265.9
107.5°	327.0	325.7	324.4	323.1
110°	386.4	385.1	383.8	382.5

TEST NUMBER: P1027368

CATALOG NUMBER: S125DIP-B1090D1270UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	444.7	444.2	443.7	443.2
115°	505.8	504.7	503.7	502.7
117.5°	564.1	563.8	563.6	563.3
120°	623.2	621.9	620.6	619.3
122.5°	680.7	680.4	680.2	679.9
125°	738.3	736.7	735.2	733.6
127.5°	795.4	794.7	793.9	793.1
130°	849.5	848.2	846.9	845.6
132.5°	905.0	902.7	900.3	898.0
135°	958.7	957.1	955.6	954.0
137.5°	1011.2	1009.6	1008.1	1006.5
140°	1060.5	1059.2	1057.9	1056.6
142.5°	1109.9	1108.9	1107.8	1106.8
145°	1158.9	1157.8	1156.8	1155.8
147.5°	1203.6	1202.9	1202.1	1201.3
150°	1246.0	1246.3	1246.5	1246.8
152.5°	1285.6	1285.1	1284.6	1284.1
155°	1322.6	1322.6	1322.6	1322.6
157.5°	1356.0	1356.5	1357.1	1357.6
160°	1385.6	1386.3	1387.1	1387.9
162.5°	1413.2	1413.7	1414.2	1414.7
165°	1436.5	1437.0	1437.5	1438.0
167.5°	1455.9	1457.0	1458.0	1459.0
170°	1472.2	1473.3	1474.3	1475.3
172.5°	1483.9	1484.9	1486.0	1487.0
175°	1492.1	1493.1	1494.2	1495.2
177.5°	1497.9	1498.9	1500.0	1501.0
180°	1498.7	1498.7	1498.7	1498.7

(END OF REPORT)