

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027101

Luminaire Tested: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027101
REPORT IS A COMBINATION OF REPORTS P1005092 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7396.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027101

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027101

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45
3	83	74	66	61	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	49	53	48	44	46	42	39	39	36	34
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	29
6	65	52	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26
7	60	47	40	34	56	45	37	32	39	34	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1027101

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	2.3
10°-20°	469.3	6.3
20°-30°	680.5	9.2
30°-40°	775.3	10.5
40°-50°	755.7	10.2
50°-60°	636.0	8.6
60°-70°	445.7	6.0
70°-80°	228.5	3.1
80°-90°	58.5	0.8
90°-100°	35.1	0.5
100°-110°	233.5	3.2
110°-120°	420.5	5.7
120°-130°	539.8	7.3
130°-140°	580.6	7.8
140°-150°	544.9	7.4
150°-160°	440.7	6.0
160°-170°	285.0	3.9
170°-180°	98.3	1.3
0°-30°	1317.8	17.8
0°-40°	2093.2	28.3
0°-60°	3484.9	47.1
0°-90°	4217.5	57.0
90°-120°	689.2	9.3
90°-150°	2354.4	31.8
90°-180°	3178.0	43.0
0°-180°	7396.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	1	7	12	16	18	6
95°	44	41	12	16	16	54
105°	226	229	229	229	228	239
115°	423	427	428	425	420	420
125°	602	608	608	604	602	538
135°	751	756	754	752	748	579
145°	871	872	872	873	868	544
155°	959	954	956	958	952	442
165°	1012	1007	1008	1012	1006	286
175°	1035	1030	1031	1037	1030	99
180°	1035	1035	1035	1035	1035	

TEST NUMBER: P1027101

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	0.8	6.9	12.3	16.1	18.4
92.5°	14.6	7.7	12.3	16.1	16.9
95°	43.7	41.4	12.3	16.1	16.1
97.5°	82.1	86.7	13.8	15.3	16.1
100°	128.1	130.4	133.5	19.2	16.1
102.5°	174.9	178.0	179.5	181.0	116.6
105°	225.5	228.6	228.6	228.6	227.8
107.5°	277.7	277.7	279.2	280.0	276.9
110°	328.3	328.3	329.8	327.5	328.3

TEST NUMBER: P1027101

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.8	378.1	378.9	375.8	374.3
115°	423.4	427.2	428.0	424.9	420.3
117.5°	473.3	473.3	476.3	471.7	470.2
120°	519.3	518.5	520.8	519.3	515.4
122.5°	559.9	563.8	564.5	563.0	558.4
125°	602.1	607.5	607.5	604.4	602.1
127.5°	642.8	646.6	645.8	644.3	638.2
130°	679.6	683.4	684.2	681.9	678.1
132.5°	716.4	721.0	718.7	718.7	714.9
135°	750.9	755.5	754.0	752.5	747.9
137.5°	783.1	787.7	786.2	786.2	782.4
140°	814.6	816.1	815.4	816.9	812.3
142.5°	843.0	843.7	845.3	845.3	840.7
145°	870.6	872.1	872.1	872.9	868.3
147.5°	895.1	895.1	895.9	896.7	891.3
150°	918.1	916.6	918.1	919.7	913.5
152.5°	940.4	936.5	938.1	939.6	934.2
155°	958.8	954.2	955.7	958.0	951.9
157.5°	973.4	971.1	971.1	973.4	967.2
160°	988.7	984.1	984.9	987.9	981.8
162.5°	1001.0	996.4	997.1	1001.7	994.8
165°	1011.7	1007.1	1007.9	1012.5	1006.3
167.5°	1020.2	1015.6	1016.3	1021.7	1014.8
170°	1027.1	1021.7	1022.5	1028.6	1021.7
172.5°	1031.7	1026.3	1027.8	1033.2	1026.3
175°	1034.7	1030.1	1030.9	1037.0	1030.1
177.5°	1037.0	1032.4	1033.2	1038.6	1032.4
180°	1034.7	1034.7	1034.7	1034.7	1034.7

(END OF REPORT)