

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027110

Luminaire Tested: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027110
REPORT IS A COMBINATION OF REPORTS P1005131 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8986.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027110

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027110

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13257	12925	12946
10°	13128	12599	12488
15°	12942	12144	11887
20°	12712	11595	11256
25°	12448	11059	10579
30°	12125	10471	9869
35°	11796	9872	9114
40°	11482	9259	8377
45°	11106	8595	7605
50°	10724	7891	6819
55°	10281	7199	6005
60°	9826	6406	5161
65°	9285	5520	4250
70°	8656	4494	3344
75°	7785	3379	2437
80°	6563	2189	1644
85°	4911	1176	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11106 cd/sqm

TEST NUMBER: P1027110

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	2.2
10°-20°	544.2	6.1
20°-30°	789.0	8.8
30°-40°	898.9	10.0
40°-50°	876.2	9.8
50°-60°	737.4	8.2
60°-70°	516.7	5.8
70°-80°	264.9	2.9
80°-90°	68.0	0.8
90°-100°	45.3	0.5
100°-110°	300.9	3.3
110°-120°	541.9	6.0
120°-130°	695.6	7.7
130°-140°	748.1	8.3
140°-150°	702.2	7.8
150°-160°	568.0	6.3
160°-170°	367.3	4.1
170°-180°	126.7	1.4
0°-30°	1527.9	17.0
0°-40°	2426.8	27.0
0°-60°	4040.3	45.0
0°-90°	4890.0	54.4
90°-120°	888.1	9.9
90°-150°	3034.1	33.8
90°-180°	4096.0	45.6
0°-180°	8986.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	94
90°	1	9	16	21	24	8
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1027110

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1027110

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)