

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027113

Luminaire Tested: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027113
REPORT IS A COMBINATION OF REPORTS P1005134 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8640.1 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027113

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027113

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12746	12746	12746
5°	12747	12428	12448
10°	12622	12115	12008
15°	12444	11677	11429
20°	12223	11149	10823
25°	11969	10634	10172
30°	11659	10068	9489
35°	11341	9493	8763
40°	11040	8902	8054
45°	10679	8265	7313
50°	10311	7588	6556
55°	9885	6922	5773
60°	9449	6160	4962
65°	8928	5308	4087
70°	8323	4322	3216
75°	7483	3249	2344
80°	6311	2104	1581
85°	4723	1131	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10679 cd/sqm

TEST NUMBER: P1027113

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.2
10°-20°	523.2	6.1
20°-30°	758.7	8.8
30°-40°	864.3	10.0
40°-50°	842.5	9.8
50°-60°	709.0	8.2
60°-70°	496.8	5.8
70°-80°	254.7	2.9
80°-90°	65.4	0.8
90°-100°	43.5	0.5
100°-110°	289.3	3.3
110°-120°	521.0	6.0
120°-130°	668.8	7.7
130°-140°	719.3	8.3
140°-150°	675.1	7.8
150°-160°	546.1	6.3
160°-170°	353.2	4.1
170°-180°	121.8	1.4
0°-30°	1469.1	17.0
0°-40°	2333.5	27.0
0°-60°	3884.9	45.0
0°-90°	4701.9	54.4
90°-120°	853.9	9.9
90°-150°	2917.1	33.8
90°-180°	3938.0	45.6
0°-180°	8640.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1986	1980	1964	1979	1976	188
15°	1889	1880	1848	1847	1833	533
25°	1713	1690	1635	1615	1599	788
35°	1475	1439	1372	1328	1307	924
45°	1208	1164	1082	1022	999	932
55°	916	868	784	717	693	820
65°	620	569	490	430	407	614
75°	330	286	222	189	179	349
85°	83	56	48	47	45	90
90°	1	9	15	20	23	7
95°	54	51	15	20	20	66
105°	279	283	283	283	282	296
115°	525	529	530	526	521	520
125°	746	753	753	749	746	666
135°	930	936	934	932	927	717
145°	1079	1080	1080	1082	1076	675
155°	1188	1182	1184	1187	1179	547
165°	1254	1248	1249	1254	1247	354
175°	1282	1276	1277	1285	1276	122
180°	1282	1282	1282	1282	1282	

TEST NUMBER: P1027113

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1989.3	1989.3	1989.3	1989.3	1989.3
2.5°	1993.8	1989.3	1974.3	1989.3	1987.8
5°	1986.3	1980.3	1963.8	1978.8	1975.8
7.5°	1971.3	1965.3	1945.7	1957.7	1954.7
10°	1948.7	1944.2	1923.2	1927.7	1923.2
12.5°	1923.2	1917.2	1887.1	1890.1	1882.6
15°	1888.6	1879.6	1848.1	1846.6	1833.0
17.5°	1852.6	1839.0	1801.5	1794.0	1783.5
20°	1809.0	1794.0	1745.9	1738.4	1724.9
22.5°	1760.9	1745.9	1694.8	1678.3	1667.8
25°	1712.8	1690.3	1634.7	1615.2	1598.6
27.5°	1658.7	1631.7	1573.1	1547.6	1531.0
30°	1598.6	1570.1	1507.0	1472.4	1458.9
32.5°	1540.1	1505.5	1440.9	1401.8	1383.8
35°	1475.4	1439.4	1371.8	1328.2	1307.2
37.5°	1413.8	1370.3	1301.2	1250.1	1229.0
40°	1347.7	1302.7	1230.5	1173.4	1155.4
42.5°	1278.6	1232.0	1156.9	1102.8	1074.3
45°	1208.0	1164.4	1081.8	1021.7	999.2
47.5°	1134.4	1089.3	1006.7	945.1	919.5
50°	1065.3	1015.7	930.0	866.9	844.4
52.5°	990.1	939.1	859.4	790.3	767.8
55°	916.5	868.4	784.3	716.7	692.6
57.5°	841.4	790.3	709.2	643.1	622.0
60°	769.3	716.7	635.6	569.4	546.9
62.5°	692.6	643.1	560.4	500.3	477.8
65°	620.5	569.4	489.8	429.7	407.2
67.5°	548.4	497.3	420.7	363.6	345.6
70°	474.8	423.7	348.6	302.0	284.0
72.5°	402.7	353.1	284.0	241.9	231.4
75°	330.5	285.5	222.4	189.3	178.8
77.5°	256.9	220.9	168.3	142.7	133.7
80°	195.3	159.3	117.2	103.7	100.7
82.5°	135.2	103.7	78.1	73.6	72.1
85°	82.6	55.6	48.1	46.6	45.1
87.5°	34.6	24.0	22.5	22.5	21.0
90°	1.0	8.6	15.2	20.0	22.8
92.5°	18.1	9.5	15.2	20.0	20.9
95°	54.2	51.3	15.2	20.0	20.0
97.5°	101.7	107.4	17.1	19.0	20.0
100°	158.7	161.6	165.4	23.8	20.0
102.5°	216.7	220.5	222.4	224.3	144.5
105°	279.4	283.2	283.2	283.2	282.3
107.5°	344.0	344.0	345.9	346.9	343.1
110°	406.7	406.7	408.7	405.8	406.7

TEST NUMBER: P1027113

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	465.7	468.5	469.5	465.7	463.8
115°	524.6	529.3	530.3	526.5	520.8
117.5°	586.4	586.4	590.2	584.5	582.6
120°	643.4	642.4	645.3	643.4	638.6
122.5°	693.8	698.5	699.5	697.6	691.9
125°	746.0	752.7	752.7	748.9	746.0
127.5°	796.4	801.1	800.2	798.3	790.7
130°	842.0	846.8	847.7	844.9	840.1
132.5°	887.6	893.3	890.5	890.5	885.7
135°	930.4	936.1	934.2	932.3	926.6
137.5°	970.3	976.0	974.1	974.1	969.4
140°	1009.3	1011.2	1010.2	1012.1	1006.4
142.5°	1044.4	1045.4	1047.3	1047.3	1041.6
145°	1078.6	1080.5	1080.5	1081.5	1075.8
147.5°	1109.1	1109.1	1110.0	1111.0	1104.3
150°	1137.6	1135.7	1137.6	1139.5	1131.9
152.5°	1165.1	1160.4	1162.3	1164.2	1157.5
155°	1187.9	1182.2	1184.1	1187.0	1179.4
157.5°	1206.0	1203.1	1203.1	1206.0	1198.4
160°	1225.0	1219.3	1220.2	1224.1	1216.4
162.5°	1240.2	1234.5	1235.5	1241.2	1232.6
165°	1253.5	1247.8	1248.8	1254.5	1246.9
167.5°	1264.0	1258.3	1259.2	1265.9	1257.3
170°	1272.5	1265.9	1266.8	1274.4	1265.9
172.5°	1278.2	1271.6	1273.5	1280.1	1271.6
175°	1282.0	1276.3	1277.3	1284.9	1276.3
177.5°	1284.9	1279.2	1280.1	1286.8	1279.2
180°	1282.0	1282.0	1282.0	1282.0	1282.0

(END OF REPORT)