

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027401

Luminaire Tested: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027401
REPORT IS A COMBINATION OF REPORTS P1001346 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D375UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5642.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027401

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027401

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	78		
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65		
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58	55		
3	86	76	69	62	82	73	66	60	67	61	56	61	57	53	56	52	49	46		
4	79	68	59	53	75	65	57	51	60	53	48	55	49	45	50	46	42	40		
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37	34		
6	67	54	46	40	64	52	44	39	48	42	37	44	39	35	41	36	33	30		
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	37	33	29	27		
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	34	30	26	24		
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24	22		
10	51	38	30	25	48	37	29	25	34	28	24	32	26	22	30	25	21	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10775	10775	10775
5°	10775	10525	10545
10°	10686	10284	10251
15°	10546	9995	9905
20°	10356	9660	9508
25°	10152	9295	9084
30°	9907	8915	8636
35°	9644	8517	8135
40°	9373	8095	7688
45°	9080	7684	7215
50°	8757	7218	6663
55°	8437	6705	6155
60°	8056	6164	5564
65°	7600	5537	4954
70°	7136	4816	4249
75°	6356	3965	3436
80°	5416	2962	2528
85°	4185	1752	1393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9080 cd/sqm

TEST NUMBER: P1027401

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	2.8
10°-20°	448.2	7.9
20°-30°	661.7	11.7
30°-40°	772.1	13.7
40°-50°	775.4	13.7
50°-60°	680.7	12.1
60°-70°	507.0	9.0
70°-80°	289.6	5.1
80°-90°	84.3	1.5
90°-100°	30.1	0.5
100°-110°	89.5	1.6
110°-120°	151.8	2.7
120°-130°	199.8	3.5
130°-140°	223.9	4.0
140°-150°	219.5	3.9
150°-160°	184.3	3.3
160°-170°	122.5	2.2
170°-180°	42.9	0.8
0°-30°	1268.7	22.5
0°-40°	2040.7	36.2
0°-60°	3496.8	62.0
0°-90°	4377.7	77.6
90°-120°	271.4	4.8
90°-150°	914.6	16.2
90°-180°	1264.0	22.4
0°-180°	5642.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1679	1676	1663	1675	1674	159
15°	1600	1596	1582	1588	1588	451
25°	1453	1446	1429	1432	1428	668
35°	1255	1249	1231	1224	1213	785
45°	1027	1022	1006	990	986	791
55°	782	778	760	748	738	698
65°	528	526	511	499	494	524
75°	281	278	271	267	262	299
85°	73	74	74	73	70	80
90°	0	3	6	7	8	6
95°	23	24	27	30	30	24
105°	80	82	84	86	87	86
115°	152	153	154	154	153	150
125°	222	224	224	224	223	199
135°	288	290	291	291	289	222
145°	349	351	352	352	351	218
155°	400	400	400	402	400	184
165°	435	434	434	436	434	123
175°	452	450	450	453	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1027401

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1681.7	1681.7	1681.7	1681.7	1681.7
2.5°	1687.0	1683.0	1669.7	1683.0	1681.7
5°	1679.0	1676.4	1663.1	1675.0	1673.7
7.5°	1667.0	1664.4	1649.7	1661.7	1660.4
10°	1649.7	1647.1	1632.5	1643.1	1641.8
12.5°	1628.5	1623.1	1609.8	1617.8	1617.8
15°	1600.5	1596.5	1581.9	1588.5	1588.5
17.5°	1571.3	1564.6	1550.0	1557.9	1551.3
20°	1532.7	1530.0	1512.7	1522.0	1515.4
22.5°	1494.1	1488.8	1472.8	1478.1	1474.1
25°	1452.8	1446.2	1428.9	1431.6	1427.6
27.5°	1404.9	1401.0	1383.7	1385.0	1381.0
30°	1358.4	1354.4	1334.4	1331.8	1327.8
32.5°	1307.8	1301.2	1283.9	1278.6	1270.6
35°	1254.6	1249.3	1230.7	1224.0	1213.4
37.5°	1200.1	1193.4	1176.1	1166.8	1160.1
40°	1144.2	1137.5	1118.9	1106.9	1102.9
42.5°	1084.3	1079.0	1060.4	1049.7	1043.1
45°	1027.1	1021.8	1005.8	989.8	985.9
47.5°	964.6	965.9	945.9	930.0	920.7
50°	904.7	900.7	884.7	867.4	858.1
52.5°	843.5	840.8	823.5	808.9	798.3
55°	782.3	778.3	759.7	747.7	738.4
57.5°	717.1	715.8	699.8	683.8	679.9
60°	655.9	650.6	636.0	622.6	613.3
62.5°	592.0	588.1	576.1	561.4	554.8
65°	528.2	525.5	510.9	498.9	493.6
67.5°	465.7	460.3	449.7	439.0	436.4
70°	407.1	400.5	388.5	380.5	375.2
72.5°	343.3	339.3	332.6	323.3	318.0
75°	280.7	278.1	271.4	267.4	262.1
77.5°	222.2	220.9	216.9	214.2	210.2
80°	167.6	167.6	165.0	163.6	161.0
82.5°	119.7	117.1	117.1	114.4	114.4
85°	73.2	74.5	74.5	73.2	70.5
87.5°	35.9	35.9	34.6	34.6	31.9
90°	0.4	3.2	5.6	7.4	8.5
92.5°	10.6	12.3	15.5	18.0	18.7
95°	22.9	23.6	27.1	29.6	30.3
97.5°	35.3	35.6	40.5	42.7	43.0
100°	49.4	49.4	53.9	57.1	57.8
102.5°	64.5	66.3	68.0	71.6	72.6
105°	80.4	82.1	84.3	86.4	87.4
107.5°	97.7	99.4	101.2	102.2	102.2
110°	115.6	117.4	118.5	119.5	119.2



TEST NUMBER: P1027401

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.0	134.7	136.1	136.4	135.7
115°	151.9	153.4	154.1	153.7	153.4
117.5°	170.3	170.6	171.3	171.7	170.3
120°	187.2	189.0	189.3	189.3	187.9
122.5°	205.5	205.9	206.9	206.6	205.5
125°	221.7	223.9	224.2	223.5	223.2
127.5°	239.7	240.8	241.1	240.8	240.1
130°	255.6	257.3	258.1	257.7	257.0
132.5°	271.4	274.6	274.3	273.9	272.9
135°	288.4	290.5	290.8	290.8	289.4
137.5°	304.2	306.3	307.1	307.4	305.6
140°	319.4	321.2	322.2	322.9	321.2
142.5°	334.6	336.0	337.4	337.7	336.0
145°	349.4	350.8	351.8	351.8	350.8
147.5°	363.1	364.2	364.9	365.9	363.1
150°	376.9	376.5	377.9	377.9	377.2
152.5°	388.1	388.8	389.2	390.3	388.8
155°	399.8	399.8	400.1	401.5	399.8
157.5°	410.3	409.6	410.0	411.4	408.9
160°	419.5	418.5	418.8	420.2	418.5
162.5°	427.6	426.9	426.9	428.7	426.6
165°	434.7	434.0	434.3	435.7	433.6
167.5°	441.0	439.6	439.6	441.7	439.6
170°	446.0	444.5	444.5	446.7	444.2
172.5°	449.5	448.1	448.1	450.2	448.1
175°	451.9	450.5	450.5	452.7	450.2
177.5°	453.7	452.3	451.9	454.1	451.6
180°	453.0	453.0	453.0	453.0	453.0

(END OF REPORT)