

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027132

Luminaire Tested: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027132
REPORT IS A COMBINATION OF REPORTS P1005213 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6326.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027132

CATALOG NUMBER: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027132

CATALOG NUMBER: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	81	76	90	84	78	73	77	72	68	70	66	63	64	61	59
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50
4	80	69	61	54	76	66	59	53	61	54	50	56	51	47	51	47	44
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38
6	68	56	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	38	34	30
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13179	13179	13179
5°	13181	12851	12872
10°	13053	12527	12417
15°	12868	12074	11818
20°	12639	11528	11191
25°	12376	10996	10519
30°	12056	10411	9812
35°	11728	9816	9062
40°	11416	9205	8328
45°	11042	8546	7561
50°	10662	7846	6779
55°	10221	7158	5970
60°	9771	6369	5131
65°	9233	5489	4225
70°	8605	4468	3325
75°	7739	3359	2424
80°	6528	2176	1634
85°	4888	1169	921

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11042 cd/sqm

TEST NUMBER: P1027132

CATALOG NUMBER: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.6	3.1
10°-20°	541.0	8.6
20°-30°	784.5	12.4
30°-40°	893.8	14.1
40°-50°	871.1	13.8
50°-60°	733.1	11.6
60°-70°	513.8	8.1
70°-80°	263.4	4.2
80°-90°	66.4	1.0
90°-100°	16.2	0.3
100°-110°	107.7	1.7
110°-120°	193.9	3.1
120°-130°	248.8	3.9
130°-140°	267.6	4.2
140°-150°	251.2	4.0
150°-160°	203.2	3.2
160°-170°	131.4	2.1
170°-180°	45.3	0.7
0°-30°	1519.1	24.0
0°-40°	2412.9	38.1
0°-60°	4017.2	63.5
0°-90°	4860.7	76.8
90°-120°	317.7	5.0
90°-150°	1085.4	17.2
90°-180°	1465.0	23.2
0°-180°	6326.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2057	2057	2057	2057	2057	
5°	2054	2048	2031	2046	2043	195
15°	1953	1944	1911	1909	1895	551
25°	1771	1748	1690	1670	1653	815
35°	1526	1488	1418	1373	1352	955
45°	1249	1204	1119	1056	1033	963
55°	948	898	811	741	716	847
65°	642	589	506	444	421	635
75°	342	295	230	196	185	361
85°	86	58	50	48	47	94
90°	0	3	6	7	8	6
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	197	197	196	194	194
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1027132

CATALOG NUMBER: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2057.0	2057.0	2057.0	2057.0	2057.0
2.5°	2061.7	2057.0	2041.5	2057.0	2055.5
5°	2053.9	2047.7	2030.6	2046.1	2043.0
7.5°	2038.4	2032.2	2012.0	2024.4	2021.3
10°	2015.1	2010.4	1988.7	1993.3	1988.7
12.5°	1988.7	1982.4	1951.4	1954.5	1946.7
15°	1952.9	1943.6	1911.0	1909.4	1895.4
17.5°	1915.6	1901.7	1862.8	1855.0	1844.2
20°	1870.6	1855.0	1805.3	1797.6	1783.6
22.5°	1820.9	1805.3	1752.5	1735.4	1724.5
25°	1771.1	1747.8	1690.4	1670.2	1653.1
27.5°	1715.2	1687.3	1626.7	1600.2	1583.2
30°	1653.1	1623.6	1558.3	1522.6	1508.6
32.5°	1592.5	1556.7	1489.9	1449.5	1430.9
35°	1525.7	1488.4	1418.5	1373.4	1351.7
37.5°	1462.0	1416.9	1345.5	1292.6	1270.9
40°	1393.6	1347.0	1272.4	1213.4	1194.7
42.5°	1322.1	1274.0	1196.3	1140.4	1110.9
45°	1249.1	1204.1	1118.6	1056.5	1033.2
47.5°	1173.0	1126.4	1040.9	977.2	950.8
50°	1101.5	1050.3	961.7	896.4	873.1
52.5°	1023.8	971.0	888.7	817.2	793.9
55°	947.7	898.0	811.0	741.1	716.2
57.5°	870.0	817.2	733.3	665.0	643.2
60°	795.5	741.1	657.2	588.8	565.5
62.5°	716.2	665.0	579.5	517.4	494.1
65°	641.7	588.8	506.5	444.3	421.0
67.5°	567.1	514.3	435.0	376.0	357.3
70°	490.9	438.1	360.4	312.3	293.6
72.5°	416.4	365.1	293.6	250.1	239.3
75°	341.8	295.2	229.9	195.8	184.9
77.5°	265.7	228.4	174.0	147.6	138.3
80°	202.0	164.7	121.2	107.2	104.1
82.5°	139.8	107.2	80.8	76.1	74.6
85°	85.5	57.5	49.7	48.2	46.6
87.5°	35.7	24.9	23.3	23.3	21.8
90°	0.4	3.2	5.7	7.4	8.5
92.5°	6.7	3.5	5.7	7.4	7.8
95°	20.2	19.1	5.7	7.4	7.4
97.5°	37.8	40.0	6.4	7.1	7.4
100°	59.1	60.1	61.5	8.8	7.4
102.5°	80.6	82.0	82.7	83.5	53.7
105°	104.0	105.4	105.4	105.4	105.0
107.5°	128.0	128.0	128.7	129.1	127.7
110°	151.3	151.3	152.1	151.0	151.3



TEST NUMBER: P1027132

CATALOG NUMBER: S125RDIP-B1270D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.3	174.3	174.7	173.3	172.6
115°	195.2	197.0	197.3	195.9	193.8
117.5°	218.2	218.2	219.6	217.5	216.8
120°	239.4	239.0	240.1	239.4	237.6
122.5°	258.1	259.9	260.3	259.5	257.4
125°	277.6	280.1	280.1	278.6	277.6
127.5°	296.3	298.1	297.7	297.0	294.2
130°	313.3	315.1	315.4	314.4	312.6
132.5°	330.3	332.4	331.3	331.3	329.6
135°	346.2	348.3	347.6	346.9	344.8
137.5°	361.0	363.2	362.4	362.4	360.7
140°	375.5	376.2	375.9	376.6	374.5
142.5°	388.6	389.0	389.7	389.7	387.6
145°	401.3	402.1	402.1	402.4	400.3
147.5°	412.7	412.7	413.0	413.4	410.9
150°	423.3	422.6	423.3	424.0	421.1
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)