

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027411

Luminaire Tested: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027411
REPORT IS A COMBINATION OF REPORTS P1001371 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D375UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5742.7 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027411

CATALOG NUMBER: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027411

CATALOG NUMBER: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81			77
1	104	99	95	91	99	95	91	88	86	83	81	78	76	74	71	70	68			65
2	94	87	80	75	90	83	77	72	76	71	67	69	65	62	63	60	57			54
3	86	76	68	62	82	73	66	60	67	61	56	61	56	52	56	52	49			46
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	50	45	42			39
5	73	60	52	45	69	58	50	44	53	47	42	49	43	39	45	40	37			34
6	67	54	46	40	64	52	44	39	48	41	36	44	39	34	41	36	32			30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29			26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26			24
9	54	41	33	28	51	40	32	27	37	30	26	34	29	25	32	27	23			21
10	50	38	30	25	48	36	29	25	34	28	23	32	26	22	29	25	21			19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1027411

CATALOG NUMBER: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.8
10°-20°	452.1	7.9
20°-30°	667.5	11.6
30°-40°	778.8	13.6
40°-50°	782.2	13.6
50°-60°	686.6	12.0
60°-70°	511.4	8.9
70°-80°	292.1	5.1
80°-90°	85.0	1.5
90°-100°	132.8	2.3
100°-110°	275.8	4.8
110°-120°	257.6	4.5
120°-130°	208.4	3.6
130°-140°	167.5	2.9
140°-150°	126.4	2.2
150°-160°	89.0	1.5
160°-170°	52.5	0.9
170°-180°	17.1	0.3
0°-30°	1279.7	22.3
0°-40°	2058.4	35.8
0°-60°	3527.2	61.4
0°-90°	4415.7	76.9
90°-120°	666.2	11.6
90°-150°	1168.5	20.3
90°-180°	1327.0	23.1
0°-180°	5742.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	0	3	6	7	8	6
95°	12	35	315	143	84	12
105°	40	56	258	507	471	42
115°	72	87	207	446	525	71
125°	100	117	198	355	413	88
135°	117	140	197	297	343	90
145°	136	156	198	246	271	85
155°	155	167	193	218	227	71
165°	169	174	185	196	199	48
175°	176	176	177	180	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1027411

CATALOG NUMBER: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	0.4	3.2	5.7	7.4	8.2
92.5°	5.3	29.2	141.8	37.8	26.3
95°	11.7	34.7	314.9	142.9	83.5
97.5°	18.1	37.5	340.2	258.0	183.1
100°	24.9	43.0	321.0	364.7	277.3
102.5°	32.3	49.2	287.2	455.0	382.5
105°	40.2	56.2	257.7	507.4	471.0
107.5°	47.6	63.4	235.7	522.2	524.3
110°	55.8	71.1	221.1	508.2	548.5

TEST NUMBER: P1027411

CATALOG NUMBER: S125DIP-B1090D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.0	78.8	212.6	478.8	545.7
115°	71.8	86.6	206.9	446.0	524.7
117.5°	78.9	94.6	203.7	416.1	493.0
120°	86.0	102.2	201.6	391.0	462.5
122.5°	93.5	109.6	199.8	370.9	435.5
125°	99.5	116.6	198.4	354.8	413.4
127.5°	104.5	123.4	197.6	340.9	393.2
130°	109.1	129.8	196.9	326.8	377.2
132.5°	112.7	135.4	196.9	311.8	361.2
135°	116.6	140.2	196.9	297.4	343.4
137.5°	121.6	144.7	197.3	282.2	324.9
140°	125.8	148.4	197.6	268.4	305.4
142.5°	130.8	152.0	198.0	256.5	287.2
145°	135.8	155.5	197.6	246.2	270.9
147.5°	141.1	158.8	196.9	237.2	256.3
150°	145.7	161.6	195.9	230.0	244.6
152.5°	150.7	164.4	194.4	223.8	235.3
155°	155.0	166.7	192.7	217.8	227.1
157.5°	158.9	169.0	190.9	212.0	219.7
160°	162.8	170.8	189.1	206.4	212.2
162.5°	166.0	172.6	187.0	201.2	205.5
165°	169.2	173.9	184.8	196.0	199.1
167.5°	171.3	174.5	182.7	191.2	193.0
170°	173.5	175.4	180.9	186.6	187.7
172.5°	174.9	175.8	178.8	182.9	182.7
175°	176.0	176.0	177.4	179.5	178.8
177.5°	176.7	176.0	176.3	177.4	176.3
180°	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)