

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027160

Luminaire Tested: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027160
REPORT IS A COMBINATION OF REPORTS P1005331 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.0 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027160

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027160

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	48	40	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3197 cd/sqm

TEST NUMBER: P1027160

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	1.0
10°-20°	156.6	2.8
20°-30°	227.1	4.1
30°-40°	258.7	4.7
40°-50°	252.2	4.6
50°-60°	212.2	3.9
60°-70°	148.7	2.7
70°-80°	76.3	1.4
80°-90°	21.0	0.4
90°-100°	45.3	0.8
100°-110°	300.9	5.5
110°-120°	541.9	9.8
120°-130°	695.6	12.6
130°-140°	748.1	13.6
140°-150°	702.2	12.8
150°-160°	568.0	10.3
160°-170°	367.3	6.7
170°-180°	126.7	2.3
0°-30°	439.8	8.0
0°-40°	698.5	12.7
0°-60°	1163.0	21.1
0°-90°	1409.0	25.6
90°-120°	888.1	16.1
90°-150°	3034.1	55.1
90°-180°	4096.0	74.4
0°-180°	5505.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	9	16	21	24	4
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1027160

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1027160

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)