

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027183

Luminaire Tested: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027183
REPORT IS A COMBINATION OF REPORTS P1005414 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027183

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027183

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	71	68	60	59	57	49	48	47
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	37	58	48	41	35	41	35	31	34	30	27	28	25	23
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	28	34	28	24	29	24	21	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3670	3578	3584
10°	3634	3487	3457
15°	3582	3361	3290
20°	3519	3210	3115
25°	3446	3061	2928
30°	3356	2898	2732
35°	3265	2733	2523
40°	3179	2562	2319
45°	3075	2379	2105
50°	2969	2184	1888
55°	2845	1993	1662
60°	2721	1774	1428
65°	2570	1528	1176
70°	2396	1243	925
75°	2156	935	675
80°	1816	605	455
85°	1361	324	257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3075 cd/sqm

TEST NUMBER: P1027183

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.9
10°-20°	150.6	5.4
20°-30°	218.4	7.9
30°-40°	248.8	9.0
40°-50°	242.5	8.8
50°-60°	204.1	7.4
60°-70°	143.0	5.2
70°-80°	73.3	2.6
80°-90°	19.0	0.7
90°-100°	15.7	0.6
100°-110°	104.1	3.8
110°-120°	187.5	6.8
120°-130°	240.7	8.7
130°-140°	258.9	9.3
140°-150°	243.0	8.8
150°-160°	196.5	7.1
160°-170°	127.1	4.6
170°-180°	43.8	1.6
0°-30°	422.9	15.3
0°-40°	671.7	24.2
0°-60°	1118.4	40.4
0°-90°	1353.7	48.9
90°-120°	307.3	11.1
90°-150°	1049.8	37.9
90°-180°	1417.0	51.1
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	26
90°	0	3	6	7	8	2
95°	20	18	6	7	7	24
105°	101	102	102	102	102	107
115°	189	190	191	190	187	187
125°	268	271	271	270	268	240
135°	335	337	336	336	334	258
145°	388	389	389	389	387	243
155°	428	426	426	427	424	197
165°	451	449	449	452	449	127
175°	461	459	460	462	459	44
180°	461	461	461	461	461	

TEST NUMBER: P1027183

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.3	3.1	5.5	7.2	8.2
92.5°	6.5	3.4	5.5	7.2	7.5
95°	19.5	18.5	5.5	7.2	7.2
97.5°	36.6	38.6	6.2	6.8	7.2
100°	57.1	58.1	59.5	8.6	7.2
102.5°	78.0	79.4	80.0	80.7	52.0
105°	100.6	101.9	101.9	101.9	101.6
107.5°	123.8	123.8	124.5	124.8	123.5
110°	146.4	146.4	147.1	146.0	146.4



TEST NUMBER: P1027183

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.6	168.6	169.0	167.6	166.9
115°	188.8	190.5	190.9	189.5	187.4
117.5°	211.0	211.0	212.4	210.3	209.7
120°	231.6	231.2	232.2	231.6	229.8
122.5°	249.7	251.4	251.7	251.0	249.0
125°	268.5	270.9	270.9	269.5	268.5
127.5°	286.6	288.3	288.0	287.3	284.6
130°	303.0	304.7	305.1	304.1	302.4
132.5°	319.5	321.5	320.5	320.5	318.8
135°	334.8	336.9	336.2	335.5	333.5
137.5°	349.2	351.3	350.6	350.6	348.9
140°	363.2	363.9	363.6	364.3	362.2
142.5°	375.9	376.2	376.9	376.9	374.9
145°	388.2	388.9	388.9	389.2	387.2
147.5°	399.1	399.1	399.5	399.8	397.4
150°	409.4	408.7	409.4	410.1	407.4
152.5°	419.3	417.6	418.3	419.0	416.6
155°	427.5	425.5	426.2	427.2	424.5
157.5°	434.0	433.0	433.0	434.0	431.3
160°	440.9	438.8	439.2	440.5	437.8
162.5°	446.3	444.3	444.6	446.7	443.6
165°	451.1	449.1	449.4	451.5	448.7
167.5°	454.9	452.8	453.2	455.6	452.5
170°	458.0	455.6	455.9	458.7	455.6
172.5°	460.0	457.6	458.3	460.7	457.6
175°	461.4	459.3	459.7	462.4	459.3
177.5°	462.4	460.4	460.7	463.1	460.4
180°	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)