

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027191

Luminaire Tested: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027191
REPORT IS A COMBINATION OF REPORTS P1005452 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3793.1 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027191

CATALOG NUMBER: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027191

CATALOG NUMBER: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	40	39	38
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	27
4	72	62	54	48	65	57	50	45	46	41	38	37	33	31	28	26	24
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3832	3832	3832
5°	3833	3736	3742
10°	3795	3642	3610
15°	3741	3510	3436
20°	3675	3352	3254
25°	3598	3197	3058
30°	3505	3027	2853
35°	3410	2854	2635
40°	3319	2676	2422
45°	3211	2484	2198
50°	3100	2281	1971
55°	2971	2081	1736
60°	2841	1852	1492
65°	2685	1596	1228
70°	2501	1299	967
75°	2251	977	705
80°	1897	632	476
85°	1418	341	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3211 cd/sqm

TEST NUMBER: P1027191

CATALOG NUMBER: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.5
10°-20°	157.3	4.1
20°-30°	228.1	6.0
30°-40°	259.9	6.9
40°-50°	253.3	6.7
50°-60°	213.2	5.6
60°-70°	149.4	3.9
70°-80°	76.6	2.0
80°-90°	20.3	0.5
90°-100°	26.3	0.7
100°-110°	174.8	4.6
110°-120°	314.7	8.3
120°-130°	404.0	10.7
130°-140°	434.5	11.5
140°-150°	407.8	10.8
150°-160°	329.9	8.7
160°-170°	213.3	5.6
170°-180°	73.6	1.9
0°-30°	441.7	11.6
0°-40°	701.5	18.5
0°-60°	1168.0	30.8
0°-90°	1414.2	37.3
90°-120°	515.8	13.6
90°-150°	1762.1	46.5
90°-180°	2379.0	62.7
0°-180°	3793.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	597	595	590	595	594	57
15°	568	565	556	555	551	160
25°	515	508	492	486	481	237
35°	444	433	412	399	393	278
45°	363	350	325	307	300	280
55°	276	261	236	216	208	246
65°	187	171	147	129	122	185
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	5	9	12	14	3
95°	33	31	9	12	12	40
105°	169	171	171	171	170	179
115°	317	320	320	318	315	314
125°	451	455	455	452	451	403
135°	562	566	564	563	560	433
145°	652	653	653	653	650	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1027191

CATALOG NUMBER: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.1	598.1	598.1	598.1	598.1
2.5°	599.4	598.1	593.5	598.1	597.6
5°	597.2	595.3	590.4	594.9	594.0
7.5°	592.6	590.8	585.0	588.6	587.7
10°	585.9	584.5	578.2	579.5	578.2
12.5°	578.2	576.4	567.3	568.2	566.0
15°	567.8	565.1	555.6	555.1	551.1
17.5°	557.0	552.9	541.6	539.3	536.2
20°	543.9	539.3	524.9	522.6	518.6
22.5°	529.4	524.9	509.5	504.6	501.4
25°	514.9	508.2	491.5	485.6	480.6
27.5°	498.7	490.6	472.9	465.3	460.3
30°	480.6	472.0	453.1	442.7	438.6
32.5°	463.0	452.6	433.2	421.4	416.0
35°	443.6	432.7	412.4	399.3	393.0
37.5°	425.1	412.0	391.2	375.8	369.5
40°	405.2	391.6	369.9	352.8	347.4
42.5°	384.4	370.4	347.8	331.6	323.0
45°	363.2	350.1	325.2	307.2	300.4
47.5°	341.0	327.5	302.6	284.1	276.4
50°	320.3	305.4	279.6	260.6	253.9
52.5°	297.7	282.3	258.4	237.6	230.8
55°	275.5	261.1	235.8	215.5	208.2
57.5°	253.0	237.6	213.2	193.3	187.0
60°	231.3	215.5	191.1	171.2	164.4
62.5°	208.2	193.3	168.5	150.4	143.6
65°	186.6	171.2	147.3	129.2	122.4
67.5°	164.9	149.5	126.5	109.3	103.9
70°	142.7	127.4	104.8	90.8	85.4
72.5°	121.1	106.2	85.4	72.7	69.6
75°	99.4	85.8	66.9	56.9	53.8
77.5°	77.2	66.4	50.6	42.9	40.2
80°	58.7	47.9	35.2	31.2	30.3
82.5°	40.7	31.2	23.5	22.1	21.7
85°	24.8	16.7	14.5	14.0	13.6
87.5°	10.4	7.2	6.8	6.8	6.3
90°	0.6	5.2	9.2	12.1	13.8
92.5°	10.9	5.7	9.2	12.1	12.6
95°	32.7	31.0	9.2	12.1	12.1
97.5°	61.4	64.9	10.3	11.5	12.1
100°	95.9	97.6	99.9	14.4	12.1
102.5°	130.9	133.2	134.3	135.5	87.3
105°	168.8	171.1	171.1	171.1	170.5
107.5°	207.8	207.8	209.0	209.5	207.2
110°	245.7	245.7	246.8	245.1	245.7

TEST NUMBER: P1027191

CATALOG NUMBER: S125RDIP-B375D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.3	283.0	283.6	281.3	280.1
115°	316.9	319.8	320.3	318.0	314.6
117.5°	354.2	354.2	356.5	353.1	351.9
120°	388.6	388.1	389.8	388.6	385.8
122.5°	419.1	421.9	422.5	421.4	417.9
125°	450.6	454.7	454.7	452.4	450.6
127.5°	481.1	483.9	483.4	482.2	477.6
130°	508.6	511.5	512.1	510.3	507.5
132.5°	536.2	539.6	537.9	537.9	535.0
135°	562.0	565.5	564.3	563.2	559.7
137.5°	586.1	589.6	588.4	588.4	585.6
140°	609.7	610.8	610.2	611.4	607.9
142.5°	630.9	631.5	632.6	632.6	629.2
145°	651.6	652.7	652.7	653.3	649.8
147.5°	669.9	669.9	670.5	671.1	667.1
150°	687.2	686.0	687.2	688.3	683.7
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)