

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027200

Luminaire Tested: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027200
REPORT IS A COMBINATION OF REPORTS P1005491 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4574.0 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027200

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027200

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	67	76	71	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3197 cd/sqm

TEST NUMBER: P1027200

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	1.2
10°-20°	156.6	3.4
20°-30°	227.1	5.0
30°-40°	258.7	5.7
40°-50°	252.2	5.5
50°-60°	212.2	4.6
60°-70°	148.7	3.3
70°-80°	76.3	1.7
80°-90°	20.5	0.4
90°-100°	35.0	0.8
100°-110°	232.6	5.1
110°-120°	418.8	9.2
120°-130°	537.6	11.8
130°-140°	578.2	12.6
140°-150°	542.6	11.9
150°-160°	438.9	9.6
160°-170°	283.9	6.2
170°-180°	97.9	2.1
0°-30°	439.8	9.6
0°-40°	698.5	15.3
0°-60°	1163.0	25.4
0°-90°	1408.5	30.8
90°-120°	686.3	15.0
90°-150°	2344.8	51.3
90°-180°	3165.0	69.2
0°-180°	4574.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	7	12	16	18	4
95°	44	41	12	16	16	53
105°	225	228	228	228	227	238
115°	422	426	426	423	419	418
125°	600	605	605	602	600	536
135°	748	752	751	749	745	577
145°	867	869	869	869	865	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1027200

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	0.8	6.9	12.2	16.0	18.3
92.5°	14.5	7.6	12.2	16.0	16.8
95°	43.5	41.3	12.2	16.0	16.0
97.5°	81.7	86.3	13.8	15.3	16.0
100°	127.6	129.9	132.9	19.1	16.0
102.5°	174.2	177.2	178.8	180.3	116.1
105°	224.6	227.6	227.6	227.6	226.9
107.5°	276.5	276.5	278.1	278.8	275.8
110°	326.9	326.9	328.5	326.2	326.9

TEST NUMBER: P1027200

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.3	376.6	377.4	374.3	372.8
115°	421.7	425.5	426.3	423.2	418.6
117.5°	471.3	471.3	474.4	469.8	468.3
120°	517.2	516.4	518.7	517.2	513.3
122.5°	557.6	561.5	562.2	560.7	556.1
125°	599.7	605.0	605.0	602.0	599.7
127.5°	640.1	644.0	643.2	641.7	635.6
130°	676.8	680.6	681.4	679.1	675.3
132.5°	713.5	718.1	715.8	715.8	712.0
135°	747.9	752.4	750.9	749.4	744.8
137.5°	779.9	784.5	783.0	783.0	779.2
140°	811.3	812.8	812.0	813.6	809.0
142.5°	839.5	840.3	841.8	841.8	837.2
145°	867.0	868.6	868.6	869.3	864.7
147.5°	891.5	891.5	892.2	893.0	887.6
150°	914.4	912.9	914.4	915.9	909.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)