

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027219

Luminaire Tested: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027219
REPORT IS A COMBINATION OF REPORTS P1005570 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7121.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027219

CATALOG NUMBER: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027219

CATALOG NUMBER: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	22
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	21	19
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	18	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6366	6206	6216
10°	6303	6050	5997
15°	6214	5831	5707
20°	6103	5567	5404
25°	5977	5310	5080
30°	5822	5027	4738
35°	5664	4740	4376
40°	5513	4446	4022
45°	5332	4127	3651
50°	5149	3789	3274
55°	4936	3456	2883
60°	4718	3076	2478
65°	4459	2651	2040
70°	4156	2158	1606
75°	3738	1622	1171
80°	3151	1050	790
85°	2361	564	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5332 cd/sqm

TEST NUMBER: P1027219

CATALOG NUMBER: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.3
10°-20°	261.3	3.7
20°-30°	378.8	5.3
30°-40°	431.6	6.1
40°-50°	420.7	5.9
50°-60°	354.1	5.0
60°-70°	248.1	3.5
70°-80°	127.2	1.8
80°-90°	34.0	0.5
90°-100°	52.7	0.7
100°-110°	350.6	4.9
110°-120°	631.3	8.9
120°-130°	810.4	11.4
130°-140°	871.6	12.2
140°-150°	818.0	11.5
150°-160°	661.7	9.3
160°-170°	427.9	6.0
170°-180°	147.6	2.1
0°-30°	733.6	10.3
0°-40°	1165.2	16.4
0°-60°	1940.0	27.2
0°-90°	2349.3	33.0
90°-120°	1034.6	14.5
90°-150°	3534.5	49.6
90°-180°	4772.0	67.0
0°-180°	7121.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	45
90°	1	10	18	24	28	6
95°	66	62	18	24	24	80
105°	338	343	343	343	342	359
115°	636	641	642	638	631	630
125°	904	912	912	907	904	807
135°	1127	1134	1132	1130	1123	869
145°	1307	1309	1309	1310	1304	817
155°	1439	1432	1435	1438	1429	663
165°	1519	1512	1513	1520	1511	429
175°	1553	1546	1548	1557	1546	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1027219

CATALOG NUMBER: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	1.2	10.4	18.4	24.2	27.6
92.5°	21.9	11.5	18.4	24.2	25.3
95°	65.6	62.2	18.4	24.2	24.2
97.5°	123.2	130.1	20.7	23.0	24.2
100°	192.3	195.8	200.4	28.8	24.2
102.5°	262.5	267.2	269.5	271.8	175.0
105°	338.5	343.2	343.2	343.2	342.0
107.5°	416.8	416.8	419.2	420.3	415.7
110°	492.8	492.8	495.2	491.7	492.8

TEST NUMBER: P1027219

CATALOG NUMBER: S125RDIP-B610D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.2	567.7	568.8	564.2	561.9
115°	635.6	641.4	642.5	637.9	631.0
117.5°	710.5	710.5	715.1	708.2	705.9
120°	779.6	778.4	781.9	779.6	773.8
122.5°	840.6	846.4	847.5	845.2	838.3
125°	903.9	912.0	912.0	907.4	903.9
127.5°	965.0	970.7	969.6	967.3	958.1
130°	1020.2	1026.0	1027.2	1023.7	1017.9
132.5°	1075.5	1082.4	1079.0	1079.0	1073.2
135°	1127.3	1134.2	1131.9	1129.6	1122.7
137.5°	1175.7	1182.6	1180.3	1180.3	1174.5
140°	1222.9	1225.2	1224.1	1226.4	1219.5
142.5°	1265.5	1266.7	1269.0	1269.0	1262.1
145°	1307.0	1309.3	1309.3	1310.4	1303.5
147.5°	1343.8	1343.8	1345.0	1346.1	1338.1
150°	1378.4	1376.1	1378.4	1380.7	1371.5
152.5°	1411.8	1406.0	1408.3	1410.6	1402.5
155°	1439.4	1432.5	1434.8	1438.2	1429.0
157.5°	1461.3	1457.8	1457.8	1461.3	1452.1
160°	1484.3	1477.4	1478.5	1483.2	1473.9
162.5°	1502.7	1495.8	1497.0	1503.9	1493.5
165°	1518.8	1511.9	1513.1	1520.0	1510.8
167.5°	1531.5	1524.6	1525.8	1533.8	1523.5
170°	1541.9	1533.8	1535.0	1544.2	1533.8
172.5°	1548.8	1540.7	1543.0	1551.1	1540.7
175°	1553.4	1546.5	1547.6	1556.8	1546.5
177.5°	1556.8	1549.9	1551.1	1559.2	1549.9
180°	1553.4	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)