

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027252

Luminaire Tested: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027252
REPORT IS A COMBINATION OF REPORTS P1005693 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5502.0 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027252

CATALOG NUMBER: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027252

CATALOG NUMBER: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	19	16
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6381	6381	6381
5°	6382	6222	6232
10°	6319	6065	6012
15°	6230	5846	5722
20°	6120	5582	5418
25°	5992	5324	5092
30°	5837	5041	4751
35°	5678	4753	4387
40°	5527	4457	4032
45°	5346	4138	3661
50°	5162	3799	3282
55°	4948	3466	2891
60°	4730	3084	2484
65°	4471	2657	2045
70°	4167	2163	1610
75°	3747	1626	1173
80°	3160	1054	791
85°	2367	567	446

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5346 cd/sqm

TEST NUMBER: P1027252

CATALOG NUMBER: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	1.7
10°-20°	261.9	4.8
20°-30°	379.8	6.9
30°-40°	432.7	7.9
40°-50°	421.8	7.7
50°-60°	355.0	6.5
60°-70°	248.7	4.5
70°-80°	127.5	2.3
80°-90°	33.3	0.6
90°-100°	34.8	0.6
100°-110°	231.2	4.2
110°-120°	416.4	7.6
120°-130°	534.5	9.7
130°-140°	574.9	10.4
140°-150°	539.6	9.8
150°-160°	436.4	7.9
160°-170°	282.3	5.1
170°-180°	97.3	1.8
0°-30°	735.5	13.4
0°-40°	1168.2	21.2
0°-60°	1944.9	35.3
0°-90°	2354.5	42.8
90°-120°	682.5	12.4
90°-150°	2331.4	42.4
90°-180°	3147.0	57.2
0°-180°	5502.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	996	996	996	996	996	
5°	994	991	983	991	989	94
15°	946	941	925	924	918	267
25°	858	846	818	809	800	395
35°	739	721	687	665	654	463
45°	605	583	542	512	500	466
55°	459	435	393	359	347	410
65°	311	285	245	215	204	308
75°	166	143	111	95	90	175
85°	41	28	24	23	23	45
90°	1	7	12	16	18	5
95°	43	41	12	16	16	53
105°	223	226	226	226	226	237
115°	419	423	424	421	416	416
125°	596	602	602	598	596	533
135°	744	748	747	745	741	573
145°	862	864	864	864	860	539
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1027252

CATALOG NUMBER: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	995.9	995.9	995.9	995.9	995.9
2.5°	998.2	995.9	988.4	995.9	995.2
5°	994.4	991.4	983.1	990.7	989.1
7.5°	986.9	983.9	974.1	980.1	978.6
10°	975.6	973.4	962.8	965.1	962.8
12.5°	962.8	959.8	944.8	946.3	942.5
15°	945.5	941.0	925.2	924.5	917.7
17.5°	927.5	920.7	901.9	898.1	892.9
20°	905.7	898.1	874.1	870.3	863.5
22.5°	881.6	874.1	848.5	840.2	834.9
25°	857.5	846.2	818.4	808.6	800.3
27.5°	830.4	816.9	787.6	774.8	766.5
30°	800.3	786.1	754.5	737.2	730.4
32.5°	771.0	753.7	721.4	701.8	692.8
35°	738.7	720.6	686.8	664.9	654.4
37.5°	707.8	686.0	651.4	625.8	615.3
40°	674.7	652.2	616.1	587.5	578.4
42.5°	640.1	616.8	579.2	552.1	537.8
45°	604.8	583.0	541.6	511.5	500.2
47.5°	567.9	545.3	504.0	473.1	460.3
50°	533.3	508.5	465.6	434.0	422.7
52.5°	495.7	470.1	430.3	395.7	384.4
55°	458.8	434.8	392.7	358.8	346.8
57.5°	421.2	395.7	355.0	321.9	311.4
60°	385.1	358.8	318.2	285.1	273.8
62.5°	346.8	321.9	280.6	250.5	239.2
65°	310.7	285.1	245.2	215.1	203.8
67.5°	274.6	249.0	210.6	182.0	173.0
70°	237.7	212.1	174.5	151.2	142.2
72.5°	201.6	176.8	142.2	121.1	115.8
75°	165.5	142.9	111.3	94.8	89.5
77.5°	128.6	110.6	84.2	71.5	66.9
80°	97.8	79.7	58.7	51.9	50.4
82.5°	67.7	51.9	39.1	36.9	36.1
85°	41.4	27.8	24.1	23.3	22.6
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.8	6.8	12.2	16.0	18.2
92.5°	14.4	7.6	12.2	16.0	16.7
95°	43.3	41.0	12.2	16.0	16.0
97.5°	81.3	85.8	13.7	15.2	16.0
100°	126.8	129.1	132.2	19.0	16.0
102.5°	173.2	176.2	177.7	179.3	115.5
105°	223.3	226.3	226.3	226.3	225.6
107.5°	275.0	275.0	276.5	277.2	274.2
110°	325.1	325.1	326.6	324.3	325.1

TEST NUMBER: P1027252

CATALOG NUMBER: S125RDIP-B610D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.2	374.5	375.2	372.2	370.7
115°	419.3	423.1	423.8	420.8	416.2
117.5°	468.6	468.6	471.7	467.1	465.6
120°	514.2	513.5	515.7	514.2	510.4
122.5°	554.5	558.3	559.0	557.5	553.0
125°	596.3	601.6	601.6	598.5	596.3
127.5°	636.5	640.3	639.5	638.0	632.0
130°	673.0	676.8	677.5	675.2	671.4
132.5°	709.4	714.0	711.7	711.7	707.9
135°	743.6	748.2	746.6	745.1	740.6
137.5°	775.5	780.1	778.5	778.5	774.7
140°	806.6	808.2	807.4	808.9	804.4
142.5°	834.8	835.5	837.0	837.0	832.5
145°	862.1	863.6	863.6	864.4	859.8
147.5°	886.4	886.4	887.2	887.9	882.6
150°	909.2	907.7	909.2	910.7	904.6
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)