

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027259

Luminaire Tested: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027259
REPORT IS A COMBINATION OF REPORTS P1005730 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7301.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027259

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027259

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	33	32
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8781	8781	8781
5°	8782	8562	8576
10°	8697	8347	8273
15°	8573	8044	7874
20°	8421	7681	7456
25°	8246	7326	7008
30°	8033	6936	6537
35°	7814	6540	6038
40°	7606	6133	5549
45°	7357	5694	5038
50°	7104	5227	4517
55°	6810	4768	3978
60°	6510	4244	3419
65°	6151	3656	2815
70°	5734	2976	2215
75°	5156	2238	1615
80°	4350	1449	1089
85°	3253	778	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7357 cd/sqm

TEST NUMBER: P1027259

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.8
10°-20°	360.5	4.9
20°-30°	522.7	7.2
30°-40°	595.5	8.2
40°-50°	580.4	7.9
50°-60°	488.5	6.7
60°-70°	342.3	4.7
70°-80°	175.5	2.4
80°-90°	45.7	0.6
90°-100°	44.9	0.6
100°-110°	298.4	4.1
110°-120°	537.3	7.4
120°-130°	689.7	9.4
130°-140°	741.8	10.2
140°-150°	696.2	9.5
150°-160°	563.1	7.7
160°-170°	364.2	5.0
170°-180°	125.6	1.7
0°-30°	1012.1	13.9
0°-40°	1607.6	22.0
0°-60°	2676.5	36.7
0°-90°	3239.9	44.4
90°-120°	880.5	12.1
90°-150°	3008.1	41.2
90°-180°	4061.0	55.6
0°-180°	7301.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1370	1370	1370	1370	1370	
5°	1368	1364	1353	1363	1361	130
15°	1301	1295	1273	1272	1263	367
25°	1180	1164	1126	1113	1101	543
35°	1016	992	945	915	901	637
45°	832	802	745	704	688	642
55°	631	598	540	494	477	565
65°	428	392	337	296	280	423
75°	228	197	153	130	123	241
85°	57	38	33	32	31	62
90°	1	9	16	21	24	6
95°	56	53	16	21	21	68
105°	288	292	292	292	291	305
115°	541	546	547	543	537	536
125°	769	776	776	772	769	687
135°	959	965	963	961	956	740
145°	1112	1114	1114	1115	1109	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1027259

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1370.5	1370.5	1370.5	1370.5	1370.5
2.5°	1373.6	1370.5	1360.1	1370.5	1369.5
5°	1368.4	1364.3	1352.9	1363.3	1361.2
7.5°	1358.1	1353.9	1340.5	1348.8	1346.7
10°	1342.6	1339.4	1325.0	1328.1	1325.0
12.5°	1325.0	1320.8	1300.1	1302.2	1297.0
15°	1301.1	1294.9	1273.2	1272.2	1262.8
17.5°	1276.3	1267.0	1241.1	1235.9	1228.7
20°	1246.3	1235.9	1202.8	1197.6	1188.3
22.5°	1213.2	1202.8	1167.6	1156.2	1149.0
25°	1180.0	1164.5	1126.2	1112.8	1101.4
27.5°	1142.8	1124.1	1083.8	1066.2	1054.8
30°	1101.4	1081.7	1038.2	1014.4	1005.1
32.5°	1061.0	1037.2	992.7	965.8	953.3
35°	1016.5	991.6	945.1	915.0	900.6
37.5°	974.0	944.0	896.4	861.2	846.7
40°	928.5	897.4	847.8	808.4	796.0
42.5°	880.9	848.8	797.0	759.8	740.1
45°	832.2	802.2	745.3	703.9	688.4
47.5°	781.5	750.5	693.5	651.1	633.5
50°	733.9	699.7	640.7	597.3	581.7
52.5°	682.1	646.9	592.1	544.5	528.9
55°	631.4	598.3	540.3	493.8	477.2
57.5°	579.7	544.5	488.6	443.0	428.5
60°	530.0	493.8	437.9	392.3	376.8
62.5°	477.2	443.0	386.1	344.7	329.2
65°	427.5	392.3	337.4	296.0	280.5
67.5°	377.8	342.6	289.8	250.5	238.1
70°	327.1	291.9	240.1	208.1	195.6
72.5°	277.4	243.3	195.6	166.7	159.4
75°	227.7	196.7	153.2	130.4	123.2
77.5°	177.0	152.2	115.9	98.3	92.1
80°	134.6	109.7	80.7	71.4	69.4
82.5°	93.2	71.4	53.8	50.7	49.7
85°	56.9	38.3	33.1	32.1	31.1
87.5°	23.8	16.6	15.5	15.5	14.5
90°	1.0	8.8	15.7	20.6	23.5
92.5°	18.6	9.8	15.7	20.6	21.6
95°	55.9	52.9	15.7	20.6	20.6
97.5°	104.9	110.7	17.6	19.6	20.6
100°	163.7	166.6	170.5	24.5	20.6
102.5°	223.4	227.4	229.3	231.3	149.0
105°	288.1	292.0	292.0	292.0	291.1
107.5°	354.8	354.8	356.7	357.7	353.8
110°	419.4	419.4	421.4	418.5	419.4

TEST NUMBER: P1027259

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	480.2	483.1	484.1	480.2	478.2
115°	541.0	545.9	546.8	542.9	537.0
117.5°	604.7	604.7	608.6	602.7	600.8
120°	663.5	662.5	665.4	663.5	658.6
122.5°	715.4	720.3	721.3	719.3	713.5
125°	769.3	776.2	776.2	772.3	769.3
127.5°	821.3	826.2	825.2	823.2	815.4
130°	868.3	873.2	874.2	871.2	866.3
132.5°	915.3	921.2	918.3	918.3	913.4
135°	959.4	965.3	963.4	961.4	955.5
137.5°	1000.6	1006.5	1004.5	1004.5	999.6
140°	1040.8	1042.7	1041.8	1043.7	1037.8
142.5°	1077.0	1078.0	1080.0	1080.0	1074.1
145°	1112.3	1114.3	1114.3	1115.3	1109.4
147.5°	1143.7	1143.7	1144.7	1145.6	1138.8
150°	1173.1	1171.1	1173.1	1175.0	1167.2
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)