

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027509

Luminaire Tested: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027509
REPORT IS A COMBINATION OF REPORTS P1001499 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D850UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7186.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027509

CATALOG NUMBER: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027509

CATALOG NUMBER: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10915	10915	10915
5°	10916	10662	10682
10°	10825	10417	10384
15°	10683	10125	10034
20°	10491	9786	9632
25°	10285	9416	9202
30°	10036	9031	8749
35°	9769	8627	8241
40°	9495	8200	7789
45°	9198	7784	7309
50°	8871	7313	6750
55°	8547	6792	6235
60°	8162	6243	5637
65°	7700	5608	5018
70°	7229	4878	4305
75°	6440	4017	3480
80°	5487	3000	2560
85°	4237	1775	1410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9198 cd/sqm

TEST NUMBER: P1027509

CATALOG NUMBER: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.2
10°-20°	454.1	6.3
20°-30°	670.4	9.3
30°-40°	782.1	10.9
40°-50°	785.5	10.9
50°-60°	689.5	9.6
60°-70°	513.6	7.1
70°-80°	293.3	4.1
80°-90°	86.2	1.2
90°-100°	65.5	0.9
100°-110°	194.7	2.7
110°-120°	330.2	4.6
120°-130°	434.7	6.0
130°-140°	487.1	6.8
140°-150°	477.4	6.6
150°-160°	401.0	5.6
160°-170°	266.6	3.7
170°-180°	93.3	1.3
0°-30°	1285.2	17.9
0°-40°	2067.3	28.8
0°-60°	3542.4	49.3
0°-90°	4435.5	61.7
90°-120°	590.4	8.2
90°-150°	1989.6	27.7
90°-180°	2750.0	38.3
0°-180°	7186.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1701	1698	1685	1697	1696	161
15°	1621	1617	1602	1609	1609	457
25°	1472	1465	1448	1450	1446	677
35°	1271	1266	1247	1240	1229	795
45°	1040	1035	1019	1003	999	802
55°	792	788	770	757	748	707
65°	535	532	518	505	500	531
75°	284	282	275	271	266	303
85°	74	76	76	74	71	81
90°	1	7	12	16	18	8
95°	50	51	59	64	66	52
105°	175	179	183	188	190	186
115°	330	334	335	334	334	327
125°	482	487	488	486	486	432
135°	627	632	633	633	630	484
145°	760	763	765	765	763	475
155°	870	870	870	874	870	401
165°	946	944	945	948	943	267
175°	983	980	980	985	979	93
180°	986	986	986	986	986	

TEST NUMBER: P1027509

CATALOG NUMBER: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1703.6	1703.6	1703.6	1703.6	1703.6
2.5°	1709.0	1704.9	1691.5	1704.9	1703.6
5°	1700.9	1698.2	1684.7	1696.8	1695.5
7.5°	1688.8	1686.1	1671.2	1683.4	1682.0
10°	1671.2	1668.5	1653.7	1664.5	1663.1
12.5°	1649.7	1644.3	1630.8	1638.9	1638.9
15°	1621.4	1617.3	1602.5	1609.2	1609.2
17.5°	1591.7	1585.0	1570.2	1578.2	1571.5
20°	1552.6	1549.9	1532.4	1541.8	1535.1
22.5°	1513.5	1508.2	1492.0	1497.4	1493.3
25°	1471.8	1465.0	1447.5	1450.2	1446.2
27.5°	1423.2	1419.2	1401.7	1403.0	1399.0
30°	1376.1	1372.0	1351.8	1349.1	1345.1
32.5°	1324.9	1318.1	1300.6	1295.2	1287.1
35°	1270.9	1265.6	1246.7	1239.9	1229.2
37.5°	1215.7	1208.9	1191.4	1182.0	1175.3
40°	1159.1	1152.3	1133.5	1121.3	1117.3
42.5°	1098.4	1093.0	1074.2	1063.4	1056.7
45°	1040.5	1035.1	1018.9	1002.7	998.7
47.5°	977.1	978.5	958.3	942.1	932.7
50°	916.5	912.4	896.3	878.7	869.3
52.5°	854.5	851.8	834.3	819.4	808.7
55°	792.5	788.4	769.6	757.4	748.0
57.5°	726.4	725.1	708.9	692.8	688.7
60°	664.5	659.1	644.2	630.8	621.3
62.5°	599.8	595.7	583.6	568.8	562.0
65°	535.1	532.4	517.5	505.4	500.0
67.5°	471.7	466.3	455.5	444.8	442.1
70°	412.4	405.7	393.5	385.5	380.1
72.5°	347.7	343.7	336.9	327.5	322.1
75°	284.4	281.7	274.9	270.9	265.5
77.5°	225.1	223.7	219.7	217.0	212.9
80°	169.8	169.8	167.1	165.8	163.1
82.5°	121.3	118.6	118.6	115.9	115.9
85°	74.1	75.5	75.5	74.1	71.4
87.5°	36.4	36.4	35.0	35.0	32.3
90°	0.8	6.9	12.3	16.1	18.4
92.5°	23.0	26.8	33.7	39.1	40.6
95°	49.9	51.4	59.1	64.4	66.0
97.5°	76.7	77.5	88.2	92.8	93.6
100°	107.4	107.4	117.3	124.2	125.8
102.5°	140.3	144.2	148.0	155.7	158.0
105°	174.9	178.7	183.3	187.9	190.2
107.5°	212.4	216.3	220.1	222.4	222.4
110°	251.6	255.4	257.7	260.0	259.2



TEST NUMBER: P1027509

CATALOG NUMBER: S125DIP-B1090D850UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.4	293.0	296.0	296.8	295.3
115°	330.5	333.6	335.1	334.4	333.6
117.5°	370.4	371.2	372.7	373.5	370.4
120°	407.2	411.1	411.8	411.8	408.8
122.5°	447.1	447.9	450.2	449.4	447.1
125°	482.4	487.0	487.8	486.2	485.5
127.5°	521.5	523.8	524.6	523.8	522.3
130°	556.0	559.9	561.4	560.6	559.1
132.5°	590.5	597.4	596.7	595.9	593.6
135°	627.3	632.0	632.7	632.7	629.6
137.5°	661.9	666.5	668.0	668.8	664.9
140°	694.8	698.7	701.0	702.5	698.7
142.5°	727.8	730.9	734.0	734.7	730.9
145°	760.0	763.1	765.4	765.4	763.1
147.5°	789.9	792.2	793.8	796.1	789.9
150°	819.8	819.1	822.1	822.1	820.6
152.5°	844.4	845.9	846.7	849.0	845.9
155°	869.7	869.7	870.5	873.5	869.7
157.5°	892.7	891.2	891.9	895.0	889.6
160°	912.6	910.3	911.1	914.2	910.3
162.5°	930.3	928.8	928.8	932.6	928.0
165°	945.6	944.1	944.9	947.9	943.3
167.5°	959.4	956.4	956.4	961.0	956.4
170°	970.2	967.1	967.1	971.7	966.3
172.5°	977.8	974.8	974.8	979.4	974.8
175°	983.2	980.1	980.1	984.7	979.4
177.5°	987.0	984.0	983.2	987.8	982.4
180°	985.5	985.5	985.5	985.5	985.5

(END OF REPORT)