

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027272

Luminaire Tested: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027272
REPORT IS A COMBINATION OF REPORTS P1005773 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8035.1 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027272

CATALOG NUMBER: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027272

CATALOG NUMBER: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47			40
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40			34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34			29
3	80	71	63	58	72	65	58	54	53	49	45	43	40	37	33	31	29			25
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25			21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22			19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20			17
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	20	17			15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16			13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14			12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8805	8805	8805
5°	8806	8586	8600
10°	8720	8369	8296
15°	8597	8066	7896
20°	8444	7703	7477
25°	8269	7346	7027
30°	8054	6955	6556
35°	7835	6558	6054
40°	7628	6150	5564
45°	7377	5710	5052
50°	7123	5242	4530
55°	6829	4782	3989
60°	6528	4255	3428
65°	6169	3667	2823
70°	5750	2985	2222
75°	5172	2244	1619
80°	4359	1454	1091
85°	3265	781	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7377 cd/sqm

TEST NUMBER: P1027272

CATALOG NUMBER: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	1.6
10°-20°	361.5	4.5
20°-30°	524.1	6.5
30°-40°	597.1	7.4
40°-50°	582.0	7.2
50°-60°	489.8	6.1
60°-70°	343.3	4.3
70°-80°	176.0	2.2
80°-90°	46.2	0.6
90°-100°	52.9	0.7
100°-110°	351.6	4.4
110°-120°	633.2	7.9
120°-130°	812.7	10.1
130°-140°	874.1	10.9
140°-150°	820.4	10.2
150°-160°	663.6	8.3
160°-170°	429.2	5.3
170°-180°	148.0	1.8
0°-30°	1014.9	12.6
0°-40°	1612.1	20.1
0°-60°	2683.9	33.4
0°-90°	3249.3	40.4
90°-120°	1037.7	12.9
90°-150°	3544.9	44.1
90°-180°	4786.0	59.6
0°-180°	8035.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1372	1368	1357	1367	1365	130
15°	1305	1298	1277	1276	1266	368
25°	1183	1168	1129	1116	1104	545
35°	1019	994	948	918	903	638
45°	834	804	747	706	690	644
55°	633	600	542	495	478	566
65°	429	393	338	297	281	425
75°	228	197	154	131	124	241
85°	57	38	33	32	31	63
90°	1	10	18	24	28	7
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1027272

CATALOG NUMBER: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.3	1374.3	1374.3	1374.3	1374.3
2.5°	1377.4	1374.3	1363.9	1374.3	1373.3
5°	1372.2	1368.1	1356.7	1367.0	1365.0
7.5°	1361.9	1357.7	1344.2	1352.5	1350.4
10°	1346.3	1343.2	1328.6	1331.7	1328.6
12.5°	1328.6	1324.5	1303.7	1305.8	1300.6
15°	1304.8	1298.5	1276.7	1275.7	1266.4
17.5°	1279.8	1270.5	1244.6	1239.4	1232.1
20°	1249.7	1239.4	1206.2	1201.0	1191.6
22.5°	1216.5	1206.2	1170.9	1159.4	1152.2
25°	1183.3	1167.7	1129.3	1115.8	1104.4
27.5°	1145.9	1127.3	1086.8	1069.1	1057.7
30°	1104.4	1084.7	1041.1	1017.2	1007.9
32.5°	1063.9	1040.1	995.4	968.5	956.0
35°	1019.3	994.4	947.7	917.6	903.1
37.5°	976.8	946.7	898.9	863.6	849.1
40°	931.1	899.9	850.1	810.7	798.2
42.5°	883.3	851.2	799.3	761.9	742.2
45°	834.5	804.4	747.4	705.8	690.3
47.5°	783.7	752.5	695.5	652.9	635.3
50°	735.9	701.7	642.5	598.9	583.4
52.5°	684.0	648.7	593.7	546.0	530.4
55°	633.2	600.0	541.8	495.1	478.5
57.5°	581.3	546.0	489.9	444.3	429.7
60°	531.5	495.1	439.1	393.4	377.8
62.5°	478.5	444.3	387.2	345.7	330.1
65°	428.7	393.4	338.4	296.9	281.3
67.5°	378.9	343.6	290.6	251.2	238.7
70°	328.0	292.7	240.8	208.6	196.2
72.5°	278.2	243.9	196.2	167.1	159.9
75°	228.4	197.2	153.6	130.8	123.5
77.5°	177.5	152.6	116.3	98.6	92.4
80°	134.9	110.0	81.0	71.6	69.5
82.5°	93.4	71.6	54.0	50.9	49.8
85°	57.1	38.4	33.2	32.2	31.1
87.5°	23.9	16.6	15.6	15.6	14.5
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1027272

CATALOG NUMBER: S125RDIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)