

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027281

Luminaire Tested: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027281
REPORT IS A COMBINATION OF REPORTS P1005812 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4761.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027281

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027281

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69		
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59		
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	56	53	50		
3	85	76	68	63	80	72	65	60	65	59	55	58	54	50	52	48	46	42		
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	43	40	37		
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32		
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28		
7	62	49	41	35	58	47	40	34	43	36	32	39	33	30	35	31	27	25		
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22	20		
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	28	23	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8895	8895	8895
5°	8896	8673	8687
10°	8809	8454	8380
15°	8684	8149	7976
20°	8530	7781	7553
25°	8353	7421	7099
30°	8137	7026	6622
35°	7915	6625	6115
40°	7705	6213	5621
45°	7452	5768	5103
50°	7196	5296	4576
55°	6898	4830	4030
60°	6594	4298	3463
65°	6230	3704	2852
70°	5807	3016	2245
75°	5224	2268	1636
80°	4405	1469	1104
85°	3299	790	622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7452 cd/sqm

TEST NUMBER: P1027281

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	2.7
10°-20°	365.1	7.7
20°-30°	529.4	11.1
30°-40°	603.2	12.7
40°-50°	587.9	12.3
50°-60°	494.8	10.4
60°-70°	346.7	7.3
70°-80°	177.7	3.7
80°-90°	45.0	0.9
90°-100°	16.4	0.3
100°-110°	108.8	2.3
110°-120°	195.8	4.1
120°-130°	251.4	5.3
130°-140°	270.4	5.7
140°-150°	253.8	5.3
150°-160°	205.3	4.3
160°-170°	132.7	2.8
170°-180°	45.8	1.0
0°-30°	1025.3	21.5
0°-40°	1628.5	34.2
0°-60°	2711.2	56.9
0°-90°	3280.7	68.9
90°-120°	321.0	6.7
90°-150°	1096.5	23.0
90°-180°	1480.0	31.1
0°-180°	4761.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1370	1381	1379	131
15°	1318	1312	1290	1289	1279	372
25°	1195	1180	1141	1127	1116	550
35°	1030	1004	957	927	912	645
45°	843	813	755	713	697	650
55°	640	606	547	500	483	572
65°	433	397	342	300	284	429
75°	231	199	155	132	125	244
85°	58	39	34	32	32	63
90°	0	3	6	8	9	4
95°	20	19	6	8	8	25
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	282	280	251
135°	350	352	351	350	348	270
145°	406	406	406	406	404	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1027281

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1391.4	1388.3	1377.8	1388.3	1387.2
5°	1386.2	1382.0	1370.4	1380.9	1378.8
7.5°	1375.7	1371.5	1357.9	1366.3	1364.2
10°	1360.0	1356.8	1342.1	1345.3	1342.1
12.5°	1342.1	1337.9	1317.0	1319.1	1313.8
15°	1318.0	1311.7	1289.7	1288.7	1279.2
17.5°	1292.9	1283.4	1257.2	1252.0	1244.6
20°	1262.4	1252.0	1218.4	1213.2	1203.7
22.5°	1228.9	1218.4	1182.8	1171.2	1163.9
25°	1195.3	1179.6	1140.8	1127.2	1115.7
27.5°	1157.6	1138.7	1097.8	1080.0	1068.5
30°	1115.7	1095.7	1051.7	1027.6	1018.1
32.5°	1074.8	1050.6	1005.6	978.3	965.7
35°	1029.7	1004.5	957.3	926.9	912.2
37.5°	986.7	956.3	908.0	872.4	857.7
40°	940.5	909.1	858.8	818.9	806.3
42.5°	892.3	859.8	807.4	769.6	749.7
45°	843.0	812.6	755.0	713.0	697.3
47.5°	791.7	760.2	702.5	659.5	641.7
50°	743.4	708.8	649.1	605.0	589.3
52.5°	691.0	655.3	599.8	551.5	535.8
55°	639.6	606.1	547.3	500.2	483.4
57.5°	587.2	551.5	494.9	448.8	434.1
60°	536.9	500.2	443.5	397.4	381.7
62.5°	483.4	448.8	391.1	349.2	333.4
65°	433.0	397.4	341.8	299.9	284.2
67.5°	382.7	347.1	293.6	253.7	241.2
70°	331.3	295.7	243.3	210.8	198.2
72.5°	281.0	246.4	198.2	168.8	161.5
75°	230.7	199.2	155.2	132.1	124.8
77.5°	179.3	154.1	117.4	99.6	93.3
80°	136.3	111.1	81.8	72.3	70.3
82.5°	94.4	72.3	54.5	51.4	50.3
85°	57.7	38.8	33.6	32.5	31.5
87.5°	24.1	16.8	15.7	15.7	14.7
90°	0.4	3.2	5.7	7.5	8.6
92.5°	6.8	3.6	5.7	7.5	7.9
95°	20.4	19.3	5.7	7.5	7.5
97.5°	38.2	40.4	6.4	7.1	7.5
100°	59.7	60.7	62.2	8.9	7.5
102.5°	81.4	82.9	83.6	84.3	54.3
105°	105.0	106.5	106.5	106.5	106.1
107.5°	129.3	129.3	130.0	130.4	129.0
110°	152.9	152.9	153.6	152.5	152.9



TEST NUMBER: P1027281

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	176.1	176.5	175.0	174.3
115°	197.2	199.0	199.3	197.9	195.8
117.5°	220.4	220.4	221.8	219.7	219.0
120°	241.8	241.5	242.6	241.8	240.1
122.5°	260.8	262.6	262.9	262.2	260.1
125°	280.4	282.9	282.9	281.5	280.4
127.5°	299.4	301.1	300.8	300.1	297.2
130°	316.5	318.3	318.6	317.6	315.8
132.5°	333.6	335.8	334.7	334.7	332.9
135°	349.7	351.9	351.2	350.4	348.3
137.5°	364.7	366.9	366.2	366.2	364.4
140°	379.4	380.1	379.7	380.4	378.3
142.5°	392.6	392.9	393.7	393.7	391.5
145°	405.5	406.2	406.2	406.5	404.4
147.5°	416.9	416.9	417.2	417.6	415.1
150°	427.6	426.9	427.6	428.3	425.5
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)