

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027289

Luminaire Tested: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027289
REPORT IS A COMBINATION OF REPORTS P1005850 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5587.9 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027289

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027289

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	57	55	54
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	45	42	39
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30
6	65	53	45	39	60	49	42	37	44	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	24
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8781	8781	8781
5°	8782	8562	8576
10°	8697	8347	8273
15°	8573	8044	7874
20°	8421	7681	7456
25°	8246	7326	7008
30°	8033	6936	6537
35°	7814	6540	6038
40°	7606	6133	5549
45°	7357	5694	5038
50°	7104	5227	4517
55°	6810	4768	3978
60°	6510	4244	3419
65°	6151	3656	2815
70°	5734	2976	2215
75°	5156	2238	1615
80°	4350	1449	1089
85°	3253	778	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7357 cd/sqm

TEST NUMBER: P1027289

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	2.3
10°-20°	360.5	6.5
20°-30°	522.7	9.4
30°-40°	595.5	10.7
40°-50°	580.4	10.4
50°-60°	488.5	8.7
60°-70°	342.3	6.1
70°-80°	175.5	3.1
80°-90°	44.9	0.8
90°-100°	26.0	0.5
100°-110°	172.6	3.1
110°-120°	310.8	5.6
120°-130°	398.9	7.1
130°-140°	429.0	7.7
140°-150°	402.7	7.2
150°-160°	325.7	5.8
160°-170°	210.6	3.8
170°-180°	72.6	1.3
0°-30°	1012.1	18.1
0°-40°	1607.6	28.8
0°-60°	2676.5	47.9
0°-90°	3239.1	58.0
90°-120°	509.3	9.1
90°-150°	1739.8	31.1
90°-180°	2349.0	42.0
0°-180°	5587.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1370	1370	1370	1370	1370	
5°	1368	1364	1353	1363	1361	130
15°	1301	1295	1273	1272	1263	367
25°	1180	1164	1126	1113	1101	543
35°	1016	992	945	915	901	637
45°	832	802	745	704	688	642
55°	631	598	540	494	477	565
65°	428	392	337	296	280	423
75°	228	197	153	130	123	241
85°	57	38	33	32	31	62
90°	1	5	9	12	14	5
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1027289

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1370.5	1370.5	1370.5	1370.5	1370.5
2.5°	1373.6	1370.5	1360.1	1370.5	1369.5
5°	1368.4	1364.3	1352.9	1363.3	1361.2
7.5°	1358.1	1353.9	1340.5	1348.8	1346.7
10°	1342.6	1339.4	1325.0	1328.1	1325.0
12.5°	1325.0	1320.8	1300.1	1302.2	1297.0
15°	1301.1	1294.9	1273.2	1272.2	1262.8
17.5°	1276.3	1267.0	1241.1	1235.9	1228.7
20°	1246.3	1235.9	1202.8	1197.6	1188.3
22.5°	1213.2	1202.8	1167.6	1156.2	1149.0
25°	1180.0	1164.5	1126.2	1112.8	1101.4
27.5°	1142.8	1124.1	1083.8	1066.2	1054.8
30°	1101.4	1081.7	1038.2	1014.4	1005.1
32.5°	1061.0	1037.2	992.7	965.8	953.3
35°	1016.5	991.6	945.1	915.0	900.6
37.5°	974.0	944.0	896.4	861.2	846.7
40°	928.5	897.4	847.8	808.4	796.0
42.5°	880.9	848.8	797.0	759.8	740.1
45°	832.2	802.2	745.3	703.9	688.4
47.5°	781.5	750.5	693.5	651.1	633.5
50°	733.9	699.7	640.7	597.3	581.7
52.5°	682.1	646.9	592.1	544.5	528.9
55°	631.4	598.3	540.3	493.8	477.2
57.5°	579.7	544.5	488.6	443.0	428.5
60°	530.0	493.8	437.9	392.3	376.8
62.5°	477.2	443.0	386.1	344.7	329.2
65°	427.5	392.3	337.4	296.0	280.5
67.5°	377.8	342.6	289.8	250.5	238.1
70°	327.1	291.9	240.1	208.1	195.6
72.5°	277.4	243.3	195.6	166.7	159.4
75°	227.7	196.7	153.2	130.4	123.2
77.5°	177.0	152.2	115.9	98.3	92.1
80°	134.6	109.7	80.7	71.4	69.4
82.5°	93.2	71.4	53.8	50.7	49.7
85°	56.9	38.3	33.1	32.1	31.1
87.5°	23.8	16.6	15.5	15.5	14.5
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6

TEST NUMBER: P1027289

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)