

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027305

Luminaire Tested: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027305
REPORT IS A COMBINATION OF REPORTS P1001220 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7938.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	39	36	33
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10041	10041	10041	10041
5°	10048	11390	10057	8641
10°	9987	12982	9969	7417
15°	9913	14076	9852	6702
20°	9789	15425	9699	6118
25°	9677	17674	9500	5773
30°	9517	18646	9353	5460
35°	9264	14946	9070	5208
40°	8870	10331	8740	4943
45°	8372	7691	8279	4722
50°	7802	6332	7674	4545
55°	7188	5400	7130	4391
60°	6585	4623	6470	4272
65°	5934	3991	5838	4099
70°	5246	3315	5176	3796
75°	4517	2563	4458	3295
80°	3568	1733	3438	2422
85°	2281	867	2207	1235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15336 cd/sqm

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	1.9
10°-20°	449.2	5.7
20°-30°	729.7	9.2
30°-40°	891.8	11.2
40°-50°	809.0	10.2
50°-60°	644.3	8.1
60°-70°	448.8	5.7
70°-80°	239.1	3.0
80°-90°	61.2	0.8
90°-100°	83.7	1.1
100°-110°	248.7	3.1
110°-120°	421.8	5.3
120°-130°	555.3	7.0
130°-140°	622.3	7.8
140°-150°	610.0	7.7
150°-160°	512.4	6.5
160°-170°	340.6	4.3
170°-180°	119.2	1.5
0°-30°	1329.8	16.8
0°-40°	2221.6	28.0
0°-60°	3674.9	46.3
0°-90°	4424.0	55.7
90°-120°	754.3	9.5
90°-150°	2541.9	32.0
90°-180°	3514.0	44.3
0°-180°	7938.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1567	1567	1567	1567	1567	
5°	1566	1808	1567	1372	1566	149
15°	1504	2258	1495	1075	1504	425
25°	1385	2778	1360	907	1385	638
35°	1205	2230	1180	777	1205	753
45°	947	1051	936	645	947	730
55°	666	648	661	527	666	596
65°	412	398	406	408	412	409
75°	200	196	197	251	200	212
85°	40	44	39	62	40	48
90°	1	24	1	24	1	7
95°	64	84	64	84	64	67
105°	223	243	223	243	223	238
115°	422	426	422	426	422	418
125°	616	620	616	620	616	552
135°	802	804	802	804	802	618
145°	971	975	971	975	971	607
155°	1111	1111	1111	1111	1111	512
165°	1208	1205	1208	1205	1208	341
175°	1256	1251	1256	1251	1256	119
180°	1259	1259	1259	1259	1259	

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1569.7	1579.0	1589.7	1597.7	1611.0	1614.9	1621.6	1625.6	1629.6	1633.6	1636.2
5°	1565.7	1588.3	1608.3	1622.9	1648.2	1657.5	1669.5	1684.1	1701.4	1716.0	1725.4
7.5°	1555.1	1591.0	1617.6	1646.9	1681.5	1704.1	1716.0	1746.6	1774.6	1795.9	1823.8
10°	1541.8	1584.3	1625.6	1669.5	1718.7	1744.0	1767.9	1810.5	1849.1	1883.7	1911.6
12.5°	1527.1	1579.0	1628.2	1685.4	1752.0	1782.6	1798.5	1871.7	1919.6	1938.2	1992.7
15°	1504.5	1565.7	1636.2	1706.7	1762.6	1798.5	1842.4	1901.0	1948.8	1990.1	2034.0
17.5°	1483.2	1549.8	1621.6	1700.1	1781.2	1827.8	1861.0	1912.9	1964.8	2018.0	2059.3
20°	1448.7	1535.1	1608.3	1692.1	1787.9	1821.1	1855.7	1916.9	1972.8	2030.0	2081.9
22.5°	1420.7	1503.2	1603.0	1682.8	1763.9	1797.2	1839.8	1903.6	1970.1	2035.3	2111.1
25°	1384.8	1476.6	1563.1	1648.2	1732.0	1767.9	1806.5	1889.0	1958.2	2042.0	2125.8
27.5°	1346.2	1440.7	1527.1	1604.3	1682.8	1732.0	1773.2	1859.7	1951.5	2043.3	2152.4
30°	1305.0	1394.1	1476.6	1552.4	1638.9	1689.4	1730.7	1831.8	1934.2	2051.3	2181.6
32.5°	1261.1	1344.9	1415.4	1492.6	1584.3	1630.9	1686.8	1797.2	1918.2	2057.9	2221.5
35°	1205.2	1285.0	1347.6	1426.0	1517.8	1577.7	1636.2	1759.9	1901.0	2056.6	2244.2
37.5°	1149.4	1211.9	1271.7	1355.5	1462.0	1516.5	1577.7	1713.4	1874.3	2052.6	2253.5
40°	1082.8	1144.0	1195.9	1281.0	1392.8	1455.3	1519.2	1661.5	1843.7	2038.0	2220.2
42.5°	1016.3	1068.2	1125.4	1214.5	1322.3	1388.8	1456.6	1614.9	1803.8	1995.4	2128.4
45°	947.1	987.1	1049.6	1130.7	1245.1	1309.0	1386.1	1557.7	1748.0	1918.2	1984.8
47.5°	875.3	915.2	973.8	1052.2	1165.3	1241.1	1314.3	1485.9	1677.5	1809.2	1809.2
50°	806.1	838.1	895.3	973.8	1088.2	1157.3	1231.8	1414.1	1568.4	1665.5	1579.0
52.5°	731.6	767.6	815.5	897.9	1011.0	1073.5	1154.7	1310.3	1456.6	1496.6	1363.5
55°	666.5	695.7	741.0	819.4	924.5	989.7	1058.9	1207.9	1331.6	1328.9	1186.6
57.5°	598.6	622.6	670.5	742.3	839.4	897.9	967.1	1096.1	1197.2	1161.3	1027.0
60°	536.1	553.4	600.0	658.5	751.6	806.1	872.7	977.7	1054.9	1004.4	868.7
62.5°	470.9	490.9	528.1	585.3	667.8	711.7	760.9	867.3	916.6	871.3	733.0
65°	412.4	428.3	461.6	509.5	584.0	623.9	666.5	754.3	800.8	735.6	621.2
67.5°	353.9	372.5	396.4	439.0	497.5	534.8	572.0	647.8	669.1	610.6	514.8
70°	299.3	315.3	337.9	368.5	417.7	451.0	478.9	541.4	556.1	501.5	425.7
72.5°	246.1	256.7	275.4	300.6	345.9	364.5	393.8	436.3	455.0	405.7	351.2
75°	199.5	207.5	219.5	238.1	268.7	288.7	312.6	352.5	351.2	316.6	278.0
77.5°	154.3	155.6	168.9	186.2	204.9	222.2	234.1	262.1	264.7	243.4	211.5
80°	110.4	114.4	119.7	133.0	149.0	155.6	170.3	187.6	190.2	174.3	153.0
82.5°	70.5	73.2	77.2	85.1	95.8	103.8	111.7	118.4	125.0	115.7	98.4
85°	39.9	41.2	45.2	47.9	53.2	57.2	63.9	70.5	69.2	62.5	57.2
87.5°	20.0	20.0	20.0	22.6	25.3	25.3	27.9	29.3	30.6	27.9	25.3
90°	1.0	2.7	4.5	6.2	7.9	8.8	9.6	11.1	12.6	14.2	15.7
92.5°	29.4	30.5	31.6	32.7	33.8	34.3	35.3	37.2	39.2	41.1	43.1
95°	63.7	64.1	64.5	65.0	65.4	65.6	66.7	68.9	71.0	73.2	75.4
97.5°	98.0	98.2	98.4	98.7	98.9	99.0	100.5	103.6	106.6	109.7	112.7
100°	137.2	137.2	137.2	137.2	137.2	137.2	138.6	141.4	144.3	147.1	149.9
102.5°	179.3	180.4	181.5	182.6	183.7	184.2	184.7	185.8	186.9	188.0	189.1
105°	223.4	224.5	225.6	226.7	227.8	228.3	229.0	230.3	231.6	232.9	234.2
107.5°	271.4	272.5	273.6	274.7	275.8	276.3	276.8	277.9	279.0	280.1	281.2
110°	321.4	322.5	323.6	324.7	325.8	326.3	326.6	327.3	327.9	328.6	329.2

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	372.3	372.7	373.2	373.6	374.1	374.3	374.7	375.6	376.5	377.3	378.2
115°	422.3	423.2	424.0	424.9	425.8	426.2	426.4	426.9	427.3	427.8	428.2
117.5°	473.3	473.5	473.7	473.9	474.1	474.2	474.4	474.9	475.3	475.8	476.2
120°	520.3	521.4	522.5	523.6	524.7	525.2	525.3	525.5	525.8	526.0	526.2
122.5°	571.2	571.4	571.6	571.9	572.1	572.2	572.5	573.2	573.9	574.5	575.2
125°	616.3	617.6	618.9	620.2	621.5	622.2	622.3	622.5	622.8	623.0	623.2
127.5°	666.3	666.9	667.6	668.2	668.9	669.2	669.3	669.5	669.8	670.0	670.2
130°	710.4	711.5	712.6	713.7	714.8	715.3	715.5	715.9	716.4	716.8	717.2
132.5°	754.5	756.5	758.4	760.4	762.3	763.3	763.2	763.0	762.7	762.5	762.3
135°	801.5	802.8	804.1	805.4	806.7	807.4	807.5	807.7	808.0	808.2	808.4
137.5°	845.6	846.9	848.2	849.5	850.8	851.5	851.7	852.1	852.6	853.0	853.4
140°	887.7	888.8	889.9	891.0	892.1	892.6	892.9	893.6	894.3	894.9	895.6
142.5°	929.9	930.8	931.6	932.5	933.4	933.8	934.2	935.1	936.0	936.8	937.7
145°	971.0	971.9	972.7	973.6	974.5	974.9	975.2	975.9	976.6	977.2	977.9
147.5°	1009.2	1009.9	1010.5	1011.2	1011.9	1012.2	1012.4	1012.8	1013.3	1013.7	1014.1
150°	1047.5	1047.3	1047.1	1046.8	1046.6	1046.5	1046.9	1047.8	1048.7	1049.5	1050.4
152.5°	1078.8	1079.2	1079.7	1080.1	1080.6	1080.8	1080.9	1081.1	1081.3	1081.5	1081.7
155°	1111.1	1111.1	1111.1	1111.1	1111.1	1111.1	1111.2	1111.4	1111.7	1111.9	1112.1
157.5°	1140.5	1140.1	1139.7	1139.2	1138.8	1138.6	1138.7	1138.9	1139.2	1139.4	1139.6
160°	1166.0	1165.4	1164.7	1164.1	1163.4	1163.1	1163.2	1163.4	1163.7	1163.9	1164.1
162.5°	1188.5	1188.1	1187.7	1187.2	1186.8	1186.6	1186.6	1186.6	1186.6	1186.6	1186.6
165°	1208.1	1207.7	1207.3	1206.8	1206.4	1206.2	1206.3	1206.5	1206.8	1207.0	1207.2
167.5°	1225.8	1224.9	1224.1	1223.2	1222.3	1221.9	1221.9	1221.9	1221.9	1221.9	1221.9
170°	1239.5	1238.6	1237.8	1236.9	1236.0	1235.6	1235.6	1235.6	1235.6	1235.6	1235.6
172.5°	1249.3	1248.4	1247.6	1246.7	1245.8	1245.4	1245.4	1245.4	1245.4	1245.4	1245.4
175°	1256.2	1255.3	1254.4	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1252.2
177.5°	1261.1	1260.2	1259.3	1258.4	1257.5	1257.1	1257.0	1256.8	1256.6	1256.4	1256.2
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1638.9	1648.2	1656.2	1662.8	1668.2	1676.1	1670.8	1672.1	1674.8	1680.1	1680.1
5°	1745.3	1759.9	1767.9	1794.5	1801.2	1799.9	1795.9	1817.1	1815.8	1807.8	1806.5
7.5°	1849.1	1874.3	1897.0	1918.2	1924.9	1942.2	1946.2	1955.5	1952.8	1966.1	1959.5
10°	1943.5	1983.4	2004.7	2036.6	2044.6	2052.6	2063.2	2068.6	2080.5	2079.2	2079.2
12.5°	2016.7	2064.6	2092.5	2100.5	2131.1	2140.4	2149.7	2167.0	2163.0	2164.3	2172.3
15°	2073.9	2120.4	2144.4	2181.6	2202.9	2213.6	2229.5	2248.2	2245.5	2257.5	2254.8
17.5°	2116.5	2160.4	2204.3	2260.1	2261.5	2289.4	2326.6	2334.6	2351.9	2339.9	2339.9
20°	2151.0	2209.6	2272.1	2343.9	2351.9	2369.2	2414.4	2445.0	2465.0	2458.3	2462.3
22.5°	2188.3	2272.1	2345.3	2417.1	2455.7	2486.3	2530.2	2578.1	2595.4	2606.0	2603.3
25°	2236.2	2324.0	2431.7	2531.5	2571.4	2629.9	2688.5	2735.0	2748.3	2777.6	2751.0
27.5°	2285.4	2409.1	2543.5	2660.5	2711.1	2759.0	2829.5	2864.1	2881.4	2894.7	2885.3
30°	2326.6	2496.9	2643.2	2751.0	2786.9	2814.8	2854.8	2862.7	2856.1	2866.7	2880.0
32.5°	2390.5	2556.8	2680.5	2732.4	2728.4	2727.0	2696.5	2653.9	2644.6	2619.3	2653.9
35°	2425.1	2558.1	2606.0	2536.8	2508.9	2458.3	2361.2	2297.4	2241.5	2229.5	2232.2
37.5°	2405.1	2457.0	2399.8	2217.6	2172.3	2095.2	1966.1	1875.7	1834.4	1802.5	1843.7
40°	2297.4	2240.2	2083.2	1861.0	1795.9	1722.7	1601.6	1552.4	1493.9	1481.9	1536.5
42.5°	2119.1	1944.8	1722.7	1551.1	1483.2	1442.0	1340.9	1294.3	1253.1	1234.5	1265.1
45°	1877.0	1665.5	1442.0	1301.0	1243.8	1194.6	1134.7	1085.5	1058.9	1050.9	1076.2
47.5°	1626.9	1403.4	1225.2	1120.1	1060.2	1023.0	967.1	939.2	917.9	920.5	924.5
50°	1387.5	1183.9	1046.9	941.8	912.6	883.3	846.0	822.1	811.5	815.5	812.8
52.5°	1181.3	1016.3	900.6	819.4	806.1	778.2	747.6	727.7	723.7	725.0	729.0
55°	1000.4	871.3	779.5	721.0	706.4	686.4	667.8	654.5	643.8	647.8	646.5
57.5°	863.3	750.3	679.8	631.9	621.2	609.3	592.0	585.3	581.3	573.3	580.0
60°	742.3	650.5	589.3	560.0	550.7	542.7	524.1	516.1	513.5	509.5	520.1
62.5°	627.9	562.7	516.1	489.5	480.2	472.2	462.9	456.3	457.6	452.3	457.6
65°	537.4	484.2	451.0	427.0	415.0	409.7	408.4	397.7	396.4	397.7	399.1
67.5°	453.6	408.4	383.1	368.5	359.2	353.9	349.9	343.2	348.5	344.5	347.2
70°	377.8	347.2	320.6	306.0	302.0	303.3	296.6	294.0	295.3	292.7	295.3
72.5°	304.6	279.4	268.7	258.1	252.8	251.4	247.4	243.4	247.4	246.1	246.1
75°	243.4	224.8	212.8	206.2	206.2	203.5	196.9	196.9	196.9	195.5	196.9
77.5°	187.6	171.6	166.3	159.6	159.6	155.6	154.3	154.3	151.7	155.6	153.0
80°	139.7	127.7	119.7	115.7	115.7	114.4	111.7	110.4	111.7	110.4	110.4
82.5°	90.5	85.1	81.1	77.2	75.8	77.2	75.8	73.2	74.5	73.2	75.8
85°	51.9	46.6	46.6	43.9	45.2	42.6	43.9	41.2	39.9	43.9	41.2
87.5°	22.6	21.3	21.3	18.6	18.6	18.6	17.3	18.6	17.3	16.0	17.3
90°	16.8	17.9	19.0	20.1	20.6	20.9	21.6	22.2	22.9	23.5	22.9
92.5°	44.6	46.2	47.7	49.2	50.0	50.2	50.6	51.1	51.5	51.9	51.5
95°	76.9	78.5	80.0	81.5	82.3	82.5	83.0	83.4	83.9	84.3	83.9
97.5°	114.0	115.3	116.6	117.9	118.6	118.7	118.9	119.1	119.3	119.5	119.3
100°	151.9	153.8	155.8	157.7	158.7	158.9	159.4	159.8	160.3	160.7	160.3
102.5°	191.3	193.5	195.6	197.8	198.9	199.2	199.9	200.5	201.2	201.8	201.2
105°	235.5	236.8	238.1	239.4	240.1	240.4	241.1	241.7	242.4	243.0	242.4
107.5°	281.9	282.5	283.2	283.9	284.2	284.2	284.2	284.2	284.2	284.2	284.2
110°	329.9	330.5	331.2	331.9	332.2	332.1	331.9	331.6	331.4	331.2	331.4

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	378.4	378.6	378.9	379.1	379.2	379.0	378.5	378.1	377.6	377.2	377.6
115°	428.0	427.8	427.5	427.3	427.2	427.1	426.9	426.6	426.4	426.2	426.4
117.5°	476.4	476.6	476.9	477.1	477.2	476.8	475.9	475.0	474.2	473.3	474.2
120°	526.2	526.2	526.2	526.2	526.2	525.8	524.9	524.0	523.2	522.3	523.2
122.5°	575.0	574.8	574.5	574.3	574.2	573.9	573.2	572.5	571.9	571.2	571.9
125°	622.8	622.3	621.9	621.4	621.2	621.1	620.9	620.6	620.4	620.2	620.4
127.5°	670.0	669.8	669.5	669.3	669.2	669.0	668.6	668.1	667.7	667.3	667.7
130°	717.0	716.8	716.6	716.4	716.3	716.1	715.6	715.2	714.7	714.3	714.7
132.5°	762.1	761.9	761.6	761.4	761.3	761.0	760.3	759.7	759.0	758.4	759.0
135°	808.4	808.4	808.4	808.4	808.4	808.0	807.1	806.2	805.4	804.5	805.4
137.5°	853.6	853.8	854.1	854.3	854.4	853.9	852.8	851.7	850.6	849.5	850.6
140°	896.0	896.4	896.9	897.3	897.5	897.0	895.9	894.8	893.7	892.6	893.7
142.5°	937.9	938.1	938.4	938.6	938.7	938.2	937.1	936.0	934.9	933.8	934.9
145°	977.9	977.9	977.9	977.9	977.9	977.6	976.9	976.2	975.6	974.9	975.6
147.5°	1014.8	1015.4	1016.1	1016.8	1017.1	1016.2	1014.5	1012.7	1011.0	1009.2	1011.0
150°	1050.4	1050.4	1050.4	1050.4	1050.4	1050.2	1049.7	1049.3	1048.8	1048.4	1048.8
152.5°	1082.4	1083.0	1083.7	1084.4	1084.7	1084.3	1083.4	1082.5	1081.7	1080.8	1081.7
155°	1113.0	1113.8	1114.7	1115.6	1116.0	1115.5	1114.4	1113.3	1112.2	1111.1	1112.2
157.5°	1140.5	1141.3	1142.2	1143.1	1143.5	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1
160°	1165.0	1165.8	1166.7	1167.6	1168.0	1167.5	1166.4	1165.3	1164.2	1163.1	1164.2
162.5°	1187.7	1188.8	1189.9	1191.0	1191.5	1190.8	1189.5	1188.2	1186.9	1185.6	1186.9
165°	1208.1	1208.9	1209.8	1210.7	1211.1	1210.4	1209.1	1207.8	1206.5	1205.2	1206.5
167.5°	1223.2	1224.5	1225.8	1227.1	1227.7	1227.1	1225.8	1224.5	1223.2	1221.9	1223.2
170°	1236.9	1238.2	1239.5	1240.8	1241.5	1240.7	1239.2	1237.7	1236.1	1234.6	1236.1
172.5°	1246.7	1248.0	1249.3	1250.6	1251.3	1250.6	1249.3	1248.0	1246.7	1245.4	1246.7
175°	1253.5	1254.8	1256.1	1257.4	1258.1	1257.3	1255.8	1254.3	1252.8	1251.3	1252.8
177.5°	1257.5	1258.8	1260.1	1261.4	1262.0	1261.2	1259.7	1258.2	1256.7	1255.2	1256.7
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1677.5	1668.2	1670.8	1668.2	1661.5	1657.5	1646.9	1633.6	1628.2	1621.6	1617.6
5°	1811.8	1805.2	1803.8	1793.2	1790.5	1774.6	1748.0	1734.7	1718.7	1702.7	1686.8
7.5°	1958.2	1950.2	1923.6	1919.6	1922.2	1902.3	1867.7	1841.1	1807.8	1785.2	1754.6
10°	2079.2	2063.2	2040.6	2042.0	2032.6	2006.0	1971.5	1943.5	1895.6	1866.4	1822.5
12.5°	2152.4	2139.1	2136.4	2123.1	2115.1	2080.5	2039.3	2003.4	1967.5	1927.6	1894.3
15°	2241.5	2224.2	2212.2	2193.6	2188.3	2152.4	2107.1	2065.9	2024.7	1987.4	1916.9
17.5°	2339.9	2321.3	2276.1	2272.1	2240.2	2205.6	2161.7	2100.5	2056.6	2003.4	1951.5
20°	2451.7	2425.1	2366.5	2351.9	2326.6	2269.4	2209.6	2141.7	2071.2	2016.7	1955.5
22.5°	2576.7	2530.2	2487.6	2441.0	2422.4	2351.9	2269.4	2187.0	2101.8	2027.3	1954.2
25°	2739.0	2677.8	2618.0	2571.4	2539.5	2447.7	2337.3	2228.2	2129.8	2032.6	1936.9
27.5°	2866.7	2813.5	2748.3	2687.1	2645.9	2536.8	2410.4	2269.4	2147.1	2028.7	1926.2
30°	2876.0	2860.1	2820.2	2786.9	2741.7	2624.6	2484.9	2325.3	2173.7	2030.0	1904.9
32.5°	2701.8	2733.7	2751.0	2756.3	2747.0	2679.2	2551.5	2375.9	2197.6	2018.0	1886.3
35°	2326.6	2411.8	2516.9	2556.8	2595.4	2631.3	2564.8	2411.8	2205.6	2015.4	1857.1
37.5°	1915.6	1992.7	2167.0	2246.8	2292.0	2434.4	2488.9	2406.5	2221.5	2018.0	1829.1
40°	1545.8	1668.2	1793.2	1901.0	1971.5	2131.1	2300.0	2318.7	2198.9	1992.7	1793.2
42.5°	1301.0	1372.8	1467.3	1567.1	1629.6	1818.5	2047.3	2181.6	2128.4	1951.5	1749.3
45°	1108.1	1161.3	1250.5	1283.7	1363.5	1544.4	1786.5	1980.8	2007.4	1886.3	1698.8
47.5°	951.1	996.4	1053.6	1094.8	1158.7	1294.3	1499.2	1713.4	1841.1	1797.2	1628.2
50°	838.1	875.3	923.2	947.1	988.4	1110.8	1265.1	1477.9	1649.5	1664.2	1536.5
52.5°	743.6	764.9	802.2	828.8	862.0	936.5	1076.2	1251.8	1444.7	1524.5	1423.4
55°	661.1	678.4	711.7	729.0	746.3	810.1	919.2	1078.8	1259.8	1364.9	1307.7
57.5°	586.6	601.3	629.2	645.2	654.5	715.7	799.5	924.5	1086.8	1214.5	1182.6
60°	525.5	538.8	554.7	566.7	577.3	627.9	686.4	787.5	932.5	1056.2	1048.3
62.5°	460.3	472.2	489.5	501.5	510.8	542.7	592.0	669.1	792.8	907.2	929.9
65°	403.1	412.4	424.4	429.7	441.6	465.6	505.5	574.7	675.8	778.2	794.2
67.5°	351.2	353.9	361.8	373.8	376.5	397.7	433.7	485.5	564.0	647.8	673.1
70°	295.3	299.3	306.0	315.3	320.6	333.9	364.5	399.1	466.9	540.1	558.7
72.5°	246.1	251.4	254.1	259.4	262.1	283.3	296.6	331.2	377.8	439.0	458.9
75°	199.5	204.9	206.2	208.9	211.5	220.8	239.4	260.7	299.3	339.2	365.8
77.5°	158.3	157.0	159.6	163.6	162.3	170.3	182.2	200.9	226.1	259.4	276.7
80°	111.7	111.7	115.7	119.7	118.4	126.4	130.4	143.7	165.0	186.2	192.9
82.5°	74.5	74.5	78.5	78.5	81.1	82.5	87.8	94.4	111.7	122.4	126.4
85°	42.6	42.6	43.9	43.9	43.9	46.6	50.6	53.2	58.5	65.2	67.8
87.5°	17.3	18.6	18.6	18.6	18.6	21.3	21.3	23.9	25.3	27.9	27.9
90°	22.2	21.6	20.9	20.6	20.1	19.0	17.9	16.8	15.7	14.2	12.6
92.5°	51.1	50.6	50.2	50.0	49.2	47.7	46.2	44.6	43.1	41.1	39.2
95°	83.4	83.0	82.5	82.3	81.5	80.0	78.5	76.9	75.4	73.2	71.0
97.5°	119.1	118.9	118.7	118.6	117.9	116.6	115.3	114.0	112.7	109.7	106.6
100°	159.8	159.4	158.9	158.7	157.7	155.8	153.8	151.9	149.9	147.1	144.3
102.5°	200.5	199.9	199.2	198.9	197.8	195.6	193.5	191.3	189.1	188.0	186.9
105°	241.7	241.1	240.4	240.1	239.4	238.1	236.8	235.5	234.2	232.9	231.6
107.5°	284.2	284.2	284.2	284.2	283.9	283.2	282.5	281.9	281.2	280.1	279.0
110°	331.6	331.9	332.1	332.2	331.9	331.2	330.5	329.9	329.2	328.6	327.9

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	378.1	378.5	379.0	379.2	379.1	378.9	378.6	378.4	378.2	377.3	376.5
115°	426.6	426.9	427.1	427.2	427.3	427.5	427.8	428.0	428.2	427.8	427.3
117.5°	475.0	475.9	476.8	477.2	477.1	476.9	476.6	476.4	476.2	475.8	475.3
120°	524.0	524.9	525.8	526.2	526.2	526.2	526.2	526.2	526.2	526.0	525.8
122.5°	572.5	573.2	573.9	574.2	574.3	574.5	574.8	575.0	575.2	574.5	573.9
125°	620.6	620.9	621.1	621.2	621.4	621.9	622.3	622.8	623.2	623.0	622.8
127.5°	668.1	668.6	669.0	669.2	669.3	669.5	669.8	670.0	670.2	670.0	669.8
130°	715.2	715.6	716.1	716.3	716.4	716.6	716.8	717.0	717.2	716.8	716.4
132.5°	759.7	760.3	761.0	761.3	761.4	761.6	761.9	762.1	762.3	762.5	762.7
135°	806.2	807.1	808.0	808.4	808.4	808.4	808.4	808.4	808.4	808.2	808.0
137.5°	851.7	852.8	853.9	854.4	854.3	854.1	853.8	853.6	853.4	853.0	852.6
140°	894.8	895.9	897.0	897.5	897.3	896.9	896.4	896.0	895.6	894.9	894.3
142.5°	936.0	937.1	938.2	938.7	938.6	938.4	938.1	937.9	937.7	936.8	936.0
145°	976.2	976.9	977.6	977.9	977.9	977.9	977.9	977.9	977.9	977.2	976.6
147.5°	1012.7	1014.5	1016.2	1017.1	1016.8	1016.1	1015.4	1014.8	1014.1	1013.7	1013.3
150°	1049.3	1049.7	1050.2	1050.4	1050.4	1050.4	1050.4	1050.4	1050.4	1049.5	1048.7
152.5°	1082.5	1083.4	1084.3	1084.7	1084.4	1083.7	1083.0	1082.4	1081.7	1081.5	1081.3
155°	1113.3	1114.4	1115.5	1116.0	1115.6	1114.7	1113.8	1113.0	1112.1	1111.9	1111.7
157.5°	1139.7	1141.2	1142.7	1143.5	1143.1	1142.2	1141.3	1140.5	1139.6	1139.4	1139.2
160°	1165.3	1166.4	1167.5	1168.0	1167.6	1166.7	1165.8	1165.0	1164.1	1163.9	1163.7
162.5°	1188.2	1189.5	1190.8	1191.5	1191.0	1189.9	1188.8	1187.7	1186.6	1186.6	1186.6
165°	1207.8	1209.1	1210.4	1211.1	1210.7	1209.8	1208.9	1208.1	1207.2	1207.0	1206.8
167.5°	1224.5	1225.8	1227.1	1227.7	1227.1	1225.8	1224.5	1223.2	1221.9	1221.9	1221.9
170°	1237.7	1239.2	1240.7	1241.5	1240.8	1239.5	1238.2	1236.9	1235.6	1235.6	1235.6
172.5°	1248.0	1249.3	1250.6	1251.3	1250.6	1249.3	1248.0	1246.7	1245.4	1245.4	1245.4
175°	1254.3	1255.8	1257.3	1258.1	1257.4	1256.1	1254.8	1253.5	1252.2	1252.2	1252.2
177.5°	1258.2	1259.7	1261.2	1262.0	1261.4	1260.1	1258.8	1257.5	1256.2	1256.4	1256.6
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1612.3	1605.6	1597.7	1597.7	1588.3	1584.3	1576.4	1573.7	1567.1	1556.4	1548.4
5°	1669.5	1652.2	1641.5	1632.2	1612.3	1597.7	1583.0	1567.1	1551.1	1532.5	1511.2
7.5°	1725.4	1693.4	1678.8	1662.8	1633.6	1603.0	1573.7	1552.4	1531.1	1501.9	1475.3
10°	1783.9	1744.0	1717.4	1696.1	1650.9	1612.3	1569.7	1539.1	1505.9	1468.6	1434.0
12.5°	1833.1	1781.2	1758.6	1718.7	1666.8	1620.3	1567.1	1520.5	1476.6	1432.7	1390.1
15°	1874.3	1825.1	1769.3	1753.3	1681.5	1614.9	1555.1	1495.2	1440.7	1396.8	1347.6
17.5°	1887.6	1825.1	1797.2	1758.6	1673.5	1604.3	1528.5	1463.3	1411.4	1346.2	1307.7
20°	1891.6	1831.8	1793.2	1757.3	1681.5	1589.7	1515.2	1435.4	1372.8	1307.7	1246.5
22.5°	1881.0	1810.5	1773.2	1738.7	1653.5	1575.0	1488.6	1400.8	1327.6	1267.7	1206.6
25°	1861.0	1778.6	1742.6	1705.4	1624.3	1537.8	1443.3	1359.5	1291.7	1219.9	1160.0
27.5°	1834.4	1740.0	1698.8	1660.2	1580.4	1499.2	1410.1	1323.6	1247.8	1172.0	1116.1
30°	1801.2	1692.1	1654.9	1604.3	1527.1	1450.0	1368.8	1282.4	1197.2	1125.4	1064.2
32.5°	1758.6	1644.2	1595.0	1547.1	1463.3	1392.8	1315.6	1234.5	1152.0	1081.5	1017.7
35°	1720.0	1589.7	1535.1	1487.2	1394.1	1319.6	1255.8	1179.9	1106.8	1033.6	976.4
37.5°	1668.2	1535.1	1469.9	1420.7	1326.3	1250.5	1190.6	1132.1	1054.9	984.4	931.2
40°	1613.6	1467.3	1406.1	1356.9	1258.4	1176.0	1118.8	1066.9	1004.4	939.2	883.3
42.5°	1564.4	1402.1	1336.9	1277.1	1177.3	1104.1	1045.6	1005.7	948.5	889.9	839.4
45°	1501.9	1332.9	1262.4	1199.9	1104.1	1024.3	968.4	936.5	893.9	836.7	792.8
47.5°	1438.0	1258.4	1185.3	1124.1	1020.3	949.8	895.3	864.7	835.4	790.2	746.3
50°	1354.2	1179.9	1113.4	1042.9	940.5	868.7	823.4	792.8	770.2	738.3	701.1
52.5°	1262.4	1098.8	1027.0	965.8	864.7	799.5	747.6	730.3	707.7	683.8	651.8
55°	1165.3	1011.0	941.8	882.0	788.8	722.3	679.8	661.1	643.8	625.2	603.9
57.5°	1068.2	919.2	854.0	800.8	714.4	650.5	615.9	590.6	578.7	568.0	550.7
60°	947.1	820.8	770.2	722.3	637.2	578.7	545.4	526.8	516.1	510.8	502.8
62.5°	840.7	737.0	681.1	634.5	566.7	514.8	482.9	468.3	458.9	456.3	447.0
65°	727.7	638.5	594.6	554.7	496.2	449.6	423.0	405.7	399.1	397.7	397.7
67.5°	621.2	549.4	505.5	477.6	427.0	385.8	360.5	353.9	349.9	344.5	343.2
70°	521.5	464.3	425.7	401.7	356.5	325.9	306.0	295.3	295.3	291.3	288.7
72.5°	433.7	376.5	351.2	331.2	294.0	267.4	252.8	250.1	240.8	239.4	239.4
75°	339.2	296.6	279.4	262.1	234.1	215.5	203.5	196.9	191.6	191.6	192.9
77.5°	255.4	226.1	210.2	196.9	176.9	165.0	155.6	153.0	147.7	147.7	147.7
80°	180.9	165.0	153.0	142.3	127.7	117.1	111.7	106.4	106.4	105.1	106.4
82.5°	117.1	103.8	97.1	95.8	82.5	78.5	71.8	73.2	69.2	67.8	70.5
85°	67.8	61.2	53.2	50.6	45.2	39.9	37.2	38.6	37.2	35.9	37.2
87.5°	26.6	22.6	21.3	21.3	17.3	16.0	14.6	16.0	13.3	13.3	14.6
90°	11.1	9.6	8.8	7.9	6.2	4.5	2.7	1.0	2.7	4.5	6.2
92.5°	37.2	35.3	34.3	33.8	32.7	31.6	30.5	29.4	30.5	31.6	32.7
95°	68.9	66.7	65.6	65.4	65.0	64.5	64.1	63.7	64.1	64.5	65.0
97.5°	103.6	100.5	99.0	98.9	98.7	98.4	98.2	98.0	98.2	98.4	98.7
100°	141.4	138.6	137.2	137.2	137.2	137.2	137.2	137.2	137.2	137.2	137.2
102.5°	185.8	184.7	184.2	183.7	182.6	181.5	180.4	179.3	180.4	181.5	182.6
105°	230.3	229.0	228.3	227.8	226.7	225.6	224.5	223.4	224.5	225.6	226.7
107.5°	277.9	276.8	276.3	275.8	274.7	273.6	272.5	271.4	272.5	273.6	274.7
110°	327.3	326.6	326.3	325.8	324.7	323.6	322.5	321.4	322.5	323.6	324.7

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	375.6	374.7	374.3	374.1	373.6	373.2	372.7	372.3	372.7	373.2	373.6
115°	426.9	426.4	426.2	425.8	424.9	424.0	423.2	422.3	423.2	424.0	424.9
117.5°	474.9	474.4	474.2	474.1	473.9	473.7	473.5	473.3	473.5	473.7	473.9
120°	525.5	525.3	525.2	524.7	523.6	522.5	521.4	520.3	521.4	522.5	523.6
122.5°	573.2	572.5	572.2	572.1	571.9	571.6	571.4	571.2	571.4	571.6	571.9
125°	622.5	622.3	622.2	621.5	620.2	618.9	617.6	616.3	617.6	618.9	620.2
127.5°	669.5	669.3	669.2	668.9	668.2	667.6	666.9	666.3	666.9	667.6	668.2
130°	715.9	715.5	715.3	714.8	713.7	712.6	711.5	710.4	711.5	712.6	713.7
132.5°	763.0	763.2	763.3	762.3	760.4	758.4	756.5	754.5	756.5	758.4	760.4
135°	807.7	807.5	807.4	806.7	805.4	804.1	802.8	801.5	802.8	804.1	805.4
137.5°	852.1	851.7	851.5	850.8	849.5	848.2	846.9	845.6	846.9	848.2	849.5
140°	893.6	892.9	892.6	892.1	891.0	889.9	888.8	887.7	888.8	889.9	891.0
142.5°	935.1	934.2	933.8	933.4	932.5	931.6	930.8	929.9	930.8	931.6	932.5
145°	975.9	975.2	974.9	974.5	973.6	972.7	971.9	971.0	971.9	972.7	973.6
147.5°	1012.8	1012.4	1012.2	1011.9	1011.2	1010.5	1009.9	1009.2	1009.9	1010.5	1011.2
150°	1047.8	1046.9	1046.5	1046.6	1046.8	1047.1	1047.3	1047.5	1047.3	1047.1	1046.8
152.5°	1081.1	1080.9	1080.8	1080.6	1080.1	1079.7	1079.2	1078.8	1079.2	1079.7	1080.1
155°	1111.4	1111.2	1111.1	1111.1	1111.1	1111.1	1111.1	1111.1	1111.1	1111.1	1111.1
157.5°	1138.9	1138.7	1138.6	1138.8	1139.2	1139.7	1140.1	1140.5	1140.1	1139.7	1139.2
160°	1163.4	1163.2	1163.1	1163.4	1164.1	1164.7	1165.4	1166.0	1165.4	1164.7	1164.1
162.5°	1186.6	1186.6	1186.6	1186.8	1187.2	1187.7	1188.1	1188.5	1188.1	1187.7	1187.2
165°	1206.5	1206.3	1206.2	1206.4	1206.8	1207.3	1207.7	1208.1	1207.7	1207.3	1206.8
167.5°	1221.9	1221.9	1221.9	1222.3	1223.2	1224.1	1224.9	1225.8	1224.9	1224.1	1223.2
170°	1235.6	1235.6	1235.6	1236.0	1236.9	1237.8	1238.6	1239.5	1238.6	1237.8	1236.9
172.5°	1245.4	1245.4	1245.4	1245.8	1246.7	1247.6	1248.4	1249.3	1248.4	1247.6	1246.7
175°	1252.2	1252.2	1252.2	1252.6	1253.5	1254.4	1255.3	1256.2	1255.3	1254.4	1253.5
177.5°	1256.8	1257.0	1257.1	1257.5	1258.4	1259.3	1260.2	1261.1	1260.2	1259.3	1258.4
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1545.8	1543.1	1536.5	1532.5	1519.2	1503.2	1497.9	1484.6	1489.9	1480.6	1480.6
5°	1504.5	1492.6	1484.6	1472.6	1447.3	1430.0	1411.4	1402.1	1396.8	1390.1	1384.8
7.5°	1451.3	1442.0	1434.0	1411.4	1383.5	1359.5	1336.9	1327.6	1310.3	1298.3	1293.0
10°	1404.8	1391.5	1372.8	1346.2	1317.0	1286.4	1266.4	1246.5	1233.2	1226.5	1211.9
12.5°	1356.9	1340.9	1321.0	1282.4	1250.5	1231.8	1195.9	1177.3	1170.6	1165.3	1148.0
15°	1307.7	1290.4	1266.4	1230.5	1202.6	1158.7	1137.4	1122.7	1106.8	1105.5	1092.1
17.5°	1263.8	1242.5	1222.5	1178.6	1144.0	1105.5	1093.5	1077.5	1062.9	1046.9	1040.3
20°	1207.9	1187.9	1173.3	1125.4	1086.8	1062.9	1042.9	1029.6	1020.3	1004.4	1001.7
22.5°	1157.3	1136.0	1116.1	1080.2	1046.9	1016.3	992.4	977.7	973.8	967.1	955.1
25°	1108.1	1086.8	1062.9	1029.6	995.0	973.8	952.5	943.2	935.2	924.5	915.2
27.5°	1066.9	1046.9	1024.3	983.1	953.8	937.8	915.2	904.6	893.9	888.6	884.6
30°	1017.7	995.0	977.7	945.8	913.9	892.6	876.6	867.3	858.0	852.7	850.0
32.5°	969.8	948.5	936.5	901.9	876.6	851.4	839.4	832.7	827.4	822.1	816.8
35°	931.2	909.9	891.3	859.4	834.1	816.8	807.5	796.8	792.8	787.5	787.5
37.5°	883.3	867.3	848.7	818.1	795.5	782.2	774.2	760.9	759.6	756.9	752.9
40°	842.1	826.1	808.8	782.2	762.2	746.3	735.6	729.0	725.0	722.3	719.7
42.5°	798.2	780.9	772.9	742.3	725.0	709.0	703.7	697.1	695.7	690.4	683.8
45°	755.6	741.0	725.0	702.4	687.7	674.4	666.5	661.1	654.5	653.2	649.2
47.5°	718.3	701.1	686.4	665.1	649.2	638.5	631.9	625.2	619.9	615.9	611.9
50°	670.5	657.2	645.2	622.6	609.3	598.6	589.3	584.0	578.7	578.7	578.7
52.5°	623.9	611.9	601.3	585.3	569.4	560.0	549.4	545.4	542.7	538.8	542.7
55°	578.7	566.7	556.1	544.1	525.5	517.5	506.8	502.8	504.2	504.2	508.2
57.5°	530.8	521.5	514.8	500.2	482.9	474.9	468.3	464.3	464.3	469.6	470.9
60°	484.2	474.9	462.9	449.6	439.0	429.7	425.7	427.0	427.0	429.7	436.3
62.5°	432.3	427.0	420.4	401.7	395.1	388.4	383.1	387.1	385.8	392.4	401.7
65°	384.4	379.1	369.8	360.5	352.5	345.9	344.5	345.9	348.5	355.2	365.8
67.5°	331.2	331.2	323.3	315.3	308.6	302.0	303.3	304.6	307.3	315.3	331.2
70°	287.3	282.0	274.0	268.7	263.4	260.7	258.1	263.4	271.4	276.7	288.7
72.5°	239.4	235.5	228.8	223.5	222.2	219.5	218.2	220.8	228.8	238.1	251.4
75°	188.9	190.2	186.2	182.2	182.2	178.3	180.9	180.9	188.9	198.2	208.9
77.5°	146.3	145.0	143.7	141.0	139.7	139.7	139.7	142.3	150.3	155.6	166.3
80°	103.8	105.1	101.1	102.4	101.1	102.4	102.4	107.8	111.7	118.4	126.4
82.5°	69.2	69.2	66.5	67.8	67.8	67.8	69.2	71.8	77.2	82.5	87.8
85°	38.6	39.9	37.2	39.9	39.9	39.9	41.2	42.6	46.6	47.9	53.2
87.5°	14.6	17.3	17.3	14.6	16.0	17.3	18.6	17.3	20.0	22.6	23.9
90°	7.9	8.8	9.6	11.1	12.6	14.2	15.7	16.8	17.9	19.0	20.1
92.5°	33.8	34.3	35.3	37.2	39.2	41.1	43.1	44.6	46.2	47.7	49.2
95°	65.4	65.6	66.7	68.9	71.0	73.2	75.4	76.9	78.5	80.0	81.5
97.5°	98.9	99.0	100.5	103.6	106.6	109.7	112.7	114.0	115.3	116.6	117.9
100°	137.2	137.2	138.6	141.4	144.3	147.1	149.9	151.9	153.8	155.8	157.7
102.5°	183.7	184.2	184.7	185.8	186.9	188.0	189.1	191.3	193.5	195.6	197.8
105°	227.8	228.3	229.0	230.3	231.6	232.9	234.2	235.5	236.8	238.1	239.4
107.5°	275.8	276.3	276.8	277.9	279.0	280.1	281.2	281.9	282.5	283.2	283.9
110°	325.8	326.3	326.6	327.3	327.9	328.6	329.2	329.9	330.5	331.2	331.9

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	374.1	374.3	374.7	375.6	376.5	377.3	378.2	378.4	378.6	378.9	379.1
115°	425.8	426.2	426.4	426.9	427.3	427.8	428.2	428.0	427.8	427.5	427.3
117.5°	474.1	474.2	474.4	474.9	475.3	475.8	476.2	476.4	476.6	476.9	477.1
120°	524.7	525.2	525.3	525.5	525.8	526.0	526.2	526.2	526.2	526.2	526.2
122.5°	572.1	572.2	572.5	573.2	573.9	574.5	575.2	575.0	574.8	574.5	574.3
125°	621.5	622.2	622.3	622.5	622.8	623.0	623.2	622.8	622.3	621.9	621.4
127.5°	668.9	669.2	669.3	669.5	669.8	670.0	670.2	670.0	669.8	669.5	669.3
130°	714.8	715.3	715.5	715.9	716.4	716.8	717.2	717.0	716.8	716.6	716.4
132.5°	762.3	763.3	763.2	763.0	762.7	762.5	762.3	762.1	761.9	761.6	761.4
135°	806.7	807.4	807.5	807.7	808.0	808.2	808.4	808.4	808.4	808.4	808.4
137.5°	850.8	851.5	851.7	852.1	852.6	853.0	853.4	853.6	853.8	854.1	854.3
140°	892.1	892.6	892.9	893.6	894.3	894.9	895.6	896.0	896.4	896.9	897.3
142.5°	933.4	933.8	934.2	935.1	936.0	936.8	937.7	937.9	938.1	938.4	938.6
145°	974.5	974.9	975.2	975.9	976.6	977.2	977.9	977.9	977.9	977.9	977.9
147.5°	1011.9	1012.2	1012.4	1012.8	1013.3	1013.7	1014.1	1014.8	1015.4	1016.1	1016.8
150°	1046.6	1046.5	1046.9	1047.8	1048.7	1049.5	1050.4	1050.4	1050.4	1050.4	1050.4
152.5°	1080.6	1080.8	1080.9	1081.1	1081.3	1081.5	1081.7	1082.4	1083.0	1083.7	1084.4
155°	1111.1	1111.1	1111.2	1111.4	1111.7	1111.9	1112.1	1113.0	1113.8	1114.7	1115.6
157.5°	1138.8	1138.6	1138.7	1138.9	1139.2	1139.4	1139.6	1140.5	1141.3	1142.2	1143.1
160°	1163.4	1163.1	1163.2	1163.4	1163.7	1163.9	1164.1	1165.0	1165.8	1166.7	1167.6
162.5°	1186.8	1186.6	1186.6	1186.6	1186.6	1186.6	1186.6	1187.7	1188.8	1189.9	1191.0
165°	1206.4	1206.2	1206.3	1206.5	1206.8	1207.0	1207.2	1208.1	1208.9	1209.8	1210.7
167.5°	1222.3	1221.9	1221.9	1221.9	1221.9	1221.9	1221.9	1223.2	1224.5	1225.8	1227.1
170°	1236.0	1235.6	1235.6	1235.6	1235.6	1235.6	1235.6	1236.9	1238.2	1239.5	1240.8
172.5°	1245.8	1245.4	1245.4	1245.4	1245.4	1245.4	1245.4	1246.7	1248.0	1249.3	1250.6
175°	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1252.2	1253.5	1254.8	1256.1	1257.4
177.5°	1257.5	1257.1	1257.0	1256.8	1256.6	1256.4	1256.2	1257.5	1258.8	1260.1	1261.4
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1485.9	1476.6	1475.3	1477.9	1472.6	1480.6	1477.9	1480.6	1473.9	1480.6	1476.6
5°	1383.5	1380.8	1375.5	1368.8	1370.2	1371.5	1378.2	1371.5	1376.8	1378.2	1384.8
7.5°	1287.7	1282.4	1286.4	1283.7	1271.7	1269.1	1271.7	1275.7	1283.7	1289.0	1293.0
10°	1210.5	1207.9	1202.6	1198.6	1191.9	1187.9	1193.2	1187.9	1198.6	1207.9	1207.9
12.5°	1152.0	1141.4	1134.7	1133.4	1118.8	1121.4	1126.7	1130.7	1142.7	1148.0	1148.0
15°	1090.8	1082.8	1080.2	1074.9	1069.5	1074.9	1072.2	1076.2	1081.5	1086.8	1089.5
17.5°	1037.6	1036.3	1037.6	1024.3	1028.3	1021.6	1023.0	1029.6	1025.6	1029.6	1037.6
20°	989.7	992.4	988.4	983.1	983.1	975.1	984.4	981.7	983.1	991.0	1003.0
22.5°	953.8	952.5	948.5	944.5	939.2	940.5	941.8	939.2	949.8	956.5	957.8
25°	915.2	912.6	911.2	907.2	901.9	907.2	905.9	907.2	909.9	920.5	912.6
27.5°	879.3	874.0	876.6	872.7	871.3	872.7	872.7	874.0	876.6	878.0	879.3
30°	848.7	843.4	842.1	839.4	838.1	839.4	842.1	839.4	850.0	848.7	848.7
32.5°	815.5	811.5	808.8	808.8	807.5	806.1	807.5	808.8	816.8	811.5	816.8
35°	783.5	780.9	780.9	778.2	776.9	776.9	776.9	782.2	779.5	783.5	783.5
37.5°	752.9	752.9	751.6	748.9	747.6	748.9	747.6	750.3	748.9	750.3	751.6
40°	721.0	718.3	717.0	717.0	713.0	709.0	713.0	713.0	714.4	718.3	719.7
42.5°	682.4	683.8	683.8	678.4	678.4	678.4	679.8	681.1	681.1	683.8	683.8
45°	649.2	646.5	646.5	646.5	643.8	645.2	647.8	647.8	647.8	647.8	645.2
47.5°	611.9	611.9	613.3	613.3	617.2	615.9	615.9	614.6	611.9	611.9	613.3
50°	577.3	581.3	582.7	582.7	584.0	585.3	585.3	582.7	581.3	577.3	577.3
52.5°	544.1	546.7	549.4	553.4	556.1	554.7	554.7	552.1	546.7	545.4	544.1
55°	508.2	512.2	517.5	521.5	525.5	526.8	526.8	521.5	516.1	509.5	509.5
57.5°	474.9	478.9	488.2	492.2	497.5	497.5	494.9	490.9	482.9	477.6	473.6
60°	441.6	448.3	455.0	462.9	469.6	470.9	466.9	461.6	452.3	445.6	440.3
62.5°	405.7	412.4	425.7	433.7	439.0	439.0	439.0	432.3	420.4	411.1	403.1
65°	371.1	377.8	389.8	400.4	404.4	408.4	404.4	397.7	388.4	377.8	369.8
67.5°	335.2	343.2	355.2	363.2	368.5	372.5	369.8	364.5	352.5	337.9	332.6
70°	295.3	299.3	316.6	324.6	332.6	335.2	332.6	324.6	312.6	296.6	291.3
72.5°	258.1	262.1	278.0	284.7	291.3	294.0	290.0	284.7	274.0	259.4	252.8
75°	215.5	222.2	230.1	240.8	248.8	251.4	247.4	243.4	230.1	220.8	215.5
77.5°	170.3	176.9	187.6	196.9	204.9	203.5	198.2	199.5	184.9	174.3	170.3
80°	129.0	134.4	142.3	150.3	154.3	154.3	153.0	147.7	142.3	134.4	127.7
82.5°	89.1	95.8	102.4	107.8	107.8	109.1	106.4	105.1	99.8	93.1	91.8
85°	53.2	54.5	59.9	59.9	65.2	62.5	61.2	65.2	59.9	55.9	54.5
87.5°	23.9	22.6	23.9	23.9	22.6	25.3	25.3	23.9	25.3	23.9	23.9
90°	20.6	20.9	21.6	22.2	22.9	23.5	22.9	22.2	21.6	20.9	20.6
92.5°	50.0	50.2	50.6	51.1	51.5	51.9	51.5	51.1	50.6	50.2	50.0
95°	82.3	82.5	83.0	83.4	83.9	84.3	83.9	83.4	83.0	82.5	82.3
97.5°	118.6	118.7	118.9	119.1	119.3	119.5	119.3	119.1	118.9	118.7	118.6
100°	158.7	158.9	159.4	159.8	160.3	160.7	160.3	159.8	159.4	158.9	158.7
102.5°	198.9	199.2	199.9	200.5	201.2	201.8	201.2	200.5	199.9	199.2	198.9
105°	240.1	240.4	241.1	241.7	242.4	243.0	242.4	241.7	241.1	240.4	240.1
107.5°	284.2	284.2	284.2	284.2	284.2	284.2	284.2	284.2	284.2	284.2	284.2
110°	332.2	332.1	331.9	331.6	331.4	331.2	331.4	331.6	331.9	332.1	332.2

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	379.2	379.0	378.5	378.1	377.6	377.2	377.6	378.1	378.5	379.0	379.2
115°	427.2	427.1	426.9	426.6	426.4	426.2	426.4	426.6	426.9	427.1	427.2
117.5°	477.2	476.8	475.9	475.0	474.2	473.3	474.2	475.0	475.9	476.8	477.2
120°	526.2	525.8	524.9	524.0	523.2	522.3	523.2	524.0	524.9	525.8	526.2
122.5°	574.2	573.9	573.2	572.5	571.9	571.2	571.9	572.5	573.2	573.9	574.2
125°	621.2	621.1	620.9	620.6	620.4	620.2	620.4	620.6	620.9	621.1	621.2
127.5°	669.2	669.0	668.6	668.1	667.7	667.3	667.7	668.1	668.6	669.0	669.2
130°	716.3	716.1	715.6	715.2	714.7	714.3	714.7	715.2	715.6	716.1	716.3
132.5°	761.3	761.0	760.3	759.7	759.0	758.4	759.0	759.7	760.3	761.0	761.3
135°	808.4	808.0	807.1	806.2	805.4	804.5	805.4	806.2	807.1	808.0	808.4
137.5°	854.4	853.9	852.8	851.7	850.6	849.5	850.6	851.7	852.8	853.9	854.4
140°	897.5	897.0	895.9	894.8	893.7	892.6	893.7	894.8	895.9	897.0	897.5
142.5°	938.7	938.2	937.1	936.0	934.9	933.8	934.9	936.0	937.1	938.2	938.7
145°	977.9	977.6	976.9	976.2	975.6	974.9	975.6	976.2	976.9	977.6	977.9
147.5°	1017.1	1016.2	1014.5	1012.7	1011.0	1009.2	1011.0	1012.7	1014.5	1016.2	1017.1
150°	1050.4	1050.2	1049.7	1049.3	1048.8	1048.4	1048.8	1049.3	1049.7	1050.2	1050.4
152.5°	1084.7	1084.3	1083.4	1082.5	1081.7	1080.8	1081.7	1082.5	1083.4	1084.3	1084.7
155°	1116.0	1115.5	1114.4	1113.3	1112.2	1111.1	1112.2	1113.3	1114.4	1115.5	1116.0
157.5°	1143.5	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2	1142.7	1143.5
160°	1168.0	1167.5	1166.4	1165.3	1164.2	1163.1	1164.2	1165.3	1166.4	1167.5	1168.0
162.5°	1191.5	1190.8	1189.5	1188.2	1186.9	1185.6	1186.9	1188.2	1189.5	1190.8	1191.5
165°	1211.1	1210.4	1209.1	1207.8	1206.5	1205.2	1206.5	1207.8	1209.1	1210.4	1211.1
167.5°	1227.7	1227.1	1225.8	1224.5	1223.2	1221.9	1223.2	1224.5	1225.8	1227.1	1227.7
170°	1241.5	1240.7	1239.2	1237.7	1236.1	1234.6	1236.1	1237.7	1239.2	1240.7	1241.5
172.5°	1251.3	1250.6	1249.3	1248.0	1246.7	1245.4	1246.7	1248.0	1249.3	1250.6	1251.3
175°	1258.1	1257.3	1255.8	1254.3	1252.8	1251.3	1252.8	1254.3	1255.8	1257.3	1258.1
177.5°	1262.0	1261.2	1259.7	1258.2	1256.7	1255.2	1256.7	1258.2	1259.7	1261.2	1262.0
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1488.6	1480.6	1489.9	1477.9	1480.6	1495.2	1493.9	1507.2	1515.2	1513.8	1520.5
5°	1390.1	1390.1	1394.1	1392.8	1406.1	1418.1	1434.0	1447.3	1462.0	1469.9	1479.3
7.5°	1293.0	1306.3	1309.0	1315.6	1331.6	1351.6	1367.5	1387.5	1408.8	1423.4	1434.0
10°	1213.2	1223.8	1234.5	1239.8	1257.1	1283.7	1306.3	1338.2	1364.9	1380.8	1395.4
12.5°	1142.7	1154.7	1160.0	1183.9	1195.9	1213.2	1245.1	1279.7	1309.0	1326.3	1338.2
15°	1092.1	1098.8	1110.8	1125.4	1137.4	1158.7	1185.3	1223.8	1251.8	1266.4	1307.7
17.5°	1049.6	1057.6	1064.2	1070.9	1089.5	1112.1	1137.4	1170.6	1206.6	1231.8	1253.1
20°	1005.7	1009.7	1017.7	1028.3	1041.6	1062.9	1085.5	1120.1	1152.0	1172.0	1199.9
22.5°	953.8	965.8	973.8	981.7	996.4	1020.3	1041.6	1066.9	1106.8	1129.4	1158.7
25°	923.2	928.5	933.8	943.2	953.8	975.1	999.0	1025.6	1057.6	1081.5	1106.8
27.5°	883.3	891.3	897.9	909.9	916.6	933.8	956.5	983.1	1021.6	1041.6	1062.9
30°	850.0	858.0	863.3	868.7	878.0	896.6	917.9	939.2	975.1	1000.4	1021.6
32.5°	816.8	824.8	831.4	835.4	844.7	856.7	874.0	900.6	931.2	948.5	976.4
35°	787.5	787.5	795.5	800.8	808.8	819.4	835.4	855.4	887.3	909.9	935.2
37.5°	754.3	755.6	762.2	766.2	774.2	784.9	800.8	819.4	846.0	863.3	888.6
40°	719.7	723.7	726.3	733.0	742.3	746.3	762.2	783.5	810.1	826.1	847.4
42.5°	685.1	687.7	694.4	699.7	707.7	714.4	725.0	744.9	764.9	788.8	806.1
45°	646.5	653.2	657.2	666.5	670.5	677.1	687.7	703.7	727.7	742.3	762.2
47.5°	613.3	615.9	618.6	630.5	638.5	642.5	653.2	662.5	687.7	701.1	719.7
50°	577.3	577.3	581.3	586.6	596.0	603.9	613.3	623.9	643.8	657.2	675.8
52.5°	544.1	540.1	542.7	545.4	554.7	562.7	572.0	586.6	605.3	613.3	629.2
55°	508.2	501.5	505.5	509.5	512.2	522.8	533.4	542.7	557.4	569.4	584.0
57.5°	469.6	468.3	465.6	466.9	473.6	480.2	488.2	500.2	517.5	526.8	534.8
60°	435.0	427.0	424.4	427.0	431.0	435.0	445.6	456.3	470.9	480.2	489.5
62.5°	399.1	391.1	385.8	381.8	385.8	395.1	401.7	409.7	421.7	432.3	440.3
65°	364.5	352.5	347.2	344.5	343.2	349.9	355.2	365.8	376.5	380.5	389.8
67.5°	325.9	315.3	308.6	304.6	304.6	304.6	310.0	320.6	331.2	332.6	341.9
70°	287.3	275.4	268.7	263.4	260.7	263.4	270.0	271.4	280.7	283.3	288.7
72.5°	246.1	235.5	227.5	220.8	222.2	224.8	224.8	227.5	232.8	239.4	239.4
75°	207.5	192.9	188.9	183.6	180.9	180.9	180.9	186.2	190.2	195.5	194.2
77.5°	163.6	155.6	147.7	145.0	141.0	139.7	142.3	142.3	145.0	149.0	150.3
80°	126.4	117.1	111.7	109.1	103.8	102.4	103.8	103.8	107.8	106.4	107.8
82.5°	87.8	81.1	77.2	73.2	70.5	71.8	70.5	70.5	71.8	70.5	70.5
85°	50.6	49.2	46.6	45.2	43.9	41.2	43.9	42.6	41.2	39.9	42.6
87.5°	23.9	22.6	22.6	20.0	20.0	18.6	20.0	20.0	18.6	18.6	18.6
90°	20.1	19.0	17.9	16.8	15.7	14.2	12.6	11.1	9.6	8.8	7.9
92.5°	49.2	47.7	46.2	44.6	43.1	41.1	39.2	37.2	35.3	34.3	33.8
95°	81.5	80.0	78.5	76.9	75.4	73.2	71.0	68.9	66.7	65.6	65.4
97.5°	117.9	116.6	115.3	114.0	112.7	109.7	106.6	103.6	100.5	99.0	98.9
100°	157.7	155.8	153.8	151.9	149.9	147.1	144.3	141.4	138.6	137.2	137.2
102.5°	197.8	195.6	193.5	191.3	189.1	188.0	186.9	185.8	184.7	184.2	183.7
105°	239.4	238.1	236.8	235.5	234.2	232.9	231.6	230.3	229.0	228.3	227.8
107.5°	283.9	283.2	282.5	281.9	281.2	280.1	279.0	277.9	276.8	276.3	275.8
110°	331.9	331.2	330.5	329.9	329.2	328.6	327.9	327.3	326.6	326.3	325.8

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	379.1	378.9	378.6	378.4	378.2	377.3	376.5	375.6	374.7	374.3	374.1
115°	427.3	427.5	427.8	428.0	428.2	427.8	427.3	426.9	426.4	426.2	425.8
117.5°	477.1	476.9	476.6	476.4	476.2	475.8	475.3	474.9	474.4	474.2	474.1
120°	526.2	526.2	526.2	526.2	526.2	526.0	525.8	525.5	525.3	525.2	524.7
122.5°	574.3	574.5	574.8	575.0	575.2	574.5	573.9	573.2	572.5	572.2	572.1
125°	621.4	621.9	622.3	622.8	623.2	623.0	622.8	622.5	622.3	622.2	621.5
127.5°	669.3	669.5	669.8	670.0	670.2	670.0	669.8	669.5	669.3	669.2	668.9
130°	716.4	716.6	716.8	717.0	717.2	716.8	716.4	715.9	715.5	715.3	714.8
132.5°	761.4	761.6	761.9	762.1	762.3	762.5	762.7	763.0	763.2	763.3	762.3
135°	808.4	808.4	808.4	808.4	808.4	808.2	808.0	807.7	807.5	807.4	806.7
137.5°	854.3	854.1	853.8	853.6	853.4	853.0	852.6	852.1	851.7	851.5	850.8
140°	897.3	896.9	896.4	896.0	895.6	894.9	894.3	893.6	892.9	892.6	892.1
142.5°	938.6	938.4	938.1	937.9	937.7	936.8	936.0	935.1	934.2	933.8	933.4
145°	977.9	977.9	977.9	977.9	977.9	977.2	976.6	975.9	975.2	974.9	974.5
147.5°	1016.8	1016.1	1015.4	1014.8	1014.1	1013.7	1013.3	1012.8	1012.4	1012.2	1011.9
150°	1050.4	1050.4	1050.4	1050.4	1050.4	1049.5	1048.7	1047.8	1046.9	1046.5	1046.6
152.5°	1084.4	1083.7	1083.0	1082.4	1081.7	1081.5	1081.3	1081.1	1080.9	1080.8	1080.6
155°	1115.6	1114.7	1113.8	1113.0	1112.1	1111.9	1111.7	1111.4	1111.2	1111.1	1111.1
157.5°	1143.1	1142.2	1141.3	1140.5	1139.6	1139.4	1139.2	1138.9	1138.7	1138.6	1138.8
160°	1167.6	1166.7	1165.8	1165.0	1164.1	1163.9	1163.7	1163.4	1163.2	1163.1	1163.4
162.5°	1191.0	1189.9	1188.8	1187.7	1186.6	1186.6	1186.6	1186.6	1186.6	1186.6	1186.8
165°	1210.7	1209.8	1208.9	1208.1	1207.2	1207.0	1206.8	1206.5	1206.3	1206.2	1206.4
167.5°	1227.1	1225.8	1224.5	1223.2	1221.9	1221.9	1221.9	1221.9	1221.9	1221.9	1222.3
170°	1240.8	1239.5	1238.2	1236.9	1235.6	1235.6	1235.6	1235.6	1235.6	1235.6	1236.0
172.5°	1250.6	1249.3	1248.0	1246.7	1245.4	1245.4	1245.4	1245.4	1245.4	1245.4	1245.8
175°	1257.4	1256.1	1254.8	1253.5	1252.2	1252.2	1252.2	1252.2	1252.2	1252.2	1252.6
177.5°	1261.4	1260.1	1258.8	1257.5	1256.2	1256.4	1256.6	1256.8	1257.0	1257.1	1257.5
180°	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1	1259.1

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1567.1	1567.1	1567.1	1567.1
2.5°	1529.8	1543.1	1552.4	1569.7
5°	1495.2	1519.2	1541.8	1565.7
7.5°	1460.6	1488.6	1524.5	1555.1
10°	1422.1	1458.0	1500.5	1541.8
12.5°	1383.5	1426.0	1472.6	1527.1
15°	1336.9	1391.5	1446.0	1504.5
17.5°	1295.7	1351.6	1410.1	1483.2
20°	1249.1	1310.3	1374.2	1448.7
22.5°	1207.9	1275.7	1342.2	1420.7
25°	1161.3	1227.8	1301.0	1384.8
27.5°	1122.7	1183.9	1255.8	1346.2
30°	1076.2	1142.7	1214.5	1305.0
32.5°	1032.3	1096.1	1172.0	1261.1
35°	987.1	1052.2	1120.1	1205.2
37.5°	944.5	1000.4	1068.2	1149.4
40°	896.6	957.8	1019.0	1082.8
42.5°	852.7	908.6	965.8	1016.3
45°	803.5	851.4	905.9	947.1
47.5°	758.3	800.8	843.4	875.3
50°	713.0	746.3	778.2	806.1
52.5°	659.8	697.1	714.4	731.6
55°	611.9	633.2	649.2	666.5
57.5°	565.4	574.7	582.7	598.6
60°	504.2	514.8	524.1	536.1
62.5°	451.0	456.3	458.9	470.9
65°	400.4	399.1	405.7	412.4
67.5°	345.9	344.5	351.2	353.9
70°	292.7	291.3	292.7	299.3
72.5°	242.1	242.1	243.4	246.1
75°	195.5	195.5	196.9	199.5
77.5°	147.7	150.3	149.0	154.3
80°	107.8	105.1	107.8	110.4
82.5°	70.5	73.2	73.2	70.5
85°	39.9	39.9	39.9	39.9
87.5°	17.3	17.3	18.6	20.0
90°	6.2	4.5	2.7	1.0
92.5°	32.7	31.6	30.5	29.4
95°	65.0	64.5	64.1	63.7
97.5°	98.7	98.4	98.2	98.0
100°	137.2	137.2	137.2	137.2
102.5°	182.6	181.5	180.4	179.3
105°	226.7	225.6	224.5	223.4
107.5°	274.7	273.6	272.5	271.4
110°	324.7	323.6	322.5	321.4

TEST NUMBER: P1027305

CATALOG NUMBER: S125DIP-B1090D1090UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	373.6	373.2	372.7	372.3
115°	424.9	424.0	423.2	422.3
117.5°	473.9	473.7	473.5	473.3
120°	523.6	522.5	521.4	520.3
122.5°	571.9	571.6	571.4	571.2
125°	620.2	618.9	617.6	616.3
127.5°	668.2	667.6	666.9	666.3
130°	713.7	712.6	711.5	710.4
132.5°	760.4	758.4	756.5	754.5
135°	805.4	804.1	802.8	801.5
137.5°	849.5	848.2	846.9	845.6
140°	891.0	889.9	888.8	887.7
142.5°	932.5	931.6	930.8	929.9
145°	973.6	972.7	971.9	971.0
147.5°	1011.2	1010.5	1009.9	1009.2
150°	1046.8	1047.1	1047.3	1047.5
152.5°	1080.1	1079.7	1079.2	1078.8
155°	1111.1	1111.1	1111.1	1111.1
157.5°	1139.2	1139.7	1140.1	1140.5
160°	1164.1	1164.7	1165.4	1166.0
162.5°	1187.2	1187.7	1188.1	1188.5
165°	1206.8	1207.3	1207.7	1208.1
167.5°	1223.2	1224.1	1224.9	1225.8
170°	1236.9	1237.8	1238.6	1239.5
172.5°	1246.7	1247.6	1248.4	1249.3
175°	1253.5	1254.4	1255.3	1256.2
177.5°	1258.4	1259.3	1260.2	1261.1
180°	1259.1	1259.1	1259.1	1259.1

(END OF REPORT)