

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027586

Luminaire Tested: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027586
REPORT IS A COMBINATION OF REPORTS P1001609 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9956.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027586

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1027586

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1027586

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	1.9
10°-20°	526.5	5.3
20°-30°	777.2	7.8
30°-40°	906.8	9.1
40°-50°	910.8	9.1
50°-60°	799.5	8.0
60°-70°	595.5	6.0
70°-80°	340.1	3.4
80°-90°	100.5	1.0
90°-100°	53.2	0.5
100°-110°	353.6	3.6
110°-120°	636.8	6.4
120°-130°	817.3	8.2
130°-140°	879.0	8.8
140°-150°	825.0	8.3
150°-160°	667.3	6.7
160°-170°	431.6	4.3
170°-180°	148.8	1.5
0°-30°	1490.1	15.0
0°-40°	2396.9	24.1
0°-60°	4107.2	41.3
0°-90°	5143.3	51.7
90°-120°	1043.5	10.5
90°-150°	3564.9	35.8
90°-180°	4813.0	48.3
0°-180°	9956.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	1	10	19	24	28	9
95°	66	63	19	24	24	81
105°	342	346	346	346	345	362
115°	641	647	648	643	636	636
125°	912	920	920	915	912	814
135°	1137	1144	1142	1139	1132	877
145°	1318	1320	1320	1322	1315	824
155°	1452	1445	1447	1451	1441	669
165°	1532	1525	1526	1533	1524	433
175°	1567	1560	1561	1570	1560	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1027586

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	1.2	10.5	18.6	24.4	27.9
92.5°	22.1	11.6	18.6	24.4	25.6
95°	66.2	62.7	18.6	24.4	24.4
97.5°	124.3	131.2	20.9	23.2	24.4
100°	194.0	197.4	202.1	29.0	24.4
102.5°	264.8	269.4	271.8	274.1	176.5
105°	341.5	346.1	346.1	346.1	344.9
107.5°	420.4	420.4	422.8	423.9	419.3
110°	497.1	497.1	499.4	495.9	497.1



TEST NUMBER: P1027586

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	569.1	572.6	573.7	569.1	566.8
115°	641.1	646.9	648.1	643.4	636.4
117.5°	716.6	716.6	721.2	714.3	711.9
120°	786.3	785.1	788.6	786.3	780.5
122.5°	847.8	853.6	854.8	852.5	845.5
125°	911.7	919.8	919.8	915.2	911.7
127.5°	973.3	979.1	977.9	975.6	966.3
130°	1029.0	1034.8	1036.0	1032.5	1026.7
132.5°	1084.8	1091.7	1088.2	1088.2	1082.4
135°	1137.0	1144.0	1141.7	1139.3	1132.4
137.5°	1185.8	1192.8	1190.4	1190.4	1184.6
140°	1233.4	1235.7	1234.6	1236.9	1229.9
142.5°	1276.4	1277.5	1279.9	1279.9	1272.9
145°	1318.2	1320.5	1320.5	1321.7	1314.7
147.5°	1355.4	1355.4	1356.5	1357.7	1349.6
150°	1390.2	1387.9	1390.2	1392.5	1383.2
152.5°	1423.9	1418.1	1420.4	1422.7	1414.6
155°	1451.8	1444.8	1447.1	1450.6	1441.3
157.5°	1473.8	1470.3	1470.3	1473.8	1464.5
160°	1497.0	1490.1	1491.2	1495.9	1486.6
162.5°	1515.6	1508.7	1509.8	1516.8	1506.3
165°	1531.9	1524.9	1526.1	1533.1	1523.8
167.5°	1544.7	1537.7	1538.9	1547.0	1536.5
170°	1555.1	1547.0	1548.2	1557.4	1547.0
172.5°	1562.1	1554.0	1556.3	1564.4	1554.0
175°	1566.7	1559.8	1560.9	1570.2	1559.8
177.5°	1570.2	1563.2	1564.4	1572.5	1563.2
180°	1566.7	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)