

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027396

Luminaire Tested: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027396
REPORT IS A COMBINATION OF REPORTS P1001341 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D375UB27-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5736.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69
2	95	88	81	76	91	84	78	73	77	72	68	70	67	63	64	61	59
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50
4	80	69	61	54	76	66	59	53	61	54	50	56	51	47	51	47	44
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38
6	68	55	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	34	30
8	58	46	38	32	56	44	37	31	41	34	30	38	32	28	35	30	27
9	55	42	34	29	52	40	33	28	38	31	27	35	30	26	32	28	24
10	51	39	31	26	49	37	30	25	35	29	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10041	10041	10041	10041
5°	10048	11390	10057	8641
10°	9987	12982	9969	7417
15°	9913	14076	9852	6702
20°	9789	15425	9699	6118
25°	9677	17674	9500	5773
30°	9517	18646	9353	5460
35°	9264	14946	9070	5208
40°	8870	10331	8740	4943
45°	8372	7691	8279	4722
50°	7802	6332	7674	4545
55°	7188	5400	7130	4391
60°	6585	4623	6470	4272
65°	5934	3991	5838	4099
70°	5246	3315	5176	3796
75°	4517	2563	4458	3295
80°	3568	1733	3438	2422
85°	2281	867	2207	1235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15336 cd/sqm

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	2.6
10°-20°	449.2	7.8
20°-30°	729.7	12.7
30°-40°	891.8	15.5
40°-50°	809.0	14.1
50°-60°	644.3	11.2
60°-70°	448.8	7.8
70°-80°	239.1	4.2
80°-90°	60.0	1.0
90°-100°	127.2	2.2
100°-110°	274.3	4.8
110°-120°	255.7	4.5
120°-130°	207.1	3.6
130°-140°	166.3	2.9
140°-150°	125.4	2.2
150°-160°	88.3	1.5
160°-170°	52.1	0.9
170°-180°	16.9	0.3
0°-30°	1329.8	23.2
0°-40°	2221.6	38.7
0°-60°	3674.9	64.1
0°-90°	4422.7	77.1
90°-120°	657.2	11.5
90°-150°	1156.0	20.2
90°-180°	1313.0	22.9
0°-180°	5736.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1567	1567	1567	1567	1567	
5°	1566	1808	1567	1372	1566	149
15°	1504	2258	1495	1075	1504	425
25°	1385	2778	1360	907	1385	638
35°	1205	2230	1180	777	1205	753
45°	947	1051	936	645	947	730
55°	666	648	661	527	666	596
65°	412	398	406	408	412	409
75°	200	196	197	251	200	212
85°	40	44	39	62	40	48
90°	0	8	0	8	0	4
95°	12	83	12	83	12	12
105°	40	467	40	467	40	42
115°	71	520	71	520	71	70
125°	99	410	99	410	99	88
135°	116	340	116	340	116	90
145°	135	269	135	269	135	84
155°	154	225	154	225	154	71
165°	168	197	168	197	168	47
175°	174	177	174	177	174	17
180°	175	175	175	175	175	

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1569.7	1579.0	1589.7	1597.7	1611.0	1614.9	1621.6	1625.6	1629.6	1633.6	1636.2
5°	1565.7	1588.3	1608.3	1622.9	1648.2	1657.5	1669.5	1684.1	1701.4	1716.0	1725.4
7.5°	1555.1	1591.0	1617.6	1646.9	1681.5	1704.1	1716.0	1746.6	1774.6	1795.9	1823.8
10°	1541.8	1584.3	1625.6	1669.5	1718.7	1744.0	1767.9	1810.5	1849.1	1883.7	1911.6
12.5°	1527.1	1579.0	1628.2	1685.4	1752.0	1782.6	1798.5	1871.7	1919.6	1938.2	1992.7
15°	1504.5	1565.7	1636.2	1706.7	1762.6	1798.5	1842.4	1901.0	1948.8	1990.1	2034.0
17.5°	1483.2	1549.8	1621.6	1700.1	1781.2	1827.8	1861.0	1912.9	1964.8	2018.0	2059.3
20°	1448.7	1535.1	1608.3	1692.1	1787.9	1821.1	1855.7	1916.9	1972.8	2030.0	2081.9
22.5°	1420.7	1503.2	1603.0	1682.8	1763.9	1797.2	1839.8	1903.6	1970.1	2035.3	2111.1
25°	1384.8	1476.6	1563.1	1648.2	1732.0	1767.9	1806.5	1889.0	1958.2	2042.0	2125.8
27.5°	1346.2	1440.7	1527.1	1604.3	1682.8	1732.0	1773.2	1859.7	1951.5	2043.3	2152.4
30°	1305.0	1394.1	1476.6	1552.4	1638.9	1689.4	1730.7	1831.8	1934.2	2051.3	2181.6
32.5°	1261.1	1344.9	1415.4	1492.6	1584.3	1630.9	1686.8	1797.2	1918.2	2057.9	2221.5
35°	1205.2	1285.0	1347.6	1426.0	1517.8	1577.7	1636.2	1759.9	1901.0	2056.6	2244.2
37.5°	1149.4	1211.9	1271.7	1355.5	1462.0	1516.5	1577.7	1713.4	1874.3	2052.6	2253.5
40°	1082.8	1144.0	1195.9	1281.0	1392.8	1455.3	1519.2	1661.5	1843.7	2038.0	2220.2
42.5°	1016.3	1068.2	1125.4	1214.5	1322.3	1388.8	1456.6	1614.9	1803.8	1995.4	2128.4
45°	947.1	987.1	1049.6	1130.7	1245.1	1309.0	1386.1	1557.7	1748.0	1918.2	1984.8
47.5°	875.3	915.2	973.8	1052.2	1165.3	1241.1	1314.3	1485.9	1677.5	1809.2	1809.2
50°	806.1	838.1	895.3	973.8	1088.2	1157.3	1231.8	1414.1	1568.4	1665.5	1579.0
52.5°	731.6	767.6	815.5	897.9	1011.0	1073.5	1154.7	1310.3	1456.6	1496.6	1363.5
55°	666.5	695.7	741.0	819.4	924.5	989.7	1058.9	1207.9	1331.6	1328.9	1186.6
57.5°	598.6	622.6	670.5	742.3	839.4	897.9	967.1	1096.1	1197.2	1161.3	1027.0
60°	536.1	553.4	600.0	658.5	751.6	806.1	872.7	977.7	1054.9	1004.4	868.7
62.5°	470.9	490.9	528.1	585.3	667.8	711.7	760.9	867.3	916.6	871.3	733.0
65°	412.4	428.3	461.6	509.5	584.0	623.9	666.5	754.3	800.8	735.6	621.2
67.5°	353.9	372.5	396.4	439.0	497.5	534.8	572.0	647.8	669.1	610.6	514.8
70°	299.3	315.3	337.9	368.5	417.7	451.0	478.9	541.4	556.1	501.5	425.7
72.5°	246.1	256.7	275.4	300.6	345.9	364.5	393.8	436.3	455.0	405.7	351.2
75°	199.5	207.5	219.5	238.1	268.7	288.7	312.6	352.5	351.2	316.6	278.0
77.5°	154.3	155.6	168.9	186.2	204.9	222.2	234.1	262.1	264.7	243.4	211.5
80°	110.4	114.4	119.7	133.0	149.0	155.6	170.3	187.6	190.2	174.3	153.0
82.5°	70.5	73.2	77.2	85.1	95.8	103.8	111.7	118.4	125.0	115.7	98.4
85°	39.9	41.2	45.2	47.9	53.2	57.2	63.9	70.5	69.2	62.5	57.2
87.5°	20.0	20.0	20.0	22.6	25.3	25.3	27.9	29.3	30.6	27.9	25.3
90°	0.4	0.7	1.4	2.1	2.8	3.2	3.5	3.9	4.6	4.9	5.6
92.5°	5.3	6.3	9.9	15.2	22.6	29.0	35.3	59.2	99.4	143.1	140.7
95°	11.6	12.0	14.8	18.7	26.4	34.3	42.3	80.0	157.6	254.9	312.3
97.5°	18.0	18.3	20.4	24.3	31.4	37.2	43.0	69.1	128.7	233.7	337.4
100°	24.7	25.4	26.8	30.7	37.4	42.6	47.9	68.4	114.2	203.1	318.3
102.5°	32.1	32.4	33.5	37.7	43.7	48.8	53.9	71.6	108.2	179.8	284.8
105°	39.8	39.8	41.6	45.1	50.8	55.7	60.6	76.1	107.5	166.4	255.6
107.5°	47.2	47.9	49.7	52.5	58.5	62.9	67.3	82.5	110.0	159.3	233.7
110°	55.3	56.1	57.5	60.6	65.9	70.5	75.1	89.5	113.9	156.5	219.3

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	63.5	64.2	65.2	68.4	73.7	78.1	82.5	96.2	118.8	156.5	210.8
115°	71.2	71.9	73.0	76.1	81.4	85.8	90.2	103.3	123.7	157.6	205.2
117.5°	78.3	79.3	80.4	83.5	89.5	93.8	98.0	110.3	129.4	159.3	202.0
120°	85.3	86.4	87.8	91.0	96.9	101.4	105.8	118.1	135.0	162.2	199.9
122.5°	92.7	93.4	94.5	97.6	104.3	108.8	113.2	125.5	141.4	164.6	198.1
125°	98.7	99.4	101.2	104.3	111.0	115.6	120.2	131.8	147.0	167.4	196.7
127.5°	103.6	104.7	106.8	110.7	117.7	122.3	126.9	138.2	152.3	170.6	196.0
130°	108.2	109.3	112.1	116.7	124.1	128.7	133.3	144.2	157.6	173.4	195.3
132.5°	111.7	113.2	116.7	122.0	129.7	134.3	138.9	149.8	162.2	176.6	195.3
135°	115.6	117.0	121.3	126.9	134.3	139.0	143.8	154.8	166.4	179.4	195.3
137.5°	120.6	121.6	125.5	131.1	138.5	143.4	148.4	158.3	169.6	182.3	195.7
140°	124.8	125.9	130.1	135.7	142.4	147.2	151.9	162.2	172.7	184.0	196.0
142.5°	129.7	130.4	134.3	140.0	146.3	150.7	155.1	164.6	174.5	185.1	196.4
145°	134.7	135.4	138.9	143.8	150.2	154.2	158.3	167.4	176.3	185.8	196.0
147.5°	140.0	140.3	143.5	148.1	153.7	157.4	161.1	169.2	177.3	186.1	195.3
150°	144.5	145.2	147.7	152.3	157.2	160.2	163.2	171.0	178.4	186.1	194.2
152.5°	149.5	149.8	151.9	155.8	160.4	163.0	165.7	172.7	179.1	185.8	192.8
155°	153.7	153.7	155.8	159.3	162.9	165.4	167.8	173.8	179.4	185.1	191.1
157.5°	157.6	157.6	159.3	162.5	165.7	167.6	169.6	174.9	179.8	184.4	189.3
160°	161.5	161.1	162.5	165.0	167.8	169.4	171.0	175.6	179.8	183.3	187.5
162.5°	164.6	164.3	165.7	167.8	169.9	171.2	172.4	176.3	179.4	182.3	185.4
165°	167.8	167.1	168.2	169.9	171.3	172.4	173.4	176.3	179.1	181.2	183.3
167.5°	169.9	169.6	170.3	171.3	172.4	173.1	173.8	176.3	178.4	179.4	181.2
170°	172.0	171.7	172.0	172.7	173.4	174.0	174.5	176.3	177.7	178.4	179.4
172.5°	173.4	172.7	173.1	173.8	174.1	174.3	174.5	175.9	177.0	177.0	177.3
175°	174.5	173.8	174.1	174.5	174.5	174.5	174.5	175.6	176.3	175.9	175.9
177.5°	175.2	174.5	174.5	174.9	174.5	174.5	174.5	175.2	175.6	174.9	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1638.9	1648.2	1656.2	1662.8	1668.2	1676.1	1670.8	1672.1	1674.8	1680.1	1680.1
5°	1745.3	1759.9	1767.9	1794.5	1801.2	1799.9	1795.9	1817.1	1815.8	1807.8	1806.5
7.5°	1849.1	1874.3	1897.0	1918.2	1924.9	1942.2	1946.2	1955.5	1952.8	1966.1	1959.5
10°	1943.5	1983.4	2004.7	2036.6	2044.6	2052.6	2063.2	2068.6	2080.5	2079.2	2079.2
12.5°	2016.7	2064.6	2092.5	2100.5	2131.1	2140.4	2149.7	2167.0	2163.0	2164.3	2172.3
15°	2073.9	2120.4	2144.4	2181.6	2202.9	2213.6	2229.5	2248.2	2245.5	2257.5	2254.8
17.5°	2116.5	2160.4	2204.3	2260.1	2261.5	2289.4	2326.6	2334.6	2351.9	2339.9	2339.9
20°	2151.0	2209.6	2272.1	2343.9	2351.9	2369.2	2414.4	2445.0	2465.0	2458.3	2462.3
22.5°	2188.3	2272.1	2345.3	2417.1	2455.7	2486.3	2530.2	2578.1	2595.4	2606.0	2603.3
25°	2236.2	2324.0	2431.7	2531.5	2571.4	2629.9	2688.5	2735.0	2748.3	2777.6	2751.0
27.5°	2285.4	2409.1	2543.5	2660.5	2711.1	2759.0	2829.5	2864.1	2881.4	2894.7	2885.3
30°	2326.6	2496.9	2643.2	2751.0	2786.9	2814.8	2854.8	2862.7	2856.1	2866.7	2880.0
32.5°	2390.5	2556.8	2680.5	2732.4	2728.4	2727.0	2696.5	2653.9	2644.6	2619.3	2653.9
35°	2425.1	2558.1	2606.0	2536.8	2508.9	2458.3	2361.2	2297.4	2241.5	2229.5	2232.2
37.5°	2405.1	2457.0	2399.8	2217.6	2172.3	2095.2	1966.1	1875.7	1834.4	1802.5	1843.7
40°	2297.4	2240.2	2083.2	1861.0	1795.9	1722.7	1601.6	1552.4	1493.9	1481.9	1536.5
42.5°	2119.1	1944.8	1722.7	1551.1	1483.2	1442.0	1340.9	1294.3	1253.1	1234.5	1265.1
45°	1877.0	1665.5	1442.0	1301.0	1243.8	1194.6	1134.7	1085.5	1058.9	1050.9	1076.2
47.5°	1626.9	1403.4	1225.2	1120.1	1060.2	1023.0	967.1	939.2	917.9	920.5	924.5
50°	1387.5	1183.9	1046.9	941.8	912.6	883.3	846.0	822.1	811.5	815.5	812.8
52.5°	1181.3	1016.3	900.6	819.4	806.1	778.2	747.6	727.7	723.7	725.0	729.0
55°	1000.4	871.3	779.5	721.0	706.4	686.4	667.8	654.5	643.8	647.8	646.5
57.5°	863.3	750.3	679.8	631.9	621.2	609.3	592.0	585.3	581.3	573.3	580.0
60°	742.3	650.5	589.3	560.0	550.7	542.7	524.1	516.1	513.5	509.5	520.1
62.5°	627.9	562.7	516.1	489.5	480.2	472.2	462.9	456.3	457.6	452.3	457.6
65°	537.4	484.2	451.0	427.0	415.0	409.7	408.4	397.7	396.4	397.7	399.1
67.5°	453.6	408.4	383.1	368.5	359.2	353.9	349.9	343.2	348.5	344.5	347.2
70°	377.8	347.2	320.6	306.0	302.0	303.3	296.6	294.0	295.3	292.7	295.3
72.5°	304.6	279.4	268.7	258.1	252.8	251.4	247.4	243.4	247.4	246.1	246.1
75°	243.4	224.8	212.8	206.2	206.2	203.5	196.9	196.9	196.9	195.5	196.9
77.5°	187.6	171.6	166.3	159.6	159.6	155.6	154.3	154.3	151.7	155.6	153.0
80°	139.7	127.7	119.7	115.7	115.7	114.4	111.7	110.4	111.7	110.4	110.4
82.5°	90.5	85.1	81.1	77.2	75.8	77.2	75.8	73.2	74.5	73.2	75.8
85°	51.9	46.6	46.6	43.9	45.2	42.6	43.9	41.2	39.9	43.9	41.2
87.5°	22.6	21.3	21.3	18.6	18.6	18.6	17.3	18.6	17.3	16.0	17.3
90°	6.0	6.3	6.7	7.1	7.4	7.8	7.8	7.8	8.1	8.1	8.1
92.5°	113.5	76.5	55.0	40.9	37.6	34.2	28.6	27.5	26.8	26.1	26.8
95°	305.6	253.5	199.9	156.5	141.7	126.9	101.9	91.3	88.5	82.8	88.5
97.5°	381.8	363.5	320.8	277.1	256.0	234.8	213.6	195.3	185.8	181.5	185.8
100°	406.5	433.6	416.3	380.0	361.7	343.4	319.0	293.7	280.6	275.0	280.6
102.5°	391.7	457.2	474.8	462.2	451.2	440.3	413.9	397.6	383.2	379.3	383.2
105°	356.8	441.4	489.7	505.2	503.2	501.3	490.0	478.4	471.3	467.1	471.3
107.5°	323.6	408.9	472.7	510.1	517.8	525.6	528.8	527.0	523.5	520.0	523.5
110°	296.1	372.3	439.2	488.9	503.9	518.9	534.8	541.5	543.9	543.9	543.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	275.7	343.4	406.1	456.5	474.8	493.2	518.2	530.9	537.9	541.1	537.9
115°	261.9	320.1	374.7	423.0	442.2	461.5	488.9	505.9	515.7	520.3	515.7
117.5°	252.8	303.9	352.2	394.5	412.6	430.8	458.6	476.3	486.1	488.9	486.1
120°	245.4	291.2	333.5	372.3	387.8	403.3	429.4	446.3	455.8	458.6	455.8
122.5°	239.0	281.7	320.1	353.6	367.8	382.1	404.7	419.9	429.4	431.8	429.4
125°	233.4	272.5	308.5	339.1	351.8	364.5	384.2	398.7	406.5	410.0	406.5
127.5°	228.1	263.0	297.2	326.1	338.1	350.1	368.0	381.1	388.5	389.9	388.5
130°	222.8	254.2	285.2	312.7	324.2	335.6	353.2	364.9	371.9	374.0	371.9
132.5°	218.6	245.4	273.9	298.2	309.2	320.1	337.7	349.4	355.7	358.2	355.7
135°	215.4	238.0	262.3	284.8	294.8	304.9	320.4	332.1	338.4	340.5	338.4
137.5°	212.2	231.3	251.7	271.1	279.9	288.7	302.8	313.7	319.7	322.2	319.7
140°	210.1	226.0	242.5	258.8	266.2	273.6	286.6	295.8	301.1	302.8	301.1
142.5°	208.3	221.4	234.8	248.2	254.4	260.5	271.1	278.5	283.4	284.8	283.4
145°	206.6	217.5	228.4	239.4	244.2	248.9	257.3	263.3	267.2	268.6	267.2
147.5°	204.8	213.6	222.8	231.6	235.3	239.0	246.1	251.0	253.5	254.2	253.5
150°	202.7	210.5	218.2	224.9	228.1	231.3	236.5	240.8	242.2	242.5	242.2
152.5°	200.2	206.9	213.6	219.6	221.9	224.2	228.4	231.6	233.0	233.4	233.0
155°	197.4	203.4	209.0	214.0	216.0	217.9	221.4	223.9	224.9	225.3	224.9
157.5°	194.9	199.9	204.8	208.7	210.3	211.9	214.7	216.8	217.9	217.9	217.9
160°	191.8	196.4	199.9	203.4	204.6	205.9	208.3	210.1	210.8	210.5	210.8
162.5°	189.0	192.5	195.7	198.5	199.6	200.6	202.3	203.8	203.8	203.8	203.8
165°	186.1	189.0	191.4	193.5	194.4	195.3	196.7	197.4	197.4	197.4	197.4
167.5°	183.3	185.4	187.2	189.0	189.7	190.4	191.1	191.8	191.4	191.4	191.4
170°	180.8	182.6	183.7	184.7	185.0	185.4	186.1	186.5	186.5	186.1	186.5
172.5°	178.4	179.4	180.5	181.2	181.4	181.5	181.5	182.3	181.5	181.2	181.5
175°	176.3	177.3	177.3	178.0	178.0	178.0	178.0	178.4	177.7	177.3	177.7
177.5°	175.2	175.6	175.9	175.9	175.9	175.9	175.6	175.9	174.9	174.9	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1677.5	1668.2	1670.8	1668.2	1661.5	1657.5	1646.9	1633.6	1628.2	1621.6	1617.6
5°	1811.8	1805.2	1803.8	1793.2	1790.5	1774.6	1748.0	1734.7	1718.7	1702.7	1686.8
7.5°	1958.2	1950.2	1923.6	1919.6	1922.2	1902.3	1867.7	1841.1	1807.8	1785.2	1754.6
10°	2079.2	2063.2	2040.6	2042.0	2032.6	2006.0	1971.5	1943.5	1895.6	1866.4	1822.5
12.5°	2152.4	2139.1	2136.4	2123.1	2115.1	2080.5	2039.3	2003.4	1967.5	1927.6	1894.3
15°	2241.5	2224.2	2212.2	2193.6	2188.3	2152.4	2107.1	2065.9	2024.7	1987.4	1916.9
17.5°	2339.9	2321.3	2276.1	2272.1	2240.2	2205.6	2161.7	2100.5	2056.6	2003.4	1951.5
20°	2451.7	2425.1	2366.5	2351.9	2326.6	2269.4	2209.6	2141.7	2071.2	2016.7	1955.5
22.5°	2576.7	2530.2	2487.6	2441.0	2422.4	2351.9	2269.4	2187.0	2101.8	2027.3	1954.2
25°	2739.0	2677.8	2618.0	2571.4	2539.5	2447.7	2337.3	2228.2	2129.8	2032.6	1936.9
27.5°	2866.7	2813.5	2748.3	2687.1	2645.9	2536.8	2410.4	2269.4	2147.1	2028.7	1926.2
30°	2876.0	2860.1	2820.2	2786.9	2741.7	2624.6	2484.9	2325.3	2173.7	2030.0	1904.9
32.5°	2701.8	2733.7	2751.0	2756.3	2747.0	2679.2	2551.5	2375.9	2197.6	2018.0	1886.3
35°	2326.6	2411.8	2516.9	2556.8	2595.4	2631.3	2564.8	2411.8	2205.6	2015.4	1857.1
37.5°	1915.6	1992.7	2167.0	2246.8	2292.0	2434.4	2488.9	2406.5	2221.5	2018.0	1829.1
40°	1545.8	1668.2	1793.2	1901.0	1971.5	2131.1	2300.0	2318.7	2198.9	1992.7	1793.2
42.5°	1301.0	1372.8	1467.3	1567.1	1629.6	1818.5	2047.3	2181.6	2128.4	1951.5	1749.3
45°	1108.1	1161.3	1250.5	1283.7	1363.5	1544.4	1786.5	1980.8	2007.4	1886.3	1698.8
47.5°	951.1	996.4	1053.6	1094.8	1158.7	1294.3	1499.2	1713.4	1841.1	1797.2	1628.2
50°	838.1	875.3	923.2	947.1	988.4	1110.8	1265.1	1477.9	1649.5	1664.2	1536.5
52.5°	743.6	764.9	802.2	828.8	862.0	936.5	1076.2	1251.8	1444.7	1524.5	1423.4
55°	661.1	678.4	711.7	729.0	746.3	810.1	919.2	1078.8	1259.8	1364.9	1307.7
57.5°	586.6	601.3	629.2	645.2	654.5	715.7	799.5	924.5	1086.8	1214.5	1182.6
60°	525.5	538.8	554.7	566.7	577.3	627.9	686.4	787.5	932.5	1056.2	1048.3
62.5°	460.3	472.2	489.5	501.5	510.8	542.7	592.0	669.1	792.8	907.2	929.9
65°	403.1	412.4	424.4	429.7	441.6	465.6	505.5	574.7	675.8	778.2	794.2
67.5°	351.2	353.9	361.8	373.8	376.5	397.7	433.7	485.5	564.0	647.8	673.1
70°	295.3	299.3	306.0	315.3	320.6	333.9	364.5	399.1	466.9	540.1	558.7
72.5°	246.1	251.4	254.1	259.4	262.1	283.3	296.6	331.2	377.8	439.0	458.9
75°	199.5	204.9	206.2	208.9	211.5	220.8	239.4	260.7	299.3	339.2	365.8
77.5°	158.3	157.0	159.6	163.6	162.3	170.3	182.2	200.9	226.1	259.4	276.7
80°	111.7	111.7	115.7	119.7	118.4	126.4	130.4	143.7	165.0	186.2	192.9
82.5°	74.5	74.5	78.5	78.5	81.1	82.5	87.8	94.4	111.7	122.4	126.4
85°	42.6	42.6	43.9	43.9	43.9	46.6	50.6	53.2	58.5	65.2	67.8
87.5°	17.3	18.6	18.6	18.6	18.6	21.3	21.3	23.9	25.3	27.9	27.9
90°	7.8	7.8	7.8	7.4	7.1	6.7	6.3	6.0	5.6	4.9	4.6
92.5°	27.5	28.6	34.2	37.6	40.9	55.0	76.5	113.5	140.7	143.1	99.4
95°	91.3	101.9	126.9	141.7	156.5	199.9	253.5	305.6	312.3	254.9	157.6
97.5°	195.3	213.6	234.8	256.0	277.1	320.8	363.5	381.8	337.4	233.7	128.7
100°	293.7	319.0	343.4	361.7	380.0	416.3	433.6	406.5	318.3	203.1	114.2
102.5°	397.6	413.9	440.3	451.2	462.2	474.8	457.2	391.7	284.8	179.8	108.2
105°	478.4	490.0	501.3	503.2	505.2	489.7	441.4	356.8	255.6	166.4	107.5
107.5°	527.0	528.8	525.6	517.8	510.1	472.7	408.9	323.6	233.7	159.3	110.0
110°	541.5	534.8	518.9	503.9	488.9	439.2	372.3	296.1	219.3	156.5	113.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	530.9	518.2	493.2	474.8	456.5	406.1	343.4	275.7	210.8	156.5	118.8
115°	505.9	488.9	461.5	442.2	423.0	374.7	320.1	261.9	205.2	157.6	123.7
117.5°	476.3	458.6	430.8	412.6	394.5	352.2	303.9	252.8	202.0	159.3	129.4
120°	446.3	429.4	403.3	387.8	372.3	333.5	291.2	245.4	199.9	162.2	135.0
122.5°	419.9	404.7	382.1	367.8	353.6	320.1	281.7	239.0	198.1	164.6	141.4
125°	398.7	384.2	364.5	351.8	339.1	308.5	272.5	233.4	196.7	167.4	147.0
127.5°	381.1	368.0	350.1	338.1	326.1	297.2	263.0	228.1	196.0	170.6	152.3
130°	364.9	353.2	335.6	324.2	312.7	285.2	254.2	222.8	195.3	173.4	157.6
132.5°	349.4	337.7	320.1	309.2	298.2	273.9	245.4	218.6	195.3	176.6	162.2
135°	332.1	320.4	304.9	294.8	284.8	262.3	238.0	215.4	195.3	179.4	166.4
137.5°	313.7	302.8	288.7	279.9	271.1	251.7	231.3	212.2	195.7	182.3	169.6
140°	295.8	286.6	273.6	266.2	258.8	242.5	226.0	210.1	196.0	184.0	172.7
142.5°	278.5	271.1	260.5	254.4	248.2	234.8	221.4	208.3	196.4	185.1	174.5
145°	263.3	257.3	248.9	244.2	239.4	228.4	217.5	206.6	196.0	185.8	176.3
147.5°	251.0	246.1	239.0	235.3	231.6	222.8	213.6	204.8	195.3	186.1	177.3
150°	240.8	236.5	231.3	228.1	224.9	218.2	210.5	202.7	194.2	186.1	178.4
152.5°	231.6	228.4	224.2	221.9	219.6	213.6	206.9	200.2	192.8	185.8	179.1
155°	223.9	221.4	217.9	216.0	214.0	209.0	203.4	197.4	191.1	185.1	179.4
157.5°	216.8	214.7	211.9	210.3	208.7	204.8	199.9	194.9	189.3	184.4	179.8
160°	210.1	208.3	205.9	204.6	203.4	199.9	196.4	191.8	187.5	183.3	179.8
162.5°	203.8	202.3	200.6	199.6	198.5	195.7	192.5	189.0	185.4	182.3	179.4
165°	197.4	196.7	195.3	194.4	193.5	191.4	189.0	186.1	183.3	181.2	179.1
167.5°	191.8	191.1	190.4	189.7	189.0	187.2	185.4	183.3	181.2	179.4	178.4
170°	186.5	186.1	185.4	185.0	184.7	183.7	182.6	180.8	179.4	178.4	177.7
172.5°	182.3	181.5	181.5	181.4	181.2	180.5	179.4	178.4	177.3	177.0	177.0
175°	178.4	178.0	178.0	178.0	178.0	177.3	177.3	176.3	175.9	175.9	176.3
177.5°	175.9	175.6	175.9	175.9	175.9	175.9	175.6	175.2	174.9	174.9	175.6
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1612.3	1605.6	1597.7	1597.7	1588.3	1584.3	1576.4	1573.7	1567.1	1556.4	1548.4
5°	1669.5	1652.2	1641.5	1632.2	1612.3	1597.7	1583.0	1567.1	1551.1	1532.5	1511.2
7.5°	1725.4	1693.4	1678.8	1662.8	1633.6	1603.0	1573.7	1552.4	1531.1	1501.9	1475.3
10°	1783.9	1744.0	1717.4	1696.1	1650.9	1612.3	1569.7	1539.1	1505.9	1468.6	1434.0
12.5°	1833.1	1781.2	1758.6	1718.7	1666.8	1620.3	1567.1	1520.5	1476.6	1432.7	1390.1
15°	1874.3	1825.1	1769.3	1753.3	1681.5	1614.9	1555.1	1495.2	1440.7	1396.8	1347.6
17.5°	1887.6	1825.1	1797.2	1758.6	1673.5	1604.3	1528.5	1463.3	1411.4	1346.2	1307.7
20°	1891.6	1831.8	1793.2	1757.3	1681.5	1589.7	1515.2	1435.4	1372.8	1307.7	1246.5
22.5°	1881.0	1810.5	1773.2	1738.7	1653.5	1575.0	1488.6	1400.8	1327.6	1267.7	1206.6
25°	1861.0	1778.6	1742.6	1705.4	1624.3	1537.8	1443.3	1359.5	1291.7	1219.9	1160.0
27.5°	1834.4	1740.0	1698.8	1660.2	1580.4	1499.2	1410.1	1323.6	1247.8	1172.0	1116.1
30°	1801.2	1692.1	1654.9	1604.3	1527.1	1450.0	1368.8	1282.4	1197.2	1125.4	1064.2
32.5°	1758.6	1644.2	1595.0	1547.1	1463.3	1392.8	1315.6	1234.5	1152.0	1081.5	1017.7
35°	1720.0	1589.7	1535.1	1487.2	1394.1	1319.6	1255.8	1179.9	1106.8	1033.6	976.4
37.5°	1668.2	1535.1	1469.9	1420.7	1326.3	1250.5	1190.6	1132.1	1054.9	984.4	931.2
40°	1613.6	1467.3	1406.1	1356.9	1258.4	1176.0	1118.8	1066.9	1004.4	939.2	883.3
42.5°	1564.4	1402.1	1336.9	1277.1	1177.3	1104.1	1045.6	1005.7	948.5	889.9	839.4
45°	1501.9	1332.9	1262.4	1199.9	1104.1	1024.3	968.4	936.5	893.9	836.7	792.8
47.5°	1438.0	1258.4	1185.3	1124.1	1020.3	949.8	895.3	864.7	835.4	790.2	746.3
50°	1354.2	1179.9	1113.4	1042.9	940.5	868.7	823.4	792.8	770.2	738.3	701.1
52.5°	1262.4	1098.8	1027.0	965.8	864.7	799.5	747.6	730.3	707.7	683.8	651.8
55°	1165.3	1011.0	941.8	882.0	788.8	722.3	679.8	661.1	643.8	625.2	603.9
57.5°	1068.2	919.2	854.0	800.8	714.4	650.5	615.9	590.6	578.7	568.0	550.7
60°	947.1	820.8	770.2	722.3	637.2	578.7	545.4	526.8	516.1	510.8	502.8
62.5°	840.7	737.0	681.1	634.5	566.7	514.8	482.9	468.3	458.9	456.3	447.0
65°	727.7	638.5	594.6	554.7	496.2	449.6	423.0	405.7	399.1	397.7	397.7
67.5°	621.2	549.4	505.5	477.6	427.0	385.8	360.5	353.9	349.9	344.5	343.2
70°	521.5	464.3	425.7	401.7	356.5	325.9	306.0	295.3	295.3	291.3	288.7
72.5°	433.7	376.5	351.2	331.2	294.0	267.4	252.8	250.1	240.8	239.4	239.4
75°	339.2	296.6	279.4	262.1	234.1	215.5	203.5	196.9	191.6	191.6	192.9
77.5°	255.4	226.1	210.2	196.9	176.9	165.0	155.6	153.0	147.7	147.7	147.7
80°	180.9	165.0	153.0	142.3	127.7	117.1	111.7	106.4	106.4	105.1	106.4
82.5°	117.1	103.8	97.1	95.8	82.5	78.5	71.8	73.2	69.2	67.8	70.5
85°	67.8	61.2	53.2	50.6	45.2	39.9	37.2	38.6	37.2	35.9	37.2
87.5°	26.6	22.6	21.3	21.3	17.3	16.0	14.6	16.0	13.3	13.3	14.6
90°	3.9	3.5	3.2	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	59.2	35.3	29.0	22.6	15.2	9.9	6.3	5.3	6.3	9.9	15.2
95°	80.0	42.3	34.3	26.4	18.7	14.8	12.0	11.6	12.0	14.8	18.7
97.5°	69.1	43.0	37.2	31.4	24.3	20.4	18.3	18.0	18.3	20.4	24.3
100°	68.4	47.9	42.6	37.4	30.7	26.8	25.4	24.7	25.4	26.8	30.7
102.5°	71.6	53.9	48.8	43.7	37.7	33.5	32.4	32.1	32.4	33.5	37.7
105°	76.1	60.6	55.7	50.8	45.1	41.6	39.8	39.8	39.8	41.6	45.1
107.5°	82.5	67.3	62.9	58.5	52.5	49.7	47.9	47.2	47.9	49.7	52.5
110°	89.5	75.1	70.5	65.9	60.6	57.5	56.1	55.3	56.1	57.5	60.6

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	96.2	82.5	78.1	73.7	68.4	65.2	64.2	63.5	64.2	65.2	68.4
115°	103.3	90.2	85.8	81.4	76.1	73.0	71.9	71.2	71.9	73.0	76.1
117.5°	110.3	98.0	93.8	89.5	83.5	80.4	79.3	78.3	79.3	80.4	83.5
120°	118.1	105.8	101.4	96.9	91.0	87.8	86.4	85.3	86.4	87.8	91.0
122.5°	125.5	113.2	108.8	104.3	97.6	94.5	93.4	92.7	93.4	94.5	97.6
125°	131.8	120.2	115.6	111.0	104.3	101.2	99.4	98.7	99.4	101.2	104.3
127.5°	138.2	126.9	122.3	117.7	110.7	106.8	104.7	103.6	104.7	106.8	110.7
130°	144.2	133.3	128.7	124.1	116.7	112.1	109.3	108.2	109.3	112.1	116.7
132.5°	149.8	138.9	134.3	129.7	122.0	116.7	113.2	111.7	113.2	116.7	122.0
135°	154.8	143.8	139.0	134.3	126.9	121.3	117.0	115.6	117.0	121.3	126.9
137.5°	158.3	148.4	143.4	138.5	131.1	125.5	121.6	120.6	121.6	125.5	131.1
140°	162.2	151.9	147.2	142.4	135.7	130.1	125.9	124.8	125.9	130.1	135.7
142.5°	164.6	155.1	150.7	146.3	140.0	134.3	130.4	129.7	130.4	134.3	140.0
145°	167.4	158.3	154.2	150.2	143.8	138.9	135.4	134.7	135.4	138.9	143.8
147.5°	169.2	161.1	157.4	153.7	148.1	143.5	140.3	140.0	140.3	143.5	148.1
150°	171.0	163.2	160.2	157.2	152.3	147.7	145.2	144.5	145.2	147.7	152.3
152.5°	172.7	165.7	163.0	160.4	155.8	151.9	149.8	149.5	149.8	151.9	155.8
155°	173.8	167.8	165.4	162.9	159.3	155.8	153.7	153.7	153.7	155.8	159.3
157.5°	174.9	169.6	167.6	165.7	162.5	159.3	157.6	157.6	157.6	159.3	162.5
160°	175.6	171.0	169.4	167.8	165.0	162.5	161.1	161.5	161.1	162.5	165.0
162.5°	176.3	172.4	171.2	169.9	167.8	165.7	164.3	164.6	164.3	165.7	167.8
165°	176.3	173.4	172.4	171.3	169.9	168.2	167.1	167.8	167.1	168.2	169.9
167.5°	176.3	173.8	173.1	172.4	171.3	170.3	169.6	169.9	169.6	170.3	171.3
170°	176.3	174.5	174.0	173.4	172.7	172.0	171.7	172.0	171.7	172.0	172.7
172.5°	175.9	174.5	174.3	174.1	173.8	173.1	172.7	173.4	172.7	173.1	173.8
175°	175.6	174.5	174.5	174.5	174.5	174.1	173.8	174.5	173.8	174.1	174.5
177.5°	175.2	174.5	174.5	174.5	174.9	174.5	174.5	175.2	174.5	174.5	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1545.8	1543.1	1536.5	1532.5	1519.2	1503.2	1497.9	1484.6	1489.9	1480.6	1480.6
5°	1504.5	1492.6	1484.6	1472.6	1447.3	1430.0	1411.4	1402.1	1396.8	1390.1	1384.8
7.5°	1451.3	1442.0	1434.0	1411.4	1383.5	1359.5	1336.9	1327.6	1310.3	1298.3	1293.0
10°	1404.8	1391.5	1372.8	1346.2	1317.0	1286.4	1266.4	1246.5	1233.2	1226.5	1211.9
12.5°	1356.9	1340.9	1321.0	1282.4	1250.5	1231.8	1195.9	1177.3	1170.6	1165.3	1148.0
15°	1307.7	1290.4	1266.4	1230.5	1202.6	1158.7	1137.4	1122.7	1106.8	1105.5	1092.1
17.5°	1263.8	1242.5	1222.5	1178.6	1144.0	1105.5	1093.5	1077.5	1062.9	1046.9	1040.3
20°	1207.9	1187.9	1173.3	1125.4	1086.8	1062.9	1042.9	1029.6	1020.3	1004.4	1001.7
22.5°	1157.3	1136.0	1116.1	1080.2	1046.9	1016.3	992.4	977.7	973.8	967.1	955.1
25°	1108.1	1086.8	1062.9	1029.6	995.0	973.8	952.5	943.2	935.2	924.5	915.2
27.5°	1066.9	1046.9	1024.3	983.1	953.8	937.8	915.2	904.6	893.9	888.6	884.6
30°	1017.7	995.0	977.7	945.8	913.9	892.6	876.6	867.3	858.0	852.7	850.0
32.5°	969.8	948.5	936.5	901.9	876.6	851.4	839.4	832.7	827.4	822.1	816.8
35°	931.2	909.9	891.3	859.4	834.1	816.8	807.5	796.8	792.8	787.5	787.5
37.5°	883.3	867.3	848.7	818.1	795.5	782.2	774.2	760.9	759.6	756.9	752.9
40°	842.1	826.1	808.8	782.2	762.2	746.3	735.6	729.0	725.0	722.3	719.7
42.5°	798.2	780.9	772.9	742.3	725.0	709.0	703.7	697.1	695.7	690.4	683.8
45°	755.6	741.0	725.0	702.4	687.7	674.4	666.5	661.1	654.5	653.2	649.2
47.5°	718.3	701.1	686.4	665.1	649.2	638.5	631.9	625.2	619.9	615.9	611.9
50°	670.5	657.2	645.2	622.6	609.3	598.6	589.3	584.0	578.7	578.7	578.7
52.5°	623.9	611.9	601.3	585.3	569.4	560.0	549.4	545.4	542.7	538.8	542.7
55°	578.7	566.7	556.1	544.1	525.5	517.5	506.8	502.8	504.2	504.2	508.2
57.5°	530.8	521.5	514.8	500.2	482.9	474.9	468.3	464.3	464.3	469.6	470.9
60°	484.2	474.9	462.9	449.6	439.0	429.7	425.7	427.0	427.0	429.7	436.3
62.5°	432.3	427.0	420.4	401.7	395.1	388.4	383.1	387.1	385.8	392.4	401.7
65°	384.4	379.1	369.8	360.5	352.5	345.9	344.5	345.9	348.5	355.2	365.8
67.5°	331.2	331.2	323.3	315.3	308.6	302.0	303.3	304.6	307.3	315.3	331.2
70°	287.3	282.0	274.0	268.7	263.4	260.7	258.1	263.4	271.4	276.7	288.7
72.5°	239.4	235.5	228.8	223.5	222.2	219.5	218.2	220.8	228.8	238.1	251.4
75°	188.9	190.2	186.2	182.2	182.2	178.3	180.9	180.9	188.9	198.2	208.9
77.5°	146.3	145.0	143.7	141.0	139.7	139.7	139.7	142.3	150.3	155.6	166.3
80°	103.8	105.1	101.1	102.4	101.1	102.4	102.4	107.8	111.7	118.4	126.4
82.5°	69.2	69.2	66.5	67.8	67.8	67.8	69.2	71.8	77.2	82.5	87.8
85°	38.6	39.9	37.2	39.9	39.9	39.9	41.2	42.6	46.6	47.9	53.2
87.5°	14.6	17.3	17.3	14.6	16.0	17.3	18.6	17.3	20.0	22.6	23.9
90°	2.8	3.2	3.5	3.9	4.6	4.9	5.6	6.0	6.3	6.7	7.1
92.5°	22.6	29.0	35.3	59.2	99.4	143.1	140.7	113.5	76.5	55.0	40.9
95°	26.4	34.3	42.3	80.0	157.6	254.9	312.3	305.6	253.5	199.9	156.5
97.5°	31.4	37.2	43.0	69.1	128.7	233.7	337.4	381.8	363.5	320.8	277.1
100°	37.4	42.6	47.9	68.4	114.2	203.1	318.3	406.5	433.6	416.3	380.0
102.5°	43.7	48.8	53.9	71.6	108.2	179.8	284.8	391.7	457.2	474.8	462.2
105°	50.8	55.7	60.6	76.1	107.5	166.4	255.6	356.8	441.4	489.7	505.2
107.5°	58.5	62.9	67.3	82.5	110.0	159.3	233.7	323.6	408.9	472.7	510.1
110°	65.9	70.5	75.1	89.5	113.9	156.5	219.3	296.1	372.3	439.2	488.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	73.7	78.1	82.5	96.2	118.8	156.5	210.8	275.7	343.4	406.1	456.5
115°	81.4	85.8	90.2	103.3	123.7	157.6	205.2	261.9	320.1	374.7	423.0
117.5°	89.5	93.8	98.0	110.3	129.4	159.3	202.0	252.8	303.9	352.2	394.5
120°	96.9	101.4	105.8	118.1	135.0	162.2	199.9	245.4	291.2	333.5	372.3
122.5°	104.3	108.8	113.2	125.5	141.4	164.6	198.1	239.0	281.7	320.1	353.6
125°	111.0	115.6	120.2	131.8	147.0	167.4	196.7	233.4	272.5	308.5	339.1
127.5°	117.7	122.3	126.9	138.2	152.3	170.6	196.0	228.1	263.0	297.2	326.1
130°	124.1	128.7	133.3	144.2	157.6	173.4	195.3	222.8	254.2	285.2	312.7
132.5°	129.7	134.3	138.9	149.8	162.2	176.6	195.3	218.6	245.4	273.9	298.2
135°	134.3	139.0	143.8	154.8	166.4	179.4	195.3	215.4	238.0	262.3	284.8
137.5°	138.5	143.4	148.4	158.3	169.6	182.3	195.7	212.2	231.3	251.7	271.1
140°	142.4	147.2	151.9	162.2	172.7	184.0	196.0	210.1	226.0	242.5	258.8
142.5°	146.3	150.7	155.1	164.6	174.5	185.1	196.4	208.3	221.4	234.8	248.2
145°	150.2	154.2	158.3	167.4	176.3	185.8	196.0	206.6	217.5	228.4	239.4
147.5°	153.7	157.4	161.1	169.2	177.3	186.1	195.3	204.8	213.6	222.8	231.6
150°	157.2	160.2	163.2	171.0	178.4	186.1	194.2	202.7	210.5	218.2	224.9
152.5°	160.4	163.0	165.7	172.7	179.1	185.8	192.8	200.2	206.9	213.6	219.6
155°	162.9	165.4	167.8	173.8	179.4	185.1	191.1	197.4	203.4	209.0	214.0
157.5°	165.7	167.6	169.6	174.9	179.8	184.4	189.3	194.9	199.9	204.8	208.7
160°	167.8	169.4	171.0	175.6	179.8	183.3	187.5	191.8	196.4	199.9	203.4
162.5°	169.9	171.2	172.4	176.3	179.4	182.3	185.4	189.0	192.5	195.7	198.5
165°	171.3	172.4	173.4	176.3	179.1	181.2	183.3	186.1	189.0	191.4	193.5
167.5°	172.4	173.1	173.8	176.3	178.4	179.4	181.2	183.3	185.4	187.2	189.0
170°	173.4	174.0	174.5	176.3	177.7	178.4	179.4	180.8	182.6	183.7	184.7
172.5°	174.1	174.3	174.5	175.9	177.0	177.0	177.3	178.4	179.4	180.5	181.2
175°	174.5	174.5	174.5	175.6	176.3	175.9	175.9	176.3	177.3	177.3	178.0
177.5°	174.5	174.5	174.5	175.2	175.6	174.9	174.9	175.2	175.6	175.9	175.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1485.9	1476.6	1475.3	1477.9	1472.6	1480.6	1477.9	1480.6	1473.9	1480.6	1476.6
5°	1383.5	1380.8	1375.5	1368.8	1370.2	1371.5	1378.2	1371.5	1376.8	1378.2	1384.8
7.5°	1287.7	1282.4	1286.4	1283.7	1271.7	1269.1	1271.7	1275.7	1283.7	1289.0	1293.0
10°	1210.5	1207.9	1202.6	1198.6	1191.9	1187.9	1193.2	1187.9	1198.6	1207.9	1207.9
12.5°	1152.0	1141.4	1134.7	1133.4	1118.8	1121.4	1126.7	1130.7	1142.7	1148.0	1148.0
15°	1090.8	1082.8	1080.2	1074.9	1069.5	1074.9	1072.2	1076.2	1081.5	1086.8	1089.5
17.5°	1037.6	1036.3	1037.6	1024.3	1028.3	1021.6	1023.0	1029.6	1025.6	1029.6	1037.6
20°	989.7	992.4	988.4	983.1	983.1	975.1	984.4	981.7	983.1	991.0	1003.0
22.5°	953.8	952.5	948.5	944.5	939.2	940.5	941.8	939.2	949.8	956.5	957.8
25°	915.2	912.6	911.2	907.2	901.9	907.2	905.9	907.2	909.9	920.5	912.6
27.5°	879.3	874.0	876.6	872.7	871.3	872.7	872.7	874.0	876.6	878.0	879.3
30°	848.7	843.4	842.1	839.4	838.1	839.4	842.1	839.4	850.0	848.7	848.7
32.5°	815.5	811.5	808.8	808.8	807.5	806.1	807.5	808.8	816.8	811.5	816.8
35°	783.5	780.9	780.9	778.2	776.9	776.9	776.9	782.2	779.5	783.5	783.5
37.5°	752.9	752.9	751.6	748.9	747.6	748.9	747.6	750.3	748.9	750.3	751.6
40°	721.0	718.3	717.0	717.0	713.0	709.0	713.0	713.0	714.4	718.3	719.7
42.5°	682.4	683.8	683.8	678.4	678.4	678.4	679.8	681.1	681.1	683.8	683.8
45°	649.2	646.5	646.5	646.5	643.8	645.2	647.8	647.8	647.8	647.8	645.2
47.5°	611.9	611.9	613.3	613.3	617.2	615.9	615.9	614.6	611.9	611.9	613.3
50°	577.3	581.3	582.7	582.7	584.0	585.3	585.3	582.7	581.3	577.3	577.3
52.5°	544.1	546.7	549.4	553.4	556.1	554.7	554.7	552.1	546.7	545.4	544.1
55°	508.2	512.2	517.5	521.5	525.5	526.8	526.8	521.5	516.1	509.5	509.5
57.5°	474.9	478.9	488.2	492.2	497.5	497.5	494.9	490.9	482.9	477.6	473.6
60°	441.6	448.3	455.0	462.9	469.6	470.9	466.9	461.6	452.3	445.6	440.3
62.5°	405.7	412.4	425.7	433.7	439.0	439.0	439.0	432.3	420.4	411.1	403.1
65°	371.1	377.8	389.8	400.4	404.4	408.4	404.4	397.7	388.4	377.8	369.8
67.5°	335.2	343.2	355.2	363.2	368.5	372.5	369.8	364.5	352.5	337.9	332.6
70°	295.3	299.3	316.6	324.6	332.6	335.2	332.6	324.6	312.6	296.6	291.3
72.5°	258.1	262.1	278.0	284.7	291.3	294.0	290.0	284.7	274.0	259.4	252.8
75°	215.5	222.2	230.1	240.8	248.8	251.4	247.4	243.4	230.1	220.8	215.5
77.5°	170.3	176.9	187.6	196.9	204.9	203.5	198.2	199.5	184.9	174.3	170.3
80°	129.0	134.4	142.3	150.3	154.3	154.3	153.0	147.7	142.3	134.4	127.7
82.5°	89.1	95.8	102.4	107.8	107.8	109.1	106.4	105.1	99.8	93.1	91.8
85°	53.2	54.5	59.9	59.9	65.2	62.5	61.2	65.2	59.9	55.9	54.5
87.5°	23.9	22.6	23.9	23.9	22.6	25.3	25.3	23.9	25.3	23.9	23.9
90°	7.4	7.8	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.4
92.5°	37.6	34.2	28.6	27.5	26.8	26.1	26.8	27.5	28.6	34.2	37.6
95°	141.7	126.9	101.9	91.3	88.5	82.8	88.5	91.3	101.9	126.9	141.7
97.5°	256.0	234.8	213.6	195.3	185.8	181.5	185.8	195.3	213.6	234.8	256.0
100°	361.7	343.4	319.0	293.7	280.6	275.0	280.6	293.7	319.0	343.4	361.7
102.5°	451.2	440.3	413.9	397.6	383.2	379.3	383.2	397.6	413.9	440.3	451.2
105°	503.2	501.3	490.0	478.4	471.3	467.1	471.3	478.4	490.0	501.3	503.2
107.5°	517.8	525.6	528.8	527.0	523.5	520.0	523.5	527.0	528.8	525.6	517.8
110°	503.9	518.9	534.8	541.5	543.9	543.9	543.9	541.5	534.8	518.9	503.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	474.8	493.2	518.2	530.9	537.9	541.1	537.9	530.9	518.2	493.2	474.8
115°	442.2	461.5	488.9	505.9	515.7	520.3	515.7	505.9	488.9	461.5	442.2
117.5°	412.6	430.8	458.6	476.3	486.1	488.9	486.1	476.3	458.6	430.8	412.6
120°	387.8	403.3	429.4	446.3	455.8	458.6	455.8	446.3	429.4	403.3	387.8
122.5°	367.8	382.1	404.7	419.9	429.4	431.8	429.4	419.9	404.7	382.1	367.8
125°	351.8	364.5	384.2	398.7	406.5	410.0	406.5	398.7	384.2	364.5	351.8
127.5°	338.1	350.1	368.0	381.1	388.5	389.9	388.5	381.1	368.0	350.1	338.1
130°	324.2	335.6	353.2	364.9	371.9	374.0	371.9	364.9	353.2	335.6	324.2
132.5°	309.2	320.1	337.7	349.4	355.7	358.2	355.7	349.4	337.7	320.1	309.2
135°	294.8	304.9	320.4	332.1	338.4	340.5	338.4	332.1	320.4	304.9	294.8
137.5°	279.9	288.7	302.8	313.7	319.7	322.2	319.7	313.7	302.8	288.7	279.9
140°	266.2	273.6	286.6	295.8	301.1	302.8	301.1	295.8	286.6	273.6	266.2
142.5°	254.4	260.5	271.1	278.5	283.4	284.8	283.4	278.5	271.1	260.5	254.4
145°	244.2	248.9	257.3	263.3	267.2	268.6	267.2	263.3	257.3	248.9	244.2
147.5°	235.3	239.0	246.1	251.0	253.5	254.2	253.5	251.0	246.1	239.0	235.3
150°	228.1	231.3	236.5	240.8	242.2	242.5	242.2	240.8	236.5	231.3	228.1
152.5°	221.9	224.2	228.4	231.6	233.0	233.4	233.0	231.6	228.4	224.2	221.9
155°	216.0	217.9	221.4	223.9	224.9	225.3	224.9	223.9	221.4	217.9	216.0
157.5°	210.3	211.9	214.7	216.8	217.9	217.9	217.9	216.8	214.7	211.9	210.3
160°	204.6	205.9	208.3	210.1	210.8	210.5	210.8	210.1	208.3	205.9	204.6
162.5°	199.6	200.6	202.3	203.8	203.8	203.8	203.8	203.8	202.3	200.6	199.6
165°	194.4	195.3	196.7	197.4	197.4	197.4	197.4	197.4	196.7	195.3	194.4
167.5°	189.7	190.4	191.1	191.8	191.4	191.4	191.4	191.8	191.1	190.4	189.7
170°	185.0	185.4	186.1	186.5	186.5	186.1	186.5	186.5	186.1	185.4	185.0
172.5°	181.4	181.5	181.5	182.3	181.5	181.2	181.5	182.3	181.5	181.5	181.4
175°	178.0	178.0	178.0	178.4	177.7	177.3	177.7	178.4	178.0	178.0	178.0
177.5°	175.9	175.9	175.6	175.9	174.9	174.9	174.9	175.9	175.6	175.9	175.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1	1567.1
2.5°	1488.6	1480.6	1489.9	1477.9	1480.6	1495.2	1493.9	1507.2	1515.2	1513.8	1520.5
5°	1390.1	1390.1	1394.1	1392.8	1406.1	1418.1	1434.0	1447.3	1462.0	1469.9	1479.3
7.5°	1293.0	1306.3	1309.0	1315.6	1331.6	1351.6	1367.5	1387.5	1408.8	1423.4	1434.0
10°	1213.2	1223.8	1234.5	1239.8	1257.1	1283.7	1306.3	1338.2	1364.9	1380.8	1395.4
12.5°	1142.7	1154.7	1160.0	1183.9	1195.9	1213.2	1245.1	1279.7	1309.0	1326.3	1338.2
15°	1092.1	1098.8	1110.8	1125.4	1137.4	1158.7	1185.3	1223.8	1251.8	1266.4	1307.7
17.5°	1049.6	1057.6	1064.2	1070.9	1089.5	1112.1	1137.4	1170.6	1206.6	1231.8	1253.1
20°	1005.7	1009.7	1017.7	1028.3	1041.6	1062.9	1085.5	1120.1	1152.0	1172.0	1199.9
22.5°	953.8	965.8	973.8	981.7	996.4	1020.3	1041.6	1066.9	1106.8	1129.4	1158.7
25°	923.2	928.5	933.8	943.2	953.8	975.1	999.0	1025.6	1057.6	1081.5	1106.8
27.5°	883.3	891.3	897.9	909.9	916.6	933.8	956.5	983.1	1021.6	1041.6	1062.9
30°	850.0	858.0	863.3	868.7	878.0	896.6	917.9	939.2	975.1	1000.4	1021.6
32.5°	816.8	824.8	831.4	835.4	844.7	856.7	874.0	900.6	931.2	948.5	976.4
35°	787.5	787.5	795.5	800.8	808.8	819.4	835.4	855.4	887.3	909.9	935.2
37.5°	754.3	755.6	762.2	766.2	774.2	784.9	800.8	819.4	846.0	863.3	888.6
40°	719.7	723.7	726.3	733.0	742.3	746.3	762.2	783.5	810.1	826.1	847.4
42.5°	685.1	687.7	694.4	699.7	707.7	714.4	725.0	744.9	764.9	788.8	806.1
45°	646.5	653.2	657.2	666.5	670.5	677.1	687.7	703.7	727.7	742.3	762.2
47.5°	613.3	615.9	618.6	630.5	638.5	642.5	653.2	662.5	687.7	701.1	719.7
50°	577.3	577.3	581.3	586.6	596.0	603.9	613.3	623.9	643.8	657.2	675.8
52.5°	544.1	540.1	542.7	545.4	554.7	562.7	572.0	586.6	605.3	613.3	629.2
55°	508.2	501.5	505.5	509.5	512.2	522.8	533.4	542.7	557.4	569.4	584.0
57.5°	469.6	468.3	465.6	466.9	473.6	480.2	488.2	500.2	517.5	526.8	534.8
60°	435.0	427.0	424.4	427.0	431.0	435.0	445.6	456.3	470.9	480.2	489.5
62.5°	399.1	391.1	385.8	381.8	385.8	395.1	401.7	409.7	421.7	432.3	440.3
65°	364.5	352.5	347.2	344.5	343.2	349.9	355.2	365.8	376.5	380.5	389.8
67.5°	325.9	315.3	308.6	304.6	304.6	304.6	310.0	320.6	331.2	332.6	341.9
70°	287.3	275.4	268.7	263.4	260.7	263.4	270.0	271.4	280.7	283.3	288.7
72.5°	246.1	235.5	227.5	220.8	222.2	224.8	224.8	227.5	232.8	239.4	239.4
75°	207.5	192.9	188.9	183.6	180.9	180.9	180.9	186.2	190.2	195.5	194.2
77.5°	163.6	155.6	147.7	145.0	141.0	139.7	142.3	142.3	145.0	149.0	150.3
80°	126.4	117.1	111.7	109.1	103.8	102.4	103.8	103.8	107.8	106.4	107.8
82.5°	87.8	81.1	77.2	73.2	70.5	71.8	70.5	70.5	71.8	70.5	70.5
85°	50.6	49.2	46.6	45.2	43.9	41.2	43.9	42.6	41.2	39.9	42.6
87.5°	23.9	22.6	22.6	20.0	20.0	18.6	20.0	20.0	18.6	18.6	18.6
90°	7.1	6.7	6.3	6.0	5.6	4.9	4.6	3.9	3.5	3.2	2.8
92.5°	40.9	55.0	76.5	113.5	140.7	143.1	99.4	59.2	35.3	29.0	22.6
95°	156.5	199.9	253.5	305.6	312.3	254.9	157.6	80.0	42.3	34.3	26.4
97.5°	277.1	320.8	363.5	381.8	337.4	233.7	128.7	69.1	43.0	37.2	31.4
100°	380.0	416.3	433.6	406.5	318.3	203.1	114.2	68.4	47.9	42.6	37.4
102.5°	462.2	474.8	457.2	391.7	284.8	179.8	108.2	71.6	53.9	48.8	43.7
105°	505.2	489.7	441.4	356.8	255.6	166.4	107.5	76.1	60.6	55.7	50.8
107.5°	510.1	472.7	408.9	323.6	233.7	159.3	110.0	82.5	67.3	62.9	58.5
110°	488.9	439.2	372.3	296.1	219.3	156.5	113.9	89.5	75.1	70.5	65.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	456.5	406.1	343.4	275.7	210.8	156.5	118.8	96.2	82.5	78.1	73.7
115°	423.0	374.7	320.1	261.9	205.2	157.6	123.7	103.3	90.2	85.8	81.4
117.5°	394.5	352.2	303.9	252.8	202.0	159.3	129.4	110.3	98.0	93.8	89.5
120°	372.3	333.5	291.2	245.4	199.9	162.2	135.0	118.1	105.8	101.4	96.9
122.5°	353.6	320.1	281.7	239.0	198.1	164.6	141.4	125.5	113.2	108.8	104.3
125°	339.1	308.5	272.5	233.4	196.7	167.4	147.0	131.8	120.2	115.6	111.0
127.5°	326.1	297.2	263.0	228.1	196.0	170.6	152.3	138.2	126.9	122.3	117.7
130°	312.7	285.2	254.2	222.8	195.3	173.4	157.6	144.2	133.3	128.7	124.1
132.5°	298.2	273.9	245.4	218.6	195.3	176.6	162.2	149.8	138.9	134.3	129.7
135°	284.8	262.3	238.0	215.4	195.3	179.4	166.4	154.8	143.8	139.0	134.3
137.5°	271.1	251.7	231.3	212.2	195.7	182.3	169.6	158.3	148.4	143.4	138.5
140°	258.8	242.5	226.0	210.1	196.0	184.0	172.7	162.2	151.9	147.2	142.4
142.5°	248.2	234.8	221.4	208.3	196.4	185.1	174.5	164.6	155.1	150.7	146.3
145°	239.4	228.4	217.5	206.6	196.0	185.8	176.3	167.4	158.3	154.2	150.2
147.5°	231.6	222.8	213.6	204.8	195.3	186.1	177.3	169.2	161.1	157.4	153.7
150°	224.9	218.2	210.5	202.7	194.2	186.1	178.4	171.0	163.2	160.2	157.2
152.5°	219.6	213.6	206.9	200.2	192.8	185.8	179.1	172.7	165.7	163.0	160.4
155°	214.0	209.0	203.4	197.4	191.1	185.1	179.4	173.8	167.8	165.4	162.9
157.5°	208.7	204.8	199.9	194.9	189.3	184.4	179.8	174.9	169.6	167.6	165.7
160°	203.4	199.9	196.4	191.8	187.5	183.3	179.8	175.6	171.0	169.4	167.8
162.5°	198.5	195.7	192.5	189.0	185.4	182.3	179.4	176.3	172.4	171.2	169.9
165°	193.5	191.4	189.0	186.1	183.3	181.2	179.1	176.3	173.4	172.4	171.3
167.5°	189.0	187.2	185.4	183.3	181.2	179.4	178.4	176.3	173.8	173.1	172.4
170°	184.7	183.7	182.6	180.8	179.4	178.4	177.7	176.3	174.5	174.0	173.4
172.5°	181.2	180.5	179.4	178.4	177.3	177.0	177.0	175.9	174.5	174.3	174.1
175°	178.0	177.3	177.3	176.3	175.9	175.9	176.3	175.6	174.5	174.5	174.5
177.5°	175.9	175.9	175.6	175.2	174.9	174.9	175.6	175.2	174.5	174.5	174.5
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1567.1	1567.1	1567.1	1567.1
2.5°	1529.8	1543.1	1552.4	1569.7
5°	1495.2	1519.2	1541.8	1565.7
7.5°	1460.6	1488.6	1524.5	1555.1
10°	1422.1	1458.0	1500.5	1541.8
12.5°	1383.5	1426.0	1472.6	1527.1
15°	1336.9	1391.5	1446.0	1504.5
17.5°	1295.7	1351.6	1410.1	1483.2
20°	1249.1	1310.3	1374.2	1448.7
22.5°	1207.9	1275.7	1342.2	1420.7
25°	1161.3	1227.8	1301.0	1384.8
27.5°	1122.7	1183.9	1255.8	1346.2
30°	1076.2	1142.7	1214.5	1305.0
32.5°	1032.3	1096.1	1172.0	1261.1
35°	987.1	1052.2	1120.1	1205.2
37.5°	944.5	1000.4	1068.2	1149.4
40°	896.6	957.8	1019.0	1082.8
42.5°	852.7	908.6	965.8	1016.3
45°	803.5	851.4	905.9	947.1
47.5°	758.3	800.8	843.4	875.3
50°	713.0	746.3	778.2	806.1
52.5°	659.8	697.1	714.4	731.6
55°	611.9	633.2	649.2	666.5
57.5°	565.4	574.7	582.7	598.6
60°	504.2	514.8	524.1	536.1
62.5°	451.0	456.3	458.9	470.9
65°	400.4	399.1	405.7	412.4
67.5°	345.9	344.5	351.2	353.9
70°	292.7	291.3	292.7	299.3
72.5°	242.1	242.1	243.4	246.1
75°	195.5	195.5	196.9	199.5
77.5°	147.7	150.3	149.0	154.3
80°	107.8	105.1	107.8	110.4
82.5°	70.5	73.2	73.2	70.5
85°	39.9	39.9	39.9	39.9
87.5°	17.3	17.3	18.6	20.0
90°	2.1	1.4	0.7	0.4
92.5°	15.2	9.9	6.3	5.3
95°	18.7	14.8	12.0	11.6
97.5°	24.3	20.4	18.3	18.0
100°	30.7	26.8	25.4	24.7
102.5°	37.7	33.5	32.4	32.1
105°	45.1	41.6	39.8	39.8
107.5°	52.5	49.7	47.9	47.2
110°	60.6	57.5	56.1	55.3

TEST NUMBER: P1027396

CATALOG NUMBER: S125DIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	68.4	65.2	64.2	63.5
115°	76.1	73.0	71.9	71.2
117.5°	83.5	80.4	79.3	78.3
120°	91.0	87.8	86.4	85.3
122.5°	97.6	94.5	93.4	92.7
125°	104.3	101.2	99.4	98.7
127.5°	110.7	106.8	104.7	103.6
130°	116.7	112.1	109.3	108.2
132.5°	122.0	116.7	113.2	111.7
135°	126.9	121.3	117.0	115.6
137.5°	131.1	125.5	121.6	120.6
140°	135.7	130.1	125.9	124.8
142.5°	140.0	134.3	130.4	129.7
145°	143.8	138.9	135.4	134.7
147.5°	148.1	143.5	140.3	140.0
150°	152.3	147.7	145.2	144.5
152.5°	155.8	151.9	149.8	149.5
155°	159.3	155.8	153.7	153.7
157.5°	162.5	159.3	157.6	157.6
160°	165.0	162.5	161.1	161.5
162.5°	167.8	165.7	164.3	164.6
165°	169.9	168.2	167.1	167.8
167.5°	171.3	170.3	169.6	169.9
170°	172.7	172.0	171.7	172.0
172.5°	173.8	173.1	172.7	173.4
175°	174.5	174.1	173.8	174.5
177.5°	174.9	174.5	174.5	175.2
180°	174.9	174.9	174.9	174.9

(END OF REPORT)