

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027605

Luminaire Tested: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027605
REPORT IS A COMBINATION OF REPORTS P1001628 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9254.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027605

CATALOG NUMBER: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027605

CATALOG NUMBER: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	53	51
2	90	82	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12582	12582	12582
5°	12582	12289	12313
10°	12478	12008	11970
15°	12314	11671	11566
20°	12093	11280	11103
25°	11855	10854	10607
30°	11568	10410	10084
35°	11262	9944	9498
40°	10945	9452	8978
45°	10602	8973	8425
50°	10225	8429	7780
55°	9852	7829	7187
60°	9407	7197	6498
65°	8875	6465	5785
70°	8333	5623	4961
75°	7422	4630	4011
80°	6324	3458	2951
85°	4883	2046	1626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10602 cd/sqm

TEST NUMBER: P1027605

CATALOG NUMBER: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	2.0
10°-20°	523.4	5.7
20°-30°	772.7	8.4
30°-40°	901.5	9.7
40°-50°	905.5	9.8
50°-60°	794.8	8.6
60°-70°	592.0	6.4
70°-80°	338.1	3.7
80°-90°	99.9	1.1
90°-100°	98.7	1.1
100°-110°	293.1	3.2
110°-120°	497.1	5.4
120°-130°	654.4	7.1
130°-140°	733.3	7.9
140°-150°	718.7	7.8
150°-160°	603.7	6.5
160°-170°	401.3	4.3
170°-180°	140.4	1.5
0°-30°	1481.4	16.0
0°-40°	2383.0	25.8
0°-60°	4083.2	44.1
0°-90°	5113.3	55.3
90°-120°	888.8	9.6
90°-150°	2995.2	32.4
90°-180°	4141.0	44.7
0°-180°	9254.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1961	1958	1942	1956	1954	186
15°	1869	1864	1847	1855	1855	527
25°	1696	1689	1668	1672	1667	781
35°	1465	1459	1437	1429	1417	916
45°	1199	1193	1174	1156	1151	924
55°	914	909	887	873	862	815
65°	617	614	597	583	576	612
75°	328	325	317	312	306	349
85°	85	87	87	85	82	94
90°	1	10	18	24	28	11
95°	75	77	89	97	99	78
105°	263	269	276	283	286	281
115°	498	502	504	503	502	492
125°	726	733	734	732	731	651
135°	944	951	952	952	948	728
145°	1144	1149	1152	1152	1149	715
155°	1309	1309	1310	1315	1309	603
165°	1424	1421	1422	1427	1420	402
175°	1480	1476	1476	1482	1474	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1027605

CATALOG NUMBER: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1963.7	1963.7	1963.7	1963.7	1963.7
2.5°	1969.9	1965.2	1949.7	1965.2	1963.7
5°	1960.6	1957.5	1941.9	1955.9	1954.4
7.5°	1946.6	1943.5	1926.4	1940.4	1938.8
10°	1926.4	1923.3	1906.2	1918.6	1917.1
12.5°	1901.5	1895.3	1879.8	1889.1	1889.1
15°	1868.9	1864.3	1847.2	1854.9	1854.9
17.5°	1834.7	1827.0	1809.9	1819.2	1811.4
20°	1789.7	1786.6	1766.4	1777.3	1769.5
22.5°	1744.6	1738.4	1719.8	1726.0	1721.3
25°	1696.5	1688.7	1668.5	1671.6	1667.0
27.5°	1640.6	1635.9	1615.7	1617.2	1612.6
30°	1586.2	1581.5	1558.2	1555.1	1550.4
32.5°	1527.1	1519.4	1499.2	1493.0	1483.6
35°	1465.0	1458.8	1437.0	1429.3	1416.8
37.5°	1401.3	1393.5	1373.3	1362.5	1354.7
40°	1336.1	1328.3	1306.5	1292.6	1287.9
42.5°	1266.1	1259.9	1238.2	1225.8	1218.0
45°	1199.3	1193.1	1174.5	1155.8	1151.2
47.5°	1126.3	1127.9	1104.6	1085.9	1075.1
50°	1056.4	1051.8	1033.1	1012.9	1002.0
52.5°	985.0	981.8	961.6	944.6	932.1
55°	913.5	908.8	887.1	873.1	862.2
57.5°	837.4	835.8	817.2	798.5	793.9
60°	765.9	759.7	742.6	727.1	716.2
62.5°	691.3	686.7	672.7	655.6	647.8
65°	616.8	613.7	596.6	582.6	576.4
67.5°	543.7	537.5	525.1	512.7	509.6
70°	475.4	467.6	453.6	444.3	438.1
72.5°	400.8	396.2	388.4	377.5	371.3
75°	327.8	324.7	316.9	312.3	306.0
77.5°	259.4	257.9	253.2	250.1	245.5
80°	195.7	195.7	192.6	191.1	188.0
82.5°	139.8	136.7	136.7	133.6	133.6
85°	85.4	87.0	87.0	85.4	82.3
87.5°	41.9	41.9	40.4	40.4	37.3
90°	1.2	10.4	18.5	24.2	27.7
92.5°	34.6	40.4	50.8	58.9	61.2
95°	75.0	77.4	88.9	97.0	99.3
97.5°	115.5	116.6	132.8	139.7	140.9
100°	161.6	161.6	176.7	187.0	189.4
102.5°	211.3	217.1	222.8	234.4	237.8
105°	263.2	269.0	275.9	282.9	286.3
107.5°	319.8	325.6	331.4	334.8	334.8
110°	378.7	384.5	387.9	391.4	390.2



TEST NUMBER: P1027605

CATALOG NUMBER: S125DIP-B1270D1270UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	438.7	441.0	445.7	446.8	444.5
115°	497.6	502.2	504.5	503.4	502.2
117.5°	557.7	558.8	561.1	562.3	557.7
120°	613.1	618.9	620.0	620.0	615.4
122.5°	673.1	674.3	677.7	676.6	673.1
125°	726.2	733.2	734.3	732.0	730.8
127.5°	785.1	788.6	789.7	788.6	786.3
130°	837.1	842.8	845.1	844.0	841.7
132.5°	889.0	899.4	898.3	897.1	893.6
135°	944.4	951.4	952.5	952.5	947.9
137.5°	996.4	1003.3	1005.6	1006.8	1001.0
140°	1046.0	1051.8	1055.3	1057.6	1051.8
142.5°	1095.7	1100.3	1104.9	1106.1	1100.3
145°	1144.2	1148.8	1152.3	1152.3	1148.8
147.5°	1189.2	1192.7	1195.0	1198.4	1189.2
150°	1234.2	1233.1	1237.7	1237.7	1235.4
152.5°	1271.2	1273.5	1274.7	1278.1	1273.5
155°	1309.3	1309.3	1310.4	1315.1	1309.3
157.5°	1343.9	1341.6	1342.8	1347.4	1339.3
160°	1373.9	1370.5	1371.6	1376.3	1370.5
162.5°	1400.5	1398.2	1398.2	1404.0	1397.0
165°	1423.6	1421.3	1422.4	1427.1	1420.1
167.5°	1444.4	1439.8	1439.8	1446.7	1439.8
170°	1460.5	1455.9	1455.9	1462.8	1454.8
172.5°	1472.1	1467.5	1467.5	1474.4	1467.5
175°	1480.2	1475.5	1475.5	1482.5	1474.4
177.5°	1485.9	1481.3	1480.2	1487.1	1479.0
180°	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)