

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027461

Luminaire Tested: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027461
REPORT IS A COMBINATION OF REPORTS P1001436 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB35-4F0-XX-W2A-D1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6318.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027461

CATALOG NUMBER: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1027461

CATALOG NUMBER: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	100	95	91	87	93	89	85	82	78	75	73	68	66	64	59	57	56
2	91	82	76	70	85	77	72	67	68	63	59	59	56	53	51	49	46
3	82	72	64	58	77	68	61	55	60	54	50	52	48	44	45	42	39
4	75	64	55	49	70	60	52	47	53	47	42	46	42	38	40	37	33
5	69	57	48	42	64	54	46	40	47	41	36	42	37	33	36	32	29
6	64	51	42	36	59	48	40	35	43	36	32	38	32	28	33	29	25
7	59	46	38	32	55	43	36	30	39	32	28	34	29	25	30	26	23
8	55	42	34	28	51	40	32	27	35	29	25	31	26	22	27	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	25	21	18
10	48	35	28	23	45	33	26	22	30	24	20	27	22	18	24	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8807	8807	8807
5°	8821	8622	8643
10°	8755	8446	8422
15°	8648	8241	8150
20°	8504	7994	7880
25°	8334	7731	7554
30°	8127	7445	7257
35°	7935	7180	6984
40°	7738	6902	6708
45°	7517	6661	6460
50°	7304	6399	6236
55°	7049	6149	5976
60°	6770	5864	5709
65°	6477	5564	5409
70°	6142	5162	5097
75°	5615	4765	4716
80°	4922	4282	4295
85°	4237	3899	4073

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7517 cd/sqm

TEST NUMBER: P1027461

CATALOG NUMBER: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	2.1
10°-20°	369.2	5.8
20°-30°	549.1	8.7
30°-40°	650.3	10.3
40°-50°	672.3	10.6
50°-60°	619.3	9.8
60°-70°	500.6	7.9
70°-80°	335.0	5.3
80°-90°	174.3	2.8
90°-100°	146.6	2.3
100°-110°	217.6	3.4
110°-120°	295.3	4.7
120°-130°	352.6	5.6
130°-140°	376.5	6.0
140°-150°	359.7	5.7
150°-160°	300.2	4.8
160°-170°	199.5	3.2
170°-180°	69.8	1.1
0°-30°	1048.4	16.6
0°-40°	1698.6	26.9
0°-60°	2990.2	47.3
0°-90°	4000.1	63.3
90°-120°	659.5	10.4
90°-150°	1748.4	27.7
90°-180°	2318.0	36.7
0°-180°	6318.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1374	1372	1362	1373	1372	130
15°	1312	1314	1304	1312	1307	370
25°	1193	1197	1188	1194	1187	549
35°	1032	1042	1038	1042	1042	646
45°	850	865	872	881	883	656
55°	654	675	697	712	717	584
65°	450	481	513	534	539	447
75°	248	283	326	353	360	263
85°	74	119	166	195	206	77
90°	22	70	120	154	165	17
95°	55	91	143	176	187	53
105°	143	168	211	242	253	152
115°	256	267	304	327	335	253
125°	366	368	396	417	423	328
135°	472	474	484	502	506	364
145°	570	571	573	580	583	356
155°	651	651	652	654	651	300
165°	708	707	707	710	706	200
175°	736	734	734	737	733	70
180°	738	738	738	738	738	

TEST NUMBER: P1027461

CATALOG NUMBER: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.5	1374.5	1374.5	1374.5	1374.5
2.5°	1378.6	1375.9	1366.4	1375.9	1374.5
5°	1374.5	1371.8	1362.4	1373.2	1371.8
7.5°	1365.1	1363.7	1354.3	1363.7	1362.4
10°	1351.6	1351.6	1340.8	1350.3	1348.9
12.5°	1332.7	1334.1	1326.0	1332.7	1328.7
15°	1312.5	1313.9	1304.4	1312.5	1307.1
17.5°	1286.9	1289.6	1280.2	1286.9	1282.9
20°	1258.6	1261.3	1251.9	1255.9	1255.9
22.5°	1226.3	1231.7	1220.9	1226.3	1222.2
25°	1192.6	1196.6	1188.5	1193.9	1187.2
27.5°	1156.2	1161.6	1152.2	1156.2	1153.5
30°	1114.4	1122.5	1114.4	1117.1	1115.8
32.5°	1076.7	1083.4	1078.0	1080.7	1079.4
35°	1032.2	1041.7	1037.6	1041.7	1041.7
37.5°	989.1	997.2	995.8	1001.2	999.9
40°	944.6	955.4	954.1	959.5	962.2
42.5°	896.1	911.0	915.0	921.7	921.7
45°	850.3	865.1	871.9	881.3	882.7
47.5°	803.1	816.6	827.4	840.9	843.6
50°	754.6	769.5	784.3	799.1	803.1
52.5°	703.4	722.3	741.2	757.3	760.0
55°	653.6	675.1	696.7	711.5	716.9
57.5°	602.4	628.0	652.2	668.4	672.4
60°	551.2	578.1	605.1	625.3	629.3
62.5°	501.3	528.2	557.9	580.8	586.2
65°	450.1	481.1	513.4	533.6	539.0
67.5°	402.9	432.6	464.9	489.2	495.9
70°	350.4	381.4	416.4	442.0	450.1
72.5°	299.2	331.5	370.6	398.9	404.3
75°	248.0	283.0	326.1	353.1	359.8
77.5°	198.1	238.5	278.9	308.6	314.0
80°	152.3	192.7	238.5	268.2	273.6
82.5°	110.5	153.6	200.8	229.1	239.9
85°	74.1	118.6	165.8	195.4	206.2
87.5°	47.2	90.3	136.1	167.1	176.5
90°	22.2	69.9	119.7	153.6	164.7
92.5°	36.1	78.0	130.4	164.1	174.6
95°	54.8	91.1	142.6	176.2	186.9
97.5°	73.6	106.5	159.0	190.8	200.7
100°	95.2	123.5	174.0	207.5	216.7
102.5°	118.6	147.0	191.7	224.3	234.2
105°	143.0	167.5	211.3	241.8	252.9
107.5°	169.8	191.5	233.5	262.2	270.3
110°	197.7	216.8	256.2	283.5	292.4

TEST NUMBER: P1027461

CATALOG NUMBER: S125DIP-B1090D610UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.6	240.9	279.5	304.4	312.6
115°	255.5	267.2	303.5	327.1	334.6
117.5°	284.0	291.4	326.2	349.7	356.8
120°	311.5	318.5	350.1	373.0	378.8
122.5°	340.1	342.0	373.4	394.3	400.7
125°	366.5	368.5	396.1	416.6	422.7
127.5°	394.4	394.8	418.3	437.9	444.9
130°	420.2	421.8	441.8	460.1	465.7
132.5°	444.7	449.9	462.8	481.1	484.7
135°	472.3	474.3	484.4	501.9	506.3
137.5°	498.1	500.2	506.7	523.5	526.0
140°	521.4	524.3	527.4	543.4	545.9
142.5°	546.1	547.1	549.4	562.1	564.6
145°	570.2	571.2	572.9	579.6	583.3
147.5°	591.3	593.0	594.2	598.6	596.7
150°	613.7	613.1	615.4	615.4	615.6
152.5°	632.1	633.2	633.8	635.5	633.2
155°	651.0	651.0	651.6	653.9	651.0
157.5°	668.2	667.1	667.7	670.0	665.9
160°	683.2	681.4	682.0	684.3	681.4
162.5°	696.4	695.2	695.2	698.1	694.6
165°	707.8	706.7	707.3	709.6	706.1
167.5°	718.2	715.9	715.9	719.3	715.9
170°	726.2	723.9	723.9	727.4	723.3
172.5°	732.0	729.7	729.7	733.1	729.7
175°	736.0	733.7	733.7	737.1	733.1
177.5°	738.8	736.5	736.0	739.4	735.4
180°	737.7	737.7	737.7	737.7	737.7

(END OF REPORT)