

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027755

Luminaire Tested: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027755
REPORT IS A COMBINATION OF REPORTS P1001826 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4983.0 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027755

CATALOG NUMBER: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027755

CATALOG NUMBER: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	60	55	52	49	41	39	37	29	28	26
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	21	18	17
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	19	16	15
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	15	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3043 cd/sqm

TEST NUMBER: P1027755

CATALOG NUMBER: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	1.1
10°-20°	150.2	3.0
20°-30°	221.8	4.5
30°-40°	258.8	5.2
40°-50°	259.9	5.2
50°-60°	228.1	4.6
60°-70°	169.9	3.4
70°-80°	97.1	1.9
80°-90°	30.0	0.6
90°-100°	83.7	1.7
100°-110°	248.7	5.0
110°-120°	421.8	8.5
120°-130°	555.3	11.1
130°-140°	622.3	12.5
140°-150°	610.0	12.2
150°-160°	512.4	10.3
160°-170°	340.6	6.8
170°-180°	119.2	2.4
0°-30°	425.2	8.5
0°-40°	684.0	13.7
0°-60°	1172.0	23.5
0°-90°	1468.9	29.5
90°-120°	754.3	15.1
90°-150°	2541.9	51.0
90°-180°	3514.0	70.5
0°-180°	4983.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	1	9	16	21	24	6
95°	64	66	75	82	84	67
105°	223	228	234	240	243	238
115°	422	426	428	427	426	418
125°	616	622	623	621	620	552
135°	802	807	808	808	804	618
145°	971	975	978	978	975	607
155°	1111	1111	1112	1116	1111	512
165°	1208	1206	1207	1211	1205	341
175°	1256	1252	1252	1258	1251	119
180°	1259	1259	1259	1259	1259	

TEST NUMBER: P1027755

CATALOG NUMBER: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	1.0	8.8	15.7	20.6	23.5
92.5°	29.4	34.3	43.1	50.0	51.9
95°	63.7	65.6	75.4	82.3	84.3
97.5°	98.0	99.0	112.7	118.6	119.5
100°	137.2	137.2	149.9	158.7	160.7
102.5°	179.3	184.2	189.1	198.9	201.8
105°	223.4	228.3	234.2	240.1	243.0
107.5°	271.4	276.3	281.2	284.2	284.2
110°	321.4	326.3	329.2	332.2	331.2

TEST NUMBER: P1027755

CATALOG NUMBER: S125DIP-B375D1090UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.3	374.3	378.2	379.2	377.2
115°	422.3	426.2	428.2	427.2	426.2
117.5°	473.3	474.2	476.2	477.2	473.3
120°	520.3	525.2	526.2	526.2	522.3
122.5°	571.2	572.2	575.2	574.2	571.2
125°	616.3	622.2	623.2	621.2	620.2
127.5°	666.3	669.2	670.2	669.2	667.3
130°	710.4	715.3	717.2	716.3	714.3
132.5°	754.5	763.3	762.3	761.3	758.4
135°	801.5	807.4	808.4	808.4	804.5
137.5°	845.6	851.5	853.4	854.4	849.5
140°	887.7	892.6	895.6	897.5	892.6
142.5°	929.9	933.8	937.7	938.7	933.8
145°	971.0	974.9	977.9	977.9	974.9
147.5°	1009.2	1012.2	1014.1	1017.1	1009.2
150°	1047.5	1046.5	1050.4	1050.4	1048.4
152.5°	1078.8	1080.8	1081.7	1084.7	1080.8
155°	1111.1	1111.1	1112.1	1116.0	1111.1
157.5°	1140.5	1138.6	1139.6	1143.5	1136.6
160°	1166.0	1163.1	1164.1	1168.0	1163.1
162.5°	1188.5	1186.6	1186.6	1191.5	1185.6
165°	1208.1	1206.2	1207.2	1211.1	1205.2
167.5°	1225.8	1221.9	1221.9	1227.7	1221.9
170°	1239.5	1235.6	1235.6	1241.5	1234.6
172.5°	1249.3	1245.4	1245.4	1251.3	1245.4
175°	1256.2	1252.2	1252.2	1258.1	1251.3
177.5°	1261.1	1257.1	1256.2	1262.0	1255.2
180°	1259.1	1259.1	1259.1	1259.1	1259.1

(END OF REPORT)