

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027551

Luminaire Tested: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027551
REPORT IS A COMBINATION OF REPORTS P1001559 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8725.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027551

CATALOG NUMBER: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027551

CATALOG NUMBER: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	84	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10710 cd/sqm

TEST NUMBER: P1027551

CATALOG NUMBER: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.1
10°-20°	528.7	6.1
20°-30°	780.6	8.9
30°-40°	910.7	10.4
40°-50°	914.7	10.5
50°-60°	802.9	9.2
60°-70°	598.0	6.9
70°-80°	341.6	3.9
80°-90°	100.6	1.2
90°-100°	84.8	1.0
100°-110°	252.0	2.9
110°-120°	427.4	4.9
120°-130°	562.6	6.4
130°-140°	630.4	7.2
140°-150°	617.9	7.1
150°-160°	519.1	5.9
160°-170°	345.0	4.0
170°-180°	120.7	1.4
0°-30°	1496.5	17.2
0°-40°	2407.2	27.6
0°-60°	4124.8	47.3
0°-90°	5165.0	59.2
90°-120°	764.2	8.8
90°-150°	2575.2	29.5
90°-180°	3560.0	40.8
0°-180°	8725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	1	9	16	21	24	10
95°	64	66	76	83	85	67
105°	226	231	237	243	246	241
115°	428	432	434	433	432	423
125°	624	630	631	629	628	559
135°	812	818	819	819	815	626
145°	984	988	991	991	988	615
155°	1126	1126	1127	1131	1126	519
165°	1224	1222	1223	1227	1221	345
175°	1273	1269	1269	1275	1268	121
180°	1276	1276	1276	1276	1276	

TEST NUMBER: P1027551

CATALOG NUMBER: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	1.0	8.9	15.9	20.8	23.8
92.5°	29.8	34.7	43.7	50.6	52.6
95°	64.5	66.5	76.4	83.4	85.4
97.5°	99.3	100.3	114.2	120.1	121.1
100°	139.0	139.0	151.9	160.8	162.8
102.5°	181.7	186.6	191.6	201.5	204.5
105°	226.3	231.3	237.2	243.2	246.2
107.5°	275.0	279.9	284.9	287.9	287.9
110°	325.6	330.6	333.5	336.5	335.5



TEST NUMBER: P1027551

CATALOG NUMBER: S125DIP-B1270D1090UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.2	379.2	383.2	384.2	382.2
115°	427.8	431.8	433.8	432.8	431.8
117.5°	479.5	480.4	482.4	483.4	479.5
120°	527.1	532.1	533.1	533.1	529.1
122.5°	578.7	579.7	582.7	581.7	578.7
125°	624.4	630.3	631.3	629.3	628.4
127.5°	675.0	678.0	679.0	678.0	676.0
130°	719.7	724.6	726.6	725.6	723.7
132.5°	764.3	773.3	772.3	771.3	768.3
135°	812.0	818.0	818.9	818.9	815.0
137.5°	856.7	862.6	864.6	865.6	860.6
140°	899.4	904.3	907.3	909.3	904.3
142.5°	942.0	946.0	950.0	951.0	946.0
145°	983.7	987.7	990.7	990.7	987.7
147.5°	1022.4	1025.4	1027.4	1030.4	1022.4
150°	1061.2	1060.2	1064.1	1064.1	1062.1
152.5°	1092.9	1094.9	1095.9	1098.9	1094.9
155°	1125.7	1125.7	1126.7	1130.6	1125.7
157.5°	1155.5	1153.5	1154.5	1158.4	1151.5
160°	1181.3	1178.3	1179.3	1183.3	1178.3
162.5°	1204.1	1202.1	1202.1	1207.1	1201.1
165°	1224.0	1222.0	1223.0	1226.9	1221.0
167.5°	1241.8	1237.8	1237.8	1243.8	1237.8
170°	1255.7	1251.7	1251.7	1257.7	1250.8
172.5°	1265.6	1261.7	1261.7	1267.6	1261.7
175°	1272.6	1268.6	1268.6	1274.6	1267.6
177.5°	1277.6	1273.6	1272.6	1278.5	1271.6
180°	1275.6	1275.6	1275.6	1275.6	1275.6

(END OF REPORT)