

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027569

Luminaire Tested: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027569
REPORT IS A COMBINATION OF REPORTS P1001577 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8353.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027569

CATALOG NUMBER: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027569

CATALOG NUMBER: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1027569

CATALOG NUMBER: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	2.1
10°-20°	506.2	6.1
20°-30°	747.3	8.9
30°-40°	871.9	10.4
40°-50°	875.7	10.5
50°-60°	768.7	9.2
60°-70°	572.6	6.9
70°-80°	327.0	3.9
80°-90°	96.3	1.2
90°-100°	81.2	1.0
100°-110°	241.2	2.9
110°-120°	409.1	4.9
120°-130°	538.6	6.4
130°-140°	603.5	7.2
140°-150°	591.6	7.1
150°-160°	496.9	5.9
160°-170°	330.3	4.0
170°-180°	115.6	1.4
0°-30°	1432.7	17.2
0°-40°	2304.6	27.6
0°-60°	3949.0	47.3
0°-90°	4944.9	59.2
90°-120°	731.6	8.8
90°-150°	2465.3	29.5
90°-180°	3408.0	40.8
0°-180°	8353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	1	9	15	20	23	10
95°	62	64	73	80	82	65
105°	217	221	227	233	236	231
115°	410	413	415	414	413	405
125°	598	603	604	602	602	536
135°	777	783	784	784	780	599
145°	942	946	948	948	946	589
155°	1078	1078	1079	1082	1078	496
165°	1172	1170	1171	1175	1169	331
175°	1218	1214	1214	1220	1214	116
180°	1221	1221	1221	1221	1221	

TEST NUMBER: P1027569

CATALOG NUMBER: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	1.0	8.6	15.2	20.0	22.8
92.5°	28.5	33.3	41.8	48.5	50.4
95°	61.8	63.7	73.2	79.8	81.7
97.5°	95.0	96.0	109.3	115.0	115.9
100°	133.0	133.0	145.4	153.9	155.8
102.5°	173.9	178.7	183.4	192.9	195.8
105°	216.7	221.4	227.1	232.8	235.7
107.5°	263.2	268.0	272.7	275.6	275.6
110°	311.7	316.5	319.3	322.2	321.2

TEST NUMBER: P1027569

CATALOG NUMBER: S125DIP-B1270D1090UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	361.1	363.0	366.8	367.8	365.9
115°	409.6	413.4	415.3	414.3	413.4
117.5°	459.0	459.9	461.8	462.8	459.0
120°	504.6	509.4	510.3	510.3	506.5
122.5°	554.0	555.0	557.8	556.9	554.0
125°	597.7	603.4	604.4	602.5	601.5
127.5°	646.2	649.1	650.0	649.1	647.2
130°	689.0	693.7	695.6	694.7	692.8
132.5°	731.7	740.3	739.3	738.4	735.5
135°	777.3	783.0	784.0	784.0	780.2
137.5°	820.1	825.8	827.7	828.7	823.9
140°	861.0	865.7	868.6	870.5	865.7
142.5°	901.8	905.6	909.4	910.4	905.6
145°	941.7	945.6	948.4	948.4	945.6
147.5°	978.8	981.7	983.6	986.4	978.8
150°	1015.9	1014.9	1018.7	1018.7	1016.8
152.5°	1046.3	1048.2	1049.1	1052.0	1048.2
155°	1077.6	1077.6	1078.6	1082.4	1077.6
157.5°	1106.2	1104.3	1105.2	1109.0	1102.4
160°	1130.9	1128.0	1129.0	1132.8	1128.0
162.5°	1152.7	1150.8	1150.8	1155.6	1149.9
165°	1171.7	1169.8	1170.8	1174.6	1168.9
167.5°	1188.8	1185.0	1185.0	1190.7	1185.0
170°	1202.1	1198.3	1198.3	1204.0	1197.4
172.5°	1211.6	1207.8	1207.8	1213.5	1207.8
175°	1218.3	1214.5	1214.5	1220.2	1213.5
177.5°	1223.0	1219.2	1218.3	1224.0	1217.3
180°	1221.1	1221.1	1221.1	1221.1	1221.1

(END OF REPORT)