

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027578

Luminaire Tested: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027578
REPORT IS A COMBINATION OF REPORTS P1001586 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9227.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027578

CATALOG NUMBER: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027578

CATALOG NUMBER: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	53	51
2	90	82	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1027578

CATALOG NUMBER: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.0
10°-20°	521.9	5.7
20°-30°	770.4	8.3
30°-40°	898.9	9.7
40°-50°	902.8	9.8
50°-60°	792.5	8.6
60°-70°	590.3	6.4
70°-80°	337.1	3.7
80°-90°	99.6	1.1
90°-100°	98.4	1.1
100°-110°	292.2	3.2
110°-120°	495.6	5.4
120°-130°	652.5	7.1
130°-140°	731.2	7.9
140°-150°	716.7	7.8
150°-160°	602.0	6.5
160°-170°	400.2	4.3
170°-180°	140.0	1.5
0°-30°	1477.1	16.0
0°-40°	2376.0	25.8
0°-60°	4071.3	44.1
0°-90°	5098.3	55.3
90°-120°	886.2	9.6
90°-150°	2986.5	32.4
90°-180°	4129.0	44.7
0°-180°	9227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	10	18	24	28	11
95°	75	77	89	97	99	78
105°	262	268	275	282	286	280
115°	496	501	503	502	501	491
125°	724	731	732	730	729	649
135°	942	949	950	950	945	726
145°	1141	1146	1149	1149	1146	713
155°	1306	1306	1307	1311	1306	601
165°	1420	1417	1418	1423	1416	401
175°	1476	1471	1471	1478	1470	140
180°	1479	1479	1479	1479	1479	

TEST NUMBER: P1027578

CATALOG NUMBER: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	1.2	10.4	18.4	24.2	27.6
92.5°	34.5	40.3	50.7	58.7	61.0
95°	74.8	77.1	88.6	96.7	99.0
97.5°	115.1	116.3	132.4	139.3	140.5
100°	161.2	161.2	176.1	186.5	188.8
102.5°	210.7	216.4	222.2	233.7	237.2
105°	262.5	268.2	275.1	282.1	285.5
107.5°	318.9	324.6	330.4	333.9	333.9
110°	377.6	383.4	386.8	390.3	389.1

TEST NUMBER: P1027578

CATALOG NUMBER: S125DIP-B1270D1270UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	439.8	444.4	445.5	443.2
115°	496.2	500.8	503.1	501.9	500.8
117.5°	556.0	557.2	559.5	560.6	556.0
120°	611.3	617.1	618.2	618.2	613.6
122.5°	671.2	672.3	675.8	674.6	671.2
125°	724.1	731.0	732.2	729.9	728.7
127.5°	782.8	786.3	787.4	786.3	784.0
130°	834.6	840.4	842.7	841.6	839.2
132.5°	886.4	896.8	895.7	894.5	891.1
135°	941.7	948.6	949.8	949.8	945.2
137.5°	993.5	1000.4	1002.7	1003.9	998.1
140°	1043.0	1048.8	1052.2	1054.5	1048.8
142.5°	1092.5	1097.1	1101.7	1102.9	1097.1
145°	1140.9	1145.5	1148.9	1148.9	1145.5
147.5°	1185.8	1189.2	1191.5	1195.0	1185.8
150°	1230.7	1229.5	1234.1	1234.1	1231.8
152.5°	1267.5	1269.8	1271.0	1274.4	1269.8
155°	1305.5	1305.5	1306.6	1311.3	1305.5
157.5°	1340.0	1337.7	1338.9	1343.5	1335.4
160°	1370.0	1366.5	1367.7	1372.3	1366.5
162.5°	1396.4	1394.1	1394.1	1399.9	1393.0
165°	1419.5	1417.2	1418.3	1422.9	1416.0
167.5°	1440.2	1435.6	1435.6	1442.5	1435.6
170°	1456.3	1451.7	1451.7	1458.6	1450.6
172.5°	1467.8	1463.2	1463.2	1470.1	1463.2
175°	1475.9	1471.3	1471.3	1478.2	1470.1
177.5°	1481.6	1477.0	1475.9	1482.8	1474.7
180°	1479.3	1479.3	1479.3	1479.3	1479.3

(END OF REPORT)