

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027613

Luminaire Tested: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027613
REPORT IS A COMBINATION OF REPORTS P1001636 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB50-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9573.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027613

CATALOG NUMBER: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1027613

CATALOG NUMBER: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1027613

CATALOG NUMBER: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	1.9
10°-20°	506.2	5.3
20°-30°	747.3	7.8
30°-40°	871.9	9.1
40°-50°	875.7	9.1
50°-60°	768.7	8.0
60°-70°	572.6	6.0
70°-80°	327.0	3.4
80°-90°	96.6	1.0
90°-100°	51.2	0.5
100°-110°	340.0	3.6
110°-120°	612.3	6.4
120°-130°	785.9	8.2
130°-140°	845.3	8.8
140°-150°	793.3	8.3
150°-160°	641.7	6.7
160°-170°	415.0	4.3
170°-180°	143.1	1.5
0°-30°	1432.7	15.0
0°-40°	2304.6	24.1
0°-60°	3949.0	41.3
0°-90°	4945.2	51.7
90°-120°	1003.5	10.5
90°-150°	3428.0	35.8
90°-180°	4628.0	48.3
0°-180°	9573.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	1	10	18	24	27	9
95°	64	60	18	24	24	78
105°	328	333	333	333	332	348
115°	616	622	623	619	612	611
125°	877	884	884	880	877	783
135°	1093	1100	1098	1096	1089	843
145°	1268	1270	1270	1271	1264	793
155°	1396	1389	1392	1395	1386	643
165°	1473	1466	1468	1474	1465	416
175°	1506	1500	1501	1510	1500	143
180°	1506	1506	1506	1506	1506	

TEST NUMBER: P1027613

CATALOG NUMBER: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	1.1	10.1	17.9	23.5	26.8
92.5°	21.2	11.2	17.9	23.5	24.6
95°	63.7	60.3	17.9	23.5	23.5
97.5°	119.5	126.2	20.1	22.3	23.5
100°	186.5	189.9	194.3	27.9	23.5
102.5°	254.6	259.1	261.3	263.6	169.8
105°	328.3	332.8	332.8	332.8	331.7
107.5°	404.3	404.3	406.5	407.6	403.2
110°	478.0	478.0	480.2	476.9	478.0

TEST NUMBER: P1027613

CATALOG NUMBER: S125DIP-B1270D1270UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	547.2	550.6	551.7	547.2	545.0
115°	616.5	622.0	623.2	618.7	612.0
117.5°	689.1	689.1	693.5	686.8	684.6
120°	756.1	754.9	758.3	756.1	750.5
122.5°	815.3	820.8	822.0	819.7	813.0
125°	876.7	884.5	884.5	880.0	876.7
127.5°	935.9	941.4	940.3	938.1	929.2
130°	989.5	995.1	996.2	992.8	987.2
132.5°	1043.1	1049.8	1046.4	1046.4	1040.8
135°	1093.3	1100.0	1097.8	1095.6	1088.9
137.5°	1140.2	1146.9	1144.7	1144.7	1139.1
140°	1186.0	1188.3	1187.1	1189.4	1182.7
142.5°	1227.3	1228.5	1230.7	1230.7	1224.0
145°	1267.5	1269.8	1269.8	1270.9	1264.2
147.5°	1303.3	1303.3	1304.4	1305.5	1297.7
150°	1336.8	1334.6	1336.8	1339.0	1330.1
152.5°	1369.2	1363.6	1365.8	1368.1	1360.2
155°	1396.0	1389.3	1391.5	1394.9	1385.9
157.5°	1417.2	1413.8	1413.8	1417.2	1408.3
160°	1439.5	1432.8	1433.9	1438.4	1429.5
162.5°	1457.4	1450.7	1451.8	1458.5	1448.5
165°	1473.0	1466.3	1467.5	1474.2	1465.2
167.5°	1485.3	1478.6	1479.7	1487.6	1477.5
170°	1495.4	1487.6	1488.7	1497.6	1487.6
172.5°	1502.1	1494.3	1496.5	1504.3	1494.3
175°	1506.5	1499.8	1501.0	1509.9	1499.8
177.5°	1509.9	1503.2	1504.3	1512.1	1503.2
180°	1506.5	1506.5	1506.5	1506.5	1506.5

(END OF REPORT)