

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027631

Luminaire Tested: S125DIP-B1270D375UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027631
REPORT IS A COMBINATION OF REPORTS P1001669 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027631

CATALOG NUMBER: S125DIP-B1270D375UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1027631

CATALOG NUMBER: S125DIP-B1270D375UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58
3	86	76	69	62	82	73	66	60	67	61	57	61	57	53	56	52	49
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	42
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	38	33	29
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	34	30	26
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1027631

CATALOG NUMBER: S125DIP-B1270D375UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.8
10°-20°	526.5	8.0
20°-30°	777.2	11.7
30°-40°	906.8	13.7
40°-50°	910.8	13.8
50°-60°	799.5	12.1
60°-70°	595.5	9.0
70°-80°	340.1	5.1
80°-90°	98.9	1.5
90°-100°	16.3	0.2
100°-110°	108.2	1.6
110°-120°	194.9	2.9
120°-130°	250.2	3.8
130°-140°	269.1	4.1
140°-150°	252.6	3.8
150°-160°	204.3	3.1
160°-170°	132.1	2.0
170°-180°	45.6	0.7
0°-30°	1490.1	22.5
0°-40°	2396.9	36.2
0°-60°	4107.2	62.1
0°-90°	5141.7	77.7
90°-120°	319.5	4.8
90°-150°	1091.3	16.5
90°-180°	1473.0	22.3
0°-180°	6615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	0	3	6	8	8	7
95°	20	19	6	8	8	25
105°	104	106	106	106	106	111
115°	196	198	198	197	195	195
125°	279	282	282	280	279	249
135°	348	350	350	349	347	268
145°	404	404	404	405	402	252
155°	444	442	443	444	441	205
165°	469	467	467	469	466	132
175°	480	478	478	481	478	46
180°	480	480	480	480	480	

TEST NUMBER: P1027631

CATALOG NUMBER: S125DIP-B1270D375UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	0.4	3.2	5.7	7.5	8.5
92.5°	6.8	3.6	5.7	7.5	7.8
95°	20.3	19.2	5.7	7.5	7.5
97.5°	38.0	40.2	6.4	7.1	7.5
100°	59.4	60.4	61.9	8.9	7.5
102.5°	81.1	82.5	83.2	83.9	54.0
105°	104.5	105.9	105.9	105.9	105.6
107.5°	128.7	128.7	129.4	129.8	128.3
110°	152.2	152.2	152.9	151.8	152.2

TEST NUMBER: P1027631

CATALOG NUMBER: S125DIP-B1270D375UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.2	175.3	175.6	174.2	173.5
115°	196.3	198.0	198.4	197.0	194.8
117.5°	219.4	219.4	220.8	218.7	217.9
120°	240.7	240.3	241.4	240.7	238.9
122.5°	259.5	261.3	261.7	261.0	258.8
125°	279.1	281.6	281.6	280.2	279.1
127.5°	297.9	299.7	299.4	298.7	295.8
130°	315.0	316.8	317.1	316.1	314.3
132.5°	332.1	334.2	333.1	333.1	331.4
135°	348.1	350.2	349.5	348.8	346.6
137.5°	363.0	365.1	364.4	364.4	362.6
140°	377.6	378.3	377.9	378.6	376.5
142.5°	390.7	391.1	391.8	391.8	389.7
145°	403.5	404.2	404.2	404.6	402.5
147.5°	414.9	414.9	415.3	415.6	413.1
150°	425.6	424.9	425.6	426.3	423.4
152.5°	435.9	434.1	434.8	435.5	433.0
155°	444.4	442.3	443.0	444.1	441.2
157.5°	451.2	450.1	450.1	451.2	448.3
160°	458.3	456.2	456.5	457.9	455.1
162.5°	464.0	461.8	462.2	464.3	461.1
165°	469.0	466.8	467.2	469.3	466.5
167.5°	472.9	470.7	471.1	473.6	470.4
170°	476.1	473.6	473.9	476.8	473.6
172.5°	478.2	475.7	476.4	478.9	475.7
175°	479.6	477.5	477.8	480.7	477.5
177.5°	480.7	478.6	478.9	481.4	478.6
180°	479.6	479.6	479.6	479.6	479.6

(END OF REPORT)