

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027659

Luminaire Tested: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027659
REPORT IS A COMBINATION OF REPORTS P1001697 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB50-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6170.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027659

CATALOG NUMBER: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027659

CATALOG NUMBER: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	59
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51
4	80	68	60	53	76	65	58	52	60	54	49	56	51	46	52	47	44
5	73	61	52	46	70	59	51	45	54	48	42	50	45	40	46	42	38
6	68	55	46	40	64	53	45	39	49	42	37	45	40	35	42	37	34
7	63	50	41	35	60	48	40	34	45	38	33	41	36	31	39	34	30
8	58	45	37	31	56	44	36	31	41	34	29	38	32	28	35	30	27
9	54	41	34	28	52	40	33	28	37	31	26	35	29	25	33	28	24
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1027659

CATALOG NUMBER: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	2.9
10°-20°	506.2	8.2
20°-30°	747.3	12.1
30°-40°	871.9	14.1
40°-50°	875.7	14.2
50°-60°	768.7	12.5
60°-70°	572.6	9.3
70°-80°	327.0	5.3
80°-90°	95.1	1.5
90°-100°	29.2	0.5
100°-110°	86.8	1.4
110°-120°	147.2	2.4
120°-130°	193.8	3.1
130°-140°	217.2	3.5
140°-150°	212.9	3.4
150°-160°	178.8	2.9
160°-170°	118.9	1.9
170°-180°	41.6	0.7
0°-30°	1432.7	23.2
0°-40°	2304.6	37.4
0°-60°	3949.0	64.0
0°-90°	4943.7	80.1
90°-120°	263.2	4.3
90°-150°	887.1	14.4
90°-180°	1226.0	19.9
0°-180°	6170.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	0	3	6	7	8	7
95°	22	23	26	29	29	23
105°	78	80	82	84	85	83
115°	147	149	149	149	149	146
125°	215	217	218	217	216	193
135°	280	282	282	282	281	216
145°	339	340	341	341	340	212
155°	388	388	388	390	388	179
165°	422	421	421	423	421	119
175°	438	437	437	439	437	42
180°	439	439	439	439	439	

TEST NUMBER: P1027659

CATALOG NUMBER: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	0.3	3.1	5.5	7.2	8.2
92.5°	10.3	12.0	15.0	17.4	18.1
95°	22.2	22.9	26.3	28.7	29.4
97.5°	34.2	34.5	39.3	41.4	41.7
100°	47.9	47.9	52.3	55.4	56.1
102.5°	62.6	64.3	66.0	69.4	70.4
105°	78.0	79.7	81.7	83.8	84.8
107.5°	94.7	96.4	98.1	99.2	99.2
110°	112.2	113.9	114.9	115.9	115.6

TEST NUMBER: P1027659

CATALOG NUMBER: S125DIP-B1270D375UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	129.9	130.6	132.0	132.3	131.6
115°	147.4	148.7	149.4	149.1	148.7
117.5°	165.2	165.5	166.2	166.5	165.2
120°	181.6	183.3	183.6	183.6	182.3
122.5°	199.4	199.7	200.7	200.4	199.4
125°	215.1	217.1	217.5	216.8	216.4
127.5°	232.5	233.5	233.9	233.5	232.9
130°	247.9	249.6	250.3	250.0	249.3
132.5°	263.3	266.4	266.0	265.7	264.7
135°	279.7	281.8	282.1	282.1	280.7
137.5°	295.1	297.1	297.8	298.2	296.5
140°	309.8	311.5	312.5	313.2	311.5
142.5°	324.5	325.9	327.2	327.6	325.9
145°	338.9	340.2	341.3	341.3	340.2
147.5°	352.2	353.2	353.9	354.9	352.2
150°	365.5	365.2	366.6	366.6	365.9
152.5°	376.5	377.2	377.5	378.5	377.2
155°	387.8	387.8	388.1	389.5	387.8
157.5°	398.0	397.3	397.7	399.0	396.7
160°	406.9	405.9	406.2	407.6	405.9
162.5°	414.8	414.1	414.1	415.8	413.7
165°	421.6	420.9	421.3	422.6	420.6
167.5°	427.8	426.4	426.4	428.5	426.4
170°	432.6	431.2	431.2	433.2	430.8
172.5°	436.0	434.6	434.6	436.7	434.6
175°	438.4	437.0	437.0	439.1	436.7
177.5°	440.1	438.7	438.4	440.4	438.0
180°	439.4	439.4	439.4	439.4	439.4

(END OF REPORT)