

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027908

Luminaire Tested: S125DIP-B375D610UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027908
REPORT IS A COMBINATION OF REPORTS P1002039 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3546.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027908

CATALOG NUMBER: S125DIP-B375D610UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027908

CATALOG NUMBER: S125DIP-B375D610UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	41	36	56	46	38	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3658	3573	3580
10°	3628	3491	3480
15°	3580	3393	3363
20°	3516	3280	3228
25°	3446	3156	3084
30°	3364	3026	2932
35°	3274	2891	2761
40°	3183	2748	2610
45°	3083	2609	2450
50°	2973	2451	2262
55°	2865	2276	2090
60°	2735	2092	1889
65°	2580	1879	1682
70°	2423	1635	1443
75°	2158	1346	1167
80°	1839	1005	859
85°	1418	595	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3083 cd/sqm

TEST NUMBER: P1027908

CATALOG NUMBER: S125DIP-B375D610UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.5
10°-20°	152.2	4.3
20°-30°	224.7	6.3
30°-40°	262.1	7.4
40°-50°	263.3	7.4
50°-60°	231.1	6.5
60°-70°	172.1	4.9
70°-80°	98.3	2.8
80°-90°	29.5	0.8
90°-100°	49.1	1.4
100°-110°	145.7	4.1
110°-120°	247.2	7.0
120°-130°	325.4	9.2
130°-140°	364.6	10.3
140°-150°	357.4	10.1
150°-160°	300.2	8.5
160°-170°	199.5	5.6
170°-180°	69.8	2.0
0°-30°	430.7	12.1
0°-40°	692.8	19.5
0°-60°	1187.2	33.5
0°-90°	1487.1	41.9
90°-120°	442.0	12.5
90°-150°	1489.3	42.0
90°-180°	2059.0	58.1
0°-180°	3546.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	27
90°	1	5	9	12	14	4
95°	37	38	44	48	49	39
105°	131	134	137	141	142	140
115°	247	250	251	250	250	245
125°	361	364	365	364	363	324
135°	470	473	474	474	471	362
145°	569	571	573	573	571	356
155°	651	651	652	654	651	300
165°	708	707	707	710	706	200
175°	736	734	734	737	733	70
180°	738	738	738	738	738	

TEST NUMBER: P1027908

CATALOG NUMBER: S125DIP-B375D610UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	0.6	5.2	9.2	12.1	13.8
92.5°	17.2	20.1	25.3	29.3	30.4
95°	37.3	38.5	44.2	48.2	49.4
97.5°	57.4	58.0	66.0	69.5	70.0
100°	80.4	80.4	87.8	93.0	94.1
102.5°	105.1	107.9	110.8	116.5	118.3
105°	130.9	133.8	137.2	140.7	142.4
107.5°	159.0	161.9	164.8	166.5	166.5
110°	188.3	191.2	192.9	194.6	194.0

TEST NUMBER: P1027908

CATALOG NUMBER: S125DIP-B375D610UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.2	219.3	221.6	222.2	221.0
115°	247.4	249.7	250.9	250.3	249.7
117.5°	277.3	277.9	279.0	279.6	277.3
120°	304.8	307.7	308.3	308.3	306.0
122.5°	334.7	335.3	337.0	336.4	334.7
125°	361.1	364.5	365.1	364.0	363.4
127.5°	390.4	392.1	392.7	392.1	391.0
130°	416.2	419.1	420.2	419.7	418.5
132.5°	442.0	447.2	446.6	446.1	444.3
135°	469.6	473.0	473.6	473.6	471.3
137.5°	495.4	498.9	500.0	500.6	497.7
140°	520.1	523.0	524.7	525.9	523.0
142.5°	544.8	547.1	549.4	550.0	547.1
145°	568.9	571.2	572.9	572.9	571.2
147.5°	591.3	593.0	594.2	595.9	591.3
150°	613.7	613.1	615.4	615.4	614.3
152.5°	632.1	633.2	633.8	635.5	633.2
155°	651.0	651.0	651.6	653.9	651.0
157.5°	668.2	667.1	667.7	670.0	665.9
160°	683.2	681.4	682.0	684.3	681.4
162.5°	696.4	695.2	695.2	698.1	694.6
165°	707.8	706.7	707.3	709.6	706.1
167.5°	718.2	715.9	715.9	719.3	715.9
170°	726.2	723.9	723.9	727.4	723.3
172.5°	732.0	729.7	729.7	733.1	729.7
175°	736.0	733.7	733.7	737.1	733.1
177.5°	738.8	736.5	736.0	739.4	735.4
180°	737.7	737.7	737.7	737.7	737.7

(END OF REPORT)