

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027944

Luminaire Tested: S125DIP-B375D850UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027944
REPORT IS A COMBINATION OF REPORTS P1002090 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D850UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4220.0 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027944

CATALOG NUMBER: S125DIP-B375D850UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027944

CATALOG NUMBER: S125DIP-B375D850UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	37	36
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	26
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1027944

CATALOG NUMBER: S125DIP-B375D850UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.3
10°-20°	151.6	3.6
20°-30°	223.8	5.3
30°-40°	261.1	6.2
40°-50°	262.2	6.2
50°-60°	230.2	5.5
60°-70°	171.4	4.1
70°-80°	97.9	2.3
80°-90°	29.8	0.7
90°-100°	65.2	1.5
100°-110°	193.8	4.6
110°-120°	328.7	7.8
120°-130°	432.8	10.3
130°-140°	485.0	11.5
140°-150°	475.3	11.3
150°-160°	399.3	9.5
160°-170°	265.4	6.3
170°-180°	92.9	2.2
0°-30°	429.0	10.2
0°-40°	690.0	16.4
0°-60°	1182.4	28.0
0°-90°	1481.5	35.1
90°-120°	587.8	13.9
90°-150°	1980.9	46.9
90°-180°	2738.0	64.9
0°-180°	4220.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	7	12	16	18	5
95°	50	51	59	64	66	52
105°	174	178	182	187	189	186
115°	329	332	334	333	332	326
125°	480	485	486	484	483	430
135°	625	629	630	630	627	481
145°	757	760	762	762	760	473
155°	866	866	867	870	866	399
165°	942	940	941	944	939	266
175°	979	976	976	980	975	93
180°	981	981	981	981	981	

TEST NUMBER: P1027944

CATALOG NUMBER: S125DIP-B375D850UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	0.8	6.9	12.2	16.0	18.3
92.5°	22.9	26.7	33.6	38.9	40.5
95°	49.6	51.2	58.8	64.1	65.7
97.5°	76.4	77.1	87.8	92.4	93.2
100°	106.9	106.9	116.8	123.7	125.2
102.5°	139.7	143.6	147.4	155.0	157.3
105°	174.1	177.9	182.5	187.1	189.4
107.5°	211.5	215.3	219.1	221.4	221.4
110°	250.5	254.3	256.6	258.9	258.1

TEST NUMBER: P1027944

CATALOG NUMBER: S125DIP-B375D850UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	291.7	294.7	295.5	294.0
115°	329.1	332.2	333.7	332.9	332.2
117.5°	368.8	369.6	371.1	371.9	368.8
120°	405.5	409.3	410.0	410.0	407.0
122.5°	445.2	445.9	448.2	447.5	445.2
125°	480.3	484.9	485.6	484.1	483.3
127.5°	519.2	521.5	522.3	521.5	520.0
130°	553.6	557.4	558.9	558.2	556.7
132.5°	588.0	594.8	594.1	593.3	591.0
135°	624.6	629.2	630.0	630.0	626.9
137.5°	659.0	663.6	665.1	665.8	662.0
140°	691.8	695.6	697.9	699.4	695.6
142.5°	724.6	727.7	730.8	731.5	727.7
145°	756.7	759.8	762.1	762.1	759.8
147.5°	786.5	788.8	790.3	792.6	786.5
150°	816.3	815.5	818.6	818.6	817.0
152.5°	840.7	842.2	843.0	845.3	842.2
155°	865.9	865.9	866.7	869.7	865.9
157.5°	888.8	887.3	888.1	891.1	885.8
160°	908.7	906.4	907.1	910.2	906.4
162.5°	926.2	924.7	924.7	928.5	923.9
165°	941.5	940.0	940.7	943.8	939.2
167.5°	955.2	952.2	952.2	956.8	952.2
170°	965.9	962.9	962.9	967.5	962.1
172.5°	973.6	970.5	970.5	975.1	970.5
175°	978.9	975.9	975.9	980.4	975.1
177.5°	982.7	979.7	978.9	983.5	978.2
180°	981.2	981.2	981.2	981.2	981.2

(END OF REPORT)