

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027712

Luminaire Tested: S125DIP-B1270D850UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027712
REPORT IS A COMBINATION OF REPORTS P1001765 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D850UB27-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8235.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027712

CATALOG NUMBER: S125DIP-B1270D850UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1027712

CATALOG NUMBER: S125DIP-B1270D850UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1027712

CATALOG NUMBER: S125DIP-B1270D850UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.2
10°-20°	521.9	6.3
20°-30°	770.4	9.4
30°-40°	898.9	10.9
40°-50°	902.8	11.0
50°-60°	792.5	9.6
60°-70°	590.3	7.2
70°-80°	337.1	4.1
80°-90°	98.8	1.2
90°-100°	34.7	0.4
100°-110°	230.5	2.8
110°-120°	415.1	5.0
120°-130°	532.8	6.5
130°-140°	573.1	7.0
140°-150°	537.9	6.5
150°-160°	435.1	5.3
160°-170°	281.4	3.4
170°-180°	97.0	1.2
0°-30°	1477.1	17.9
0°-40°	2376.0	28.9
0°-60°	4071.3	49.4
0°-90°	5097.5	61.9
90°-120°	680.3	8.3
90°-150°	2324.0	28.2
90°-180°	3137.0	38.1
0°-180°	8235.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	7	12	16	18	8
95°	43	41	12	16	16	53
105°	223	226	226	226	225	236
115°	418	422	422	420	415	414
125°	594	600	600	597	594	531
135°	741	746	744	743	738	571
145°	859	861	861	862	857	537
155°	946	942	943	946	940	436
165°	999	994	995	999	993	282
175°	1021	1017	1018	1024	1017	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1027712

CATALOG NUMBER: S125DIP-B1270D850UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.2	40.9	12.1	15.9	15.9
97.5°	81.0	85.6	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.7	177.2	178.7	115.1
105°	222.6	225.6	225.6	225.6	224.9
107.5°	274.1	274.1	275.6	276.4	273.3
110°	324.1	324.1	325.6	323.3	324.1



TEST NUMBER: P1027712

CATALOG NUMBER: S125DIP-B1270D850UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.0	373.3	374.0	371.0	369.5
115°	417.9	421.7	422.5	419.5	414.9
117.5°	467.2	467.2	470.2	465.6	464.1
120°	512.6	511.8	514.1	512.6	508.8
122.5°	552.7	556.5	557.3	555.7	551.2
125°	594.4	599.7	599.7	596.6	594.4
127.5°	634.5	638.3	637.5	636.0	629.9
130°	670.8	674.6	675.4	673.1	669.3
132.5°	707.2	711.7	709.4	709.4	705.7
135°	741.2	745.8	744.3	742.8	738.2
137.5°	773.0	777.6	776.1	776.1	772.3
140°	804.1	805.6	804.8	806.4	801.8
142.5°	832.1	832.9	834.4	834.4	829.8
145°	859.4	860.9	860.9	861.6	857.1
147.5°	883.6	883.6	884.3	885.1	879.8
150°	906.3	904.8	906.3	907.8	901.8
152.5°	928.3	924.5	926.0	927.5	922.2
155°	946.4	941.9	943.4	945.7	939.6
157.5°	960.8	958.5	958.5	960.8	954.8
160°	976.0	971.4	972.2	975.2	969.1
162.5°	988.1	983.5	984.3	988.8	982.0
165°	998.7	994.1	994.9	999.4	993.4
167.5°	1007.0	1002.5	1003.2	1008.5	1001.7
170°	1013.8	1008.5	1009.3	1015.3	1008.5
172.5°	1018.4	1013.1	1014.6	1019.9	1013.1
175°	1021.4	1016.8	1017.6	1023.7	1016.8
177.5°	1023.7	1019.1	1019.9	1025.2	1019.1
180°	1021.4	1021.4	1021.4	1021.4	1021.4

(END OF REPORT)