

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027987

Luminaire Tested: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027987
REPORT IS A COMBINATION OF REPORTS P1002151 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1090UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6180.5 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027987

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027987

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40			34
2	87	80	74	68	79	73	68	63	60	56	53	48	45	43	37	35	33			28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28			24
4	72	62	54	48	66	57	50	45	47	42	38	38	34	31	29	26	24			21
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21			18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19			16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17			14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15			12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13			11
10	45	34	26	22	41	31	25	20	26	21	18	21	18	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1027987

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	1.5
10°-20°	254.9	4.1
20°-30°	376.3	6.1
30°-40°	439.0	7.1
40°-50°	440.9	7.1
50°-60°	387.1	6.3
60°-70°	288.3	4.7
70°-80°	164.6	2.7
80°-90°	49.5	0.8
90°-100°	369.2	6.0
100°-110°	766.8	12.4
110°-120°	716.2	11.6
120°-130°	579.6	9.4
130°-140°	465.6	7.5
140°-150°	351.5	5.7
150°-160°	247.5	4.0
160°-170°	145.9	2.4
170°-180°	47.4	0.8
0°-30°	721.4	11.7
0°-40°	1160.5	18.8
0°-60°	1988.5	32.2
0°-90°	2491.0	40.3
90°-120°	1852.2	30.0
90°-150°	3248.8	52.6
90°-180°	3690.0	59.7
0°-180°	6180.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	1	9	16	21	23	5
95°	33	96	876	397	232	34
105°	112	156	717	1411	1310	118
115°	200	241	575	1240	1459	197
125°	277	324	552	986	1150	246
135°	324	390	548	827	955	252
145°	378	432	550	684	753	237
155°	431	464	536	605	632	198
165°	470	483	514	545	554	133
175°	489	489	493	499	497	46
180°	490	490	490	490	490	

TEST NUMBER: P1027987

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	1.0	8.9	15.8	20.8	22.7
92.5°	14.8	81.0	394.4	105.2	73.1
95°	32.6	96.4	875.7	397.3	232.3
97.5°	50.4	104.3	945.9	717.5	509.0
100°	69.2	119.6	892.5	1014.0	770.9
102.5°	89.9	136.9	798.6	1265.1	1063.5
105°	111.7	156.2	716.6	1410.8	1309.6
107.5°	132.4	176.4	655.3	1451.8	1457.8
110°	155.2	197.6	614.8	1412.8	1525.0

TEST NUMBER: P1027987

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.9	219.0	591.0	1331.3	1517.1
115°	199.6	240.6	575.2	1239.9	1458.8
117.5°	219.4	262.9	566.3	1156.9	1370.8
120°	239.2	284.2	560.4	1087.2	1285.8
122.5°	259.9	305.0	555.5	1031.4	1210.7
125°	276.7	324.2	551.5	986.4	1149.5
127.5°	290.6	343.0	549.5	947.8	1093.1
130°	303.4	360.8	547.5	908.8	1048.6
132.5°	313.3	376.5	547.5	866.8	1004.2
135°	324.2	389.9	547.5	826.8	954.7
137.5°	338.0	402.2	548.5	784.8	903.4
140°	349.9	412.6	549.5	746.2	849.0
142.5°	363.7	422.6	550.5	713.1	798.6
145°	377.6	432.4	549.5	684.4	753.1
147.5°	392.4	441.3	547.5	659.7	712.6
150°	405.2	449.2	544.6	639.5	680.0
152.5°	419.1	457.1	540.6	622.2	654.3
155°	430.9	463.6	535.7	605.3	631.6
157.5°	441.8	470.0	530.7	589.6	610.8
160°	452.7	475.0	525.8	573.8	590.0
162.5°	461.6	479.8	519.9	559.4	571.3
165°	470.5	483.3	513.9	545.0	553.5
167.5°	476.4	485.3	508.0	531.8	536.7
170°	482.3	487.8	503.1	518.9	521.8
172.5°	486.3	488.7	497.1	508.5	508.0
175°	489.2	489.2	493.2	499.1	497.1
177.5°	491.2	489.2	490.2	493.2	490.2
180°	490.2	490.2	490.2	490.2	490.2

(END OF REPORT)