

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027731

Luminaire Tested: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027731
REPORT IS A COMBINATION OF REPORTS P1001799 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D850UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7915.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027731

CATALOG NUMBER: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027731

CATALOG NUMBER: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36
5	71	59	50	44	66	55	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10710 cd/sqm

TEST NUMBER: P1027731

CATALOG NUMBER: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.4
10°-20°	528.7	6.7
20°-30°	780.6	9.9
30°-40°	910.7	11.5
40°-50°	914.7	11.6
50°-60°	802.9	10.1
60°-70°	598.0	7.6
70°-80°	341.6	4.3
80°-90°	100.1	1.3
90°-100°	65.5	0.8
100°-110°	194.7	2.5
110°-120°	330.2	4.2
120°-130°	434.7	5.5
130°-140°	487.1	6.2
140°-150°	477.4	6.0
150°-160°	401.0	5.1
160°-170°	266.6	3.4
170°-180°	93.3	1.2
0°-30°	1496.5	18.9
0°-40°	2407.2	30.4
0°-60°	4124.8	52.1
0°-90°	5164.5	65.3
90°-120°	590.4	7.5
90°-150°	1989.6	25.1
90°-180°	2750.0	34.7
0°-180°	7915.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	1	7	12	16	18	9
95°	50	51	59	64	66	52
105°	175	179	183	188	190	186
115°	330	334	335	334	334	327
125°	482	487	488	486	486	432
135°	627	632	633	633	630	484
145°	760	763	765	765	763	475
155°	870	870	870	874	870	401
165°	946	944	945	948	943	267
175°	983	980	980	985	979	93
180°	986	986	986	986	986	

TEST NUMBER: P1027731

CATALOG NUMBER: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	0.8	6.9	12.3	16.1	18.4
92.5°	23.0	26.8	33.7	39.1	40.6
95°	49.9	51.4	59.1	64.4	66.0
97.5°	76.7	77.5	88.2	92.8	93.6
100°	107.4	107.4	117.3	124.2	125.8
102.5°	140.3	144.2	148.0	155.7	158.0
105°	174.9	178.7	183.3	187.9	190.2
107.5°	212.4	216.3	220.1	222.4	222.4
110°	251.6	255.4	257.7	260.0	259.2

TEST NUMBER: P1027731

CATALOG NUMBER: S125DIP-B1270D850UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.4	293.0	296.0	296.8	295.3
115°	330.5	333.6	335.1	334.4	333.6
117.5°	370.4	371.2	372.7	373.5	370.4
120°	407.2	411.1	411.8	411.8	408.8
122.5°	447.1	447.9	450.2	449.4	447.1
125°	482.4	487.0	487.8	486.2	485.5
127.5°	521.5	523.8	524.6	523.8	522.3
130°	556.0	559.9	561.4	560.6	559.1
132.5°	590.5	597.4	596.7	595.9	593.6
135°	627.3	632.0	632.7	632.7	629.6
137.5°	661.9	666.5	668.0	668.8	664.9
140°	694.8	698.7	701.0	702.5	698.7
142.5°	727.8	730.9	734.0	734.7	730.9
145°	760.0	763.1	765.4	765.4	763.1
147.5°	789.9	792.2	793.8	796.1	789.9
150°	819.8	819.1	822.1	822.1	820.6
152.5°	844.4	845.9	846.7	849.0	845.9
155°	869.7	869.7	870.5	873.5	869.7
157.5°	892.7	891.2	891.9	895.0	889.6
160°	912.6	910.3	911.1	914.2	910.3
162.5°	930.3	928.8	928.8	932.6	928.0
165°	945.6	944.1	944.9	947.9	943.3
167.5°	959.4	956.4	956.4	961.0	956.4
170°	970.2	967.1	967.1	971.7	966.3
172.5°	977.8	974.8	974.8	979.4	974.8
175°	983.2	980.1	980.1	984.7	979.4
177.5°	987.0	984.0	983.2	987.8	982.4
180°	985.5	985.5	985.5	985.5	985.5

(END OF REPORT)